



AC-Capacitors, Suppression Capacitors Class X2 AC440 V (MKT)

Dimensions in mm



LEAD LENGTH X (mm)	ORDERING CODE***
4 ⁻¹	F1772-...-4004
6 ⁻¹	F1772-...-4000
15 ⁻¹	F1772-...-4015
30 ⁺⁵	F1772-...-4030


MAXIMUM PULSE RISE TIME: (d_v/d_t) in V/μs

RATED VOLTAGE	PITCH (mm)			
	15.0	22.5	27.5	37.5
AC 440 V	200	150	100	100

RATED VOLTAGE:

AC 440 V, 50/60 Hz

PERMISSIBLE DC VOLTAGE:

DC 1000 V

TERMINALS:

Radial tinned copper wire

COATING:

Plastic case, epoxy resin sealed, flame retardant UL 94V-0

CLIMATIC TESTING CLASS ACC.TO EN 60068-1:
40/100/56

CAPACITANCE RANGE:

 E12 series 0.01 μFX2 - 1.0 μFX2
preferred values acc. to E6

FURTHER TECHNICAL DATA:

See page 21 (Document No 26504)

FEATURES:

 Product is completely lead (Pb)-free
Product is RoHS compliant

CAPACITANCE TOLERANCE:

Standard: ± 10 %

DISSIPATION FACTOR TANδ:

< 1 % measured at 1 kHz

INSULATION RESISTANCE: FOR C ≤ 0.33 μF:

 30 GΩ average value
15 GΩ minimum value

TIME CONSTANT FOR C > 0.33 μF:

 10 000 sec. average value
5000 sec. minimum value

TEST VOLTAGE:

(Electrode/electrode): DC 2150 V/2 sec.

REFERENCE STANDARDS:

 EN 132 400, 1994
EN 60068-1
IEC 60384-14/2, 1993
UL 1283
UL 1414
CSA 22.2 No. 8-M 86
CSA 22.2 No. 1-M 90

DIELECTRIC:


Polyester film

ELECTRODES:

Metal evaporated




CONSTRUCTION:

 Metallized film capacitor
Internal series connection

 Between interconnected terminations and case (foil method):
AC 2500 V for 2 sec. at 25 °C.

 Impedance (Z) as a function of frequency (f) at $T_a = 20\text{ °C}$ (average). Measurement with lead length 6 mm.

RoHS
COMPLIANT

APPROVALS

COUNTRY	SPECIFICATION	ELECTRICAL VALUES	APPROVAL REFERENCE	APPROVAL MARK
U.S.A. (for AC 250 V)	UL 1283 UL 1414	0.01 - 1.0 μ FX 0.01 - 1.0 μ FX	E 76297 E 100682	
Canada (for AC 250 V)	C 22.2 No. 8-M 1986 C 22.2 No. 1-M 1994	0.01 - 1.0 μ FX 0.01 - 0.82 μ FX	LR 64546 LR 64546-8	
CB TEST-CERTIFICATE (for AC 440 V)		0.01 - 1.0 μ FX2	DE 1-8221	
Germany	EN 132 400; 1999 IEC 60384-14, 2nd edition, 1995	0.01 - 1.0 μ FX2	40005095	
This approval mark together with the CB-Certificate replace all national approval marks of the following countries (they have already signed the CB-Agreement):				
Austria	Belgium	Denmark	Finland	Sweden
France	Germany	Ireland	Italy	Switzerland
Netherlands	Israel	Portugal	Spain	Great Britain
Japan	Norway	China	Poland	Czech. Republic
Singapore	Rep. of Korea	Hungary	Iceland	Slovenia

CAPACITANCE	TOL. (%)	PITCH (mm)	BOX NO.	DIMENSIONS W x H x L (+ 0.2/- 0.4 mm)	WEIGHT LEAD LENGTH 6 ⁻¹ mm (g)	QUANTITY PACKAGE LEAD LENGTH 6 ⁻¹ mm (pcs)**	ORDERING CODE***
0.01 μFX2	± 10	15.0	06	6.3 x 12.3 x 17.8	2.0	500	F1772-310-4 ...
0.012 μ FX2	± 10	15.0	06	6.3 x 12.3 x 17.8	2.0	500	F1772-312-4 ...
0.015 μFX2	± 10	15.0	07	7.3 x 13.3 x 17.8	2.4	450	F1772-315-4 ...
0.018 μ FX2	± 10	15.0	07	7.3 x 13.3 x 17.8	2.4	450	F1772-318-4 ...
0.022 μFX2	± 10	15.0	08	8.3 x 14.3 x 17.8	2.7	325	F1772-322-4 ...
0.027 μ FX2	± 10	15.0	08	8.3 x 14.3 x 17.8	2.7	325	F1772-327-4 ...
0.033 μFX2	± 10	15.0	28	8.3 x 17.3 x 17.8	2.7	300	F1772-333-4 ...
0.039 μ FX2	± 10	22.5*	09	6.3 x 14.3 x 26.3	3.3	260	F1772-339-4 ...
0.047 μFX2	± 10	22.5*	11	7.3 x 15.3 x 26.3	4.1	235	F1772-347-4 ...
0.056 μ FX2	± 10	22.5*	12	8.3 x 16.3 x 26.3	4.6	200	F1772-356-4 ...
0.068 μFX2	± 10	22.5*	12	8.3 x 16.3 x 26.3	4.6	200	F1772-368-4 ...
0.082 μ FX2	± 10	22.5*	12	8.3 x 16.3 x 26.3	4.6	200	F1772-382-4 ...
0.1 μFX2	± 10	22.5*	13	10.3 x 18.3 x 26.3	6.7	170	F1772-410-4 ...
0.12 μ FX2	± 10	22.5*	13	10.3 x 18.3 x 26.3	6.7	170	F1772-412-4 ...
0.15 μFX2	± 10	27.5*	14	11.0 x 20.3 x 31.3	9.1	125	F1772-415-4 ...
0.18 μ FX2	± 10	27.5*	14	11.0 x 20.3 x 31.3	9.1	125	F1772-418-4 ...
0.22 μFX2	± 10	27.5*	15	13.0 x 23.3 x 31.3	12.9	110	F1772-422-4 ...
0.27 μ FX2	± 10	27.5*	15	13.0 x 23.3 x 31.3	12.9	110	F1772-427-4 ...
0.33 μFX2	± 10	27.5*	18	14.5 x 24.3 x 31.3	15.0	100	F1772-433-4 ...
0.39 μ FX2	± 10	37.5*	14	12.0 x 22.3 x 41.3	15.2	90	F1772-439-4 ...
0.47 μFX2	± 10	37.5*	16	14.0 x 24.3 x 41.3	18.9	80	F1772-447-4 ...
0.56 μ FX2	± 10	37.5*	19	15.5 x 28.3 x 41.3	24.0	70	F1772-456-4 ...
0.68 μFX2	± 10	37.5*	19	15.5 x 28.3 x 41.3	24.0	70	F1772-468-4 ...
0.82 μ FX2	± 10	37.5*	20	17.9 x 32.4 x 41.3	31.6	60	F1772-482-4 ...
1.0 μFX2	± 10	37.5*	42	19.8 x 39.9 x 42.3	44.2	55	F1772-510-4 ...

Preferred values in bold print.

Inbuilt discharging resistor on request (with larger case dimensions).

* Different pitch on request.

** Further information about packaging quantities with different lead length and/or taped versions.

See page 16 (Document No 27608 Packing Quantities). Use Box No. as reference

*** These capacitors can be delivered on continuous tape and reel - see page 14/15 (Document Number 27622).

The ordering code is F1772-. . .-4900 at H = 16.5 mm, F1772-. . .-4901 at H = 18.5 mm.

**APPLICATION NOTES**

- For X2 electromagnetic interference suppression in **across the line applications** (50/60 Hz) with a maximum mains voltage of 440 V (AC).
- These capacitors are not intended for continuous pulse applications. For these situations, capacitors of the AC and pulse programs must be used.
- These capacitors can be used for series impedance application in case safety approvals are requested.
- The maximum ambient temperature must not exceed 100 °C.
- Rated voltage pulse slope:
If the pulse voltage is lower than the rated voltage, the values of the specific reference data can be multiplied by 620 V (DC) and divided by the applied voltage.



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.