

USB 3.0 to DisplayPort® External Video Card Multi Monitor Adapter – 2560x1600

StarTech ID: USB32DPPRO



The USB32DPPRO USB 3.0 to DisplayPort® Multi Monitor Adapter functions as an external DisplayPort video card, turning an available USB 3.0 port into a DisplayPort output, with support for high resolution 2560x1600 video, and 5.1 surround sound audio. The USB 3.0 DisplayPort adapter delivers a convenient, high-performance external video solution that makes it easy to add multi-monitor capability to a USB 3.0-enabled desktop or laptop computer (optimal performance from USB 3.0, backward compatible with USB 2.0).

Leveraging the high-bandwidth (5 Gbps) SuperSpeed USB 3.0 interface, the adapter delivers smooth, high-definition content to your DisplayPort-capable display, and can be used to mirror your primary desktop, showing the same image on each display, or to extend your desktop to double your workspace and increase your productivity.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Recommended System Requirements:

CPU: Quad Core 2.4GHz or Higher (i5 recommended)

RAM: 4GB or higher

Applications

- Add a secondary DisplayPort display and extend your desktop, without taking apart your computer to install a new video card
- Add multi-monitor capability to a single computer, to enhance multimedia presentations
- Great for researchers and writers, offering the ability to have reference material on one display while working on a separate document on another
- Increase productivity by running multiple applications on different screens - check your email on one display and search the web on the other
- View large or several spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using USB 3.0-capable laptop PCs, enabling connection to a secondary display/projector

Features

- SuperSpeed USB 3.0 (5 Gbps) Interface, backward compatible with USB 2.0
- Supports resolutions up to 2560x1600
- Quick, easy installation
- USB-powered - No external power adapter required
- Choose between Mirrored, Extended or Primary display configurations
- Driver software supports display rotation
- Supports the Windows® Aero interface
- Supports 5.1 channel audio
- Supports the use of multiple USB32DPPRO USB 3.0 DisplayPort adapters on a single system (up to 5)

Technical Specifications

Warranty	2 Years
Audio	Yes
Memory	512MB DDR II
Industry Standards	Standard DisplayPort, SuperSpeed USB 3.0, USB 2.0
Chipset ID	DisplayLink - DL3500
Output Signal	DisplayPort
Connector A	1 - USB 3.0 A (9 pin; SuperSpeed) Male
Connector B	1 - DisplayPort (20 pin) Female
Maximum Digital Resolutions	2560x1600
Supported Resolutions	Widescreen(16/32 bit): 2560x1600, 2560x1440, 2048x1152, 1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720
	Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
Wide Screen Supported	Yes
Audio Specifications	5.1-Channel Surround (48Khz)
OS Compatibility	Windows® 8 (32/64bit), 7 (32/64bit), Vista(32/64) (Aero 3D interface supported)
Color	Black
Enclosure Type	Plastic
Cable Length	0.9 m [3 ft]
Product Length	81 mm [3.2 in]
Product Width	26 mm [1 in]
Product Height	11 mm [0.4 in]
Product Weight	20 g [0.7 oz]
Power Adapter Included	USB Powered
Operating Temperature	0°C to 35°C (32°F to 95°F)
Storage Temperature	-5°C to 40°C (23°F to 104°F)
Humidity	20°C to 80°C (68°F to 176°F)
System and Cable Requirements	1~2 USB Displays Office Application:

CPU: i3 Dual core 2.8GHz
RAM: 2GB or higher

Full HD Video:
CPU: Quad Core 2.4GHz or Higher (i5 recommended)
RAM: 4GB or higher

Note Connect a maximum of five USB32DPPRO adapters on a single PC - See manual for system requirements

Shipping (Package) 175 g [6.2 oz]
Weight

Included in Package 1 - USB 3.0 to Displayport Adapter

Included in Package 1 - Driver CD

Included in Package 1 - Installation Guide

Certifications, Reports and Compatibility

