



General Information

Kit Part Number:	2110856-2
Description:	Panel Mount Double-Row Dual-Barrier Strip with Binding Head Screws and Hardware Kit
Application:	HVAC Systems, Industrial Controls, Power Supplies, Telecommunications, Test Equipment, Traffic Signals
Family:	Double-Row Dual-Barrier Strip
TE Brand:	BUCHANAN Products
Solution:	Field Wiring
Product Type:	Double-Row Dual-Barrier
Number of Pieces:	14
RoHS:	Yes

Specifications

Circuit Size(s):	2, 3, 4, 5, 6, 8, 10
Current Rating:	20A
Mounting Style:	Panel Mount
Pitch:	0.437"
Rows:	Double Row
Terminal Type:	Binding Head Screw
Tool Included:	No
Voltage Rating:	300V
Wire Gauge (AWG):	22-14

Product Highlights

Double-Row Dual-Barrier Strips for wire-to-wire applications allow end users to complete the wiring to a separate screw without disturbing the factory wiring. They also have increased current carrying capability.

Features and Benefits

- Closed bottom design allows for mounting direct to sheet metal panel
- Molding to length
- Accessories such as Quick Connect Tabs and Jumpers are available

Applications

- Industrial Controls
- Test Equipment
- HVAC
- Power Supplies
- Traffic Signals
- Telecom



Bill of Materials

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
1546670-2	2	0.437" Pitch, 2 Circuit Double-Row Dual-Barrier Strip, 22-14...	Datasheet	Details	Search
1546670-3	2	0.437" Pitch, 3 Circuit Double-Row Dual-Barrier Strip, 22-14...	Datasheet	Details	Search
1546670-4	2	0.437" Pitch, 4 Circuit Double-Row Dual-Barrier Strip, 22-14...	Datasheet	Details	Search
1546670-5	2	0.437" Pitch, 5 Circuit Double-Row Dual-Barrier Strip, 22-14...	Datasheet	Details	Search
1546670-6	2	0.437" Pitch, 6 Circuit Double-Row Dual-Barrier Strip, 22-14...	Datasheet	Details	Search
1546670-8	2	0.437" Pitch, 8 Circuit Double-Row Dual-Barrier Strip, 22-14...	Datasheet	Details	Search
1-1546670-0	2	0.437" Pitch, 10 Circuit Double-Row Dual-Barrier Strip, 22-1...	Datasheet	Details	Search

Recommended Tool

Part No.	Included in Kit
----------	-----------------





