

### 3.5 x2.8mm SMD CHIP LED LAMP

Part Number: KPED-3528QBC-D Blue



**ATTENTION** OBSERVE PRECAUTIONS FOR HANDLING ELECTROSTATIC DISCHARGE SENSITIVE **DEVICES** 

#### **Features**

- Single color.
- Suitable for all SMT assembly and solder process.
- Ideal for backlighting.
- Available on tape and reel.
- Package: 500pcs / reel.
- Moisture sensitivity level : level 3.
- RoHS compliant.

### Description


The Blue source color devices are made with InGaN Light Emitting Diode.


Static electricity and surge damage the LEDS.

It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs.


All devices, equipment and machinery must be electrically grounded.


## **Package Dimensions**











SPEC NO: DSAC7318

APPROVED: WYNEC

- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is  $\pm 0.2 (0.008")$  unless otherwise noted.
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
   The device has a single mounting surface. The device must be mounted according to the specifications.

**REV NO: V.10A** DATE: JUL/05/2012 PAGE: 1 OF 5 **CHECKED: Allen Liu** DRAWN: D.M.Su ERP: 1203001135

## **Selection Guide**

Part No.	Dice	Lens Type	lv (mcd) [2] @ 20mA		Viewing Angle [1]
			Min.	Тур.	201/2
KPED-3528QBC-D	Blue (InGaN)	Water Clear	300	400	40°

#### Notes:

- 1.  $\theta$ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
- Luminous intensity/ luminous Flux: +/-15%.
   Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

# Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.		Тур.		Max.	Units	Test Conditions
λpeak	Peak Wavelength	Blue	468	*460	nm		IF=20mA		
λD [1]	Dominant Wavelength	Blue	470	*465		nm	IF=20mA		
Δλ1/2	Spectral Line Half-width	Blue	25			nm	IF=20mA		
С	Capacitance	Blue	100			pF	VF=0V;f=1MHz		
VF [2]	Forward Voltage	Blue	3.3		4	V	I=20mA		
lr	Reverse Current	Blue			50	uA	VR = 5V		

1.Wavelength: +/-1nm.


# Absolute Maximum Ratings at TA=25°C

Parameter	Blue	Units		
Power dissipation	120	mW		
DC Forward Current	30	mA		
Peak Forward Current [1]	150	mA		
Reverse Voltage	5	V		
Operating Temperature	-40°C To +85°C			
Storage Temperature	-40°C To +85°C			

1. 1/10 Duty Cycle, 0.1ms Pulse Width.

**SPEC NO: DSAC7318 REV NO: V.10A** DATE: JUL/05/2012 PAGE: 2 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: D.M.Su ERP: 1203001135

Forward Voltage: +/-0.1V.
 \*Wavelength value is traceable to the CIE127-2007 compliant national standards.




 SPEC NO: DSAC7318
 REV NO: V.10A
 DATE: JUL/05/2012
 PAGE: 3 OF 5

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: D.M.Su
 ERP: 1203001135

### KPED-3528QBC-D

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

  1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.


  2.Don't cause stress to the epoxy resin while it is exposed to high temperature.

  3.Number of reflow process shall be 2 times or less.


## **Recommended Soldering Pattern** (Units: mm; Tolerance: ± 0.1)



# **Reel Dimension**



**Tape Dimensions** (Units : mm)



SPEC NO: DSAC7318 APPROVED: WYNEC


**REV NO: V.10A CHECKED: Allen Liu** 


DATE: JUL/05/2012 DRAWN: D.M.Su


PAGE: 4 OF 5 ERP: 1203001135

### **PACKING & LABEL SPECIFICATIONS**

### KPED-3528QBC-D







Detailed application notes are listed on our website. <a href="http://www.kingbright.com/application\_notes">http://www.kingbright.com/application\_notes</a>

SPEC NO: DSAC7318
APPROVED: WYNEC

REV NO: V.10A CHECKED: Allen Liu DATE: JUL/05/2012 DRAWN: D.M.Su PAGE: 5 OF 5 ERP: 1203001135