

Ball End L-Wrenches

- ProGuard™ Finish -

L-Wrenches

- Ball End inserts into a screw at a 25° angle
- Ball End saves time by quickly funneling tool into screw
- 25° angle allows natural hand and wrist movement
- Superior Ball End strength and working angle
- Works in hard to reach places



Sets	PART#	MODEL#	PCS	LENGTH	CONTENTS	QTY	LIST
Metric	10946	BLX6M	6	Long	1.5, 2, 2.5, 3, 4, 5mm	1	
	10992	BLX7M	7	Long	1.5, 2, 2.5, 3, 4, 5, 6mm	1	
	10999	BLX9M	9	Long	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10mm	1	
	10995	BLX15M	15	Long	1.27, 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10mm	1	
	10989	MBLX13	13	Long	1.27, 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10, 12, 14, 17mm (in metal box)	1	
	16099	BLX9MXL	9	Extra Long	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10mm	1	



Singles	SIZE	INCH		MM		PACKAGED			BULK			TAGGED/BARCODED		
		INCH	MM	INCH	MM	PART#	QTY	LIST EA	PART#	QTY	LIST EA	PART#	QTY	LIST EA
LONG Metric	1.27	2.8	72	0.53	13	10949	10		12949	100		15749	10	
	1.5	3.0	77	0.53	14	10950	10		12950	100		15750	10	
	2.0	3.2	82	0.61	16	10952	10		12952	100		15752	10	
	2.5	3.5	88	0.69	17	10954	10		12954	100		15754	10	
	3.0	3.9	98	0.75	19	10956	10		12956	100		15756	10	
	3.5	3.9	100	0.85	21	10958	1		12958	100		15758	1	
	4.0	4.3	110	0.87	22	10960	10		12960	100		15760	10	
	4.5	4.5	114	1.00	25	10962	1		12962	100		15762	1	
	5.0	4.7	119	1.06	27	10964	5		12964	100		15764	5	
	5.5	4.9	124	1.14	29	10966	1		12966	50		15766	1	
	6	5.5	139	1.22	31	10968	5		12968	50		15768	5	
	7	5.5	140	1.30	33	10970	1		12970	50		15770	1	
	8	6.0	152	1.38	35	10972	5		12972	50		15772	5	
	9	6.2	159	1.46	37	10974	1		12974	50		15774	1	
	10	6.7	171	1.54	39	10976	5		12976	50		15776	5	
	11	7.9	200	1.63	42	10978	1		12978	25		15778	1	
	12	8.7	220	1.73	44	10980	1		12980	25		15780	1	
14	10.2	260	2.15	55	10984	1		12984	10		15784	1		
17	11.0	280	2.42	61	10986	1		12986	10		15786	1		
19	11.6	295	2.70	69	10988	1		12988	5		15788	1		
22	13.0	330	3.07	78	10991	1		-	-		-	-		
24	14.5	370	3.47	88	10993	1		-	-		-	-		



Singles	SIZE	INCH	MM	INCH	MM	PART#	QTY	LIST EA
EXTRA LONG Metric	1.5	3.5	90	0.53	14	16050	10	
	2.0	3.9	100	0.61	16	16052	10	
	2.5	4.4	112	0.69	17	16054	10	
	3.0	5.0	126	0.75	19	16056	10	
	4.0	5.6	142	0.87	22	16060	10	
	5.0	6.3	160	1.06	27	16064	5	
	6	6.8	172	1.22	31	16068	5	
	8	7.7	195	1.38	35	16072	5	
10	8.4	213	1.54	39	16076	5		

Did you know...?

Bondhus' extremely precise manufacturing methods create Ball End tools that work very well, even in sizes as small as .050", 1.27mm, and T6 (BallStar™ Tip).