


## AX104241-S1 Modular Connectors - Brilliance LC Connector OM2



For more Information  
please call

1-800-Belden1



### Description:

FiberExpress Brilliance Field Installable Connector, LC, Multimode 50  $\mu$ m, OM2, for 900  $\mu$ m tight buffered fiber

### Usage (Overall)

**Suitable Applications:** Indoor termination of fiber cables: Patch panels, Communication outlets, Fiber-to-the-desk, Distribution frames, Campus, Customer premise, Access network, Data Centers, OM4 solutions

**Related Parts:** FiberExpress Brilliance installation kits, Breakout kits

### Physical Characteristics (Connectivity)

#### Dimensions

Dimensions:

Height (in.)	Width (in.)	Length (in.)
0.395	0.232	1.594

#### Materials

Materials:

Description	Type	Material	Color
Connector Body	N/A	Plastic	Black

#### Color

**Color:** Black

### Included Parts

**Included Parts:** 900  $\mu$ m boot, dust cap

### Packaging

**Packaging:** Individually packaged in a plastic bag.

### Mechanical Characteristics (Connectivity)

**Mechanical Specifications:**

Parameters	Specifications
Interconnection Compatibility	compliant with TIA/EIA-604-10A (FOCIS 10)
Field Assembly Time	40 seconds
Durability (Multimode)	500 cycles, less than 0.2 dB change, FOTP-21
Durability (Single-mode)	500 cycles, less than 0.3 dB change, FOTP-21
Nominal Fiber OD	125 $\mu$ m
Storage Temperature	-40°F to +140°F (-40°C to +60°C)
Operating Temperature	-40°F to +167°F (-40°C to +75°C)
Tensile strength on 900 $\mu$ m tight buffered fiber	1.12 lb (0.5 Kg), less than 0.2 dB change, FOTP-6
Ferrule	Ceramic

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

**EU Directive 2002/95/EC (RoHS):** Yes

**EU RoHS Compliance Date (mm/dd/yyyy):** 07/01/2006

**MII Order #39 (China RoHS):** EUP 50

## AX104241-S1 Modular Connectors - Brilliance LC Connector OM2

**Telecommunications Standards:** TIA 568-C.3

**Safety Listing:** ACA

### Suitability

**Suitability - Indoor:** Yes - Indoor

### Transmission Characteristics (Connectivity)

#### Transmission Specifications:

Maximum Insertion Loss (Field cleaver)	Typical Insertion Loss (Field cleaver)	Maximum Insertion Loss (Precision cleaver)	Typical Insertion Loss (Precision cleaver)	Minimum reflectance	Fiber type
0.75 dB	0.30 dB	0.50 dB	0.20 dB	-25 dB	Multimode
0.75 dB	0.40 dB	0.50 dB	0.30 dB	-40 dB	Singlemode

### Notes (Overall)

**Notes:** Refer to Installation Guide PX105234 for installation procedures. Supplied with FiberExpress Brilliance installation kit.

**Notes (Cont'd.):** Fiber can be reterminated up to 5 times with the same connector.

### Product Family

#### Part Number List:

Description	Belden Part Number
LC 62.5 μm Multimode OM1	AX104240-S1
LC 50 μm Multimode OM2	AX104241-S1
LC 50 μm Multimode OM3-4	AX104242-S1
LC, Singlemode OS2	AX104243-S1
LC 62.5 μm Multimode OM1, 25 per package	AX104240-B25
LC 50 μm Multimode OM2, 25 per package	AX104241-B25
LC 50 μm Multimode OM3-4, 25 per package	AX104242-B25
LC Singlemode OS2, 25 per package	AX104243-B25

### Related Documents:

No related documents are available for this product

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX104241-S1	1 EA	0.007 LB			Brilliance LC OM2 900um 1 per

Revision Number: 1    Revision Date: 03-21-2012

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.