

Industrial Panel Meters


Metal Cased Sealed Meters

2-1/2"



17/3 MM - D.C Moving Coil
552-MM - A.C. Repulsion

3-1/2"




6351 - D.C. Moving Coil
6352 - A.C. Repulsion

The 17/3-MM, 552-MM and 6351/2 Industrial Panel Meters are designed for extreme duty applications where high degree of resistance to environment is required. They are dustproof and waterproof, meeting NEMA 4 and ANSI C39.1 specifications and performance standards. These meters have $\pm 2\%$ accuracy, $\pm 1\%$ repeatability and a resistance of $\pm 20\%$. Response time is 1.5 seconds and a temperature range of -50°F to 150°F . Custom meter ranges and scales are available to meet customer specifications.

Case and Composition: Thermo plastic window, brass or steel case, ruggedized, gasket sealed.

Movement: DC Moving Coil, AC Repulsion or Rectified, all with Pivot and Jewel Movements, Heavy Damping



MODELS	A	B	C	D	E	F	G	H	I	J	K	L	M	N	O
17/3mm/552mm	2.70	1.22	.29	2.20	.58	.59	.97	.48	0.00	1.22	.610	2.113	1.0565	.484	N/A
6351 / 6352	3.53	1.12	.38	2.50	N/A	.84	.97	.48	+25	1.58	.79	2.73	1.36	.800	3.65

