

# Double Row Terminal Blocks

## Kulka® 603 GP Series

### 600 Volts

#### Specifications:

- Base, General Purpose Phenolic, 150° C
- JJ (GDI-30F) Material Available
- Open Back Design (Insulator Strip Required for Voltage Rating)
- Screws, #10-32 Binder Head, Phil-Slot
- Terminals, Plated Brass
- 1-12 Poles
- 11/16" Centers
- Wire Range With Wire Binding Screw #10-#12 AWG – 50 Amps
- Will Accommodate Lugs For Wire Sizes #6-#16 AWG – 65 Amps
- The Suitability Of These Devices For Greater Currents Shall Be Determined In The End-Use Application
- UL Recognized File No. E47811
- CSA Certified File No. LR19766
- CE



#### Hardware Options:

LL (J 603)	=	Line to Line Jumper	See Page 91
Y	=	Feed Thru Solder (.60)	See Page 90
2302	=	Stud	See Page 93

Catalog #	# of poles	Dimensions	
		A	B
603 GP 01	1	1.81	1.38
603 GP 02	2	2.50	2.06
603 GP 03	3	3.19	2.75
603 GP 04	4	3.88	3.44
603 GP 05	5	4.56	4.12
603 GP 06	6	5.25	4.81
603 GP 07	7	5.94	5.50
603 GP 08	8	6.62	6.19
603 GP 09	9	7.31	6.88
603 GP 10	10	8.00	7.56
603 GP 11	11	8.68	8.25
603 GP 12	12	9.37	8.94

MM = Dim X 25.4

