

# Heavy Duty Terminal Blocks

## 1600 Series

600 Volts AC/DC (UL/CSA)  
1000 Volts (CE)



1604 H



1604 STD

### Specifications:

- Base, General Purpose Phenolic, 150°C
- Connector, Brass, Nickel Plated
- Phil-Slot Screws standard (slotted screws also available), Brass, Nickel Plated, 10-32
- Current rated up to 30 Amps with unprepared wire, #10-22 AWG Copper
- Current rated up to 75 Amps when wired with crimp type ring, spade or fork terminal
- 21/32" (.65625") Line To Line Spacing
- UL Recognized File No. XCFR2.E62806
- CSA Certified File No. LR19766
- CE
- RoHS Compliant

# of Poles	Catalog #							Dimensions	
								A	B
2	1602 MCJ	1602 STD	1602 DJ	1602 DJSV	1602 ST	1602 SC	1602 H	2.44	1.78
4	1604 MCJ	1604 STD	1604 DJ	1604 DJSV	1604 ST	1604 SC	1604 H	3.75	3.09
6	1606 MCJ	1606 STD	1606 DJ	1606 DJSV	1606 ST	1606 SC	1606 H	5.06	4.41
8	1608 MCJ	1608 STD	1608 DJ	1608 DJSV	1608 ST	1608 SC	1608 H	6.38	5.72
12	1612 MCJ	1612 STD	1612 DJ	1612 DJSV	1612 ST	1612 SC	1612 H	9.00	8.34

See page 34 for DIN Rail Adapter

mm = dim X 25.4

<p><b>16XX MCJ</b></p> <p>Multiple Circuit Jumper</p>	<p><b>16XX STD</b></p> <p>Standard Connector with Serrations for Anti-Rotation</p>	<p><b>16XX DJ</b></p> <p>Removable Connector with Brass Insert</p>	<p><b>16XX DJSV</b></p> <p>Removable Connector with Brass Insert, Removable Cover</p>	<p><b>16XX ST*</b></p> <p>10-32 Stud, Removable Connector</p>	<p><b>16XX SC</b></p> <p>Short Circuiting Bar with Brass Insert, 4 Shorting Pins per Block</p>	<p><b>16XX H</b></p> <p>Standard Connector with Hinge Cover</p>
---	--	--	---	---	--	---

For electronic drawings or 2D/3D CAD data, send request to [drawings@marathonsp.com](mailto:drawings@marathonsp.com)

\* STRC: 10-32 Stud with Riveted Connector

