

## 2-Channel Digital Output Module 24 V DC

Short-circuit protected; high-side switching




Fig. 750 Series/Technical data see page 24/Delivered without miniature WSB markers  
750/753 Series marking see pages 10 ... 11 / 12 ... 13

The connected load is switched via the digital output from the control system.

All outputs are electronically short-circuit-protected.

The module is a 2-channel, 4-conductor device and actuators with a ground (earth) wire may be directly connected to the module.

Each output is electrically isolated from the bus by use of optocouplers.

Description	Item No.	Pack. Unit
2DO 24V DC 2.0A	750-502	10 <sup>1)</sup>
2DO 24V DC 2.0A/R*	750-502/000-800	1
2DO 24V DC 2.0A (without connector)	753-502	1
* /R: Interference-free for safety function applications (see manual)		
<sup>1)</sup> Also available individually		
Accessories	Item No.	Pack. Unit
753 Series Connectors	753-110	25
Coding elements	753-150	100
<b>Miniature WSB Quick marking system</b>		
plain	248-501	5
with marking	see pages 352 ... 353	
Approvals	Also see "Approvals Overview" in Section 1	
Conformity marking	CE	
Shipbuilding (versions upon request)	ABS, BV, DNV, GL, KR, LR*, NKK*, PRS*, RINA* *753 Series, pending	
UL 508		
ANSI/ISA 12.12.01	Class I, Div. 2, Grp. ABCD, T4	
EN 60079-0, -15	I M2 / II 3 GD Ex nA IIC T4	750-502/000-800
EN 61241-0, -1		753-502
EN 60079-0, -11, -15	I M2 Ex d I	750-502*
EN 61241-0, -1, -11	II 3 G Ex nA IIC T4	750-502*
	II 3 D Ex tD A22 IP6X T135°C	750-502*
	* Permissible operating temperature: 0°C ... +60°C	

Technical Data	
No. of outputs	2
Current consumption (internal)	3.5 mA
Voltage via power jumper contacts	24 V DC (-25 % ... +30 %)
Type of load	resistive, inductive, lamps
Max. switching frequency	2.5 kHz
Output current (max.)	2 A
Short-circuit limitation (typ.) Pwm	35 A (44 A peak)
Inductive load switch off energy dissipation W (max.)	1.7 J; $L_{max} = 2 \times W_{max} / I^2$
Current consumption typ. (field side)	15 mA / module + charge
Isolation	500 V system/supply
Internal bit width	2 bits
Wire connection	CAGE CLAMP®
Cross sections	0.08 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> / AWG 28 ... 14
Stripped lengths, 750/753 Series	8 ... 9 mm / 0.33 in 9 ... 10 mm / 0.37 in
Width	12 mm
Weight	51.5 g
EMC: CE - immunity to interference	acc. to EN 60000-6-2 (2005)
EMC: CE - emission of interference	acc. to EN 61000-6-4 (2007)
EMC: marine applications	
- immunity to interference	acc. to Germanischer Lloyd (2003)
EMC: marine applications	
- emission of interference	acc. to Germanischer Lloyd (2003)