



## Description:

Type KYS is an irradiated, Thin-Wall, Heat Shrinkable Tubing Fabricated from Modified Polyvinylidene Fluoride. Upon the Application of Heat in Excess of 175°C, The Tubing Shrinks to the Geometry of the Part to be Covered.

## Typical Properties

### Physical

Tensile Strength	: 5,500 PSI
Ultimate Elongation	: 350%
Longitudinal Change	: +1, -10%
Specific Gravity	: 1.7 g/cm <sup>2</sup> Max.
Operating Temp	: -55°C ~ +175°C
Shrink Temp	: 175°C (347°F)
Low Temp. Flexibility (4 hrs @ -55°C)	: No Cracking
Shrinkage	: 2:1
Colour	: Clear

### Electrical

Dielectric Strength	: 900 V/Mil
Volume Resistivity	: 10 <sup>14</sup> Ohms-cm

### Chemical

Corrosion Resistance	: Non-Corrosive
Fuel & Oil Resistance	: Excellent
Solvent Resistance	: Excellent
Abrasion Resistance	: Excellent
Acids & Alkalis Resistance	: Excellent

## MIL. Spec. Nos.

MIL-1-23053/8, AMS-3632  
MIL-1-2305318, Class 1

## Part Number Table

Description	Dimensions				Standard Packages					
	Size (Inch)	Expanded I.D. (Min.) (Inch)	Recovered I.D. (Max.) (Inch)	Recovered Nominal Wall Thickness (Inch)	4 Foot Lengths (+1, -0)			6 Inch Lengths (± .125)		
					Part Number	Qty	Total Footage (Feet)	Part Number	Qty	Total Footage (Feet)
General Purpose Kynar Heat Shrink Tubing	3/64	0.046	0.023	0.01	KYS-003-4025-CLR	25	100	N/A	---	---
	1/16	0.063	0.031		KYS-004-4025-CLR			KYS-004-6028-CLR	28	14
	3/32	0.093	0.046		KYS-006-4025-CLR			KYS-006-6024-CLR	24	12
	1/8	0.125	0.062		KYS-008-4025-CLR			KYS-008-6020-CLR	20	10
	3/16	0.187	0.093		KYS-012-4025-CLR			KYS-012-6016-CLR	16	8
	1/4	0.25	0.125	0.012	KYS-016-4025-CLR	5	20	KYS-016-6012-CLR	12	6
	3/8	0.375	0.187		KYS-024-4025-CLR			KYS-024-6008-CLR	8	4
	1/2	0.5	0.25		KYS-032-4005-CLR			KYS-032-6004-CLR	4	2
	3/4	0.75	0.375		0.017			KYS-048-4005-CLR	KYS-048-6002-CLR	2

**Important Notice :** This data sheet and its contents (the Information) belong to the members of the Premier Farnell group of companies (the Group) or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.