Digital Storage Scope





Specification Table

Bandwidth	150 MHz	
Rise Time	≤2.3 ns	
Sample Range	500 MS / s	
Vertical Sensitivity	2 mV to 5 V / div	
Maximum Record Length	1,024 k	
Sample Rate	Real time 500 MS / s, Equivalent : 25 GS / s	
Scan Time Base	2 ns to 50 s / div	
Trigger Type	Edge, Pulse, Video and Alternate	
Automatic Waveform Measurements	28	
Ports	Standard : USB Device USB Host : RS-232C Optional : LAN	
Mathematics	Add, Subtract, Multiply, Divide, Reverse and FFT	
Applications	College Education, R and D, Electronic Product Assemble Line, Industrial Control etc	
Display	64 k, Full Colour LCD 320 × 240	

General Characteristics

Power	100 - 240 V _{rms} ac, 45 - 440 Hz, CAT II
LCD Size	Diagonal 145 mm (5.7 inches)
Colour	Red and Grey, White and Grey
Size	320 mm (wide) × 150 mm (high) × 130 mm (deep)
Standard Accessories	Probe x 2 (1x, 10x Switchable; Optional Purchase; 100x probe), Power Cord and English Manual

Part Number Table

Description		Part Number
	Digital Storage Scope, 150 MHz, 2 CH	72-8245

Important Notice: This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA" is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk www.mcmelectronics.com



09/06/12 V1.1