

**NO
EXCUSES!**



18 Point Terminal Cabinet

The TC1 18 point "FIRE ALARM TERMINAL CABINET" is designed to enhance your fire alarm systems. Ideally suited for maintenance and troubleshooting with easy identification of system wiring.


White 7/8" highly visible lettering and a "lift-a-way" hinged door with captive fastener or high security Cam Lock makes this an ideal "quick and easy" termination point. This surface mount cabinet is fabricated from 16 gauge steel with a durable red textured, baked-on powder coat finish.

The TC1 is UL listed for life safety.



Standard Features:

- Dimensions:
6 1/2" wide x 8 1/2" high x 2 1/2" deep
- 16 gauge cold rolled steel construction
- Captive Screw or Cam Lock securing devices
- Wall mounting holes
- Durable red textured finish
- White 7/8" indelible lettering
- "FIRE ALARM TERMINAL CABINET"
- Lift-a-way hinge
- Interior labeling of terminal strip
- Field identification label inside cover
- Standard 1/2" & 3/4" EMT knockouts
- Single 18 point high barrier terminal strip
- Terminal points rated for 12 gauge wire
- Terminal strip rated for 20 amp max 250V
- (Class B/UL) 300V (CSA)



The TC1 door can be equipped with a friction catch or a high security CAT 30 key and lock set.



Uses UL Recognized Components




**ISO 9001
REGISTERED
COMPANY**

ACEBOX

Space Age Electronics, Inc.
www.1sac.com
800.486.1723 Toll Free
508.485.0966 Local
508.485.4740 Fax

Specifications:

The TC1 18 Point Terminal Cabinet is constructed of 16 gauge (.062 thk.) cold rolled steel and finished with a durable red textured, heat-resistant baked-on enamel finish. The front cover displays "FIRE ALARM TERMINAL CABINET" in 7/8" white screened indelible lettering, and is engineered with a removable formed lift-a-way hinge. The choice of a captive fastener or CAT-30 Cam Lock secures the front cover. The interior of the box has a field identification label on the inside cover, corresponding to the terminal strip's labeling inside the back box. Overall dimensions measure 6 1/2" wide by 8 1/2" high by 2 1/2" deep. The cabinet includes standard 1/2" and 3/4" EMT knockouts on the top and bottom. A single 18 point high barrier terminal strip is rated for 12 gauge wire and 20 amp max 250V (Class B/UL) 300V (CSA).



Ordering Information:

| Part # | Description |
|----------|--|
| SSU00635 | TC1 18 Point Terminal Cabinet w/Captive Fastener |
| SSU00536 | TC1 18 Point Terminal Cabinet w/CAT30 Lock* |

Agency Approvals:

| | |
|------------|------------------------------------|
| UOXX.S2580 | UL Listed Control Unit Accessories |
|------------|------------------------------------|

* TC1 w/CAT30 Lock is not UL Listed

ACEBOX

Space Age Electronics, Inc.
www.1sae.com
800.486.1723 Toll Free
508.485.0966 Local
508.485.4740 Fax

No Excuses, Just Solutions!

This document is subject to change without notice, see doc # ED0479 for legal disclaimer

ED0150

LT10221

Rev.B

2/2