



# Customer Specification

## PART NO. SF61118CY

### Construction

		Diameters (In)			
1) Component 1		4 X 1 COND			
a) Conductor		18 (19/30) AWG TC		0.050	
b) Insulation		0.016" Wall, Nom. PVC/ 0.005" Wall NYLON		0.092	
(1) Print		ALPHANUMERIC NUMBERS - 1-ONE ALTERNATING AND INVERTED			
(2) Color Code		Alpha Wire Color Code KX			
Cond	Color	Cond	Color	Cond	Color
1	GREEN/YELLOW	3	BLACK#2		
2	BLACK#1	4	BLACK#3		
2) Cable Assembly		4 Components Cabled			
a) Twists:		4.0 Twists/foot (min)			
b) Core Wrap		REMA Y Tape, 25% Overlap, Min.			
3) Shield:		A/P/A Tape, 25% Overlap, Min.			
a) Drain Wire		20 (19/32) AWG TC			
b) Braid		TC,85% Coverage, Min.			
4) Jacket		0.055" Wall, Nom.,TPE		0.384+/- 0.020	
a) Color(s)		ORANGE			
b) Jacket Separator		Tissue Tape, 25% Overlap, Min.			
c) Print		ALPHA WIRE-* P/N SF61118CY 4C 18 AWG TFFN E324185 (UL) WTTC 90C 1000 VOLT OR (UL) TC-ER 90C 600V OIL RES I/II SUN RES OR C(UL) C/C CONTROL/TC 90C PVC/NYLON INS FT4 18 AWG --- LLXXXXXX CSA AWM I/II A/B 90C 600V FT4 CE ROHS (DATE CODE) (SEQ FOOTAGE) * = Factory Code <i>[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]</i>			

### Applicable Specifications

1) UL		
a) Component 1	TFFN	90°C / 600 V <sub>RMS</sub>
b) Overall	TC	90°C / 600 V <sub>RMS</sub>
	EXPOSED RUN	
	OIL RES I/II	
	SUN RES	
	WTTC	90°C / 1000 V <sub>RMS</sub>
2) CSA International	AWM I/II A/B	90°C / 600 V <sub>RMS</sub>
	FT4	
	C(UL) CIC CONTROL	90°C / 600 V <sub>RMS</sub>
	C(UL) TC	90°C / 600 V <sub>RMS</sub>
3) CE:	LVD 73/23/EEC Amendment 93/68/EEC	

## Environmental

1) EU Directive 2002/95/EC(RoHS):	
	All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.
2) California Proposition 65:	The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

## Properties

Physical & Mechanical Properties	
1) Temperature Range	-25 to 90°C(static), -5 to 90°C (dynamic)
2) Bend Radius	10X Cable Diameter
3) Pull Tension	76 Lbs, Maximum
4) Sunlight Resistance	Yes
Electrical Properties (For Engineering purposes only)	
1) Voltage Rating	600 V <sub>RMS</sub>
2) Capacitance	43 pf/ft @ 1 kHz, Nominal Conductor to Conductor
3) Ground Capacitance	77 pf/ft @ 1 kHz, Nominal
4) Inductance	0.19 µH/ft, Nominal
5) Conductor DCR	6 /1000ft @20°C, Nominal
6) OA Shield DCR	2.28 /1000ft @20°C, Nominal

## Other

<b>Packaging</b>	Flange x Traverse x Barrel (inches)
a) 1000 FT	20 x 11 x 8 Continuous length
b) 500 FT	16 x 11 x 8 Continuous length
c) 100 FT	12 x 10 x 5 Continuous length
	<i>[Spool dimensions may vary slightly]</i>
<b>Notes:</b>	
a) Suitable for use in Industrial Machinery per the requirements of NFPA-79	

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207

Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207

Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com



## EU/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: SF61118CY

SF61118CY , RoHS-Compliant Commencing With 2/9/2009 Production

This document certifies that the Alpha part number cited above are manufactured in accordance with Directive 2011/65/EC of the European Parliament, better known as the RoHS Directive, with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. The reader is referred to these Directives for the specific definitions and extents of these Directives. **No Exemptions are required for RoHS Compliance on this item.** Additionally, Alpha certifies that the listed part number is in compliance China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2006.

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm )
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE) , Including Deca-BDE	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire Company:

A handwritten signature in black ink, appearing to read 'Dave Watson'.

Dave Watson, Director of Engineering & QA

12/20/2012