



Market Segments:

- Residential
- Healthcare
- Hospitality
- Office
- Property Management
- Retail

ULTRA RT6 LED Recessed Downlight Kit

The SYLVANIA ULTRA RT6 is a six-inch LED recessed downlight kit creating high performing white light and is optimized for new construction and retrofit applications. Installation is done quickly and easily in most standard six inch:

- Insulated Ceiling (IC) housings
- Airtight (AT) housings
- Non-IC housings

Product Features & Benefits:

- Lumen package:
 - 625 lumens @ 11watts
 - Replacement for 65BR30 incandescent lamps
- CCT: 3000K and 2700K
- CRI of 82
- Dimmable to 20-100%
- 35,000 hour life (L₇₀)
- Suitable for indoor and damp locations
- Reduces energy consumption up to 86%
- 120V input voltage
- Lasts 17 times longer than incandescent lamps
- No warm-up time, instant-on with full light output and stable lamp to lamp color
- Meets California Title 24 fixture requirements for high efficacy luminaire
- Integrated white trim and medium base socket adaptor (included) for direct replacement



SYLVANIA 

Specifications & Ordering Information

Item Number	Ordering Abbreviation	Recessed Housing	Replaced Incandescent Wattage	Nominal Wattage (W)	Delivered Light Output (lm)	Color Temperature	CRI	Avg. Rated Life (hrs)*	Packaging Configuration
70644	LED/625/RT6/830/FL80/WRFL/WTR	6 in.	65W	11	625	3000K	82	35,000	1 Pack Blister
70651	LED/625/RT6/830/FL80/WRFL/WTR/2PK	6 in.	65W	11	625	3000K	82	35,000	2 Pack Blister
70653	LED/625/RT6/830/FL80/WRFL/WTR/BOX	6 in.	65W	11	625	3000K	82	35,000	Box


* LED lamp life is defined as the number of hours when 50% of an average group of identical lamps reached 70% of its initial lumens.

Ordering Guide


LED	/	625	/	RT6	/	8	30	/	FL	80	/	WRFL	/	WTR	/	2PK
LED		Light Output (lm)		Product Name RT6		CRI>80	Color Temperature 3000K		Flood	Beam Angle 80 degrees		White Reflector		White Trim		Package Qty.

Accessories

70650 LED/CRT6/GU24/SOCKET/ADAPTOR (sold separately)



70657 LED/CRT6/RETROFIT/ADAPTOR (sold separately)




Energy Savings

Basic Product Description	LED		Traditional Lamp Types	Lumens	Life	Watts Saved With RT6	RT6 Energy Savings*	RT6 Life Benefit
	Lumens	Life						
RT6 11W	625	35,000	Incandescent 65BR30	640	2000	54	\$208	17X
			Halogen 50WBR30/SS/HAL	585	2500	39	\$150	14X
			Halogen 50PAR30LN/WFL	660	2500	39	\$150	14X
			Compact Fluorescent 15WBR30	600	8000	4	\$15	4X


* Based on \$0.11/kwh, 3 hours a day

Lamp Dimensions




Photometric Information

Polar Chart



Illuminance at Distance



Zonal Lumen Distribution

Zone	Lumens	% Fixture
0-30	308.9	47.9
0-40	455.2	70.6
0-60	608.4	94.4
60-90	36.2	5.6
0-90	644.6	100.0
90-180	0.0	0.0
0-180	644.6	100.0

Application Notes

1. Operating temperature range between -32°F and +86°F (-0°C and +30°C).
2. Suitable for use in indoor and damp location environments.
3. Suitable for dimmers or in housings controlled by a dimmer – see www.sylvania.com/RT6 for detailed dimmer compatibility list.
4. Not intended for use with emergency light fixtures or exit lights.
5. For use in housings that can structurally support a lamp weighing one pound.
6. Designed to install in standard 6" insulated and non-insulated housings. For a list of compatible housings, please refer to www.sylvania.com/RT6.
7. For detailed warranty information, please see www.sylvania.com/RT6.

SYLVANIA is a registered trademark of OSRAM SYLVANIA Inc.
SEE THE WORLD IN A NEW LIGHT is a registered trademark of OSRAM SYLVANIA Inc.
Specifications subject to change without notice.

LED149R2

SYLVANIA
lighting facts[®]
A Program of the U.S. DOE

Light Output (Lumens)	625
Watts	11
Lumens per Watt (Efficacy)	61

Color Accuracy Color Rendering Index (CRI)	82
---	----

Light Color Correlated Color Temperature (CCT)	3000 (Bright White)
---	---------------------

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: 5BZT-1D3NNC
Model Number: LED/625/RT6/830/FL80/WRF/LWTR
Type: Recessed downlight

United States

OSRAM SYLVANIA
100 Endicott Street
Danvers, MA 01923

Trade

Phone: 1-800-255-5042
Fax: 1-800-255-5043

National Accounts

Phone: 1-800-562-4671
Fax: 1-800-562-4674

OEM/Special Markets

Phone: 1-800-762-7191
Fax: 1-800-762-7192

Display/Optic

Phone: 1-888-677-2627
Fax: 1-800-762-7192

SYLVANIA Lighting Services

Phone: 1-800-323-0572
Fax: 1-800-537-0784

Canada

OSRAM SYLVANIA LTD.
2001 Drew Road
Mississauga, ON L5S 1S4

Trade

Phone: 1-800-263-2852
Fax: 1-800-667-6772

OEM/Special Markets/Display/Optic

Phone: 1-800-265-2852
Fax: 1-800-667-6772

SYLVANIA Lighting Services

Phone: 1-800-663-4268
Fax: 1-866-239-1278

Mexico

OSRAM MEXICO
Headquarters
Tultitlan/Edo de Mexico
011-52-55-58-99-18-50

www.sylvania.com