
Belt/Pocket clip, Wall-suspension element, Wall-mounting brackets



Suitable for OKW cases:

- DATEC-POCKET-BOX L, M and S
- FLAT-PACK CASE N 100



boreholes ø 4.2 mm at a center distance of 20 mm. Simple mounting by means of 2 self-tapping screws ø 2.2 x 6 mm.


BELT/
POCKET CLIP
Universal clip. Two location
pillars for mounting into



RAY 9005



*Mounting angle (O) on the adapter serves as a support to locate the case in the right position. After attachment of the adapter, the mounting angles can be easily removed.



Version / Supply

Clip, black

Plastic/1 wall-susp. element each, 1 adapter 50 x 100 mm and assembly kit, recommended for shelf-type cases 110 (without battery compart.), flat-pack cases 120, desk cases 190. Plastic, 1 wall-susp. element each, 1 adapter 58 x 124 mm and assembly kit, recommended for shell-type cases 155/190 (without battery compart.), flat-pack cases 150/189/210, desk cases 138.

WALL-SUSPENSION ELEMENTS

Universally applicable, for small plastic cases with 3 mm wall thickness. For easy machining. The adapter is screwed down together with the base part of the case. Due to preshaped pockets, each case can be quickly and securely unlatched from the wall-suspension element.


Part-No.

B 13 60 048

WALL-MOUNTING BRACKETS

Exterior wall-mounting elements for the SHELL-TYPE CASES 110, 155 and 190. Fastening to the case by means of the case fixing screws.





 Version
 Supply

 Polyamide, pebble grey RAL 7032
 4 pieces

Part-No. A 92 04 108

ACCESSORIES

TILT FOOT BAR


Universal tilt foot bar. Can be placed in any position to choose an ergonomical reading angle.


Simple mounting with 2 self-tapping screws, ø 2.2 x 6 mm.

Necessary location holes: 2 x ø 4.2 mm at a center distance of 20 mm

Suitable for the OKW cases:

- SHELL-TYPE CASE 110 and 155
- HAND-HELD-BOX P and M
- FLAT-PACK CASE »Special version of tilt foot bar suitable for DATEC-MOBIL-BOX M and S see page 30.«









Part-No.	
A 92 50 807	
A 92 50 809	
A 02 07 150	

Article / Version	Supply
Tilt foot bar of ABS, off-white RAL 9002	1 tilt foot bar
Tilt foot bar of ABS, black RAL 9005	2 self-tapping screws ø 2.2 x 6 mm
Clear non-slip pads	2 pieces ø 6.5 mm

CASE FEFT

Available in 2 versions:


Version I:

Case feet for universal application.


Version II

sion as version I tilt foot bar (next item). Clip mechanism for two





Example of mounting:



Supply

2 feet with accessories

2 feet with accessories

Version II

	4
٦	
4	

Sama v	arc

but for combination with the different canting angles.

Part-N	0.
A 92 01	800
A 92 02	800

. ,		_	гоот	D 4 D
	ш	- 1	F()()	RAR


	Part-No.
P	93 09 009

	L
A 93 09 009	L
A 93 16 009	Γ
A 93 22 009	Γ
A 93 23 009	Γ

Dim. i	n mm	Version /
A	a	Supply
104	88	Galvanized steel
174	158	1 wire section
234	218	
246	230	7

Case feet, polystyrene, basalt grey RAL 7012

Case feet, polystyrene, basalt grey RAL 7012



Version

II




Case feet, Anti-slide feet, Self-tapping screws, Battery clips, Battery spacer



Case drilling details





Version	Colour	Material
I	off-white, RAL 9002, rubber inserts pebble grey	ABS (UL 94 HB)
II	off-white, RAL 9002, rubber inserts pebble grey	ABS (UL 94 HB)
I		ABS (UL 94 HB)
II	black, RAL 9005, rubber inserts pebble grey	ABS (UL 94 HB)

CASE FEET

Universal case feet for all types of plastic and metal enclosures with max. 4 mm wall thickness

Version I

- 4 foot mouldings.
- 4 non-slip rubber inserts. 4 self-tapping screws.

Version II:

As above but also including 2 tilt legs.

Part-No.
A 92 57 107
A 92 57 207
A 92 57 109
A 92 57 209




φ:	=A	
		<u>-</u>

Dim. in mm A = ø B	Colour	Material / Supply
6.5 2	transparent	Silicon, 2 pcs.
10 2.9	transparent	Silicon, 2 pcs.
12 3.5	transparent	Silicon, 2 pcs.

Part-No.	
A 92 07 150	
A 92 10 290	
V 05 15 550	

ANTI-SLIDE FEET






12	3.5	transparent	Silicon, 2 pcs.		
	Self-tapping crosshead screw, specifically suitable for plastics.				
For	uitable for plastics. or fastening components, boards and PCBs				


onto pillars

Version	Supply
2.5 x 6 mm	1 pc.
3 x 6 mm	1 pc.
3 x 8 mm	1 pc.

SELF-TAPPING	j
SCREWS	

Part-No.
A 03 05 031
A 03 06 031
A 03 08 031





For round cells only (AA type). Useful for
DATEC-MOBIL-BOX, SHELL-TYPE-CASE,
LUX CASE and HAND-HELD-BOX.


version/ suppry
large, double contact, tin plated, 1 pc.
small, single contact, tin plated, 1 pc.
large, double contact, nickel plated, 1 pc.
small, single contact, nickel plated, 1 pc.

BA1	TTER	Y CL	IPS

Part-No.

A 91 93 003
A 91 93 004
A 91 93 005
A 91 93 006
BATTERY SPACER





- Suitable for: - DATEC-POCKET-BOX L
- DATEC-MOBIL-BOX S - HAND-HELD-BOX N
- LUX-CASES 150 and 190 - SHELL-TYPE CASES Versions III and IV

	(PP3).
Version / Supply	

PE foam with one-sided adhesive coating, 1 pc.

the differences in height and to secure the mignon cells (AA) within the battery compartments, which can also hold a 9 V flat battery

It serves to compensate for

Part-No.



HANDLE BAR / BAIL ARM

Possible to mount from the outside and inside - removable

NEW: Universal handle – available in any width almost for any housing.

The handle can be mounted from the outside and inside. It can be removed in the 135° position. Ratchet with 30° indexing. If the handle is overloaded the ratchet will automatically disengage to avoid damaging the mechanism!



Extrusion length = Case width + 3 mm ST Case width Case width

Fmax 400 N Fmax 200 N disassembly position

Supply:

2 side arms.

Fastening elements.

1 aluminium center section (cut to your requested length).

Order data:

Order the side arm kit and give us the width of your housing. We will supply the components as a set with the aluminium profile of the required length.





STANDARD COLOURS

Side arms: Off-white, RAL 9002. Push buttons: Volcano, NCS 5502-G. Center section: Silver, matt anodized.

MATERIAL

Side arms glass reinforced polyamide. The center section extruded matt anodized aluminium. Stainless springs.

Part-No. A 93 00 722 Article Colour Side arms kit Side ar

Side arms off-white RAL 9002 / push buttons volcano

HANDLE BAR / BAIL ARM




STANDARD COLOURS


One-coloured: Off-white, RAL 9002 or black, RAL 9005.

Two-coloured: Side arms off-white. RAL 9002 and push buttons pebble grey, RAL 7032 or Side arms pebble grey, RAL 7032 and push button off-white, RAL 9002.

MATERIAL

Side arms glass reinforced polyamide. The middle section extruded matt anodized aluminium






2 side arms

- 2 fastening screws
- 1 requested aluminium center section

	Article	Colour combination
	Side arms kit	off-white RAL 9002 / push buttons pebble grey RAL 7032
	Side arms kit	off-white RAL 9002 / push buttons pebble grey RAL 9002
	Side arms kit	pebble grey RAL 7032 / push buttons off-white RAL 9002
	Side arms kit	black RAL 9005




STANDARD COLOURS

Side arms and mechanism off-white, RAL 9002, push button pebble grey, RAL 7032. Anti-glide rubber inserts black.

MATERIAL

Side arms and mechanism diecast zinc. Push button plastic moulded glass reinforced polyamide. Extruded center section matt anodized aluminium. Anti-glide inserts in rubber.



2 fastening screws

1 requested aluminium center section

Article	Colour combination			
Side arms kit	Side arms off-white RAL 9002 / push buttons pebble grey RAL 7032			

HANDIF BAR IN INJECTION MOULDED PLASTIC

Universal handle - available in any width almost for any housing.

Strong ratchet with 30° indexing.

Order data:

Order the side arm kit and give us the width of your housing. We will supply the components as a set with the aluminium profile of the required length.

Part-No

A 93 00 016	
A 93 00 017	
A 93 00 018	
A 93 00 015	

HANDIF BAR IN DIFCAST 7INC

Universal robust handle available in any width almost for any housing.

Strong ratchet with 30° indexing.


Order data:

Order the side arm kit and give us the width of your housing. We will supply the components as a set with the aluminium profile of required


In order to improve the stability, we recommend glueing the aluminium profiles with the lateral parts.

> Part-No. A 93 00 014



















ACCESSORIES

Cable glands

CABLE GLANDS WITH PULL RELIEF

















Cable glands of the best material for shake and twistproof cable lead-in for OKW housings. High protection class IP 68.

COUNTERNUTS







STANDARD COLOURS

Cable glands silver grey, RAL 7001. Counternuts light grey, RAL 7035. Sealing ring naturalcoloured.

MATERIAL


Cable glands and counternuts polyamide.
Sealing ring of polyethylene.

SEALING RING FOR EXTERNAL THREAD

Mounting between housing and gland flange to preserve the high protection class **IP 68** of the OKW cable glands.


Part-No.	
C 23 12 126	M12
C 23 16 126	M16
C 23 20 126	M20
C 23 25 126	M25
C 23 32 126	M32

M32



Comparison between PG and metric thread:

Mounting drills (ø in mm)



	KEY WIDTH				CLAMP RANGES	
Dim. in mm						of all cable glands
	SW1	SW2	D	L	H	
M12	15	17	12.5	8	5	ø 3 - 6.5
M16	22	22	16.5	8	5	ø 5-10
M20	24	26	20.5	11	6	ø 6-12
M20	27	26	20.5	15	6	ø 10 - 14
M25	33	32	25.5	15	6	ø 13 - 18

ø 18 - 25

32.5 15