



Specification Table

Type	LS00435	LS00436
Loudspeaker Diameter	10"	12"
Transducer Function	Woofer	
Sound Level Spl	87dB	91dB
Impedance	8Ω	
Power Rating Rms	85W	100W
Frequency Response Minimum	30Hz	26Hz
Frequency Response Maximum	4kHz	3kHz
External Depth	125mm	140mm
Output Power	150W	200W
Power Rating	85W	100W

Part Number Table

Description	Part Number
Woofer, Poly/rubber, 8Ω, 10"	LS00435
Woofer, Poly/rubber, 8Ω, 12"	LS00436

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of the Group. © Premier Farnell plc 2012.