



by Schneider Electric

List Price \$34.10 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Enclosure Type	General Purpose (Indoor)
Enclosure Rating	NEMA 1
Actuator Type	Diaphragm
Application	Controlling small electrically driven air compressors
Approvals	UL Listed File: E12158 CCN NKPZ - CSA Certified File: LR25490 Class 3211 06
Marketing Trade Name	Pumptrol
Contact Arrangement	DPST
Contact Rating	A600
Depth	2.78 Inches
Diaphragm	Nitrile (Buna N)
Differential	35 PSIG
Differential Type	Fixed
Pressure Setting	Off at 175 PSIG
Mounting Type	Bracket
Range on Increasing Pressure	100 to 200 PSIG
Terminal Type	Screw Clamp
Type	FHG
Weight	1.13 Pounds
Width	3.76 Inches
Height	2.80 Inches
Pressure Connection	0.25 Inch NPT
Horsepower Rating (1-Phase)	1.5HP@115VAC - 2HP@230VAC
Horsepower Rating (3-Phase)	2HP@115VAC - 3HP@230VAC - 1HP@460/575VAC
Includes	Maintained manual cut-out lever - Two-Way pressure release valve
Number of Poles	2-Pole
Maximum Allowable Pressure	220 PSIG
Maximum Voltage Rating	575VAC

Shipping and Ordering

Category	21533 - Pressure Switches, Commercial, Individual Pack, Type FHG
Discount Schedule	CP71
GTIN	00785901051176
Package Quantity	1
Weight	0.97 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 11/08/2012 16:24:04