Precision balance KERN 440









The bestseller in basic laboratory balances

Features

- Ring-shaped draft shield standard, only for models with weighing plate sizes A, weighing space ØxH 90x40 mm
- UNITS: Further weighing units see the internet

Technical data

- Backlit LCD display, digit height 15 mm
- Dimensions of weighing plate (stainless steel*)
- A ø 81 mm
- **B** ø 105 mm*
- C 130x130 mm*
- 150x170 mm*, see larger picture

- Optional battery operation, 9V, not included. AUTO-OFF function to preserve the battery
- Overall dimensions (without draft shield) WxDxH 165x230x80 mm
- Net weight approx. 1 kg
- Permissible ambient temperature 5°C / 35°C

Options

- Protective working cover over keyboard and housing, standard, can be reordered for models with weighing plate sizes
- A KERN 440-210-002
- **B** KERN 440-330-002
- **E** KERN 440-450-002
- KERN 440-530-002

- Rechargeable battery pack internal, operating time approx. 10 h, charging time approx. 10 h, KERN FCB-A01
- Matrix needle printer, KERN 911-013
- **11 Thermal printer**, KERN YKB-01N
- 2 Statistics printer, KERN YKS-01
- Individual header data: the free software KERN SHM-01 can be used to print 4 header lines on the printout for printers 911-013 and YKB-01N

For additional information on the printers see page 124









































Model	Weighing range [Max]	Read- out [d]	Repro- duci- bility	Linea- rity	Min. piece weight [PW min]	Weighing plate	Option DKD Calibr. Certificat	
							DKD	
KERN	g	g	g	g	g/piece		KERN	
440-21A	60	0,001	0,001	± 0,003	0,002	Α	963-127	
440-33N	200	0,01	0,01	± 0,02	0,02	В	963-127	
440-35N	400	0,01	0,01	± 0,03	0,02	В	963-127	
440-35A	600	0,01	0,01	± 0,03	0,02	В	963-127	
440-43N	400	0,1	0,1	± 0,2	0,2	C	963-127	
440-45N	1000	0,1	0,1	± 0,2	0,2	C	963-127	
440-47N	2000	0,1	0,1	± 0,2	0,2	C	963-127	
440-49N	4000	0,1	0,1	± 0,3	0,2	D	963-127	
440-49A	6000	0,1	0,1	± 0,3	0,2	D	963-128	
440-51N	4000	1	1	± 2	2	D	963-127	
440-53N	6000	1	1	± 2	2	D	963-128	

KERN Pictograms



Internal adjusting (CAL): Quick setting of the balance's accuracy with internal adjusting weight (motordriven).



Rechargeable battery pack: rechargeable set.



Battery operation: The battery type is specified for each device.



Data interface: The type of interface is shown by the pictogram. See the glossary for further details.



Dynamic weighing: Strong vibrations are filtered out to determine a stable weighing result.



Net-total weighing: weight of tare cup and weight of components memorized in two separate stores.



Percentage determination: Determining the deviation in % from the target value (100%).



Package shipment via courier.



Adjusting program (CAL): For quick setting of the balance's accuracy. External adjusting weight required.



Power supply: integrated in balance. 230V/50Hz in Germany. On request GB, AUS or USA version.



Piece counting: Reference quantities selectable. Display can be switched from piece to weight



GLP/ISO record keeping of weighing data with date, time and identification-no. Only with printers from KERN.



Stainless steel: the balance is protected against corrosion.



Suspended weighing: load support with hook on the underside of the balance.



Weighing with tolerance range: Upper and lower limiting can be programmed individually, e.g. dosing/sorting.



Pallet shipment via freight forwarder.



Weighing units: Can be switched to e.g. nonmetric units at the touch of a key. See balance model. Please refer to KERN's website for more details.



Mains adapter: 230V/50Hz in standard version for Germany. On request GB, AUS or USA version.



Spray and dust protection IPxxThe type of protection is shown by the pictogram. For details see the glossary.



Tare: put back displayed value to "0" during weighing process, e.g. to add or remove weighing material from a container.



Warranty: The warranty period is shown in the pictogram.



Verification possible: The time required for verification is specified in the pictogram.



DKD calibration possible: The time required for DKD calibration is specified in the pictogram.



For details on weighing technologies, see the glossary.

Precision is our business

To ensure the high level of precision of your balance, KERN offers the appropriate test weight package for your balance. This consists of the test weight, box and DKD calibration certificate, as proof of its accuracy. The best way to ensure proper balance calibration.

In the extensive KERN test weight range, you will find test weights in the international OIML error limit classes: E1, E2, F1, F2, M1, M2, and M3 with weights from 1 mg to 2000 kg.

The KERN DKD calibration laboratory for electronic balances and weights has been accredited by DKD since 1994 and today is one of the most modern and best-equipped DKD calibration laboratories for balances, test weights and force-measurement in Europe.

(DKD = German Calibration Service)

Thanks to the high level of automation, we can carry out DKD calibration of balances, test weights and force-measuring devices 24 hours a day, 7 days a week.

Range of services:

- DKD calibration of balances with a maximum load of up to 6000 kg
- DKD calibration of weights in the range of 1 mg 500 kg
- Database supported management of checking equipment and reminder service
- Calibration of force-measuring devices
- DKD calibration certificates in the following languages
 D, GB, F, I, E, NL, PL

Do you have questions about your scale, the corresponsing test weight or the calibration service? Your KERN specialist dealer will be pleased to assist you.

Your KERN specialist dealer:

KERN - Professional measuring. Measuring technology and testing services from a single source









