



## Features:

- 2 gang extension lead with 15cm

## Standard

- BSEN 60598-1

## Specifications:

Current Rating : 2A, 240V

## Conditions of Use:

This equipment is intended for domestic use only. It must be installed in accordance with the fitting instructions. It should be fixed in the approved and conventional way to a solid or stud partition wall. Wallpaper/wallpaper paste of any sort should not continue beneath the plate towards the working parts of the equipment. It should not be used in areas of high humidity (bathrooms etc.) , nor within reach of a water source. The equipment should be connected to a mains supply of the appropriate voltage (indicated on the product). Care should be taken not to overload the equipment (maximum wattage indicated on the product/packaging). If you are unsure consult a qualified electrician before fitting. No liability can be accepted if the product is installed or used in any other way.

## Safety Specifications:

Item	Conditions	Requirements
Appearance	-	No defect such as cracks, deep scratches or blemishes
Marking	-	Shall be leg
Insulation resistance	500 + 250V DC 1 minute	Shall not be less than 5MΩ
Resistance to aging	70° ±5° 168 hours	No cracks or become sticky
Torque test	Value of 0.5Nm (5.1 kgf/cm)	Terminal, cord grip and cover screws shall withstand the torque applied
Glow wire test	650°/750° electrically heated	Flame must extinguish within 30 seconds
Temperature rise	14A, 250V	Temperature rise must not exceed: 1. Terminals or terminations : 45K 2. Accessible surface : 45K
The ball presses the test	-	To use 100°C to test first for 1 hour then promotes the temperature to 125°C tests 1 hour, the zhdenation cannot surpass 2mm

## Construction:

Item	Description	Material
1	Cover	Pa
2	Bass	
3	Button	
4	Driver	
5	N plate	Bronze
6	Metal plate	Iron
7	Contact	p-bronze
8	Driver spring	Iron
9	L plate 1	Bronze
10	L plate 2	
11	Screw	Iron, 6BA * 5.5
12		Iron, M3 * 13
13	Touch	Ag

## Part Number Table

Description	Part Number
Switch, In-line, 2A, White	200

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of the Group. © Premier Farnell plc 2012.