



SOCKETS FOR C4 AND C5 RELAYS

- Built in retaining clip
- Removable label marking facility
- Two level terminals
- DIN rail, solder tag or PCB mount




S4-B

Two level screws
Logic wiring

Integrated hold-down clip and removable marking label. DIN rail or panel mountable. EN/DIN and sequential numbering. According to EN60947

Wiring diagram



Specifications

Nominal load 10 A/250 V
Dielectric strength (adjacent screws) 2,5 KV
Dielectric strength (screws/rail) 2,5 KV
Max. screw torque 1,2 Nm
Screw dimensions M3, Pozi
Wire in-lets capacity:
Solid wire 4 mm² or 2 x 2,25 mm²
Multi-core 22 - 14 AWG

Lloyd's (N) (FI)

S4-L

S4-P

S4-PO


14 pin, solder and printed circuit tags

S4-L Flange panel mountable.

S4-P Printed circuit tags.

S4-PO Printed circuit tags with flange.

Printed circuit lay-out



Specifications


Nominal load 10 A/250 V
Dielectric strength (adjacent pin) 2,5 KV
Hard brass tin-plated terminals

S5-S

Two level screws
Logic wiring

Integrated hold-down clip and removable marking label. DIN rail or panel mountable. EN/DIN and sequential numbering. According to EN60947

Wiring diagram




Specifications

Nominal load 16 A/400 V
Dielectric strength (adjacent screws) 2,5 KV
Dielectric strength (screws/rail) 2,5 KV
Max. screw torque 1,2 Nm
Screw dimensions M3, Pozi
Wire in-lets capacity:
Solid wire 4 mm² or 2 x 2,25 mm²
Multi-core 22 - 14 AWG




S4-B



S4-PO

S4-L



S5-S

