


S R M - 8 R 8 G N - V

- = Without Ground Terminal
- = With Ground Terminal
- = Non-click Actuation
- = ForceColor: Black
- = N=130±50gf cm.Actuation
- = ForceColor: Brown
- = B=40±30gf cm.Actuation
- = ForceColor: Blue
- = V=Lead Free



Chargeover Angle

MODE1	MODE2	MODE3	MODE4	MODE5	MODE6	MODE7	MODE8
COM-A	OFF	OFF	OFF	ON	ON	OFF	OFF
COM-B	ON	OFF	OFF	ON	ON	OFF	OFF
COM-C	ON	ON	OFF	ON	ON	OFF	OFF
COM-D	OFF	OFF	OFF	ON	ON	OFF	OFF

NOTE:
1. ALL DIMENSIONS ARE IN MILLIMETERS, BRACKETED DIMENSIONS ARE IN INCHES
2. GENERAL TOLERANCES MAX±0.20mm.
3. SWITCHING SHOW IN MODE5 POSITIONG

REV	DATE	DESCRIPTION	APP'D
1			

REV	DATE	DESCRIPTION	APP'D
1			

REV	DATE	DESCRIPTION	APP'D
1			

REV	DATE	DESCRIPTION	APP'D
1			

REV	DATE	DESCRIPTION	APP'D
1			

國達實業股份有限公司
DIPTRONICS MANUFACTURING INC.

PART NAME: ROTARY-8R

PART NO: SRM-8R8-V