

I.D. Pro® Plus Printer Accessories

Brady continues to manufacture and fully stock the complete range of labels, sleeves and accessories for the I.D. Pro™ Plus Printer!



| Description | Part# |
|--|-------------|
| Hard Side Carrying Case | IDPRO-HC |
| 12-volt Battery Charger | IDPRO-BC12V |
| Battery Pack | IDPRO-BP |
| Battery Charger | IDPRO-BC |
| Black High-Performance Ribbon for PermaSleeve™ and DuraSleeve™ | R5300 |
| Black High-Performance Ribbon for all labels and BradySleeve™ (Lighter Print more Smear resistant) | R7300 |

+ **May We Also Suggest...**
IDXPERT™ HandHeld Labeler.
 The newest 300dpi Thermal Transfer labeling system.
 see pg 196



U.S Patent Number D409,230



Adhesive Wire Marking Labels for I.D. Pro® Plus

- Labels are designed for use with the I.D. Pro™ Plus Portable Printer
- Highly durable and easily visible; perfect for all your on-site label or wire marking applications

| Label Material | Labels per Roll | Approx. Wire Gauge | Label Dimensions Inch (mm) | | Max. Lines of Print | Maximum Characters Across | | Part# |
|---------------------------------|-----------------|--------------------|----------------------------|-------------|---------------------|---------------------------|-------|-------------|
| | | | Width | Height | | Large | Small | |
| Nylon Cloth, Permanent Adhesive | 500 | 16-22 | .5(12.7) | .5(12.7) | 3 | 3 | 4 | WML-305-499 |
| General-Purpose Vinyl Cloth | 500 | 16-22 | .5(12.7) | .5(12.7) | 3 | 3 | 4 | WML-305-502 |
| Nylon Cloth, Permanent Adhesive | 250 | 10-16 | .5(12.7) | .75(19.05) | 4 | 3 | 4 | WML-505-499 |
| General-Purpose Vinyl Cloth | 250 | 10-16 | .5(12.7) | .75(19.05) | 4 | 3 | 4 | WML-505-502 |
| Nylon Cloth, Permanent Adhesive | 250 | 10-16 | 1.0(25.4) | .75(19.05) | 4 | 7 | 10 | WML-511-499 |
| General-Purpose Vinyl Cloth | 250 | 10-16 | 1.0(25.4) | .75(19.05) | 4 | 7 | 10 | WML-511-502 |
| Nylon Cloth, Permanent Adhesive | 250 | 10-12 | .5(12.7) | 1.0(25.4) | 6 | 3 | 4 | WML-705-499 |
| General-Purpose Vinyl Cloth | 250 | 10-12 | .5(12.7) | 1.0(25.4) | 6 | 3 | 4 | WML-705-502 |
| Nylon Cloth, Permanent Adhesive | 250 | 10-12 | 1.0(25.4) | 1.0(25.4) | 6 | 7 | 10 | WML-711-499 |
| General-Purpose Vinyl Cloth | 250 | 10-12 | 1.0(25.4) | 1.0(25.4) | 6 | 7 | 10 | WML-711-502 |
| Nylon Cloth, Permanent Adhesive | 250 | 6-10 | .5(12.7) | 1.25(31.75) | 8 | 3 | 4 | WML-905-502 |
| General-Purpose Vinyl Cloth | 250 | 6-10 | 1.0(25.4) | 1.25(31.75) | 8 | 7 | 10 | WML-911-499 |
| Nylon Cloth, Permanent Adhesive | 250 | 6-10 | 1.0(25.4) | 1.25(31.75) | 8 | 7 | 10 | WML-911-499 |
| General-Purpose Vinyl Cloth | 250 | 6-10 | 1.0(25.4) | 1.25(31.75) | 8 | 7 | 10 | WML-911-502 |

Self-Laminating Wire Marker Labels for I.D. Pro® Plus

- Vinyl labels feature clear "trailer" that wraps to protect printed text
- Resistant to oil, water, and solvents



| Approx. Wire Gauge | Max. Wire Diameter Inch (mm) | Label Dimensions Inch (mm) | | Write-on Area Height | Lines of Print | Max. Characters Across | | Part# |
|--------------------|------------------------------|----------------------------|-------------|----------------------|----------------|------------------------|-------|-----------------|
| | | Width | Height | | | Large | Small | |
| 10-12 | .21(5.3) | .5(12.7) | 1.0(25.4) | .375(9.53) | 2 | 3 | 4 | WML-205-292-1 |
| 10-14 | .185(4.7) | .5(12.7) | .75(19.05) | .4(10.16) | 2 | 3 | 4 | WML-205-292-2S* |
| 10-16 | .16(4.1) | .5(12.7) | .75(19.05) | .375(9.53) | 2 | 3 | 4 | WML-205-292-75 |
| 10-12 | .21(5.3) | 1.0(25.4) | 1.0(25.4) | .375(9.53) | 2 | 7 | 10 | WML-211-292-1 |
| 10-16 | .16(4.1) | 1.0(25.4) | .75(19.05) | .375(9.53) | 2 | 7 | 10 | WML-211-292-75 |
| 6-10 | .26(6.6) | .50(12.7) | 1.25(31.75) | .5(12.7) | 3 | 3 | 4 | WML-305-292 |
| 6-10 | .26(6.6) | .50(12.7) | 1.25(31.75) | .52(13.21) | 3 | 3 | 4 | WML-305-292-2S* |
| 6-10 | .26(6.6) | 1.0(25.4) | 1.25(31.75) | .5(12.7) | 3 | 7 | 10 | WML-311-292 |
| 6-10 | .26(6.6) | 1.5(38.1) | 1.25(31.75) | .5(12.7) | 3 | 10 | 15 | WML-317-292 |

*Labels are scored in half, length-wise. The width is only .25"