

UL TYPE CM, AWM 2464
CSA CMG FT4
300 VOLT

XTRA•GUARD® 1

MULTIPAIR, SUPRASHIELD®

EXTRA-PREMIUM GRADE PVC JACKET FOR EXTENDED CABLE LIFE

CHOOSE XTRA•GUARD 1 For:

- Unsurpassed Flame and Moisture Resistance
- Fast, Easy Stripping of Insulation and Jacket
- UL Recognition, UL Listing and CSA Certification
- **SUPRASHIELD** — Twice as Effective as Foil Shielding

XTRA•GUARD 1 APPLICATIONS:

- EIA RS 232C Interface (24, 22 AWG)
- High Technology Applications in Controlled Environments
- Point-Of-Sale Equipment
- Computer Peripherals
- Industrial Process Controls

CHARACTERISTICS

OPERATING TEMPERATURE:

- -20°C to 80°C — AWM
- -20°C to 75°C — CM

VOLTAGE RATING:

- 300 Volt

COLOR DESCRIPTION:

- Color Code: 24, 22 AWG Chart B Page 374,
20, 18 AWG Chart A Page 374
- Jacket Colors: Gray, Black

PRODUCT DESCRIPTION:

- Conductor: Stranded Tinned Copper
- Insulation: Color-Coded Premium PVC
- **SUPRASHIELD**: Aluminum/Polyester/Aluminum
Foil with Stranded Tinned Copper Drain Wire Equal in
Size to Insulated Conductors of Cable plus 70% Overall
Braid of Tinned Copper
- Nylon Rip Cord for Ease of Jacket Stripping
- Jacket: Premium PVC

SPECIFICATIONS

- UL Type CM, AWM Style 2464
- CSA CMG FT4
- Passes UL VW-1 Flame Test
- Passes CSA FT4 Flame Test

UL LISTED  Passes
UL VW-1 Flame Test  Certified
Underwriters Laboratories Inc. Canadian Standards Association




AVAILABILITY

- In Stock: Gray 100 ft (30,5m), 500 ft (152m) and
1000 ft (305m) put-ups
- Made-To-Order: Black, 1000 ft (305m) minimum

FIT® TUBING RECOMMENDATION

FIT®-221 — General Purpose, Irradiated Polyolefin (See Page 114 for
Product Specifications)

FIT®-321 — Medium Wall, Adhesive Lined, Irradiated Polyolefin (See Page 121 for Product Specifications)



24 AWG (0,23mm²), **7/32** (7x0,20mm), Insulation Thickness: **0.010"** (0,25mm)

XTRA•GUARD 1 Part No.	No. of Pairs	Jacket Thickness		Nominal Diameter	
		Inches	mm	Inches	mm
5271C	1	0.032	0,81	0.18	4,6
5272C	2	0.032	0,81	0.23	5,8
5273C	3	0.032	0,81	0.25	6,5
5274C	4	0.032	0,81	0.28	7,0
5275C	5	0.032	0,81	0.30	7,5
5276C	6	0.032	0,81	0.31	8,0
5279C	9	0.032	0,81	0.36	9,1
5279/11C	11	0.032	0,81	0.38	9,7
5279/15C	15	0.032	0,81	0.43	10,8
5279/19C	19	0.032	0,81	0.46	11,8
5279/27C	27	0.032	0,81	0.53	13,4
5279/51C	51	0.053	1,35	0.71	18,1

22 AWG (0,35mm²), **7/30** (7x0,25mm), Insulation Thickness: **0.010"** (0,25mm)

XTRA•GUARD 1 Part No.	No. of Pairs	Jacket Thickness		Nominal Diameter	
		Inches	mm	Inches	mm
5121C	1	0.032	0,81	0.20	5,1
5122C	2	0.032	0,81	0.25	6,3
5123C	3	0.032	0,81	0.28	7,1
5124C	4	0.032	0,81	0.31	7,8
5125C	5	0.032	0,81	0.33	8,3
5126C	6	0.032	0,81	0.35	8,9
5129C	9	0.032	0,81	0.40	10,1
5129/11C	11	0.032	0,81	0.43	10,9
5129/15C	15	0.032	0,81	0.48	12,1
5129/19C	19	0.032	0,81	0.52	13,2
5129/27C	27	0.053	1,35	0.64	16,2

20 AWG (0,56mm²), **7/28** (7x0,32mm), Insulation Thickness: **0.017"** (0,43mm)

XTRA•GUARD 1 Part No.	No. of Pairs	Jacket Thickness		Nominal Diameter	
		Inches	mm	Inches	mm
5292C	2	0.032	0,81	0.33	8,3
5293C	3	0.032	0,81	0.35	8,9
5296C	6	0.032	0,81	0.44	11,3
5299C	9	0.032	0,81	0.51	13,0
5299/19C	19	0.053	1,35	0.72	18,4

18 AWG (0,81mm²), **16/30** (16x0,25mm), Insulation Thickness: **0.017"** (0,43mm)

XTRA•GUARD 1 Part No.	No. of Pairs	Jacket Thickness		Nominal Diameter	
		Inches	mm	Inches	mm
5132C	2	0.032	0,81	0.36	9,1
5133C	3	0.032	0,81	0.39	9,8
5136C	6	0.032	0,81	0.49	12,5
5139C	9	0.053	1,35	0.62	15,6
5139/27C	27	0.083	2,11	0.98	24,9

FOR COMPLETE PRODUCT PERFORMANCE DATA, SEE TECHNICAL SECTION IN THE BACK OF THIS BOOK.

Web Site: www.alphawire.com
Email: info@alphawire.com

Toll Free: 1-800-52 ALPHA • Telephone: 908-925-8000 • Fax: 908-925-6923
Europe/UK Telephone: +44 (0) 1932 772422 • Europe/UK Fax: +44 (0) 1932 772433

