

Industrial and Commercial

J86-4400 Series Vandal-proof Keyboard



**Rugged, Stainless Steel
Vandal-resistant Keyboard
with 67-key Layout and
Integrated Trackball**




Key Features

- Stainless steel keytops and fascia
- 67-key US layout for public-access kiosk applications
- Durable rubber mat switches with crisp tactile action
- Ultra-rugged trackball
- Meets IP65 standards when mounted in suitable enclosure
- Key layout includes five internet-friendly, customizable shortcut keys

Main Part Numbers

J86-4400LUAUS

Stainless steel, 67-key layout with rubber mat switches and rugged trackball



Low-profile design suitable
for a variety of kiosk applications



Industrial and Commercial

J86-4400 Series Vandal-proof Keyboard

Part Number Legend



Technical Data

Interface

USB 2.0
PS/2 (Special build only)
AT (Special build only)

Cable Length

71"
1.8mm

Key Layout

67 key layout

Keys

Tactile rubber mat switch
Typical operating force 130 gm

Weight

1.1 kgs
2.43 lbs

Dimension

400 x 124 x 49mm (Approx)
15.75" x 4.88" x 0.75"

Color

Stainless steel

Trackball

Ball diameter; 38mm (1.5 inches)
Trackball material; Phenolic
Lip seal; PTFE/rubber
Resolution; 440 edges/revolution
Reliability; 50,000 hrs MTBF

Travel

0.7mm

Keyswitch Lifetime

3 million operations

Operating Temperature

0°C to 50°C

Storage Temperature

-20°C to 70°C

Compliance

FCC subpart 15, Class B
CISPR22

For information on repairs or warranty status contact:
Cherry Technical Support
Phone: 800.510.1689
E-Mail: keyboardsupport@cherrycorp.com

Contact

Call, fax or visit our website for more information.

Cherry Electrical Products

11200 88th Avenue
Pleasant Prairie, WI 53158

Phone: 262.942.6500
Web: www.cherrycorp.com

E-Mail: sales@cherrycorp.com
Fax: 262.942.6566

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice.

Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.