


Steatite Ceramic Terminal Blocks

Approved industrial high temperature terminal blocks in 2 and 3 pole options.



Approvals pending

Specifications:-					Features:-						
Inserts	<i>Nickel-plated brass (galvanised)</i>				Steatite is an alternative to Porcelain Ceramic and has many advantages such as:- Higher density, better bending/compression strength and elasticity, higher dielectric strength, non-flammable and temperature-resistant with dimensional stability up to 1000 °C						
Screw	<i>Zinc-plated steel (galvanised), blue passivated</i>										
Housing	<i>Steatite C 220, IEC 672-1, unglazed</i>										
Temp C	Continuous use temperature max. 350 °C										
					Dimensions (mm)					□ ₁	□ ₂
Part No.	Rated Cross Section	A (max)	V (Max)	Poles	W	L	H	d	D	Conductor size Min/Max mm ²	Fixing hole
HYSTB-0252	2.5 mm ²	24	450	2	18	21	15	8	11	1.5-6.0	M3
HYSTB-0253	2.5 mm ²	24	450	3	18	33	15	8	11	1.5-6.0	M3
HYSTB-0402	4.0 mm ²	32	450	2	22	24	21	10	14	2.5-10.0	M3.5
HYSTB-0403	4.0 mm ²	32	450	3	22	38	21	10	14	2.5-10.0	M3.5
HYSTB-1002	10.0 mm ²	57	450	2	30	34	23	13	19	2.5-16.0	M4
HYSTB-1003	10.0 mm ²	57	450	3	30	53	23	13	19	2.5-16.0	M4

MAKING THE RIGHT CONNECTIONS

T: +44 (0)1933 234400 ■ F: +44 (0)1933 234411
 E: sales@hylec-apl.com ■ W: www.hylec-apl.com