

Linemaster Switch Corporation

29 Plaine Hill Road POB 238

Woodstock, CT 06281-0238 USA

Toll Free: (800) 974-3668 (US Only) Telephone: (860) 974-1000 Fax: (860) 974-0691

E-Mail: service_266@linemaster.com Web site: www.linemaster.com

Item # 476-S, Duplex Foot Switch



Duplex Foot Switch

Mechanical Interlock-prevents both circuits from being operated at the same time. The operating principle is the same as that described for the Lektro-Lok switch. The cast aluminum housing is pivoted in the center for easy heel-toe operation. Black finish with nonskid base pads and an adjustable strain relief connector that accommodates a wide range of cable sizes.

SPECIFICATIONS

Description	Momentary
Circuit	Each Side SPDT
Form	C
Electrical Rating	15 A 125-250 VAC 1/2 H.P. 125-250 VAC
Standard	EN 60529 Degree of Protection IP20
Size	8 1/2 x 3 1/2 x 2 Inch
Weight Approx.	1 3/4 lbs
