



Material Safety Data Sheet

1 - Chemical Product and Company Identification

| | |
|--|--|
| Manufacturer: WD-40 Company Address: 1061 Cudahy Place (92110) P.O. Box 80607 San Diego, California, USA 92138 -0607 Telephone: Emergency only: 1-888-324-7596 (PROSAR) Information: 1-888-324-7596 Chemical Spills: 1-800-424-9300 (Chemtrec) 1-703-527-3887 (International Calls) | Chemical Name: Organic Mixture Trade Name: WD-40 Aerosol Product Use: Lubricant, Penetrant, Drives Out Moisture, Removes and Protects Surfaces From Corrosion MSDS Date Of Preparation: 3/11/10 |
|--|--|

2 – Hazards Identification

| |
|--|
| Emergency Overview: DANGER! Flammable aerosol. Contents under pressure. Harmful or fatal if swallowed. If swallowed, may be aspirated and cause lung damage. May cause eye irritation. Avoid eye contact. Use with adequate ventilation. Keep away from heat, sparks and all other sources of ignition. Symptoms of Overexposure: Inhalation: High concentrations may cause nasal and respiratory irritation and central nervous system effects such as headache, dizziness and nausea. Intentional abuse may be harmful or fatal. Skin Contact: Prolonged and/or repeated contact may produce mild irritation and defatting with possible dermatitis. Eye Contact: Contact may be irritating to eyes. May cause redness and tearing. Ingestion: This product has low oral toxicity. Swallowing may cause gastrointestinal irritation, nausea, vomiting and diarrhea. This product is an aspiration hazard. If swallowed, can enter the lungs and may cause chemical pneumonitis, severe lung damage and death. Chronic Effects: None expected. Medical Conditions Aggravated by Exposure: Preexisting eye, skin and respiratory conditions may be aggravated by exposure. Suspected Cancer Agent: Yes No <input checked="" type="checkbox"/> |
|--|

3 - Composition/Information on Ingredients

| Ingredient | CAS # | Weight Percent |
|---------------------------|--|----------------|
| Aliphatic Hydrocarbon | 64742-47-8 | 45-50 |
| Petroleum Base Oil | 64742-58-1 64742-53-6 64742-56-9 64742-65-0 | <25 |
| LVP Aliphatic Hydrocarbon | 64742-47-8 | 12-18 |
| Carbon Dioxide | 124-38-9 | 2-3 |
| Surfactant | Proprietary | <2 |
| Non-Hazardous Ingredients | Mixture | <10 |

4 – First Aid Measures

| |
|--|
| Ingestion (Swallowed): Aspiration Hazard. DO NOT induce vomiting. Call physician, poison control center or the WD-40 Safety Hotline at 1-888-324-7596 immediately. Eye Contact: Flush thoroughly with water. Remove contact lenses if present after the first 5 minutes and continue flushing for several more minutes. Get medical attention if irritation persists. |
|--|

Skin Contact: Wash with soap and water. If irritation develops and persists, get medical attention.
Inhalation (Breathing): If irritation is experienced, move to fresh air. Get medical attention if irritation or other symptoms develop and persist.

5 – Fire Fighting Measures

Extinguishing Media: Use water fog, dry chemical, carbon dioxide or foam. Do not use water jet or flooding amounts of water. Burning product will float on the surface and spread fire.
Special Fire Fighting Procedures: Firefighters should always wear positive pressure self-contained breathing apparatus and full protective clothing. Cool fire-exposed containers with water. Use shielding to protect against bursting containers.
Unusual Fire and Explosion Hazards: Contents under pressure. Keep away from ignition sources and open flames. Exposure of containers to extreme heat and flames can cause them to rupture often with violent force. Vapors are heavier than air and may travel along surfaces to remote ignition sources and flash back.

6 – Accidental Release Measures

Wear appropriate protective clothing (see Section 8). Eliminate all sources of ignition and ventilate area. Leaking cans should be placed in a plastic bag or open pail until the pressure has dissipated. Contain and collect liquid with an inert absorbent and place in a container for disposal. Clean spill area thoroughly. Report spills to authorities as required.

7 – Handling and Storage

Handling: Avoid contact with eyes. Avoid prolonged contact with skin. Avoid breathing vapors or aerosols. Use only with adequate ventilation. Keep away from heat, sparks, pilot lights, hot surfaces and open flames. Unplug electrical tools, motors and appliances before spraying or bringing the can near any source of electricity. Electricity can burn a hole in the can and cause contents to burst into flames. To avoid serious burn injury, do not let the can touch battery terminals, electrical connections on motors or appliances or any other source of electricity. Wash thoroughly with soap and water after handling. Keep containers closed when not in use. Keep out of the reach of children. Do not puncture, crush or incinerate containers, even when empty.
Storage: Store in a cool, well-ventilated area, away from incompatible materials Do not store above 120°F or in direct sunlight. U.F.C (NFPA 30B) Level 3 Aerosol.

8 – Exposure Controls/Personal Protection

| Chemical | Occupational Exposure Limits |
|---------------------------|--|
| Aliphatic Hydrocarbon | 1200 mg/m3 TWA (manufacturer recommended) |
| Petroleum Base Oil | 5 mg/m3 TWA, 10 mg/m3 STEL ACGIH TLV 5 mg/m3 TWA OSHA PEL |
| LVP Aliphatic Hydrocarbon | 1200 mg/m3 TWA (manufacturer recommended) |
| Carbon Dioxide | 5000 ppm TWA (OSHA/ACGIH), 30,000 ppm STEL (ACGIH) |
| Surfactant | None Established |
| Non-Hazardous Ingredients | None Established |

The Following Controls are Recommended for Normal Consumer Use of this Product

Engineering Controls: Use in a well-ventilated area.
Personal Protection:
Eye Protection: Avoid eye contact. Always spray away from your face.
Skin Protection: Avoid prolonged skin contact. Chemical resistant gloves recommended for operations where skin contact is likely.
Respiratory Protection: None needed for normal use with adequate ventilation.

For Bulk Processing or Workplace Use the Following Controls are Recommended

Engineering Controls: Use adequate general and local exhaust ventilation to maintain exposure levels below that occupational exposure limits.

Personal Protection:**Eye Protection:** Safety goggles recommended where eye contact is possible.**Skin Protection:** Wear chemical resistant gloves.**Respiratory Protection:** None required if ventilation is adequate. If the occupational exposure limits are exceeded, wear a NIOSH approved respirator. Respirator selection and use should be based on contaminant type, form and concentration. Follow OSHA 1910.134, ANSI Z88.2 and good Industrial Hygiene practice.**Work/Hygiene Practices:** Wash with soap and water after handling.**9 – Physical and Chemical Properties**

| | | | |
|--|---|-------------------------------------|------------------------------|
| Boiling Point: | 361 - 369°F (183 - 187°C) | Specific Gravity: | 0.8 – 0.82 @ 60°F |
| Solubility in Water: | Insoluble | pH: | Not Applicable |
| Vapor Pressure: | 95-115 PSI @ 70°F | Vapor Density: | Greater than 1 |
| Percent Volatile: | 70-75% | VOC: | 412 grams/liter (49.5%) |
| Coefficient of Water/Oil Distribution: | Not Determined | Appearance/Odor | Light amber liquid/mild odor |
| Flash Point: | 122°F (49°C) Tag Open Cup (concentrate) | Flammable Limits: (Solvent Portion) | LEL: 0.6% UEL: 8.0% |
| Pour Point: | -63°C (-81.4°F) ASTM D-97 | Kinematic Viscosity: | 2.79-2.96cSt @ 100°F |

10 – Stability and Reactivity**Stability:** Stable**Hazardous Polymerization:** Will not occur.**Conditions to Avoid:** Avoid heat, sparks, flames and other sources of ignition. Do not puncture or incinerate containers.**Incompatibilities:** Strong oxidizing agents.**Hazardous Decomposition Products:** Carbon monoxide and carbon dioxide.**11 – Toxicological Information**

The oral toxicity of this product is estimated to be greater than 5,000 mg/kg based on an assessment of the ingredients. This product is not classified as toxic by established criteria. It is an aspiration hazard. None of the components of this product is listed as a carcinogen or suspected carcinogen or is considered a reproductive hazard.

12 – Ecological Information

No data is currently available.

13 - Disposal Considerations

If this product becomes a waste, it would be expected to meet the criteria of a RCRA ignitable hazardous waste (D001). However, it is the responsibility of the generator to determine at the time of disposal the proper classification and method of disposal. Dispose in accordance with federal, state, and local regulations.

14 – Transportation Information

DOT Surface Shipping Description: Consumer Commodity, ORM-D

IMDG Shipping Description: Un1950, Aerosols, 2.1, LTD QTY

15 – Regulatory Information**U.S. Federal Regulations:**

CERCLA 103 Reportable Quantity: This product is not subject to CERCLA reporting requirements, however, oil spills are reportable to the National Response Center under the Clean Water Act and many states have more stringent release reporting requirements. Report spills required under federal, state and local regulations.

SARA TITLE III:

Hazard Category For Section 311/312: Acute Health, Fire Hazard, Sudden Release of Pressure

Section 313 Toxic Chemicals: This product contains the following chemicals subject to SARA Title III Section 313 Reporting requirements: None

Section 302 Extremely Hazardous Substances (TPQ): None

EPA Toxic Substances Control Act (TSCA) Status: All of the components of this product are listed on the TSCA inventory.

California Safe Drinking Water and Toxic Enforcement Act (Proposition 65): This product does not contain chemicals regulated under California Proposition 65.

VOC Regulations: This product complies with the consumer product VOC limits of CARB, the US EPA and states adopting the OTC VOC rules.

Canadian Environmental Protection Act: One of the components is listed on the NDSL. All of the other ingredients are listed on the Canadian Domestic Substances List or exempt from notification.

Canadian WHMIS Classification: Class B-5 (Flammable Aerosol)

This MSDS has been prepared according to the criteria of the Controlled Products Regulation (CPR) and the MSDS contains all of the information required by the CPR.

16 – Other Information:

HMIS Hazard Rating:

Health – 1 (slight hazard), Fire Hazard – 4 (severe hazard), Reactivity – 0 (minimal hazard)

SIGNATURE:  _____

TITLE: Director of Global Quality Assurance

REVISION DATE: March 2010

SUPERSEDES: August 2009