



## Benefits

- Pre-cut for rapid removal from backing sheet
- Print using ordinary standard office laser and the pro-power software\*
- For colour font / background use colour laser printer\*
- For Resistor colour-coded idents use colour laser printer\*



## Description

The wrap-around, self-laminating labels can be printed through a standard laser printer. They have been tested for high and low temperatures. These labels offer a specially extended print area, so when applied, the white printable area extends all around the cable rather than being limited to a single narrow strip. Using the special functionality included with the pro-Power Advanced software\*, it is possible to repeat the ident information all round the cable. The ident can therefore be seen/read from all sides of the cable. It is also possible to print colour background / font and even resistor colour coded labels (colour laser required)\*


\* There are 2 levels of the pro-Power software; Free Standard level (limited functionality) Advanced level (extra functionality). The free Standard level is downloadable from <http://www.silverfox.co.uk/pro-power>. Bundled with the Standard at download is the Advanced level for 6 days of trial (free of charge). TIP: If you only need a few labels, prior to printing, use variable start position option on the Advanced software and print the labels at the bottom of the sheet to keep the leading edge of the sheet intact for future runs. The Advanced level is extra cost after initial trial. The Standard level is free

Recommended printing via straight printer path

## Technical Data

Material	50 micron self-adhesive polyester
Tested Range	-40°C to 85°C (-40°F to 185°F)
Printer Type	Laser printers only

## Sample of Order Code P06/2518LW



Drawing not to scale      Dimensions : Millimetres

## Part Number Table

Cable OD Ø (mm)	Printable (mm)	Sheet Size	Labels per	Sheets Per	Colour	Part Number
4	25 × 10	A4	80	10	White	P04/2510LW
6	12 × 18		90			P06/1218LW
	25 × 18		48			P06/2518LW
	50 × 18		24			P06/5018LW
10	25 × 30		32			P10/2530LW

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.