

Productname : Tuner 600
Ref.Nr.: BDS000269_3_20121018

Creationdate : 18.10.12 Version : 1.1
Replaces: BDS000269_20110908

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Tuner 600
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Cleaners - Precision

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe bvba
Touwslagerstraat 1
9240 Zele
Belgium
Tel.: +32(0)52/45.60.11
Fax.: +32(0)52/45.00.34
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Asemanrinne 13, 08500 Lohja	+358/(19)32.921	+358/(19)383.676
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303.0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Kryptogatan 14, 431 53 Mölndal	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to 67/548/EEC or 1999/45/EC:

Health:

R38: Irritating to skin.
R67: Vapours may cause drowsiness and dizziness.



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

1 / 10




Safety Data Sheet

Regulation EC No 1907/2006 Art.31

Productname : Tuner 600
Ref.Nr.: BDS000269_3_20121018
Creationdate : 18.10.12 Version : 1.1
Replaces: BDS000269_20110908

Physical: EXTREMELY FLAMMABLE
Environment: R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

2.2. Label elements

Warning symbol(s) : EXTREMELY FLAMMABLE

Xi : IRRITANT

N : DANGEROUS FOR THE ENVIRONMENT


Risk-phrase(s) : R38: Irritating to skin.
R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67: Vapours may cause drowsiness and dizziness.

Safety-phrase(s) : S2: Keep out of the reach of children.
S16: Keep away from sources of ignition - No smoking.
S23: Do not breathe vapours/spray.
S35: This material and its container must be disposed of in a safe way.
S51: Use only in well-ventilated areas.

Extra label elements according to Aerosol Dispenser Directive 75/324/EC: Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material.
Without adequate ventilation formation of explosive mixtures may be possible.

Other extra label elements: Remark: Preparations classified as harmful on the basis of an aspiration hazard need not be labelled as harmful with R65 when placed on the market in aerosol containers or in containers fitted with a sealed spray attachment. (EU-Directive 67/548 Annex VI 9.4)

Regulation (EC) No 648/2004 on detergents: aliphatic hydrocarbons > 30 %

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

2 / 10

Productname : Tuner 600
Ref.Nr.: BDS000269_3_20121018

Creationdate : 18.10.12 Version : 1.1
Replaces: BDS000269_20110908

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
pentane	109-66-0	203-692-4	25-50	F+,Xn,N	12-51/53-65-66-67	A
Naphtha (petroleum), hydrotreated light	64742-49-0	931-254-9	25-50	F,Xn,N	11-38-51/53-65-67	B,P
carbon dioxide	124-38-9	204-696-9	5-10	-	-	A,G

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

P : not classified as carcinogen, less than 0.1% w/w benzene (Einecs-nr. 200-753-7)

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
pentane	01-2119459286-30	109-66-0	203-692-4	25-50	Flam. Liq. 2, Asp. Tox. 1, STOT SE 3, Aquatic Chronic 2	H225,H304,H336,H411	A
Naphtha (petroleum), hydrotreated light	01-2119484651-34	64742-49-0	931-254-9	25-50	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H225,H315,H336,H304,H411	B,P
carbon dioxide		124-38-9	204-696-9	5-10	Press. Gas	H280	A,G

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006

P : not classified as carcinogen, less than 0.1% w/w benzene (Einecs-nr. 200-753-7)

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water Seek medical advice
Contact with skin :	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical advice
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
Ingestion :	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

3 / 10

Productname : Tuner 600
Ref.Nr.: BDS000269_3_20121018

Creationdate : 18.10.12 Version : 1.1
Replaces: BDS000269_20110908

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	Irritating to skin Symptoms : redness and pain
Eye contact :	May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice : If you feel unwell, seek medical advice (show the label where possible)
If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

6.3. Methods and material for containment and cleaning up



Productname : Tuner 600
Ref.Nr.: BDS000269_3_20121018

Creationdate : 18.10.12 Version : 1.1
Replaces: BDS000269_20110908

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
 Take precautionary measures against static discharges
 Equipment should be earthed
 Use explosion-proof electrical/ventilating/lighting/.../equipment.
 Use only non-sparking tools.
 Do not breathe aerosols or vapours.
 Ensure adequate ventilation
 Avoid contact with skin and eyes.
 Wash thoroughly after use
 Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
 Keep out of reach of children.

7.3. Specific end use(s)

Cleaners - Precision

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
pentane	109-66-0	TWA	1000 ppm
carbon dioxide	124-38-9	TWA	5000 ppm
National established exposure limits, United Kingdom			
pentane	109-66-0	TWA	600 ppm
carbon dioxide	124-38-9	TWA	5000 ppm
		STEL	15000 ppm

Productname : Tuner 600	Creationdate : 18.10.12	Version : 1.1
Ref.Nr.: BDS000269_3_20121018	Replaces: BDS000269_20110908	

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment. Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX)
hands and skin :	Wear suitable protective gloves against chemicals (nitrile)
eyes :	Wear safety goggles.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state :	Liquid under pressure.
colour :	Colorless.
odour :	Solvent.
pH :	Not applicable.
Boiling point/range :	40-65 °C
Flash point :	< 0 °C (Closed Cup)
Evaporation rate :	1 (Ether=1)
Explosion limits : upper limit :	7.8 %
lower limit :	1.1 %
Vapour pressure :	38 kPa (at 20 °C)
Relative density :	0.645 g/cm ³ (@ 20°C).
Solubility in water :	Insoluble in water
Auto-ignition :	>200 °C

9.2. Other information

VOC: 635 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability



Productname : Tuner 600
Ref.Nr.: BDS000269_3_20121018

Creationdate : 18.10.12 Version : 1.1
Replaces: BDS000269_20110908

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion : After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact : Irritating to skin
Eye contact : May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
pentane	109-66-0	LD50 oral rat	> 5000 mg/kg
		LD50 derm.rabit	> 3000 mg/kg
Naphtha (petroleum), hydrotreated light	64742-49-0	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 3000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.



Safety Data Sheet

Regulation EC No 1907/2006 Art.31

Productname : Tuner 600
Ref.Nr.: BDS000269_3_20121018

Creationdate : 18.10.12 Version : 1.1
Replaces: BDS000269_20110908

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
Naphtha (petroleum), hydrotreated light	64742-49-0	IC50 algae	55 mg/l
		LC50 fish	> 1 mg/l
		EC50 daphnia	3.87 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.
Contaminated packaging : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS (naphta, pentane)



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium
Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

8 / 10

Productname : Tuner 600	Creationdate : 18.10.12	Version : 1.1
Ref.Nr.: BDS000269_3_20121018	Replaces: BDS000269_20110908	

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: Yes
IMDG - Marine pollutant: Marine pollutant
IATA/ICAO - Environmentally hazardous: Yes

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

The Safety Data Sheet is compiled according to the current European requirements.
Dir. 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.
EU-directive 99/45/EC
Regulation (EC) No 1907/2006 (REACH)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases: R11: Highly flammable.



Safety Data Sheet

Regulation EC No 1907/2006 Art.31

Productname : Tuner 600	Creationdate : 18.10.12	Version : 1.1
Ref.Nr.: BDS000269_3_20121018	Replaces: BDS000269_20110908	

R12: Extremely flammable.
R38: Irritating to skin.
R65: Harmful: may cause lung damage if swallowed.
R66: Repeated exposure may cause skin dryness or cracking.
R67: Vapours may cause drowsiness and dizziness.
R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

*Explanation hazard statements: H225 : Highly flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H304 : May be fatal if swallowed and enters airways.
H315 : Causes skin irritation.
H336 : May cause drowsiness or dizziness.
H411 : Toxic to aquatic life with long lasting effects.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.



CRC Industries Europe bvba

Touwslagerstraat 1, 9240 Zele – Belgium

Tel (+32) (0) 52 / 45 60 11 – Fax (+32) (0) 52 / 45 00 34 – www.crcind.com

10 / 10