

#### The SSU-PAM-1 Relav

provides 10.0 Amp Form C contacts. The relay may be energized by one of three (3) input voltages: 24VDC, 24VAC, or 120VAC. The DC input voltages are polarity sensitive and diode protected. A red LED is provided which, when illuminated, indicates the relay coil is energized. SAE PN# SSU-PAM-1



The SSU-PAM-2 Relay provides 7.0 Amp Form C contacts. The relay may be energized by one of two (2) input voltages: 12VDC or 24VDC. The input voltages are polarity sensitive and diode protected. A red LED is provided which, when illuminated, indicates the relay coil is energized.

SAE PN# SSU-PAM-2



The **SSU-PAM-SD** Relay provides 7.0 Amp Form C contacts. The relay may be energized by an input voltage between 18VDC to 32VDC, making it ideal for

1/2

24VDC NAC circuits. The input voltages are polarity sensitive and diode protected. The PAM-SD provides an additional set of wires for redundant input voltage (Class "A" circuit supervision pass through).

- Uses UL Recognized Components

SAE PN# SSU-PAM-SD







# Multi-Voltage Relay Modules

The PAM Series Relays are encapsulated multi-voltage devices with "flying" leads that offer versatile, reliable performance in a convenient package. Several of the versions provide a red LED which, when illuminated, indicates coil energization. The PAM Series Relays are packaged with a self-tapping screw and a piece of double sided tape for easy installation almost anywhere. The relays are also packaged with wire-nuts to aid installation.

PAM

PAM Relays are ideal for applications where remote relays are required for control or status feedback. They are suitable for use with HVAC, temperature control, fire alarm, security, energy management, lighting control systems and building automation systems.



The SSU-PAM-4 Relay provides 10.0 Amp Form C contacts. The relay may be energized across a wide voltage range

from 9VDC to 40VDC. The 15mA operating current is constant across the operating range. The input DC voltages are polarity sensitive and diode protected.

SAE PN# SSU-PAM-4



**ISO 9001** 

REGISTERED

COMPANY




Space Age Electronics, inc. www.1SAE.com 800.486.1723 Toll Free 508.485.0966 Local 508.485.4740 Fax


This document is subject to change without notice, see doc # ED0479 for legal disclaimer

ED0312 LT10277 Rev.D No Excuses, Just Solutions!





## Wiring:





PAM-1





### **PRODUCT SPECIFICATIONS**

MODEL NUMBER:		PAM-1	PAM-2	PAM-4	PAM-SD
COIL VOLTAGE:		24VAC/24VDC/120VAC	12VDC/24VDC	9 to 40VDC	20 to 32VDC
POLARIZED:		Y es	Yes	Yes	Yes
ENERGIZED LED INDICATOR:		: Yes	Yes	No N	0
CURRENT REQUIREMENT:					
@	12VDC		15mA	15mA	
	@24VDC	15mA	15mA	15mA	15mA
	@24VAC	50mA			
	@120VAC	30mA			
CONTACT CON	FIGURATION:	(1) SPDT dry form "C"	(1) SPDT dry form "C"	(1) SPDT dry form "C"	(1) SPDT dry form "C"
CONTACT RATINGS:					
(contact rating/ power factor)					
	@5VDC	250μA / .35 PF	250µA / .35 PF	250µA	250μA / .35 PF
	@24VDC	7A / .35 PF 7	A / .35 PF 7	Α	7A / .35 PF
	@120VAC	1 0A 7	A / .35 PF 1	0A 7	A / .35 PF
WIRE LEADS:		6 "flying" leads	6 "flying" leads	5 "flying" leads	7 "flying" leads
		12" / 18 AWG	12" / 18 AWG	12" / 18 AWG	12" / 18 AWG
		Wire-nuts provided W	ire-nuts provided W	ire-nuts provided W	ire-nuts provided
AMBIENT TEMPERATURE:		32°F to 120°F	32°F to 120°F	32°F to 120°F	32°F to 120°F
(@ 100% RH, condensing)		(0°C to 49°C) (	0°C to 49°C) (	0°C to 49°C) (	0°C to 49°C)
CONSTRUCTION: s		100% potted (sealed) with "flying" lead			
MOUNTING:		Pre-drilled mounting screw hole and self tapping screw provided. Double sided tape provided.			
DIMENSIONS:					
	Н	1 .50" (38mm) 1	.50" (38mm) 1	.50" (38mm) 1	.50" (38mm)
	W	1.20" (25mm) 1	.00" (25mm) 1	.00" (25mm) 1	.00" (25mm)
	D	0 .90" (20mm) 0	.90" (23mm) 0	.90" (23mm) 0	.80" (20mm)
LISTINGS AND APPROVALS:					
	UL*:	U0XX/7.S3403 U	0XX/7.S3403 U	0XX/7.S3403 U	0XX/7.S3403
	MEA:	73-92-E Vol. 21	73-92-E Vol. 21	73-92-E Vol. 21	73-92-E Vol. 21
	CSFM:	7300-1004:101	7300-1004:101	7300-1004:101	7300-1004:101

<sup>\*</sup>UOXX=Control Unit Accessories, System; /7=also Certified for Canada



Space Age Electronics, inc. www.1SAE.com **800.486.1723** Toll Free 508.485.0966 Local 508.485.4740 Fax