



LS 33600

3.6 V Primary lithium - thionyl chloride (Li-SOCl₂) High Drain D-size cell

For applications with continuous currents up to 250 mA, possibly combined with pulsing and exposure to extreme temperatures.

Key features

- High and stable operating voltage
- Superior drain capability
- Low self discharge rate
(less than 1% after 1 year of storage at +20°C)
- Stainless steel container
- Hermetic glass-to-metal sealing
- Built-in safety vent
- Finish with or without flat positive end
- Non flammable electrolyte
- Compliant with IEC 86-4 safety standard
- Underwriters Laboratories (UL) Component Recognition (File Number MH 12609)
- Non restricted for transport

Main applications

- Utility metering
- Automatic meter readers
- Buoys
- Measuring equipment
- Industrial applications
- Professional electronics
- ... etc.

Optional upon request

- Low magnetism version

Cell size reference

R20 - D


Electrical characteristics

(typical values for cells stored for one year or less)


Nominal capacity	16.5 Ah
<i>(at 5 mA +20°C 2.0 V cut off. The capacity restored by the cell varies according to current drain, temperature and cut off).</i>	
Open circuit voltage (at +20°C)	3.67 V
Nominal voltage (at 0.7 mA +20°C)	3.6 V
Maximum recommended continuous current	250 mA
<i>(to get 50% of the nominal capacity at +20°C with 2 V cut off. Higher currents possible, consult Saft).</i>	
Pulse capability : varies according to pulse characteristics (frequency, duration), temperature, cell history (storage conditions prior to usage) and the application's acceptable minimum voltage. Consult Saft.	
Storage (recommended)	+30°C max
(possible without leakage)	-60/+100°C
Operating temperature range	-60/+85°C
<i>(Operation above ambient T may lead to reduced capacity and lower voltage readings at the beginning of pulses).</i>	
Physical characteristics	
Diameter (max)	33.3 mm (1.31")
Height (max)	60.2 or 61.6mm (2.37 or 2.42") depending on finish type
Typical weight	90 g
Available termination suffix	CN, CNR, (STS) CNA (AX) FL
	radial tabs axial leads flying leads ... etc.




Voltage plateau versus Current and Temperature (at mid-discharge)



Discharge profiles at +20°C




Capacity versus Current and Temperature (2.0 V cut off)




LS 33600

dimensions in mm



Finished version with protruding positive end cap



Finished version with flat positive end cap



12, rue Sadi Carnot
 93170 Bagnolet - France
 Tel +33 (0)1 49 93 17 70
 Fax +33 (0)1 49 93 19 69
 Internet: <http://www.saftbatteries.com>
 Doc. N° 12.00 - 31007.2
 Published by the Communications Department

Information in this document is subject to change without notice and becomes contractual only after written confirmation by Saft.