

Male headers soldering technique

□ 0.5 mm, angled

	<p style="text-align: center;">S = 3,5 mm</p>		
<p>art. no.</p>	<p style="text-align: center;">dim. [mm]</p>		
<p>SLY 3 035 ...</p>	<p style="text-align: center;">A</p>	<p style="text-align: center;">B</p>	<p style="text-align: center;">C</p>
<p>SLY 3 041 ...</p>	<p style="text-align: center;">1.50</p>	<p style="text-align: center;">2.80</p>	<p style="text-align: center;">3.50</p>
<p>SLY 3 082 ...</p>	<p style="text-align: center;">1.50</p>	<p style="text-align: center;">2.80</p>	<p style="text-align: center;">4.10</p>
<p>SLY 3 082 ...</p>	<p style="text-align: center;">1.50</p>	<p style="text-align: center;">2.80</p>	<p style="text-align: center;">8.20</p>
<p>please indicate:</p>	<p>... no. of contacts one row 1 - 50</p>		<p>... surface S = selective gold-plated G = gold-plated Z = tin-plated</p>
	<p style="text-align: center;">S = 3,5 mm</p>		
<p>art. no.</p>	<p style="text-align: center;">dim. [mm]</p>		
<p>SLY 4 035...</p>	<p style="text-align: center;">A</p>	<p style="text-align: center;">B</p>	<p style="text-align: center;">C</p>
<p>SLY 4 041...</p>	<p style="text-align: center;">1.50</p>	<p style="text-align: center;">2.80</p>	<p style="text-align: center;">3.50</p>
<p>SLY 4 041...</p>	<p style="text-align: center;">1.50</p>	<p style="text-align: center;">2.80</p>	<p style="text-align: center;">4.10</p>
<p>SLY 4 082...</p>	<p style="text-align: center;">1.50</p>	<p style="text-align: center;">2.80</p>	<p style="text-align: center;">8.20</p>
<p>please indicate:</p>	<p>... no. of contacts two rows 4 - 100</p>		<p>... surface S = selective gold-plated G = gold-plated Z = tin-plated</p>

Therefore any required number of contacts is available.