




Dual Common-Cathode Schottky Rectifier



TO-247AD (TO-3P)



| MAJOR RATINGS AND CHARACTERISTICS | |
|-----------------------------------|----------------|
| $I_{F(AV)}$ | 40 A |
| V_{RRM} | 35 V to 60 V |
| I_{FSM} | 400 A |
| V_F | 0.60 V, 0.62 V |
| $T_j \text{ max.}$ | 150 °C |

FEATURES

- Guardring for overvoltage protection
- Lower power losses, high efficiency
- Low forward voltage drop
- High forward surge capability
- High frequency operation
- Solder Dip 260 °C, 40 seconds
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC



TYPICAL APPLICATIONS

For use in low voltage, high frequency rectifier of switching mode power supplies, free-wheeling diodes, dc-to-dc converters or polarity protection application.

MECHANICAL DATA

Case: TO-247AD (TO-3P)

Epoxy meets UL 94V-0 flammability rating

Terminals: Matte tin plated (E3 Suffix) leads, solderable per J-STD-002B and JESD22-B102D

Polarity: As marked

Mounting Torque: 10 in-lbs maximum

| MAXIMUM RATINGS ($T_A = 25\text{ °C}$ unless otherwise noted) | | | | | | |
|---|-------------|---------------|-----------|-----------|-----------|------------|
| PARAMETER | SYMBOL | MBR4035PT | MBR4045PT | MBR4050PT | MBR4060PT | UNIT |
| Maximum repetitive peak reverse voltage | V_{RRM} | 35 | 45 | 50 | 60 | V |
| Maximum working peak reverse voltage | V_{RWM} | 35 | 45 | 50 | 60 | V |
| Maximum DC blocking voltage | V_{DC} | 35 | 45 | 50 | 60 | V |
| Maximum average forward rectified current at $T_C = 125\text{ °C}$ | $I_{F(AV)}$ | 40 | | | | A |
| Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load per diode | I_{FSM} | 400 | | | | A |
| Peak repetitive reverse surge current per diode ⁽¹⁾ | I_{RRM} | 2.0 | | 1.0 | | A |
| Voltage rate of change at (rated V_R) | dv/dt | 10000 | | | | V/ μ s |
| Operating junction temperature range | T_J | - 65 to + 150 | | | | °C |
| Storage temperature range | T_{STG} | - 65 to + 175 | | | | °C |

Note:

(1) 2.0 μ s pulse width, $f = 1.0$ kHz

| ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted) | | | | | | | |
|---|---|----------------|------------|-----------|-----------|-----------|------|
| PARAMETER | TEST CONDITIONS | SYMBOL | MBR4035PT | MBR4045PT | MBR4050PT | MBR4060PT | UNIT |
| Maximum instantaneous forward voltage per diode ⁽¹⁾ | I _F = 20 A, T _C = 25 °C | V _F | 0.70 | | 0.72 | | V |
| | I _F = 20 A, T _C = 125 °C | | 0.60 | | 0.62 | | |
| | I _F = 40 A, T _C = 25 °C | | 0.80 | | - | | |
| | I _F = 40 A, T _C = 125 °C | | 0.75 | | - | | |
| Maximum instantaneous reverse current at rated DC blocking voltage per diode ⁽¹⁾ | T _C = 25 °C T _C = 125 °C | I _R | 1.0 100 | | | mA | |

Note:

(1) Pulse test: 300 μs pulse width, 1 % duty cycle

| THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted) | | | | | | |
|---|------------------|-----------|-----------|-----------|-----------|------|
| PARAMETER | SYMBOL | MBR4035PT | MBR4045PT | MBR4050PT | MBR4060PT | UNIT |
| Maximum thermal resistance from junction to case per diode | R _{θJC} | 1.2 | | | | °C/W |

| ORDERING INFORMATION | | | | | |
|----------------------|-----------------|-----------------|--------------|---------------|---------------|
| PACKAGE | PREFERRED P/N | UNIT WEIGHT (g) | PACKAGE CODE | BASE QUANTITY | DELIVERY MODE |
| TO-247AD | MBR4045PT-E3/45 | 6.13 | 45 | 30/Tube | Tube |

RATINGS AND CHARACTERISTICS CURVES

(T_A = 25 °C unless otherwise noted)




Figure 1. Forward Current Derating Curve




Figure 2. Maximum Non-Repetitive Peak Forward Surge Current Per Diode




Figure 3. Typical Instantaneous Forward Characteristics Per Diode




Figure 5. Typical Junction Capacitance Per Diode




Figure 4. Typical Reverse Characteristics Per Diode





Figure 6. Typical Transient Thermal Impedance Per Diode

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

TO-247AD (TO-3P)





Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.