



General Information

Kit Part Number:	2-2110838-8
Description:	Pre-Insulated Short Spring Spade Tongue Terminals Kit
Application:	HVAC Systems, Instrumentation and Controls, Lighting Applications, Motors, Panel Boxes, Power Supplies, Switchgear, Transportation
Family:	PLASTI-GRIP
TE Brand:	AMP Products
Solution:	MRO (Maintenance, Repair and Operation)
Product Type:	Terminals & Splices
Number of Pieces:	120
RoHS:	Yes

Specifications

Body and Plating:	Tin Plated, Phosphor Bronze and Brass
Insulation:	Vinyl
Stud/Tab Size:	4, 6, 8, 10
Temperature Rating:	90 Degrees C (Max)
Terminal Type:	Short Spring Spade Tongue
Tool Included:	No
Voltage Rating:	600V
Wire Gauge (AWG):	12-10, 16-14 , 22-16

Product Highlights

Product Highlights

Pre-insulated PLASTI-GRIP solderless terminals and splices are designed specifically to answer the need for inexpensive, insulated electrical terminations. They can be used in almost every type of commercial application and accommodate wire sizes from 22 AWG through 2/0 AWG. Carefully engineered application tooling has been developed to ensure uniformly high quality terminations. Tool and terminal have been designed as a team to promote ease and speed of application and at the same time to provide precise crimping pressure for every wire size. The wire and the terminal barrel form a homogeneous mass of metal, providing a connection of maximum conductivity, tensile strength, and high resistance to corrosion. The quality performance, the facility of installation and the inherent simplicity make them ideal for many industrial applications. PLASTI-GRIP products are available as rings, spades, flanged spaded, slotted rings, splices and several other varieties. Wire ranges for the terminals and splices are 22 AWG through 2/0 and stud sizes from #2 through 3/8".

Features and Benefits

- Vinyl insulation sleeve provides good dielectric strength and supports the wire insulation so that no bare wire is exposed
- Most product rated to 90 degrees C, with an operating voltage of 600 V
- Insulation is 94V-0 rated
- Funneled wire entry on terminal prevents turned back wire strands and permits rapid wire insertion during high speed production
- Serrations in the crimp barrel provide maximum contact and tensile strength after crimping

Applications

- HVAC
- Instruments / Controls
- Lighting
- Switchgear



- Power Supplies
- Panel Boxes
- Transportation
- Motors



Bill of Materials

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
53247-1	10	Short Spring Spade AWG 12-10, Stud 8		Details	Search
52950	10	Short Spring Spade AWG 22-16, Stud 8		Details	Search
53246-1	10	Short Spring Spade AWG 12-10, Stud 6		Details	Search
52947	10	Short Spring Spade AWG 22-16, Stud 4		Details	Search
53242-1	10	Short Spring Spade AWG 22-16, Stud 10		Details	Search
52949	10	Short Spring Spade AWG 22-16, Stud 6		Details	Search
53248-1	10	Short Spring Spade AWG 12-10, Stud 10		Details	Search
52963-4	10	Short Spring Spade AWG 12-10 Stud 10		Details	Search
52957-1	10	Short Spring Spade AWG 16-14, Stud 10		Details	Search
52955	10	Short Spring Spade AWG 16-14, Stud 6		Details	Search
53244-1	20	Short Spring Spade AWG 16-14, Stud 8		Details	Search

Recommended Tool

Part No.

Included in Kit





