




Compliant

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


REVISIONS			DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1876	Α	RELEASED	EO	07/25/06	SA	07/25/06	но	07/25/06







PANEL CUTOUT



## 12.6±0.25 [0.496±0.010] 3.00 [0.118]

DRAWING TITLE

## SPECIFICATIONS:

Shell: Steel, Zinc Yellow- Chromated Insulator: PBT+30% Fiber-Glass UL 94V-0,

Blue Color

Contact: Brass, Stamped, Gold-Plated on

Contact Area Tin-Plated on

Solder Cup

Current Rating: 5 Amps

Contact Resistance: 15 miliohms Max. Insulator Resistance: 1000 Megohms Min.

Voltage: 500 VAC for 1 Minute Temperature: -50°C to +100°C

## DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT

FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

Unless Otherwise Specified							
	Spe	сттеа					
.X	±0.35	5 [0.014]					
.xx	±0.1	5 [0.006]					

TOLERANCES:

DRAWN BY:	DATE:
EKLAS ODISH	07/25/0
CHECKED BY:	DATE:
SAMI ALNADI	07/25/06
APPROVED BY:	DATE:
HISHAM ODISH	07/25/06

		Pin	D-Sub	Solder	Plug,	Stamped	Contacts	
SIZE	D۷	VG. NO	٠.			ELECTRONI	C FILE	Г

	SIZE	DWG. NO.		ELEC	TRONIC FILI	Ξ	REV
)6	Α	SPC	15230	79	K4829.	DWG	Α
16	SCALI	E: NTS	U.O.M.: mm [INCHES]		SHEET:	1 0	F 1