



## General Information

<b>Kit Part Number:</b>	<a href="#">2110844-2</a>
<b>Description:</b>	12 AWG Female Minus Keyed Coupler and Male Neutral Keyed Coupler with Ground Bolt and Locking Collar Connector Accessory and Crimp Tool
<b>Industry:</b>	Alternative Energy
<b>Application:</b>	Approved for field termination, Connectivity Systems for PV Installers, Keyed Housing Provide Mating and System Safety, PV Cable, Solar
<b>Family:</b>	SOLARLOK
<b>TE Brand:</b>	TYCO ELECTRONICS Products
<b>Solution:</b>	Solar Energy
<b>Product Type:</b>	Wire-to-Wire Connectors
<b>Number of Pieces:</b>	74
<b>RoHS:</b>	Yes

## Specifications

<b>Current Rating:</b>	25A
<b>Tool Included:</b>	Yes
<b>Voltage Rating:</b>	600V
<b>Wire Gauge (AWG):</b>	12

## Product Highlights

The SOLARLOK male and female cable coupler was designed for high voltage and high current-carrying capacity in addition to the well established IP 67 sealing requirement in the photovoltaic industry. Mating safety is provided by polarity keyed housings, fully shrouded high cycle life contacts and a squeeze to release connection system. In addition fulfillment of worldwide standards for photovoltaic connection systems complement the robust product specification.

### Features and Benefits

- Ground Bolt grounding solution
- Designed with a simple wire crimp, these latching connectors accommodate a wide range of wire sizes for a low applied cost
- Polarity keyed housing helps to prevent mismating
- UL approved
- The SOLARLOK hand crimping tool contains precision dies and ratcheting handles to help ensure repeatable crimp performance
- The SOLARLOK locking collar is required by NEC 2008, Article 690.33(c). A small flathead screwdriver is used to remove the collar from the mated connectors to achieve the required tooled extraction
- Current carrying capacity up to 25 Amps
- Operating temperature range of -40°C to 110°C
- UL and TÜV approved - UL File E 226440/TÜV 0000021303

### Applications

- Approved for field termination
- Keyed housings provide mating and system safety
- Housing is rated for 50 mating cycles
- Accommodates 12 AWG PV cable



**Bill of Materials**

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
<a href="#">CL3803-000</a>	2	Solar Disconnect Label		<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">CL3804-000</a>	2	Warning Dual Power Sources Label		<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">CL3805-000</a>	2	Warning - Electric Shock Hazard		<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">CL3806-000</a>	2	DC Disconnect Label		<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">1-1579004-2</a>	1	CSV10 Crimping Tool	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">4-1394462-9</a>	5	Female Minus Keyed Coupler	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">7-1394461-2</a>	5	Male Neutral Keyed Coupler	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">2106207-1</a>	5	Locking Collar Connector Accessory	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">2058729-1</a>	50	Grounding Clamp	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>

**Recommended Tool**

Part No.	Included in Kit
<a href="#">1-1579004-2</a>	Yes







Alternative Energy Industry

**TE** connectivity Authorized Distributor

Kit Part No. **2110844-2**

## SOLARLOK Photovoltaic Balance of System Products Connector Kit

12 AWG Female Minus Keyed Coupler and Male Neutral Keyed Coupler with Ground Bolt and Locking Collar Connector Accessory and Crimp Tool

- NEC 2008 Compliant
- Photovoltaic Module Installations
- IP 67 Sealing
- Fully Shrouded Silver Plated Contacts
- 25 Amps, 600 Volts

Additional kits available at: [www.productkits.com](http://www.productkits.com)

SOLARLOK, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks of the TE Connectivity Ltd. family of companies.

**DANGER:** Failure to follow all instructions in Application Specification [14-10408-1] and [14-10305-1] (available at [www.te.com/resources](http://www.te.com/resources)), including using only approved TE tooling (if applicable), can result in improper installation and/or crimping which is dangerous and may cause or contribute to electrical fires. Should be used only by individuals with proper training and experience.

**74**  
pieces



Product from TE Connectivity.  
Kits designed and assembled  
by Waldom Electronics.