



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG		


REVISIONS		DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398						
DCP # REV DESCRIPTION		DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
1876	Α	RELEASED	EO	07/25/06	SA	07/25/06	но	07/25/06








PANEL CUTOUT





SPECIFICATIONS:

Shell: Steel, Zinc Yellow Chromated Insulator: UL 94V-0 Rated, Black 1. PBT+30% Fiber Glass

2. Nylon-66

Current Rating: 5 Amps

Contact Resistance: 15 miliohms Max Insulator Resistance: 1000 Megohms Min

Voltage: 500 VAC for 1 Minute Temperature: -50°C to +100°C

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE

DISCLAIMER:

CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

Un	less Ot	herwise
	Specif	fied
.X	±0.35	[0.014]
.XX	±0.15	[0.006]


TOLERANCES:

DRAWN BY:	DATE:
EKLAS ODISH	07/25/06
CHECKED BY:	DATE:
SAMI ALNADI	07/25/06
APPROVED BY:	DATE:
HISHAM ODISH	07/25/06

DRAW	ING TITLE:				
		25	Pin	Crimp	Тур
SIZE	DWG. NO).			
Δ			PC1	5272	
, ,		<u>_</u>			

SCALE: NTS

5 Pin	Crimp Type D-				
		ELEC	TRONIC FIL	E.	REV
SPC	15272	79	TRONIC FIL K4869.	DWG	Α
	U.O.M.: mm [INCHES		SHFFT:	1 OF	- 2



SPECIFICATIONS

Contact: Brass, Stamped Gold—Plated on Contact Area Nickel—Plated on Crimp—Area

ALL RICHTS RESERVED. NO PORTION OF THIS PURLICATION WHETHER IN	WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE	SIZE	DWG. NO.			ELECTRONIC FILE	
EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.		Α	SPC	15272	79	K4869.DWG	A
SPC-F005.DWG	DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398	SCALE	: NTS	U.O.M.: mm [INCHES]		SHEET: 2 0	F 2