


U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® MSR-M	12.09.2012

For the benefits, refer to SKINTOP® MS-M



Info

SKINTOP® MSR-M 75 x 1.5 with innovative double lamella gasket for easier assembling of cables with large diameters.
Now with IP 69 K approval! Proven to withstand the most demanding cleaning procedures for industrial machinery with high-pressure cleaners and hot water!

Application range

With reducing seal insert, to seal cables with smaller outer diameters.

Design

Metric connection thread acc. to EN 50262

Approvals (Norm references)

UL File Nr. E79903

Note

Counter nut to be used: SKINDICHT® SM-M
Refer to SKINTOP® metric accessories for suitable accessories

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Caution:	Refer to Appendix T21 for the installation dimensions and torques
Approvals:	IP 69 K approval from size M75 x 1.5 pending. UL, CSA, DNV and VDE approval for sizes M90 x 2 to M110 x 2 pending.
Material:	Body: nickel-plated brass Insert: polyamide Sealing ring: CR O-ring: NBR
Protection rating:	IP 68 IP 69 K
Temperature range:	Dynamic: -30 °C to +100 °C Fixed: -40 °C to +100 °C





Product Management	Document: LAPP_PRO990EN.pdf	1 / 3
--------------------	-----------------------------	-------

SKINTOP® MSR-M

12.09.2012

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Overall length/ C (mm)	Thread length inner mm	Pieces / PU
SKINTOP® MSR-M						
53112100	12 x 1,5	1-5	16	26,5	6.5	100
53112110	16 x 1,5	2-7	20	32.0	7.0	100
53112120	20 x 1,5	5-10	24	35,5	8.0	50
53112130	25 x 1,5	6-13	29	37,5	8.0	25
53112140	32 x 1,5	7-15	36	42,2	9.0	25
53112150	40 x 1,5	15-23	45	49,5	9.0	10
53112160	50 x 1,5	22-29	54	52.0	10.0	5
53112170	63 x 1,5	28-39	67	61,3	15.0	5
53112511	75 x 1,5	53-63	95	105.0	15.0	1
53112515	110 x 2	76-88	135	154.0	25.0	1

U.I. Lapp GmbH	PRODUCT INFORMATION	 LAPP GROUP
	SKINTOP® MSR-M	12.09.2012



Product Management	Document: LAPP_PRO990EN.pdf	3 / 3
--------------------	-----------------------------	-------