



Quick Reference Guide

Company profile


Weidmüller is the leading manufacturer of components for electrical and electronic interconnection technologies.

The company develops, produces and sells customer-oriented solutions comprising the entire Weidmüller product portfolio. As an OEM supplier, the company sets global standards in the field of electrical connection technology.

The Weidmüller product portfolio ranges from terminal blocks, PCB connectors and terminals, protected components, Industrial Ethernet components and relay sockets to power supply and overvoltage protection modules suitable for all applications. Electrical installation and marking solutions, basic I/O components and a variety of tools round off the range. Weidmüller products are mainly used in control cabinets and for field wiring. Customers also benefit from our wide range of services.

In addition to our expertise in manufacturing precision mechanics, we offer a customer oriented product portfolio for our international customers in the fields of industrial, process and transportation technology. Our developments and activities are driven solely by the individual requirements of our customers in these areas.

The Weidmüller Group has a strong international orientation with production facilities, sales companies and agencies in over 70 countries. Due to our high standards of quality and service, customers around the world value us as a highly competent and flexible partner.




All the catalogues at a glance

Catalogue 1: Modular Terminal Blocks

Order number: 5650110000

- P-Series (Push In technology)
- I-Series (IDC technology)
- Z-Series (Tension clamp technology)
- W-Series (Screw connection technology)
- Stud style (Screw connection technology)



Catalogue 3: RockStar® – Heavy Duty Connectors

Order number: 5650130000

- Inserts
- Modular system
- Housings IP65 + IP69K



Catalogue 5: Enclosures and Cable Glands

Order number: 5650150000

- Enclosures
- Cable gland and Cabtite



Catalogue 2: PCB Terminals and Connectors

Order number: 5650120000

PCB Terminals with

- leaf spring connection, clamping yoke connection, TOP clamp connection, tension clamp connection, Push In spring connection, spade connection

PCB Connectors of

- Minimate, Omnimate, Unimate, Powermate and Crimpmate Ranges



Catalogue 4: Electronics

Order number: 5650140000

- Interface units
- Digital signal processing - relays, optos, timers
- Analogue signal processing
- Power supplies
- Overvoltage protection



Catalogue 6: Tools

Order number: 5650160000

- Cutting
- Stripping
- Crimping
- Screwdrivers
- Measuring/Testing
- Automatic machines



Catalogue 7: Marking Systems

Order number: 5650170000

- Terminal markers
- Wire and cable markers
- Device and equipment markers
- Printing systems
- Software



Catalogue 9: Industrial Ethernet

Order number: 5650190000

- Active components
- Passive components
- Accessories



Online Catalogue

If you have questions about the specifications and details of our products, perhaps even outside normal business hours, then our online catalogue at <http://catalog.weidmuller.com> – open 24 hours a day, 365 days a year – is the perfect source of information. Besides product features and part numbers, it contains extensive additional information on all product groups. For further information, specials and contacts, simply consult the Weidmüller website at www.weidmuller.ca

To access the online catalog click on the button:

**On-Line
Catalog Search**

Catalogue 8: Sensor Actuator Interface

Order number: 5650180000

- SAI Passive
- SAI Active
- Cables and connectors
- JACKPAC® IP67



Complete Set

Order number: 5650100000

- composed of catalogue 1 to catalogue 9 inclusive



CD-ROM

Order number: 5650500000

As well as browsing through our printed and online catalogues you can now gain an overview of our products with the help of our CD-ROM. You don't need Internet access nor do you have to install the CD. Simply insert the CD-ROM into the drive and browse away.

Please note that this Short Form Catalog is a **condensed** version of our complete catalog set, which is comprised of nine individual product line catalogs. Only a **selected** range of products are represented here. For details on SAI, PCB, enclosures or other products not referenced within, please refer to the applicable individual catalog, the catalog CD or our on-line catalog service.

This catalog has been created to provide an targeted overview of our vast range of products and as such will serve as a guide to your interface solutions. It is not, however, a replacement for technical discussion with a Product or Technical Applications Specialists when necessary. We welcome the opportunity to help our customers solve their individual challenges and to specify our products. Please call your local Sales Representative or speak to our Inside Sales staff or Technical Support staff at (905) 475-1507 or (800) 268-4080.

Every care has been taken to ensure the accuracy of our catalog data. We do not, however, accept responsibility for damage, loss or expense resulting from any error or omission. We reserve the right to make alterations in line with technical advances and industry standards. Goods are supplied accordance with our Terms and Conditions of Sale.

Note: Dimensions are in mm unless otherwise stated.

Short Form Catalogue

Terminal Blocks

Circuit Breakers

Heavy Duty Connectors

Electronics

Tools

Installation Products

Industrial Ethernet

Appendix

Index

Search according to description or part number

Notes

A

B

C

D

E

F

G

Terminal Blocks

Terminal Blocks

W-Series	A.2
SAK-Series	A.6
Z-Series	A.10
I-Series	A.14
P-Series	A.16
DIN Mounting Rail and Accessories	A.16

Terminal Blocks - W Series

W Series - Feed Through Terminal Blocks




WDU 2.5



WDK 2.5 ZQV

W Series - Ground Terminal Blocks




WPE 2.5



WDK 2.5PE

W Series - Fuse Terminal Blocks



WSI 6

* Note: WSI 6 uses 5x20mm fuses
WSI 6/2 uses 1¼"x¼" fuses

Ratings/Width	Wire Range	Part Number	Description
600V/20A/5mm	26-12 AWG	1020000000	WDU 2.5
600V/20A/6mm	26-10 AWG	1020100000	WDU 4
600V/45A/8mm	20-8 AWG	1020200000	WDU 6
600V/65A/10mm	16-6 AWG	1020300000	WDU 10
600V/65A/12mm	14-6 AWG	1020400000	WDU 16
600V/120A/16mm	12-2 AWG	1020500000	WDU 35
600V/205A/27mm	6-2/0 AWG	1024600000	WDU 70/95
600V/285A/32mm	2-250MCM	1024500000	WDU 120/150
600V/400A/36mm	1/0-500MCM	1802780000	WDU 240
300V/10A/5mm	26-12 AWG	1021500000	WDK 2.5
300V/25A/5mm	26-12 AWG	1041100000	WDK 2.5 ZQV
300V/10A/5mm	26-12 AWG	1022300000	WDK 2.5V
300V/20A/5mm	26-12 AWG	1041600000	WDK 2.5N
300V/20A/5mm	26-12 AWG	1041610000	WDK 2.5NV
300V/30A/6mm	26-10 AWG	1041900000	WDK 4N
300V/30A/6mm	26-10 AWG	1041910000	WDK 4NV
600V/5mm	26-12 AWG	1010000000	WPE 2.5
600V/6mm	26-10AWG	1010100000	WPE 4
600V/8mm	20-8 AWG	1010200000	WPE 6
600V/10mm	16-6 AWG	1010300000	WPE 10
600V/12mm	14-6 AWG	1010400000	WPE 16
600V/16mm	12-2 AWG	1010500000	WPE 35
600V/27mm	6-2/0 AWG	1037300000	WPE 70/95
600V/32mm	2-250MCM AWG	1019700000	WPE 120/150
300V/5mm	26-12 AWG	1036300000	WDK 2.5PE
300V/5mm	26-12 AWG	1041620000	WDK 2.5N PE
300V/6mm	26-10 AWG	1041920000	WDK 4N PE
300V/10A/8mm	20-8 AWG	1011000000	WSI 6 *
300V/10A/8mm	20-8 AWG	1011300000	WSI 6 LD 10-36VAC/DC *
300V/10A/8mm	20-8 AWG	1012200000	WSI 6 LD 30-70VAC/DC *
300V/10A/8mm	20-8 AWG	1012300000	WSI 6 LD 60-150VAC/DC *
300V/10A/8mm	20-8 AWG	1012400000	WSI 6 LD 140-250VAC/DC *
300V/10A/12mm	20-8 AWG	1014000000	WSI 6/2 *
300V/10A/12mm	20-8 AWG	1014100000	WSI 6/2 LD 10-36VAC/DC *
300V/10A/12mm	20-8 AWG	1014200000	WSI 6/2 LD 30-70VAC/DC *
300V/10A/12mm	20-8 AWG	1014300000	WSI 6/2 LD 60-150VAC/DC *
300V/10A/12mm	20-8 AWG	1014400000	WSI 6/2 LD 140-250VAC/DC *

Terminal Blocks - W Series

End Plate / Partition	End Bracket *	Jumpers (# of poles)	Labels	DIN Rail *	Screwdriver
1050000000/1050100000	0383560000/1061200000	1054460000/1909000000 (10/20)	1609860000	0514500000	9008320000
1050000000/1050100000	0383560000/1061200000	1052060000/1909000000 (10/20)	1609900000	0514500000	9008330000
1050000000/1050100000	0383560000/1061200000	1052260000/0545400000 (10/58)	1609920000	0514500000	9008340000
1050000000/1050100000	0383560000/1061200000	1052460000 (10)	1609920000	0514500000	9008350000
1050100000	1061200000/1059000000	1053360000 (10)	1609920000	0514500000	9009350000
1050100000	1061200000/1059000000	1053160000 (10)	1609920000	0514500000	9009010000
N/A	1061200000/1059000000	1063600000 (3)	1609920000	0514500000	9008860000
N/A	1061200000/1059000000	1063300000/1063400000 (2/3)	1609920000	0514500000	9008860000
N/A	1061200000/1059000000	1802790000/1802800000 (2/3)	1609880000	0514500000	9008860000
1059100000/1058800000	0383560000/1061200000	1054460000 (10)	1640740000	0514500000	9008320000
1059100000/1058800000	0383560000/1061200000	1909000000 (20)	1640740000	0514500000	9008320000
1059100000/1058800000	0383560000/1061200000	1054460000 (10)	1640740000	0514500000	9008320000
1084000000/1058800000	0383560000/1061200000	1909000000 (20)	1640740000	0514500000	9008320000
1084000000/1058800000	0383560000/1061200000	1909000000 (20)	1640740000	0514500000	9008320000
1084000000/1058800000	0383560000/1061200000	1909000000 (20)	1640740000	0514500000	9008320000
1084000000/1058800000	0383560000/1061200000	1909000000 (20)	1640740000	0514500000	9008320000
1050000000/1050100000	0383560000/1061200000	N/A	1609860000	0514500000	9008320000
N/A	0383560000/1061200000	N/A	1609900000	0514500000	9008330000
N/A	0383560000/1061200000	N/A	1609920000	0514500000	9008340000
N/A	0383560000/1061200000	N/A	1609920000	0514500000	9008350000
N/A	0383560000/1061200000	N/A	1609920000	0514500000	9008350000
N/A	0383560000/1061200000	N/A	1609920000	0514500000	9009010000
N/A	1061200000/1059000000	N/A	1609920000	0514500000	9008860000
N/A	1061200000/1059000000	N/A	1609920000	0514500000	9008860000
1059100000	0383560000/1061200000	N/A	1640740000	0514500000	9008320000
1084000000	0383560000/1061200000	N/A	1640740000	0514500000	9008320000
1084000000	0383560000/1061200000	N/A	1640740000	0514500000	9008320000
1050000000/1050100000	0383560000/1061200000	0338000000 + 1052100000 (10)	1609920000	0514500000	9008340000
1050000000/1050100000	0383560000/1061200000	0338000000 + 1052100000 (10)	1609920000	0514500000	9008340000
1050000000/1050100000	0383560000/1061200000	0338000000 + 1052100000 (10)	1609920000	0514500000	9008340000
1050000000/1050100000	0383560000/1061200000	0338000000 + 1052100000 (10)	1609920000	0514500000	9008340000
1050000000/1050100000	0383560000/1061200000	0338000000 + 1052100000 (10)	1609920000	0514500000	9008340000
1050000000/1050100000	0383560000/1061200000	0338000000 + 1052100000 (10)	1609920000	0514500000	9008340000
1050000000/1050100000	0383560000/1061200000	0338000000 + 1052100000 (10)	1609920000	0514500000	9008340000
1050000000/1050100000	0383560000/1061200000	0338000000 + 1052100000 (10)	1609920000	0514500000	9008340000
1050000000/1050100000	0383560000/1061200000	0338000000 + 1052100000 (10)	1609920000	0514500000	9008340000
1050000000/1050100000	0383560000/1061200000	0338000000 + 1052100000 (10)	1609920000	0514500000	9008340000

* See page A.16 for details or other options

W Series - Fuse Terminal Blocks



* Note: WSI 4/2 uses 1¼"x¼" fuses

WTR 2.5

Weidmüller

Terminal Blocks

A

SAK Series - Feed Through Terminal Blocks



Note: KRG: melamine, PA: polyamide, EN: combifoot

Terminal Blocks

A


[illegible]

SAK Series - Ground Terminal Blocks



EK 2.5N

SAK Series - Fuse Terminal Blocks



ASK 1/FN



KDKS 1/EN

* Note: ASK /SAKS 1 uses 5x20mm fuses
KDKS uses 5x20mm/5x25mm fuses
SAKS 3/SAKS 6 uses 1¼"x1¼" fuses

Ratings/Width	Wire Range	Part Number	Description
600V/6mm	26-10 AWG	0661060000	EK 2.5/35 PA
600V/6mm	26-10 AWG	0474360000	EK 2.5N PA
600V/8mm	26-10 AWG	0661160000	EK 4/35 PA
600V/8mm	26-10 AWG	0354560000	EK 4 PA
600V/8mm	20-8 AWG	0661260000	EK 6/35 PA
600V/10mm	14-6 AWG	0661360000	EK 10/35 PA
600V/10mm	14-6 AWG	0354660000	EK 10 PA
600V/12mm	10-4 AWG	0190160000	EK 16/35 PA
600V/12mm	10-2 AWG	0374660000	EK 16 PA
600V/18mm	12-2 AWG	0661460000	EK 35/35 PA
600V/18mm	10-2 AWG	0354760000	EK 35 PA
300V/10A/8mm	26-12 AWG	0474560000	ASK 1 EN PA
300V/10A/8mm	26-12 AWG	0222760001	ASK1EN/SMT10-60Vuc BFI H-
300V/10A/8mm	26-12 AWG	9123140001	ASK1EN/SMT10-60Vuc BFI H+
300V/10A/8mm	26-12 AWG	0225560001	ASK1EN/SMT100-250Vuc BFI H-
300V/10A/8mm	26-12 AWG	9118290001	ASK1EN/SMT100-250Vuc BFI H+
300V/10A/8mm	26-12 AWG	9503350000	KDKS 1 EN PA
300V/10A/8mm	26-12 AWG	9802720001	KDKS1EN/SMT10-60Vuc BFI H-
300V/10A/8mm	26-12 AWG	9908510001	KDKS1EN/SMT10-60Vuc BFI H+
300V/10A/8mm	26-12 AWG	9802760001	KDKS1EN/SMT100-250Vuc BFI H-
300V/10A/8mm	26-12 AWG	9915820001	KDKS1EN/SMT100-250Vuc BFI H+
300V/10A/8mm	26-12 AWG	9528110000	KDKS 1 PE PA
300V/10A/8mm	26-12 AWG	9158330001	KDKS1PE/SMT10-60Vuc BFI H-
300V/10A/8mm	26-12 AWG	9158340001	KDKS1PE/SMT10-60Vuc BFI H+
300V/10A/8mm	26-12 AWG	9158350001	KDKS1PE/SMT100-250Vuc BFI H-
300V/10A/8mm	26-12 AWG	9915150001	KDKS1PE/SMT100-250Vuc BFI H+
600V/10A/13mm	26-10 AWG	0501600000	SAKS 1/35
600V/10A/13mm	26-10 AWG	0191220000	SAKS 1 KRG
600V/10A/13mm	26-10 AWG	0501620000	SAKS 1/35/35 KRG
600V/10A/13mm	22-10 AWG	0328920000	SAKS 3/35 KRG
600V/10A/13mm	22-10 AWG	0297520000	SAKS 3 KRG
300V/10A/13mm	20-8 AWG	0531820000	SAKS 6/32 KRG

Terminal Blocks - SAK Series

End Plate / Partition	End Bracket *	Jumpers (# of poles)	Labels	DIN Rail *	Screwdriver
N/A	N/A	N/A	1609820000	0514500000	9008330000
N/A	N/A	N/A	1609820000	0122800000	9008330000
N/A	N/A	N/A	1609840000	0514500000	9008330000
N/A	N/A	N/A	1609840000	0122800000	9008330000
N/A	N/A	N/A	1609840000	0514500000	9008340000
N/A	N/A	N/A	1609800000	0514500000	9008350000
N/A	N/A	N/A	1609800000	0122800000	9008350000
N/A	N/A	N/A	1609800000	0514500000	9008350000
N/A	N/A	N/A	1609800000	0122800000	9008350000
N/A	N/A	N/A	1609800000	0514500000	9009010000
N/A	N/A	N/A	1609800000	0122800000	9008350000
0380360000	0383560000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
0380360000	0383560000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
0380360000	0383560000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
0380360000	0383560000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
0380360000	0383560000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
9503330000	1061200000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
9503330000	1061200000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
9503330000	1061200000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
9503330000	1061200000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
9503330000	1061200000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
9503330000	1061200000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
9503330000	1061200000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
9503330000	1061200000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
9503330000	1061200000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
9503330000	1061200000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
9503330000	1061200000	0545400000 + 0546000000 (58)	1609800000	0514500000 / 0122800000	9008330000
0191320000	1061200000	N/A	1609800000	0514500000	9008350000
0191320000	1061200000	N/A	1609800000	0514500000	9008350000
0191320000	1061200000	N/A	1609800000	0514500000	9008350000
0191320000	1061200000	N/A	1609800000	0514500000	9008350000
0191320000	1061200000	N/A	1609800000	0514500000	9008350000
0146720000	0206160000	0338800000 + 0346200000 (10)	1609820000	0122800000	9008350000


* See page A.16 for details or other options

Terminal Blocks - SAK & Z Series

SAK Series - Disconnect Terminal Blocks




SAKR



DKT 4

Ratings/Width	Wire Range	Part Number	Description
300V/10A/6.5mm	26-12 AWG	0412120000	SAKR KRG
300V/10A/6.5mm	26-12 AWG	0172160000	SAKR/35 PA
300V/10A/6.5mm	26-12 AWG	0412160000	SAKR PA
300V/10A/6.5mm	26-12 AWG	0687460000	DKT 4/35 KRG
300V/10A/6mm	26-12 AWG	0687360000	DKT 4 KRG
300V/10A/6mm	26-12 AWG	0687460000	DKT 4/35 PA
300V/10A/6mm	26-12 AWG	0687460000	DKT 4 PA
300V/25A/6.5mm	22-10 AWG	0357520000	SAKC 4/35 KRG
300V/25A/6.5mm	22-10 AWG	0340720000	SAKC 4 KRG
600V/25A/12mm	20-10 AWG	1404620000	SAKC 10/35 KRG
600V/25A/12mm	20-10 AWG	0324120000	SAKC 10 KRG

Z Series - Feed Through Terminal Blocks



ZDU 1.5



ZDU 6-2/2AN

300V/20A/3.5mm	26-14 AWG	1775480000	ZDU 1.5
300V/20A/3.5mm	26-14AWG	1775530000	ZDU 1.5/3AN
600V/27A/5mm	26-12 AWG	1608510000	ZDU 2.5
600V/23A/5mm	26-14 AWG	1772060000	ZDU 2.5-2
600V/35A/6mm	26-10 AWG	1632050000	ZDU 4
600V/35A/6mm	26-10 AWG	1770370000	ZDU 4-2/2AN
600V/35A/6mm	26-10 AWG	7904180000	ZDU 4/3AN
600V/50A/8mm	20-8 AWG	1608620000	ZDU 6
600V/50A/8mm	20-8 AWG	1771380000	ZDU 6-2/2AN
600V/50A/8mm	20-8 AWG	7907410000	ZDU 6/3AN
600V/55A/10mm	16-6 AWG	1746750000	ZDU 10
600V/55A/10mm	16-6 AWG	1767690000	ZDU 10/3AN
600V/65A/12mm	14-4 AWG	1745230000	ZDU 16
600V/65A/12mm	14-4 AWG	1768320000	ZDU 16/3 AN
600V/120A/16mm	12-2 AWG	1739620000	ZDU 35

Z Series - Ground Terminal Blocks



ZPE 2.5



ZDK 2.5-2 PE

300V/3.5mm	26-14 AWG	1775510000	ZPE 1.5
600V/5mm	26-12 AWG	1608640000	ZPE 2.5
600V/5mm	26-14 AWG	1772090000	ZPE 2.5-2
600V/3.5mm	26-12 AWG	1791010000	ZDK 2.5-2 PE
600V/6mm	26-10 AWG	1632080000	ZPE 4
600V/6mm	26-10 AWG	1770380000	ZPE 4-2/2AN
600V/8mm	20-8 AWG	1608670000	ZPE 6
600V/8mm	20-8 AWG	1771370000	ZPE 6-2/2AN
600V/10mm	16-6 AWG	1746770000	ZPE 10
600V/12mm	14-4 AWG	1745250000	ZPE 16
600V/16mm	12-2 AWG	1739650000	ZPE 35

Terminal Blocks - SAK & Z Series

End Plate / Partition	End Bracket *	Jumpers (# of poles)	Labels	DIN Rail *	Screwdriver
0211320000	0206160000	0482900000 (4)	1609840000	0122800000	9008330000
0211360000	0383560000	0482900000 (4)	1609840000	0514500000	9008330000
0211360000	0206160000	0482900000 (4)	1609840000	0122800000	9008330000
0687560000	0383560000	0482900000 (4)	1609820000	0514500000	9008330000
0687360000	0206160000	0482900000 (4)	1609820000	0122800000	9008330000
0687560000	0383560000	0482900000 (4)	1609820000	0514500000	9008330000
0687560000	0206160000	0482900000 (4)	1609820000	0122800000	9008330000
0117920000	0383560000	0482900000 (4)	1609840000	0514500000	9008330000
0117920000	0206160000	0482900000 (4)	1609840000	0122800000	9008330000
0146720000	0383560000	0338500000 (10)	1609840000	0514500000	9008330000
0146720000	0206160000	0338500000 (10)	1609840000	0122800000	9008330000
1776030000	9540000000	1776200000 (10)	1778270000	0514500000	9037160000
1776060000	9540000000	1776200000 (10)	1609900000	0514500000	9037160000
1608740000	9540000000	1908960000 (20)	1635000000	0514500000	9008330000
1706110000	9540000000	1608940000 (10)	1768090000	0514500000	9008330000
1632090000	9540000000	1609030000 (10)	1828450000	0514500000	9008330000
1770400000	9540000000	1609030000 (10)	1609900000	0514500000	9008330000
7904100000	9540000000	1609030000 (10)	1609900000	0514500000	9009330000
1608830000	9540000000	1908990000 (24)	1609900000	0514500000	9008350000
1771440000	9540000000	1908990000 (24)	1277060000	0514500000	9008340000
7907410000	9540000000	1908990000 (24)	1609900000	0514500000	9008350000
1748660000	9540000000	1739680000 (2)	1609860000	0514500000	9008350000
1749580000	9540000000	1739680000 (2)	1609860000	0514500000	9008350000
1745150000	9540000000	1739690000 (2)	1609880000	0514500000	9008350000
1749580000	9540000000	N/A	1609880000	0514500000	9008350000
1739620000	9540000000	1739700000 (2)	1609880000	0514500000	9008350000
1776030000	9540000000	N/A	1778270000	0514500000	9037160000
1608740000	9540000000	N/A	1635000000	0514500000	9008330000
1706110000	9540000000	N/A	1768090000	0514500000	9008330000
1791050000	9540000000	N/A	1635000000	0514500000	9008320000
1632080000	9540000000	N/A	1609900000	0514500000	9008330000
1770400000	9540000000	N/A	1609900000	0514500000	9008330000
1608830000	9540000000	N/A	1609900000	0514500000	9008350000
1771440000	9540000000	N/A	1277060000	0514500000	9008340000
1748660000	9540000000	N/A	1609900000	0514500000	9008350000
1745150000	9540000000	N/A	1609880000	0514500000	9008350000
N/A	9540000000	N/A	1609880000	0514500000	9008350000

* See page A.16 for details or other options

Terminal Blocks - Z Series

Z Series - Fuse Terminal Blocks



ZSI 2.5



ZSI 6-2

* Note: ZSI 2.5 uses 5x25mm fuses
ZSI 6 uses 5x20mm/5x25mm fuses
ZSI 16-2/FC uses automotive fuses

Z Series - Disconnect Terminal Blocks



ZTR 2.5

Ratings/Width	Wire Range	Part Number	Description
600V/15A/8mm	26-12 AWG	1616400000	ZSI 2.5 *
600V/15A/8mm	26-12 AWG	1616440000	ZSI 2.5/LD 10-36 AC/DC *
600V/15A/8mm	26-12 AWG	1616430000	ZSI 2.5/LD 30-70 AC/DC *
600V/15A/8mm	26-12 AWG	1616420000	ZSI 2.5/LD 60-150 AC/DC *
600V/15A/8mm	26-12 AWG	1616410000	ZSI 2.5/LD 140-250 AC/DC *
600V/15A/8mm	26-12 AWG	1730900000	ZSI 2.5/ 5X25 *
600V/15A/8mm	26-12 AWG	1616460000	ZSI 2.5/2 *
600V/15A/8mm	26-12 AWG	1616470000	ZSI 2.5/2/LD 10-36 AC/DC *
600V/15A/8mm	26-12 AWG	1616480000	ZSI 2.5/2/LD 30-70 AC/DC *
300V/10A/8mm	26-12 AWG	1616490000	ZSI 2.5/2/LD 60-150 AC/DC *
300V/15A/8mm	26-12 AWG	1616500000	ZSI 2.5/2/LD 140-250 AC/DC *
300V/10A/12.2mm	26-8 AWG	1820930000	ZSI 6-2 *
300/25A/8mm	22-10 AWG	1814690000	ZSI 6-2/FC *
300V/10A/5mm	26-12 AWG	1831130000 + 7921590000	ZTR 2.5/SI
300V/10A/5mm	26-12 AWG	1831130000 + 7921570000	ZTR 2.5/SI LD 10-36V
300V/10A/5mm	26-12 AWG	1831130000 + 7921580000	ZTR 2.5/SI LD 30-70V
300V/10A/5mm	26-12 AWG	1831130000 + 7921590000	ZTR 2.5/SI LD 60-150V
300V/10A/5mm	26-12 AWG	1831130000 + 7921600000	ZTR 2.5/SI LD 140-250V
300V/15A/5mm	26-12 AWG	1831280000	ZTR 2.5
300V/15A/5mm	26-12 AWG	8731720000	ZTR 2.5/3AN
300V/10A/5mm	26-12 AWG	7920900000	ZTR 2.5/4AN
300V/10A/5mm	26-12 AWG	1745400000	ZDTR 2.5

Terminal Blocks - Z Series


End Plate / Partition	End Bracket *	Jumpers (# of poles)	Labels	DIN Rail *	Screwdriver
1608800000	9540000000	1627870000 (4)	1635000000	0514500000	9008330000
1608800000	9540000000	1627870000 (4)	1635000000	0514500000	9008330000
1608800000	9540000000	1627870000 (4)	1635000000	0514500000	9008330000
1608800000	9540000000	1627870000 (4)	1635000000	0514500000	9008330000
1608800000	9540000000	1627870000 (4)	1635000000	0514500000	9008330000
1608800000	9540000000	1627870000 (4)	1635000000	0514500000	9008330000
N/A	9540000000	1633220000 (4)	1635000000	0514500000	9008330000
N/A	9540000000	1633220000 (4)	1635000000	0514500000	9008330000
N/A	9540000000	1633220000 (4)	1635000000	0514500000	9008330000
N/A	9540000000	1633220000 (4)	1635000000	0514500000	9008330000
N/A	9540000000	1633220000 (4)	1635000000	0514500000	9008330000
1814710000	9540000000	1627870000 (4)	1635000000	0514500000	9008340000
1814711111	9540000000	1627870000 (4)	1635000000	0514500000	9008340000
1608770000	9540000000	1608940000 (10)	1635000000	0514500000	9008330000
1608770000	9540000000	1608940000 (10)	1635000000	0514500000	9008330000
1608770000	9540000000	1608940000 (10)	1635000000	0514500000	9008330000
1608770000	9540000000	1608940000 (10)	1635000000	0514500000	9008330000
1608770000	9540000000	1608940000 (10)	1635000000	0514500000	9008330000
1608770000	9540000000	1608940000 (10)	1609860000	0514500000	9008330000
1608800000	9540000000	1608940000 (10)	1609860000	0514500000	9008330000
1608800000	9540000000	1608940000 (10)	1609900000	0514500000	9008330000
1745200000	9540000000	1693880000 (10)	1609900000	0514500000	9008330000

* See page A.16 for details or other options

I Series - Feed Through Terminal Blocks



I Series - Ground Terminal Blocks



I Series - Fuse Terminal Blocks



* Note: ITR uses 5x20mm fuses

I Series - Disconnect Terminal Blocks



A.14

Terminal Blocks - I Series

End Plate / Partition	End Bracket *	Jumpers (# of poles)	Labels	DIN Rail *	Screwdriver
1792430000	0383560000/9540000000	1908960000 (20)	1635000000	0514500000	9006060000
1792450000	0383560000/9540000000	1908960000 (20)	1635000000	0514500000	9006060000
1792600000	0383560000/9540000000	1908960000 (20)	1635000000	0514500000	9006060000
1792430000	0383560000/9540000000	1908960000 (20)	1635000000	0514500000	9006060000
1792450000	0383560000/9540000000	1908960000 (20)	1635000000	0514500000	9006060000
1792430000	0383560000/9540000000	1908960000 (20)	1635000000	0514500000	9006060000
1792450000	0383560000/9540000000	1908960000 (20)	1635000000	0514500000	9006060000
1792650000	1061200000/9540000000	1908960000 (20)	1635000000	0514500000	9006060000
1813020000	1061200000/9540000000	1609030000 (10)	1828450000	0514500000	9006060000
1813040000	0383560000/9540000000	1609030000 (10)	1828450000	0514500000	9006060000
1813070000	0383560000/9540000000	1609030000 (10)	1828450000	0514500000	9006060000
1813020000	0383560000/9540000000	1609030000 (10)	1828450000	0514500000	9006060000
1813020000	0383560000/9540000000	1609030000 (10)	1828450000	0514500000	9006060000
1813040000	0383560000/9540000000	1609030000 (10)	1828450000	0514500000	9006060000
1792430000	0383560000/9540000000	N/A	1635000000	0514500000	9006060000
1792450000	0383560000/9540000000	N/A	1635000000	0514500000	9006060000
1792470000	0383560000/9540000000	N/A	1635000000	0514500000	9006060000
1792430000	0383560000/9540000000	N/A	1635000000	0514500000	9006060000
1792450000	0383560000/9540000000	N/A	1635000000	0514500000	9006060000
1792430000	0383560000/9540000000	N/A	1635000000	0514500000	9006060000
1792450000	0383560000/9540000000	N/A	1635000000	0514500000	9006060000
1803800000	0383560000/9540000000	N/A	1635000000	0514500000	9006060000
1813020000	0383560000/9540000000	N/A	1828450000	0514500000	9006060000
1813040000	0383560000/9540000000	N/A	1828450000	0514500000	9006060000
1813070000	0383560000/9540000000	N/A	1828450000	0514500000	9006060000
1813020000	0383560000/9540000000	N/A	1828450000	0514500000	9006060000
1813020000	0383560000/9540000000	N/A	1828450000	0514500000	9006060000
1813040000	0383560000/9540000000	N/A	1828450000	0514500000	9006060000
1792450000	0383560000/9540000000	1608940000 (10)	1635000000	0514500000	9006060000
1792470000	0383560000/9540000000	1608940000 (10)	1635000000	0514500000	9006060000
1792450000	0383560000/9540000000	1608940000 (10)	1635000000	0514500000	9006060000
1792470000	0383560000/9540000000	1608940000 (10)	1635000000	0514500000	9006060000
1813040000	0383560000/9540000000	1609030000 (10)	1828450000	0514500000	9006060000
1813020000	0383560000/9540000000	1609030000 (10)	1828450000	0514500000	9006060000

* See page A.16 for details or other options

Terminal Blocks - P Series & Rail Accessories

P Series - Feed Through Terminal Blocks



PDU 2.5/4

Ratings/Width

Wire Range

Part Number

Description

600V/30/5mm

26-10 AWG

1896110000

PDU 2.5/4

600V/30/5mm

26-10 AWG

1896120000

PDU 2.5/4 3AN

600V/30/5mm

26-10 AWG

1896130000

PDU 2.5/4 4AN

P Series - Ground Terminal Blocks



PPE 2.5/4

600V/5mm

26-10 AWG

1896170000

PPE 2.5/4

600V/5mm

26-10 AWG

1896200000

PPE 2.5/4 3AN

600V/5mm

26-10 AWG

1896160000

PPE 2.5/4 4AN

Rail Accessories

Solid

M5 Slot

M6 Slot

End Bracket



TS35 7.5x1.0

TS35x7.5

0383400000

TS35x7.5

0514500000

TS35x7.5

0676200000

EW35

0383560000

WEW/2

1061200000


WEW35/1

1059000000

ZEW TS35

9540000000

ZEW 35/2

8630740000

TS35 15x1.5

TS35x15

0236400000

TS35x15

0236500000

EW35

0383560000

WEW/2

1061200000

WEW35/1

1059000000

ZEW TS35

9540000000

ZEW 35/2

8630740000

TS35 15x2.3

TS35x15

0498000000

EW35

0383560000

WEW/2

1061200000

WEW35/1

1059000000

ZEW TS35

9540000000

ZEW 35/2

8630740000

TS32

TS32

0122800000

TS32

0514400000

TS32

0676100000

EWK1

0206160000

EWK2

0199360000

WEW32/1

1067600000


EWK

0495160000


Terminal Blocks

A

Rail Support - screws




TSTW 78mm	7924273578
TSTW 88mm	7924273588
TSTW 98mm	7924273598






SchT5S



Accessories - End Brackets


	Fits on	Width	Part Number	Description
 EWK 1	TS32	8.5mm	0206160000	EWK1
 EWK 1 ALT	TS32	12.2mm	0495160000	EWK 1 ALT
 EWK 2	TS32	8mm	0199360000	EWK 2
 EW 35	TS35	8.5mm	0383560000	EW 35
 WEW 35/2	TS35	8mm	1061200000	WEW 35/2
 ZEW 35/2	TS35	8mm	9540000000 8630740000	ZEW 35 ZEW 35/2
 WEW 35/1	TS35	12.2mm	1059000000	WEW35/1

Circuit Breakers

Circuit Breakers

Branch Circuit Protectors	B.2
Supplementary Circuit Breakers 91H Series	B.2
Supplementary Circuit Breakers 2210 Series	B.3
Supplementary Circuit Breakers 4201 Series	B.4

Branch Circuit Protectors




Accessories:
Lockout piece QFAP001
Busbar SABBM54

[illegible]

Circuit Breakers

Part Number 3 Pole





Y30484501 Lockout piece

B

Supplementary Circuit Breakers 2210 Series



0.1 to 5A	400A interrupting capacity
6 to 16A	800A interrupting capacity
20A	1000A at AC, 800A at DC interrupting capacity

[illegible]



Supplementary Circuit Breakers 4201 Series




1,2 pole versions available
TS 35 and TS32 DIN rail mountable (with adaptor)
CSA, UL, VDE approvals
250Vac (0.05 to 16A)
65Vdc (0.05 to 16A)

0.05 to 2A 100x rated current or
200A max. interrupting capacity
2.0 to 16A 200A max. interrupting capacity
20A max. 400A interrupting capacity

Typical time/current Characteristics



Adaptor foot
9102100000



Current / Internal Resistance	Part Number 1 Pole	Part Number 2 Pole
0.05amp / 447ohms	9124080000	9124220000
0.08amp / 220ohms	9104650000	9124230000
0.1amp / 131ohms	9104170000	9120350000
0.2amp / 40ohms	9104180000	9124240000
0.3amp / 19.3ohms	9129810000	9124260000
0.4amp / 10.4ohms	9124090000	9124270000
0.5amp / 7.1ohms	9101000000	9129580000
0.6amp / 4.3ohms	9124110000	9124280000
0.7amp / 3.57ohms	9129560000	9124290000
0.8amp / 2.5ohms	9101100000	9129590000
1.0amp / 1.67ohms	9101200000	9129610000
1.2amp / 1.22ohms	9101300000	9129620000
1.3amps / 1.08ohms	9124120000	9124310000
1.4amps / 1.0ohms	9124130000	9124320000
1.5amps / 0.61ohms	9101400000	9129630000
1.8amps / 0.56ohms	9124140000	9124330000
2.0amps / 0.38ohms	9101500000	9129640000
2.5amps / 0.24ohms	9101600000	9129650000
3.0amps / 0.19ohms	9101700000	9129660000
3.5amps / 0.14ohms	9124160000	9124340000
4.0amps / 0.090ohms	9104350000	9129710000
4.5amps / 0.090ohms	9124170000	9124350000
5.0amps / 0.061ohms	9101800000	9129670000
5.5amps / 0.07ohms	9107830000	9124360000
6.0amps / 0.041ohms	9103810000	9124370000
6.5amps / 0.46ohms	9120040000	9124380000
7.0amps / 0.034ohms	9104150000	9124390000
8.0amps / <0.02ohms	9103000000	9104670000
9.0amps / <0.02ohms	9104610000	9124420000
10.0amps / <0.02ohms	9101900000	9129680000
11.0amps / <0.02ohms	9124180000	9124430000
12.0amps / <0.02ohms	9107840000	9124440000
13.0amps / <0.02ohms	9124190000	9124450000
14.0amps / <0.02ohms	9107850000	9124460000
15.0amps / <0.02ohms	9102000000	9129690000
16.0amps / <0.02ohms	9124210000	9124470000

Notes

Heavy Duty Connectors

Heavy Duty Connectors	Heavy Duty Connector Kits	C.2
-----------------------	---------------------------	-----

Heavy Duty Connectors - Kits

Number of Poles		Specifications	Version 1	Version 2	Version 3
HA-3 Group Size 1		Voltage / Current	Screw / Side	Screw / Top	Screw / Side DSTV
		600V / 10A	1712580000 PG11/P METAL	1712560000 PG11/P METAL	
		600V / 10A	1712630000 PG11/P PLASTIC	1712570000 PG11/P PLASTIC	
		600V / 10A	1802450000 M20G METAL	1802470000 M20G METAL	
		600V / 10A		1802460000 M20G PLASTIC	
HA-4 Group Size 1					
		600V / 16A	1712590000 PG11/P METAL	1712610000 PG11/P METAL	
		600V / 16A	1712600000 PG11/P PLASTIC	1712650000 PG11/P PLASTIC	
		600V / 16A	1802440000 M20G METAL	1802700000 M20 METAL	
		600V / 16A	1802430000 M20G PLASTIC		
HE-6 Group Size 3					
		600V / 16A	1712460000 PG16/P METAL	1712660000 PG16/P METAL	1712700000 PG16/P METAL
		600V / 16A	1802730000 M20 METAL	1802740000 M20 METAL	
HE-10 Group Size 4					
		600V / 16A	1712510000 PG16/P METAL	1712670000 PG 16/P METAL	1712710000 PG16/P METAL
		600V / 16A	1802420000 M25 METAL	1802410000 M25 METAL	
		600V / 16A	1763870000 NPT1/2" METAL	1763910000 NPT1/2" METAL	
HE-16 Group Size 6					
		600V / 16A	1712520000 PG21/P METAL	1712680000 PG21/P METAL	1712720000 PG21/P METAL
		600V / 16A	1802400000 M25 METAL	1802390000 M25 METAL	
		600V / 16A	1763860000 NPT3/4" METAL	1763920000 NPT3/4" METAL	
HE-24 Group Size 8					
		600V / 16A	1712530000 PG21/P METAL	1712690000 PG21/P METAL	1712730000 PG21/P METAL
		600V / 16A	1802380000 M32 METAL	1802480000 M32 METAL	
		600V / 16A	1763890000 NPT3/4" METAL	1763930000 NPT3/4" METAL	
HE-32 Group Size 10					
		600V / 16A	1712540000 PG29/P METAL		
		600V / 16A	1802370000 M32 METAL		
		600V / 16A	1763900000 NPT1" METAL		
HE-48 Group Size 12					
		600V / 16A	1712550000 PG29/P METAL		
		600V / 16A	1802360000 M40 METAL		
HSB-6 Group Size 6					
		600V / 35A	1724000000 PG21/P METAL		

Heavy Duty Connectors

C


Notes

Electronics


Electronics

Interface Modules	D.2
DIN Rail Mountable Outlets	D.4
Non-Incendive Barriers	D.5
Instrumentation Make-before-break Terminals	D.5
Relays	D.6
Optocouplers	D.10
Delcon Pulse Transformer Modules	D.14
Analog Signal Conditioners	D.18
Power Supplies	D.26

Electronics - Interface Modules




Sample wiring diagram for Universal QUICKbloc



Universal QUICKbloc

RSF Poles/Dimensions



# of Poles	Width
10	50.00mm
14	50.00mm
20	65.00mm
34	110.00mm
40	115.00mm

Connection Type (Control)

Connection Type (Field)

Voltage

Current per contact

Cross-Section

Ambient Temperature

Mounting Options

Approvals

Part Number

RSF (2 Tier Compact)



Ribbon cable connector to DIN 41651

Screw Connection (AWG 26-14)

60Vac, 75Vdc

1A

2.5mm²

0°C to +55°C

TS32 / TS35

CE

10 Pole - 8155610000

14 Pole - 8258980000

20 Pole - 8155600000

34 Pole - 8155590000

40 Pole - 8155580000

Other pole counts available on request

RSF (2 Tier)



Ribbon cable connector to DIN 41651

Screw Connection (AWG 26-14)

60Vac, 75Vdc

1A

2.5mm²

0°C to +55°C

TS32 / TS35

CE

10 Pole - 0224961001

14 Pole - 0225061001

20 Pole - 0224261001

34 Pole - 0224361001

40 Pole - 0224461001

Other pole counts available on request

RSF (3 Tier)



Ribbon cable connector to DIN 41651

Screw Connection (AWG 26-14)

60Vac, 75Vdc

1A

2.5mm²

0°C to +55°C

TS32 / TS35

CE

10 Pole - 8012850000

14 Pole - 8012860000


20 Pole - 8012910000

34 Pole - 8012930000

40 Pole - 8012940000

Other pole counts available on request

RSSD Poles/Dimensions



# of Poles	Width
9	40.00mm
15	60.00mm
25	80.00mm
37	110.00mm
50	145.00mm

Connection Type (Control)

Connection Type (Field)

Voltage

Current per contact

Cross-Section

Ambient Temperature

Mounting Options

Approvals

Part Number

RSSD S



Male D-Sub connector to DIN 41 652

Screw Connection (AWG 26-14)

125Vac, 150Vdc

1.5A

0.5 - 2.5mm²

0°C to +55°C

TS32 / TS35

CE

9 Pole - 8003901001

15 Pole - 8005201001

25 Pole - 8005181001

37 Pole - 8003881001

50 Pole - 8005161001

RSSD B



Female D-Sub connector to DIN 41 652

Screw Connection (AWG 26-14)

125Vac, 150Vdc

1.5A

0.5 - 2.5mm²

0°C to +55°C

TS32 / TS35

CE

9 Pole - 8003911001

15 Pole - 8005211001

25 Pole - 8005191001

37 Pole - 8003891001

50 Pole - 8005171001

Universal QuickBLOC



18 pole male S2L with locking screws

Screw Connection (AWG26-12)

125Vmax

5A (supply); 1A (signal box)

0.5 - 4mm²

0°C to +55°C

TS32 / TS35

CE

16 ch w/ 1 fuse - 7940000602

16 ch w/ 2 fuses - 7940000604

cable 2m - - 7940000628 *

Electronics - DIN Rail Mountable Outlets

	120Vac Single w/ Breaker	120Vac Duplex	230Vac Single		
					
Input Voltage	120Vac	120Vac	230Vac		
Rated Current	5A max via outlet 10A via redundant terminals	15A max	16A		
Breaker interrupting capacity	1kA	-	-		
Terminations	Side Entry LP 5.08	Side Entry LP 5.08	Side Entry Molded screw connections		
Wire Range	26-12AWG (0.14-4.0mm ²)	26-12AWG (0.14-4.0mm ²)	14AWG (1.5mm ²)		
Dimensions (LxWxH)	70 x 35 x 55mm	70 x 75 x 48mm	76 x 45 x 60mm		
Mounting Options	TS32  / TS35 	TS32  / TS35 	TS35 		
Part Number	9915480001	9915490000	8734580000		
Type	RS-AC/CB 120Vac	RS-DUPLEX 120Vac	AC OUTLET EUROPEAN		
Approvals	 LR-229352, UL E252394	 LR-82859, UR E141197			

	120Vac GFI Outlet	120Vac Duplex			DIN Rail Mountable Drawer
					
Input Voltage	120Vac	120Vac			-
Rated Current	15A max.	15A via Duplex 20A via Terminals			-
Terminations	Top Entry, Tension Clamp LPZF	Side Entry, screw clamp (LLP 6.35)			-
Wire Range	26-14AWG (0.14-6.0mm ²)	26-14AWG (0.14-6.0mm ²)			-
Dimensions (LxWxH)	95 x 130 x 67mm	95 x 130 x 67mm			54.5 x 54.5 x 80.8mm
Mounting Options	TS35  / opt. direct mount	TS35  / opt. direct mount			TS35 
Part Number	7940000037	7940000038			7914760001
Type	GFI Outlet, 15A	GFI Outlet, 20A			DIN Rail Mountable Utility Box
Approvals	 LR-82859, UR E232318	 LR-82859, UR E232318			-
Notes	Direct mounting kit - 7920560000	Direct mounting kit - 7920560000			Can be mounted on horizontal or vertical rails

Electronics - Non-Incendive Barriers and Make-before-break Terminals

Digital Non-Incendive Barrier



Analogue Current Limiter




Rated Voltage	24Vdc	24Vdc			
Rated Current	51.1mA	20mA			
Max. Voltage	35Vdc	24Vdc (2.5Vdc drop max)			
Max. Current	75mA	24mA			
Output Alarm	-	24Vdc @50mA transistor output			
Status Led	-	Red LED (ON indicates Fault)			
Wire Size	22-12AWG	22-12AWG			
Mounting Options	TS32  / TS35 	TS32  / TS35 			
Dimensions (LxWxH)	88.4 x 12 x 68.2mm	88.4 x 9.5 x 68.2mm			
Part Number	9916290000	9918010000			
Description	MC6 Non-Incendive Barrier Digital	MC6 Non-Incendive Barrier Analogue			
Approvals	 Class 1, Division 2, Groups A, B, C & D, T3C (160°C)	 Class 1, Division 2, Groups A, B, C & D, T3C (160°C)			

MC6 Instrumentation Terminal




Voltage	30Vdc		
Current	25mA max.		
Wire Size	22-12AWG		
Moulding Material	polyamid 6.6, UL94-V2		
Temperature Rating	0-60deg C.		
Meter Connection	1/8" phono jack (see accessories)		
Mounting Options	TS32  / TS35 		
Dimensions	89 x 9.5 x 68mm		
Part Number	9917841000		
Description	MC6 MBB-INS		
Accessories	Endplate - C9040396 Test Leads - 9917851000		



Picture Shows MC6 MBB-INS and Test Leads

Electronics - Relays

PicoPak DK4/5



Accessories	Description	Part Number
End plate	AP DK4	0687560000
	AP DK5	C9039986
Jumper		
Comb Insulated	2 Pole -	QB2 0482700000
	3 Pole -	QB3 0482800000
	4 Pole -	QB4 0482900000
Jumper Comb		
Uninsulated	75 Pole straight	QB75 0535200000
	75 Pole angled	QB75 0526400000
Insulating cover strip	75 Pole	IP75 0526700000
Marking Tag		
	Blank - White	DEK5/6 1609820000

MicroSeries



Accessories	Description	Part Number
Pluggable jumpers*		
	2 Pole Red	ZQV 4N / 2 RT 1793950000
	3 Pole Red	ZQV 4N / 3 RT 1793980000
	41 Pole Red	ZQV 4N / 41 RT 1794070000
	2 Pole Black	ZQV 4N / 2 SW 1793970000
	3 Pole Black	ZQV 4N / 3 SW 1794000000
	41 Pole Black	ZQV 4N / 41 SW 1794090000
	2 Pole Blue	ZQV 4N / 2 BL 1793960000
	3 Pole Blue	ZQV 4N / 3 BL 1793990000
	41 Pole Blue	ZQV 4N / 41 BL 1794080000
Marking Tag		
	Blank - White	WS 12/6 1609900000

*other colours and pole counts also available

MCZ




Accessories	Description	Part Number
Endplate	ZAP	8389030000
Pluggable Jumpers		
	4 Pole -	ZQV4/4 1608970000
	10 Pole -	ZQV4/10 1609030000
Marking Tag		
	Blank - White	DEK5/6 1609820000

Input	Output Configuration	Max Contact Rating	Part Number
5Vdc	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8556080000 8556150000
5-15V logic (24Vdc aux.)	 NO (Normally Open)	4A@30Vdc 4A@250Vac	7901580000
5-15V logic (24Vdc aux.)	 NO (Normally Open)	4A@30Vdc 4A@250Vac	7901590000
12Vdc	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8556070000 8556140000
12Vdc	 1CO (SPDT)	6A@24Vdc 4A@120Vac	7940004779 7940004780
12Vdc	 2CO (DPDT)	5A @ 224 Vdc 5A @ 120Vdc	330075
12Vdc	 1CO (SPDT)	10A@24Vdc 10A@120Vac	8536471001 8536571001
12Vdc	 2CO (DPDT)	10A@24Vdc 10A@120Vac	8536501001 8536591001
12Vdc (24Vdc)	 NO (Normally Open)	4A@30Vdc 4A@250Vac	7901540000
12Vac/dc (24Vac/dc)	 NO (Normally Open)	4A@30Vdc 4A@250Vac	7901560000
24Vdc	 1CO (SPDT)	5A@30Vdc 5A@250Vac	7901620000
24Vdc	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8533640000 8533660000
24Vdc	 1CO (SPDT)	6A@24Vdc 4A@120Vac	7940004781 7940004782
24Vdc	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8596060000 8596080000
24Vdc	 NO (Normally Open)	5A@24Vdc (fused) 5A@120Vac (fused)	7923450024
24Vdc	 1CO (SPDT)	4A@30Vdc 4A@250Vac	37SM400F
24Vdc	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8660920000 8660910000
24Vdc	 1CO (SPDT)	10A@24Vdc 10A@120Vac	8530621001 8530691001
24Vdc	 NO (Normally Open)	6A@30Vdc 5A@250Vac	1101611001
24Vdc	 NC (Normally Closed)	6A@30Vdc 5A@250Vac	1100911001
24Vdc	 1CO (SPDT)	6A@30Vdc 5A@250Vac	1100210000
24Vdc	 2CO (DPDT)	10A@24Vdc 10A@120Vac	8530631001 8530701001
24Vdc	 4CO (4PDT)	6A@24Vdc 5A@120Vac	7940007063 8798740000
24Vac/dc	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8556050000 8556120000
24Vac/dc	 NO (Normally Open)	10A@24Vdc 10A@120Vac 3.5A@125Vdc	9906310000

Description	Connection Type	Dimensions (LxWxH)	Accessories	Notes / Features	Approvals
MRS 5Vdc 1CO MRZ 5Vdc 1CO	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Replacement Relay - 4061580000	CSA, cULus, CE
MC5RL 5-15VIN/AUX	Screw Clamp	PicoPak 78x6x63mm	see Accessories for DK4/5	-	CSA, cURrs, CE
MC5RL 5-15L LOGIC	Screw Clamp	PicoPak 78x6x63mm	see Accessories for DK4/5	-	CSA, cURrs, CE
MRS 12Vdc 1CO MRZ 12Vdc 1CO	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Replacement Relay - 4061610000	CSA, cULus, CE
MRS 12Vdc 1CO C1D2 MRZ 12Vdc 1CO C1D2	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Non-replacable Relay	CSA, cULus, CE, CSA C1D2
RS70 12Vdc 2CO C1D2	Screw Clamp	Rider Series 70x20.1x57.3mm	-	-	CSA C1D2
PRS 12Vdc LD 1CO PRZ 12Vdc LD 1CO	Screw Clamp Tension Clamp	PlugSeries 92x15.3x95mm PlugSeries 92x15.3x87mm	see Accessories for PlugSeries	Replacement Relay - 4058470000	CSA, cURus, CE
PRS 12Vdc LD 2CO PRZ 12Vdc LD 2CO	Screw Clamp Tension Clamp	PlugSeries 92x15.3x95mm PlugSeries 92x15.3x87mm	see Accessories for PlugSeries	Replacement Relay - 4058560000	CSA, cURus, CE
MC5R 12V/24VDC	Screw Clamp	PicoPak 78x6x63mm	see Accessories for DK4/5	-	CSA, cURrs, CE, CSA C1D2
MC5R 12/24VAC/DC	Screw Clamp	PicoPak 78x6x63mm	see Accessories for DK4/5	-	CSA, cURrs, CE
MC5R 24VDC 1CO	Screw Clamp	PicoPak 78x6x63mm	see Accessories for DK4/5	-	CSA, cURrs, CE
MRS 24Vdc 1CO MRZ 24Vdc 1CO	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Replacement Relay - 4060120000	CSA, cULus, CE
MRS 24Vdc 1CO C1D2 MRZ 24Vdc 1CO C1D2	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Non-replacable Relay Replacement Relay - 4061590000	CSA, cULus, CE, CSA C1D2
MRS 24Vdc 1CO Au MRZ 24Vdc 1CO Au	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	(Gold Plated Contacts)	cULus, CE
MC6RF 24VUC	Screw Clamp	PicoPak 89x8x71mm	Endplate - C9040396	Ouput fused @ 5A Fuse:- Wickmann type TE5	CSA
RSHV-Fused	Screw Clamp	RS70 70x16x74mm	-	Ouput fused @ 4A Fuse:- Wickmann TR5-F 19370K	CSA, CE
MRS 24Vdc ACT MRZ 24Vdc ACT	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Replacement Relay - 4060120000	cURus, CE
PRS 24Vdc LD 1CO PRZ 24Vdc LD 1CO	Screw Clamp Tension Clamp	PlugSeries 92x15.3x95mm PlugSeries 92x15.3x87mm	see Accessories for PlugSeries	Replacement Relay - 4058480000	CSA, cURus, CE
RS 30 24Vdc, NO GN	Screw Clamp	RS30 74x11.2x51.5mm	-	-	CSA, CE
RS 30 24Vdc, NC GN	Screw Clamp	RS30 74x11.2x51.5mm	-	-	CSA, CE
RS 30 24Vdc, 1CO	Screw Clamp	RS30 74x11.2x51.5mm	-	Pluggable BL/SL	CSA, CE
PRS 24Vdc LD 2CO PRZ 24Vdc LD 2CO	Screw Clamp Tension Clamp	PlugSeries 92x15.3x95mm PlugSeries 92x15.3x87mm	see Accessories for PlugSeries	Replacement Relay - 4058570000	CSA, cURus, CE
RCMKIT 24Vdc 4CO LED GN RCMKITZ 24Vdc 4CO LED GN	Screw Clamp Tension Clamp	RiderSeries 75x27x82mm RiderSeries 96x31x60mm	-	Replacement Relay - 8690200000	cURus, CE
MRS 24Vuc 1CO MRZ 24Vuc 1CO	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Replacement Relay - 4060120000	CSA, cULus, CE
HVDC 24VAC/DC	Screw Clamp	RS HVDC 70x40x100mm	-	Uses 3PST relay contacts in series	CSA

Electronics - Relays



** relay shown with optional blocker (sold separately)

Plug Series	Input	Output Configuration	Max Contact Rating	Part Number
	24Vdc (48Vdc)	 NO (Normally Open)	4A@30Vdc 4A@250Vac	7901550000
	24Vac/dc (48Vac/dc)	 NO (Normally Open)	4A@30Vdc 4A@250Vac	7901570000
	24Vdc (120Vac)	 1CO (SPDT)	2A@30Vdc 0.5A@120Vuc	9910590000
	24Vac	 1CO (SPDT)	10A@24Vdc 10A@120Vac	8536530000 8536651001
	24Vac	 2CO (DPDT)	10A@24Vdc 10A@120Vac	8536560000 8536681001
	48Vac/dc	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8556040000 8556110000
	60Vdc	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8556060000 8556130000
	115Vdc	 1CO (SPDT)	10A@24Vdc 10A@120Vac	8536510000 8536610000
	115Vdc	 2CO (DPDT)	10A@24Vdc 10A@120Vac	8536520000 8536630000
	115Vac	 NO (Normally Open)	4A@30Vdc 4A@250Vac	7901600000
	115Vac	 NO (Normally Open)	6A@30Vdc 5A@250Vac	1102111001
	120Vac	 1CO (SPDT)	5A@30Vdc 5A@250Vac	9902860000
	120Vac	 NO (Normally Open)	5A@24Vdc (fused) 5A@120Vac (fused)	7923450120
	120Vuc	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8556030000 8556100000
	120Vac	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8825970000 8825960000
	120Vac/dc	 1CO (SPDT)	6A@24Vdc 4A@120Vac	7940004783 7940004784
	120Vac	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8652030000 8652040000
	120Vac	 1CO (SPDT)	6A@24Vdc 4A@120Vdc	7940023882* 7940023881*
	120Vac	 1CO (SPDT)	10A@24Vdc 10A@120Vac	8530641001 8530710000
	120Vac	 2CO (DPDT)	10A@24Vdc 10A@120Vac	8530661001 8530720000
	120Vac	 4CO (4PDT)	6A@24Vdc 5A@120Vac	8810150000 8810080000
	230Vac	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8596050000 8596070000
	230Vac	 1CO (SPDT)	6A@24Vdc 4A@120Vac	8556020000 8556090000
	230Vac	 2CO (DPDT)	10A@24Vdc 10A@120Vac	8530681001 8530741001
	230Vac	 1CO (SPDT)	10A@24Vdc 10A@120Vac	8530671001 8530731001


Accessories	Description	Part Number
Pluggable Jumpers *		
2 Pole black	ZQV2.5N/4-2SW	1784270000
2 Pole red	ZQV2.5N/4-2RT	1784280000
2 Pole blue	ZQV2.5N/4-2BL	1784290000
Marking Tag	WS 10/5	1635000000
	WS 15/5	1609880000
Holding Clamp	PRC	8536700000
Lever Blocking Device **	Plug Series Blocker	1836880000

* other colours and pole counts also available

Rider Series



RS30



Description	Connection Type	Dimensions (LxWxH)	Accessories	Notes / Features	Approvals
MC5R 24V/48VDC	Screw Clamp	RS70 PicoPak 78x6x63mm	see Accessories for DK4/5	-	CSA, cURRs, CE
MC5R 24/48VAC/DC	Screw Clamp	PicoPak 78x6x63mm	see Accessories for DK4/5	-	CSA, cURRs, CE
PICOPAK DK6RELAY 24VDC/120VAC	Screw Clamp	PicoPak 89x8x68mm	Endplate - C9040396	-	CSA
PRS 24Vac LD 1CO PRZ 24Vac LD 1CO	Screw Clamp Tension Clamp	PlugSeries 92x15.3x95mm PlugSeries 92x15.3x87mm	see Accessories for PlugSeries	Replacement Relay - 4058510000	CSA, cURus, CE
PRS 24Vac LD 2CO PRZ 24Vac LD 2CO	Screw Clamp Tension Clamp	PlugSeries 92x15.3x95mm PlugSeries 92x15.3x87mm	see Accessories for PlugSeries	Replacement Relay - 4058600000	CSA, cURus, CE
MRS 48Vdc 1CO MRZ 48Vdc 1CO	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Replacement Relay - 4061620000	CSA, cULus, CE
MRS 60Vdc 1CO MRZ 60Vdc 1CO	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Replacement Relay - 4061630000	CSA, cURus, CE
PRS 115Vdc LD 1CO PRZ 115Vdc LD 1CO	Screw Clamp Tension Clamp	PlugSeries 92x15.3x95mm PlugSeries 92x15.3x87mm	see Accessories for PlugSeries	Replacement Relay - 4058500000	CSA, cURus, CE
PRS 115Vdc LD 2CO PRZ 115Vdc LD 2CO	Screw Clamp Tension Clamp	PlugSeries 92x15.3x95mm PlugSeries 92x15.3x87mm	see Accessories for PlugSeries	Replacement Relay - 4058590000	CSA, cURus, CE
MC5R 115VAC	Screw Clamp	PicoPak 78x6x63mm	see Accessories for DK4/5	-	cURRs, CE
RS 30 115Vac GN	Screw Clamp	RS30 74x11.2x51.5mm	-	-	CSA, CE
RSHV-AC	Screw Clamp	RS70 70x25x62mm	-	Leakage immune up to 6.5mA	CSA, CE
MC6RF 120VAC	Screw Clamp	PicoPak 89x8x71mm	Endplate - C9040396	Ouput fused @5A Fuse - Wickmann type TE5	CSA
MRS 120Vdc 1CO MRZ 120Vdc 1CO	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Replacement Relay - 4061630000 Leakage immune up to 3mA	CSA, cULus, CE
MRS 120Vac 1CO RC MRZ 120Vac 1CO RC	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Replacement Relay - 4061630000	cULus, CE
MRS 120Vdc 1CO C1D2 MRZ 120Vdc 1CO C1D2	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Non-replacable Relay Replacement Relay - 4061600000	CSA, cULus, CE, CSA C1D2
MRS 120Vdc 1CO Au MRZ 120Vdc 1CO Au	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	(Gold Plated Contacts)	cULus, CE
MRS 120Vac RC C1D2 MRZ 120Vac RC C1D2	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Leakage immune up to 3mA Non-replacement Relay	CSA, cULus, CE, CSA pending C1D2
PRS 120Vac LD 1CO PRZ 120Vac LD 1CO	Screw Clamp Tension Clamp	PlugSeries 92x15.3x95mm PlugSeries 92x15.3x87mm	see Accessories for PlugSeries	Replacement Relay - 4058520000	CSA, cURus, CE
PRS 120Vac LD 2CO PRZ 120Vac LD 2CO	Screw Clamp Tension Clamp	PlugSeries 92x15.3x95mm PlugSeries 92x15.3x87mm	see Accessories for PlugSeries	Replacement Relay - 4058610000	CSA, cURus, CE
RCMKIT 120Vac 4CO LED RT RCMKITZ 120Vac 4CO LED RT	Screw Clamp Tension Clamp	RiderSeries 75x27x82mm RiderSeries 96x31x60mm	-	Replacement Relay - 1180800000	cURus, CE
MRS 230Vac 1CO Au MRZ 230Vac 1CO Au	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Replacement Relay - 4061590000 (Gold Plated Contacts)	cULus, CE
MRS230Vac 1CO MRZ 230Vac 1CO	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm MicroSeries 94x6.1x91mm	see Accessories for MicroSeries	Replacement Relay - 4060120000	CSA, cULus, CE
PRS230Vac LD 2CO PRZ 230Vac LD 2CO	Screw Clamp Tension Clamp	PlugSeries 92x15.3x95mm PlugSeries 92x15.3x87mm	see Accessories for PlugSeries	Replacement Relay - 4058630000	CSA, cURus, CE
PRS 230Vac LD 1CO PRZ 230Vac LD 1CO	Screw Clamp Tension Clamp	PlugSeries 92x15.3x95mm PlugSeries 92x15.3x87mm	see Accessories for PlugSeries	Replacement Relay - 4058540000	CSA, cURus, CE

Electronics - Optocouplers

PicoPak DK4/5



Accessories	Description	Part Number
End plate	AP DK4	0687560000
	AP DK5	C9039986
Jumper Comb Insulated	2 Pole - QB2	0482700000
	3 Pole - QB3	0482800000
	4 Pole - QB4	0482900000
Jumper Comb Uninsulated	75 Pole straight QB75	0535200000
	75 Pole angled QB75	0526400000
Insulating cover strip	75 Pole IP75	0526700000
Marking Tag	Blank - White	DEK5/6
		1609820000

Input	Output Configuration	Output Specs	Part Number
24Vdc (11.5 to 28Vdc) 120Vac		5-30Vdc @ 100mA	9915700000
24Vdc (11.5 to 28Vdc)	 MOSFET Switching	5-34Vdc @ 10A	7901690001
24Vdc (11.5 to 28Vdc)	 MOSFET Switching	5-34Vdc @ 10A	7940000063
24Vdc		5-48Vdc @ 20mA	8028300000
24Vdc		5-48Vdc @ 500mA	8019590000
24Vdc		5VTTL @ 8mA	8228640000
24Vac/dc		5-48Vdc @ 20mA	8365940000
24Vdc		5VTTL @ 8mA	8324610000
24Vdc		5-48Vdc @ 100mA	8607340000 8607360000
24Vdc		3-33Vdc @ 2A	8607350000 8607370000
24Vdc		3-30Vdc @ 2.5A	8610840000 8610920000
24Vdc		3-30Vdc @ 5A	8610900000 8610970000
24Vdc		3-30Vac/dc @ 1A	8610890000 8610960000
24Vdc		3-33Vdc @ 2A	8676250000 8676230000
24Vdc		12-275Vac @ 2A	8610860000 8610930000
24Vdc		12-275Vac @ 4A	8610910000 8610980000
24Vdc		75-250Vac @ 1A	8652010000 8652020000
3.2-5Vdc 12-28Vdc		5-28Vdc @ 50mA	9916080000
3.5-15Vdc		5-48Vdc @ 100mA	8275390000

MicroSeries




Accessories	Description	Part Number
Pluggable jumpers*	2 Pole Red ZQV 4N / 2RT	1793950000
	3 Pole Red ZQV 4N / 3RT	1793980000
	41 Pole Red ZQV 4N / 41RT	1794070000
	2 Pole Black ZQV 4N / 2SW	1793970000
	3 Pole Black ZQV 4N / 3SW	1794000000
Marking Tag	41 Pole Black ZQV 4N / 41SW	1794090000
	Blank - White WS 12/6	1609900000

*other colours and pole counts also available

Description	Connection Type	Dimensions / Packaging Style	Accessories	Notes / Features	Approvals
PICOPAK OPTO 24/120 C/W LEAKAGE	Screw Clamp	PicoPak DK5 78x6x63mm	see Accessories for DK5	120Vac input protected up to 5mA of leakage current	CSA, cURus, CE
MC50 24VDC/5-34VDC 10A RES	Screw Clamp	MCZ 92x6x64mm	see Accessories for MCZ	Solenoid Driver - 6A rated for Inductive loads	CSA, cURus, CE, CSA C1D2, Zone 2
MCZ50 24VDC/5-34VDC 10A RES	Tension Clamp	PicoPak DK5 78x6x63mm	see Accessories for DK5	Solenoid Driver - 6A rated for Inductive loads	CSA, cURus, CE,
DKO 35 24Vdc 3KHz	Screw Clamp	PicoPak DK4 65x6x57mm	see Accessories for DK4	-	CE
DKO 35 24Vdc	Screw Clamp	PicoPak DK4 65x6x57mm	see Accessories for DK4		CE
DKO DK5 24Vdc 50KHz	Screw Clamp	PicoPak DK4 65x6x57mm	see Accessories for DK4	5Vdc Aux. Supply on output	CE
MCZO 24Vuc	Tension Clamp	MCZ 92x6x64mm	see Accessories for MCZ	-	cURus, CE
MCZO 24Vdc	Tension Clamp	MCZ 92x6x64mm	see Accessories for MCZ	5Vdc Aux. Supply on output	cURus, CE
MOS 24Vdc/24Vdc 0.1A MOZ 24Vdc/24Vdc 0.1A	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm	see Accessories for MicroSeries	Replacement opto : 4061180000	cULus, CE
MOS 24Vdc/24Vdc 2A MOZ 24Vdc/24Vdc 2A	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm	see Accessories for MicroSeries	Replacement opto : 4061190000	cULus, CE
POS 24Vdc/24Vdc 2A POZ 24Vdc/24Vdc 2A	Screw Clamp Tension Clamp	PlugOpto 92x15.3x95mm 92x15.3x87mm	see Accessories for PlugOpto	Replacement Opto : 8576350000	CSA, cURus, CE
POS 24Vdc/24Vdc 5A POZ 24Vdc/24Vdc 5A	Screw Clamp Tension Clamp	PlugOpto 92x15.3x95mm 92x15.3x87mm	see Accessories for PlugOpto	Replacement Opto : 8576350000	CSA, cURus, CE
POS 24Vdc/24Vuc 1A POZ 24Vdc/24Vuc 1A	Screw Clamp Tension Clamp	PlugOpto 92x15.3x95mm 92x15.3x87mm	see Accessories for PlugOpto	Replacement Opto : 8576380000	CSA, cURus, CE
MOS 24Vdc/24Vdc ACT MOZ 24Vdc/24Vdc ACT	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm	see Accessories for MicroSeries	Replacement Opto : 4061190000	cULus, CE
POS 24Vdc/230Vac 2A POZ 24Vdc/230Vac 2A	Screw Clamp Tension Clamp	PlugOpto 92x15.3x95mm 92x15.3x87mm	see Accessories for PlugOpto	Replacement Opto : 8576370000	CSA, cURus, CE
POS 24Vdc/230Vac 4A POZ 24Vdc/230Vac 4A	Screw Clamp Tension Clamp	PlugOpto 92x15.3x95mm 92x15.3x87mm	see Accessories for PlugOpto	Replacement Opto : 8576360000	CSA, cURus, CE
MOS 24Vdc/230Vac 1A MOZ 24Vdc/230Vac 1A	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm	see Accessories for MicroSeries	Replacement Opto : 4061210000	cULus, CE
MPI-Opto	Screw Clamp	WaveSeries 90x17.7x105.2mm	-	50Khz response time. Dual channel output + Inverted outputs	CSA, CE, CSA C1D2, Zone 2
WOS1 3.5-15Vdc 5KHz	Screw Clamp	WaveSeries 72x22x92.4mm	-	-	cURus, CE


Electronics - Optocouplers

MCZ			Input	Output Configuration	Output Specs	Part Number
			5VTTL @ 1mA min.		5-48Vdc @ 100mA	8228650000
			5VTTL @ 1mA min.		5-48Vdc @ 100mA	8398940000
			5Vdc @ 7.1 mA min.		5-48Vdc @ 100mA	8633020000 8633010000
Accessories			5Vdc @ 11 mA min.	 MOSFET Switching	3-33Vdc @ 2A	8633000000 8632990000
Endplate		ZAP				
Jumper Comb						
Insulated*						
2 Pole -		ZQV4/2	5-250Vdc		12-32Vdc @50mA	9906660000
3 Pole -		ZQV4/3				
4 Pole -		ZQV4/4				
10 Pole -		ZQV4/10				
Marking Tag			15-60Vdc		15-60Vdc @ 500mA	8237730000
Blank - White		DEK5/6				
Plug-Opto Series			16-60Vac/dc		24-230Vac @ 3.5A	8275440000
						
			120Vac/dc		5-48Vdc @ 100mA	8607690000 8607730000
			120Vac/dc		3-33Vdc @ 2A	8607700000 8607740000
			120Vac/dc		75-250Vac @1A	8651930000 8651950000
			115Vac/dc		19-28Vdc @ 5A	8296250000
			115Vac/dc		24-230Vac @ 3.5A	8259950000
Wave Series			230Vac		5-48Vdc @ 100mA	8607710000 8607750000
			230Vac		3-33Vdc @ 2A	8607720000 8607760000
			230Vac		-230Vac @ 1A	8561990000 8651970000
Accessories						
Jumper Comb Red						
2 Pole -		ZQV 2.5N/2 RT				
Jumper Comb Black						
2 Pole -		ZQV 2.5N/2 SW				
Jumper Comb Blue						
2 Pole -		ZQV 2.5N/2 BL				
Jumper Comb Yellow						
2 Pole -		ZQV 2.5N/2 GE				
Multicard for Plotter - White			WS10/5	1635000000		

Description	Connection Type	Dimensions / Packaging Style	Accessories	Notes / Features	Approvals
DKO DK5 5VTTL	Screw Clamp	PicoPak DK5 78x6x63mm	see Accessories for DK5	-	cURus, CE
MCZ O 5VTTL	Tension Clamp	MCZ 92x6x64mm	see Accessories for MCZ	-	cURus, CE
MOS 5Vdc/24Vdc 0.1A MOZ 5Vdc/24Vdc 0.1A	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm	see Accessories for MicroSeries	Replacement opto : 4064320000	cULus, CE
MOS 5Vdc/24Vdc 2A MOZ 5Vdc/24Vdc 2A	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm	see Accessories for MicroSeries	Replacement opto : 4064310000	cULus, CE
RS-40C	Screw Clamp	RS40 70x11.2x45mm	-	Input current determined by External resistor	CSA
WOS1 15-60Vdc 1KHz	Screw Clamp	WaveSeries 72x22x92.4mm	-	-	cURus, CE
WOS2 15-60Vuc	Screw Clamp	WaveSeries 72x22x112.4mm	-	-	cURus, CE
MOS 120Vuc/24Vdc 0.1A MOZ 120Vuc/24Vdc 0.1A	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm	see Accessories for MicroSeries	Replacement opto : 4061230000	cULus, CE
MOS 120Vuc/24Vdc 2A MOZ 120Vuc/24Vdc 2A	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm	see Accessories for MicroSeries	Replacement opto : 4061200000	cULus, CE
MOS 120Vuc/230Vdc 1A MOZ 120Vuc/230Vdc 1A	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm	see Accessories for MicroSeries	Replacement opto : 4061220000	cULus, CE
WOS2 115Vuc	Screw Clamp	WaveSeries 92.4x22x112.4mm	-	-	cURus, CE
WOS2 115Vuc	Screw Clamp	WaveSeries 72x22x112.4mm	-	-	cURus, CE
MOS 230Vac/24Vdc 0.1A MOZ 230Vac/24Vdc 0.1A	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm	see Accessories for MicroSeries	Replacement opto : 4061180000	cULus, CE
MOS 230Vac/24Vdc 2A MOZ 230Vac/24Vdc 2A	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm	see Accessories for MicroSeries	Replacement opto : 4061190000	cULus, CE
MOS 230Vac/230Vac 1A MOZ 230Vac/230Vac 1A	Screw Clamp Tension Clamp	MicroSeries 93x6.1x92mm	see Accessories for MicroSeries	Replacement opto : 4061220000	cULus, CE

Electronics - Delcon


Input Modules (SLI units)



Input Base (SLI units)



Input Base only: 9908910000




Input Voltage	Output Voltage	Output Current	Part Number
5Vdc	0-60Vdc	3A	SLO5CR
5Vdc	0-250Vdc	1.8A	SLO5CRA
5Vdc	0-32Vdc	10A	SLO5CRX
5Vdc	0-240Vac/dc	1.8A	SLO5IRA
5Vdc	0-230Vac	3A	SLO5TR
12Vdc	0-60Vdc	50mA	SLI12CR
12Vdc	0-60Vdc	50mA	SLI12CRI
12Vdc	0-60Vdc	3A	SLO12CR
12Vdc	0-250Vdc	1.8A	SLO12CRA
12Vdc	0-250Vdc	4A	SLO12CRA4
12Vdc	0-24Vdc	10A	SLO12CRX
24Vac	0-60Vdc	50mA	SLI25CR
24Vac	0-60Vdc	100mA	SLI25CRI
24Vdc	0-60Vdc	50mA	SLI24CR
24Vdc	0-60Vdc	50mA	SLI24CRF
24Vdc	0-60Vdc	50mA	SLI24CRI
24Vdc	0-60Vdc	50mA	SLI24CRL
24Vdc	0-60Vdc	3A	SLO24CL
24Vdc	0-60Vdc	3A	SLO24CR
24Vdc	0-250Vdc	1.8A	SLO24CRA
24Vdc	0-250Vdc	4A	SLO24CRA4
24Vdc	0-24Vdc	10A	SLO24CRX
24Vdc	0-240Vac/dc	1.2A	SLO24IRA
24Vdc	0-240Vac	3A	SLO24TH
24Vdc	0-240Vac	3A	SLO24TL
24Vdc	0-240Vac	3A	SLO24TR
48Vac	0-60Vdc	50mA	SLI49CR
48Vac	0-60Vdc	100mA	SLI49CRI
48Vdc	0-60Vdc	50mA	SLI48CR
48Vdc	0-60Vdc	30mA	SLI48CRI
48Vdc	0-250Vdc	1.8A	SLO48CRA
48Vdc	0-250Vdc	4A	SLO48CRA4
120Vac	0-60Vdc	50mA	SLI120CH
120Vac	0-60Vdc	50mA	SLI120CR
120Vac	0-60Vdc	100mA	SLI120CRI
120Vac	0-60Vdc	50mA	SLI120CRP
120Vac	0-240Vac	1A	SLOA120TR
120Vac	0-240Vac	3A	SLOP120TR

Application	Base Part Number	Switching Devices	Plug-in packaging colour *	Output Surge @ 20 secs.	Approvals
for Standard DC applications	9908920000	power MOSFET		15A	CE, cURus
for High DC voltage on O/P	9908920000	power MOSFET		8A	CE, cURus
for High DC currents	9908920000	power MOSFET		40A	CE, cURus
for High speed AC/DC switching	9908920000	back-to-back power MOSFET		8A	CE, cURus
for Standard AC applications	9908920000	Triac		90A	CE, cURus
for Standard DC applications	9908910000	transistor		-	CE, cURus
Normally Closed	9908910000	transistor		-	CE, cURus
for Standard DC applications	9908920000	power MOSFET		15A	CE, cURus
for High DC voltage on O/P	9908920000	power MOSFET		8A	CE, cURus
for High DC voltage on O/P	9908920000	power MOSFET		15A	CE, cURus
for High DC current on O/P	9908920000	power MOSFET		40A	CE, cURus
for Standard DC applications	9908910000	transistor		-	CE, cURus
Normally Closed	9908910000	transistor		-	CE, cURus
for Standard DC applications	9908910000	transistor		-	CE, cURus
for Fast DC Applications	9908910000	transistor		-	CE, cURus
Normally Closed	9908910000	transistor		-	CE, cURus
for High Leakage immunity	9908910000	transistor		-	CE, cURus
Low Input Current Draw	9908920000	transistor		15A	CE, cURus
for Standard DC applications	9908920000	power MOSFET		15A	CE, cURus
for High DC voltage on O/P	9908920000	power MOSFET		8A	CE, cURus
for High DC voltage on O/P	9908920000	power MOSFET		15A	CE, cURus
for High DC current on O/P	9908920000	power MOSFET		20A	CE, cURus
for High speed AC/DC switching with built in Snubber for Voltage spikes	9908920000	back-to-back power MOSFET		8A	CE, cURus
	9908920000	Triac		90A	CE, cURus
Low Input Current Draw	9908920000	Triac		90A	CE, cURus
for Standard AC applications	9908920000	Triac		90A	CE, cURus
for Standard DC applications	9908910000	transistor		-	CE, cURus
Normally Closed	9908910000	transistor		-	CE, cURus
for Standard DC applications	9908910000	transistor		-	CE, cURus
Normally Closed	9908910000	transistor		-	CE, cURus
for High DC voltage on O/P	9908920000	power MOSFET		8A	CE, cURus
for High DC voltage on O/P	9908920000	power MOSFET		15A	CE, cURus
Transient Protected	9908910000	transistor		-	CE, cURus
for Standard DC applications	9908910000	transistor		-	CE, cURus
Normally Closed	9908910000	transistor		-	CE, cURus
for proxy cables	9908910000	transistor		-	CE, cURus
for Standard AC applications	9908920000	Triac		90A	CE, cURus
Low Leakage currents on input	9908920000	Triac			

* Note:  DC Input  AC Input  AC Input/Specialty  DC Output  AC Output

Output Modules (SLO units)	Input Voltage	Output Voltage	Output Current	Part Number
	120Vdc	0-250Vdc	1.8A	SLO120CRA
	120Vdc	0-250Vdc	4A	SLO120CRA4
	125Vdc	0-60Vdc	50mA	SLI125CH
	125Vdc	0-60Vdc	50mA	SLI125CR
	125Vdc	0-60Vdc	30mA	SLI125CRI
	220Vdc	0-250Vdc	1.8A	SLO220CRA
	220Vdc	0-250Vdc	4A	SLO220CRA4
	230Vac	0-60Vdc	50mA	SLI230CH
	230Vac	0-60Vdc	50mA	SLI230CR
	230Vac	0-60Vdc	100mA	SLI230CRI
	230Vac	0-60Vdc	50mA	SLI230CRP
	230Vac	0-60Vdc	50ma	SLI230CRR
	230Vac	0-240Vac	1A	SLOA230TR
	230Vac	0-240Vac	1.5A	SLOP230TR
	250Vdc	0-60Vdc	50mA	SLI250CH
	250Vdc	0-60Vdc	50mA	SLI250CR
	250Vdc	0-60Vdc	30mA	SLI250CRI


Output Base only: 9908910000



D

Electronics - Analog Signal Conditioners

PicoPak (DK6)



Type



DC Current

Accessories	Description	Part Number
Endplate	AP DK6	C9040396
Jumper Comb		
Insulated	2 Pole -	QB2
	3 Pole -	QB3
	4 Pole -	QB4
Jumper Comb Uninsulated		
	58 Pole straight -	QB58
	58 Pole angled -	QB58
Insulating cover strip		
	58 Pole -	IP58
Marking Tag		
	Blank - White	DEK5/8
		1856740000

PicoPak (DK5)



Accessories	Description	Part Number
Endplate	AP DK5	C9039986
Jumper Comb		
Insulated	2 Pole -	QB2
	3 Pole -	QB3
	4 Pole -	QB4
Jumper Comb Uninsulated		
	75 Pole straight -	QB75
	75 Pole angled -	QB75
Insulating cover strip		
	75 Pole -	IP75
Marking Tag		
	Blank - White	DEK5/6
		1609820000


Input	Output	Aux. Supply	Configuration
$\pm 1\text{mA}$ to $\pm 100\text{mA}$ selectabl (eg. 4-20mA)	$\pm 20\text{mA}$, $\pm 10\text{V}$ configurable	20-230V ac/dc	
$\pm 1\text{mA}$ to $\pm 100\text{mA}$ selectable (eg. 4-20mA)	$\pm 5\text{Vdc}$ or $\pm 10\text{Vdc}$ selectable	9-30Vdc	
$\pm 1\text{mA}$ to $\pm 100\text{mA}$ selectable (eg. 4-20mA)	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA selectable	9-30Vdc	
$\pm 1\text{mA}$ to $\pm 100\text{mA}$ selectabl (eg. 4-20mA)	relay set point x2 SPDT	9-30Vdc	
0-1mA	4-20mA	Output Loop Powered	
0(4)-20mA	0(4)-20mA	Input Loop Powered	
0(4)-20mA	0(4)-20mA	24Vdc	
0(4)-20mA	0(4)-20mA	Input Loop Powered	
0(4)-20mA	0(4)-20mA	Input Loop Powered	
0(4)-20mA	0(4)-20mA	18-30Vdc	
0(4)-20mA	0(4)-20mA	18-30Vdc	
0(4)-20mA	0(4)-20mA	18-30Vdc	
0(4)-20mA	0(4)-20mA	Output Loop Powered	
0(4)-20mA	0(4)-20mA	9-30Vdc	
0(4)-20mA	0-20A, 4-20mA, 0-10V selectable frequency	24Vdc	
0(4)-20mA (x2)	0(4)-20mA (x2)	Input Loop Powered	
0(4)-20mA (x2)	0(4)-20mA (x2)	Input Loop Powered	
0-20mA	0Hz-1kHz, 4kHz, 8kHz, 16kHz selectable frequency	24Vdc	
0-20mA	4-20mA	9-30Vdc	
0-20mA	4-20mA	Output Loop Powered	
0-20mA, 4-20mA selectable	0-20A, 4-20mA, 0-10V selectable	18-30Vdc	
0-20mA, 4-20mA selectable	relay set point x2 SPDT	18-30Vdc	
4-20mA	0-10Vdc	18-30Vdc	
4-20mA	0-10Vdc	18-30Vdc	
4-20mA	0-10Vdc	18-30Vdc	
4-20mA	0-10Vdc	9-30Vdc	
4-20mA	0-20mA	9-30Vdc	
4-20mA	0-5Vdc	9-30Vdc	
4-20mA	0Hz-1kHz, 4kHz, 8kHz, 16kHz selectable	24Vdc	
4-20mA	4-20mA	Input & Output Loop Powered	
4-20mA	4-20mA	Input & Output Loop Powered	
4-20mA	4-20mA	18-30Vdc	
4-20mA	4-20mA	120Vac	
4-20mA	4-20mA	9-30Vdc	
4-20mA	4-20mA	Input Loop Powered	
4-20mA	4-20mA	Output Loop Powered	
4-20mA	4-20mA (x2)	Output Loop Powered	
4-20mA	4-20mA (x2)	Output Loop Powered	

Electronics - Analog Signal Conditioners



Part Number	Description	Connection Type	Packing Style / Dimensions	Accessories	Approvals
8560740000	WAS4 PRO DC/DC	Screw Clamp	WaveSeries		
8560750000	WAZ4 PRO DC/DC	Tension Clamp	90.0 x 12.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CE, GL
G408-1000	UPAC Analog, X-X, BiPolar Out	Screw Clamp	Ultra SlimPak 90 x 17.7 x 112.7	Heak Sink	CSA, UL, CE
G408	UPAC Analog, X-X, UniPolar Out	Screw Clamp	Ultra SlimPak 90 x 17.7 x 112.7	Heak Sink	CSA, UL, CE
G108	UPAC ALARM DC X-X	Screw Clamp	Ultra SlimPak 90 x 17.7 x 112.7	Heak Sink	CSA, UL, CE
7940005523	DECIPAK 0-1MA		DeciPak		
Old # 992061	4-20MA/24V 2W	Screw Clamp	75.5 x 22.5 x 119.0	-	cURus, CE
8411190000	MCZ CCC	Tension Clamp	MCZ 91.0x6.0x71.0 Add 1.5mm for end plate	see Accessories MCZ	CSA, cULus, CE
8721150000	MAS RPS	Screw Clamp	MicroSeries 88.0 x 6.1 x 98.0	ZQV Jumpers	cULus, CE
8444950000	WAS5 CCC LP	Screw Clamp	WaveSeries		
8444960000	WAZ5 CCC LP	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CSA, CE
8444950000C1D2	WAS5 CCC LP	Screw Clamp	WaveSeries		cULus, CSA, CE,
8444960000C1D2	WAZ5 CCC LP	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	CSA Class 1 Div 2
8445070000	WAS4 CCC	Screw Clamp	WaveSeries		
8445080000	WAZ4 CCC	Tension Clamp	90.0 x 12.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CSA, CE
8447160000	WAS5 CCC HF	Screw Clamp	WaveSeries		
8447170000	WAZ5 CCC HF	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CSA, CE
8540180000	WAS5 CCC	Screw Clamp	WaveSeries		
8540190000	WAS5 CCC	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CSA, CE
8543720000	WAS5 OLP	Screw Clamp	WaveSeries		
8543730000	WAZ5 OLP	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CSA, CE
7940005488	DECIPAK 0-20MA		DeciPak		
Old # 992028	0-20MA/24V 4W	Screw Clamp	75.5 x 22.5 x 119.0	-	cURus, CE
8721170000	MAS RPSH	Screw Clamp	MicroSeries 88.0 x 6.1 x 98.0	ZQV Jumpers	cULus, CE
8463580000	WAS5 CCC LP 2CH.	Screw Clamp	WaveSeries		
8463590000	WAZ5 CCC LP 2CH.	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CSA, CE
8463580000C1D2	WAS5 CCC LP 2CH. C1D2	Screw Clamp	WaveSeries		cULus, CSA, CE,
8463590000C1D2	WAZ5 CCC LP 2CH. C1D2	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	CSA Class 1 Div 2
8461480000	MCZ CFC 0-20MA	Tension Clamp	MCZ 91x6.0x71.0 Add 1.5mm for end plate	see Accessories MCZ	cRUus, CE
7940005485	DECIPAK 0-20MA		DeciPak		
Old # 992025	4-20MA/24V 4W	Screw Clamp	75.5 x 22.5 x 119.0	-	cURus, CE
7940005524	DECIPAK 0-20MA		DeciPak		
Old # 992062	4-20MA/24V 2W	Screw Clamp	75.5 x 22.5 x 119.0	-	cURus, CE
8594810000	MAS DC/DC SELECT	Screw Clamp	MicroSeries		
8594840000	MAZ DC/DC SELECT	Tension Clamp	88.0 x 6.1 x 98.0	ZQV Jumpers	cULus, CE
8543820000	WAS5 WAVEANALOG DC/ALARM	Screw Clamp	WaveSerie		
8543880000	WAZ5 WAVEANALOG DC/ALARM	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CSA, CE
8445040000	WAS4 CCVC DC	Screw Clamp	WaveSeries		
8445050000	WAZ4 CVC DC	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CSA, CE
8447280000	WAS5 CVC HF	Screw Clamp	WaveSeries		
8447290000	WAZ5 CVC HF	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CSA, CE
8540230000	WAS5 CVC DC	Screw Clamp	WaveSeries		
8540240000	WAZ5 CVC DC	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CSA, CE
7940005478	DECIPAK 4-20MA		DeciPak		
Old # 992019	0-10V/24V 4W	Screw Clamp	75.5 x 22.5 x 119.0	-	cURus, CE
7940005476	DECIPAK 4-20MA		DeciPak		
Old # 992016	0-20MA/24V 4W	Screw Clamp	75.5 x 22.5 x 119.0	-	cURus, CE
7940005482	DECIPAK 4-20MA		DeciPak		
Old # 992022	0-5V/24V 4W	Screw Clamp	75.5 x 22.5 x 119.0	-	cURus, CE
8461490000	MCZ CFC 4-20MA CLP	Tension Clamp	MCZ 91x6.0x71.0 Add 1.5mm for end plate	see Accessories MCZ	cURus, CE
9908800000	PICOPAK I/I	Screw Clamp	PicoPak (DK6) 88.4x8.0x78.5 Add 1.5mm for end plate	see Accessories DK6	CSA, CE, CSA Class 1 Div 2, Zone 2
9916010000	PICOPAK MCZ I/I	Tension Clamp	MCZ 91x6.0x71.0 Add 1.5mm for end plate	see Accessories MCZ	CSA, CE
8444980000	WAS4 CCC DC	Screw Clamp	WaveSeries		
8444990000	WAZ4 CCC DC	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CSA, CE
7940005471	DECIPAK 4-20MA		DeciPak		
Old # 992011	4-20MA/120V 4W	Screw Clamp	75.5 x 22.5 x 119.0	-	cURus, CE
7940005473	DECIPAK 4-20MA		DeciPak		
Old # 992013	4-20MA/24V 4W	Screw Clamp	75.5 x 22.5 x 119.0	-	cURus, CE
7940005521	DECIPAK 4-20/4-20		DeciPak		
Old # 992059	LOOP POWERED	Screw Clamp	75.5 x 22.5 x 119.0	-	cURus, CE
7940005522	DECIPAK 4-20MA		DeciPak		
Old # 992060	4-20MA/24V 2W	Screw Clamp	75.5 x 22.5 x 119.0	-	cURus, CE
7920400000	WAVEPAK LOOP SPLITTER	Screw Clamp	WaveSeries 90.0 x 12.5 x 113.0	-	CSA, CE, CSA Class 1 Div 2, Zone 2
8581160000	WAS5 CCC 2OLP	Screw Clamp	WaveSeries		
8581170000	WAZ5 CCC 2OLP	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CSA, CE

Electronics - Analog Signal Conditioners

MCZ




Accessories	Description	Part Number
Endplate	ZAP	8389030000
Jumper Comb Insulated	2 Pole - ZQV4/2	1608950000
	3 Pole - ZQV/3	1608960000
	4 Pole - ZQV/4	1608970000
	5 Pole - ZQV/5	1608980000
	6 Pole - ZQV/6	1608990000
	7 Pole - ZQV/7	1609000000
	8 Pole - ZQV/8	1609010000
	9 Pole - ZQV/9	1609020000
	10 Pole - ZQV/10	1609030000
Marking Tag	Blank - White DEK5/6	1609820000



Type	Input	Output	Aux. Supply	Configuration
DC Current	500mA-2.5A	Single Relay NO/NC	24Vdc	
	500mA-6.5A	Single Relay NO/NC	24Vdc	
	2A-4A	Single Relay NO/NC	24Vdc	
	4.5A-10A	Single Relay NO/NC	24Vdc	
Type	Input	Output	Aux. Supply	Configuration
DC Voltage	±10mVdc to ±100Vdc selectable	+5Vdc or +10Vdc selectable	9-30Vdc	
	±10mVdc to ±100Vdc selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA selectable	9-30Vdc	
	±10mVdc to ±200Vdc selectable	relay set point x2 SPDT	9-30Vdc	
	±1mV to ±200V selectable (eg. 0-10Vdc)	+20mA, +10V configurable	20-230V ac/dc	
	0-100mVdc	4-20mA	Output Loop Powered	
	0-10mVdc	4-20mA	Output Loop Powered	
	0-10Vdc	0-10Vdc	18-30Vdc	
	0-10Vdc	0-10Vdc	18-30Vdc	
	0-10Vdc	0-10Vdc	18-30Vdc	
	0-10Vdc	0-5Vdc	9-30Vdc	
	0-10Vdc	0Hz-1kHz, 4kHz, 8kHz, 16kHz selectable	24Vdc	
	0-10Vdc	0Hz-1kHz, 4kHz, 8kHz, 16kHz selectable	24Vdc	
	0-10Vdc	4-20mA	18-30Vdc	
	0-10Vdc	4-20mA	18-30Vdc	
	0-10Vdc	4-20mA	9-30Vdc	
	0-10Vdc	4-20mA	Output Loop Powered	

MicroSeries



Accessories	Description	Part Number
Jumper Comb Red	2 Pole - ZQV 4N/2 RT	1793950000
	3 Pole - ZQV 4N/3 RT	1793980000
	4 Pole - ZQV 4N/4 RT	1794010000
	10 Pole - ZQV 4N/10 RT	1794040000
Jumper Comb Blue	41 Pole - ZQV 4N/41 RT	1794070000
	2 Pole - ZQV 4N/2 BL	1793960000
	3 Pole - ZQV 4N/3 BL	1793990000
	4 Pole - ZQV 4N/4 BL	1794020000
	10 Pole - ZQV 4N/10 BL	1794050000
	41 Pole - ZQV 4N/41 BL	1794080000
Marking Tag	Blank - White WS10/6	1828450000



Type	Input	Output	Aux. Supply	Configuration
RTD	Pt100, Pt500, Pt1000, Cu10, Cu100, Ni120 or NiFe604 selectable	relay set point x2 SPDT	9-30Vdc	
	Pt100, Pt500, Pt1000, Cu10, Cu25, Cu100 selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA selectable	9-30Vdc	
	Pt100 -200°C to +850°C, Ni100 -60°C to +250°C configurable	0-20mA, 4-20mA, 0-10Vdc selectable	18-30Vdc	
	Pt100 -200°C to +850°C, Ni100 -60°C to +250°C configurable	0-20mA, 4-20mA, 0-10Vdc selectable	18-30Vdc	
	Pt100 -40 to +100° C	4-20mA	Output Loop Powered	
	Pt100 -50 to +150° C	4-20mA	Output Loop Powered	
	Pt100 0 to +100° C	4-20mA	Output Loop Powered	
	Pt100 0 to +100° C	0-20mA, 4-20mA, 0-5Vdc, 0-10Vdc selectable	19-30Vdc	
	Pt100 0 to +120° C	4-20mA	Output Loop Powered	

Electronics - Analog Signal Conditioners

Part Number	Description	Connection Type	Packing Style / Dimensions	Accessories	Approvals
8742610000	PAS CMR 0.52.5A DC	Screw Clamp	PlugControl 92 x 15.3 x 95	-	CE, cULus
9916450000	DC CURRENT SENSOR + AMP	Screw Clamp	WaveSeries 72.0 x 22.5 x 92.4	-	CE
8742620000	PAS CMR 2.05.0 A DC	Screw Clamp	PlugControl 92 x 15.3 x 95	-	CE, cULus
8742630000	PAS CMR 4.510A DC	Screw Clamp	PlugControl 92 x 15.3 x 95	-	CE, cULus
Part Number	Description	Connection Type	Packing Style / Dimensions	Accessories	Approvals
G408-1000	UPAC Analog, X-X, BiPolar Out	Screw Clamp	Ultra SlimPak 90 x 17.7 x 112.7	Heak Sink	CSA, UL, CE
G408	UPAC Analog, X-X, UniPolar Out	Screw Clamp	Ultra SlimPak 90 x 17.7 x 112.7	Heak Sink	CSA, UL, CE
G108	UPAC ALARM DC X-X	Screw Clamp	Ultra SlimPak 90 x 17.7 x 112.7	Heak Sink	CSA, UL, CE
8560740000	WAS4 PRO DC/DC	Screw Clamp	WaveSeries		
8560750000	WAZ4 PRO DC/DC	Tension Clamp	90.0 x 12.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CE, GL
7940005531	DECIPAK 0-100MV//		DeciPak		
Old # 992070	4-20MA/24V 2W	Screw Clamp	75.5 x 45.0 x 119.0	-	cURus, CE
7940005529	DECIPAK 0-10MV//		DeciPak		
Old # 992067	4-20MA/24V 2W	Screw Clamp	75.5 x 45.0 x 119.0	-	cURus, CE
8447130000	WAS4 VVC DC	Screw Clamp	WaveSeries		
8447140000	WAZ4 VVC DC	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CE, GL
8447370000	WAS5 VCC HF	Screw Clamp	WaveSeries		
8447380000	WAZ5 VCC HF	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CE, GL
8540330000	WAS5 VVC DC	Screw Clamp	WaveSeries		
8540340000	WAZ5 VVC DC	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CE, GL
7940005508			DeciPak		
Old # 992046	DECIPAK 0-10V/0-5V/24V 4W	Screw Clamp	75.5 x 45.0 x 119.0	-	cURus, CE
8242040000	DK U-F DK5 0-10V	Screw Clamp	PicoPak (DK6) 88.4x8.0x78.5 Add 1.5mm for end plate	see Accessories DK6	cURus, CE
8461470000	MCZ VFC 0-10V	Tension Clamp	MCZ 91x6.0x71.0 Add 1.5mm for end plate	see Accessories MCZ	cURus, CE
8447100000	WAS4 VCC DC	Screw Clamp	WaveSeries		
8447110000	WAZ4 VCC DC	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CE, GL
8447340000	WAS5 VCC HF	Screw Clamp	WaveSeries		
8447350000	WAZ5 VCC HF	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CE, GL
8540290000	WAS5 VCC DC	Screw Clamp	WaveSeries		
8540300000	WAZ5 VCC DC	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CE, GL
7940005499	DECIPAK 0-10V//		DeciPak		
Old # 992037	4-20MA/24V 4W	Screw Clamp	75.5 x 45.0 x 119.0	-	cURus, CE
7940005528	DECIPAK 0-10V//		DeciPak		
Old # 992066	4-20MA/24V 2W	Screw Clamp	75.5 x 45.0 x 119.0	-	cURus, CE
8543820000	WAS5 WAVEANALOG DC/ALARM	Screw Clamp	WaveSeries		
8543880000	WAZ5 WAVEANALOG DC/ALARM	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CE, GL
8019640000	DKSC 0-10V IN/ 2 SET POINT OUT	Screw Clamp	PicoPak (DK5) 78.0x6.0x60.5 Add 1.5mm for end plate	see Accessories DK5	cURus, CE
8260280000	MCZ SC 0-10VDC SET POINT	Tension Clamp	PicoPak (MCZ) 91.0x6.0x71.0 Add 1.5mm for end plate	see Accessories MCZ	cURus, CE
9916340000	WAVEPAK 0-300VDC/ 4-20MA/24V 3W	Screw Clamp	WaveSeries 72.5 x 22.5 x 91.5	-	CSA, CE
Part Number	Description	Connection Type	Packing Style / Dimensions	Accessories	Approvals
G118	UPAC RTD input, Setpoint Relay Out	Screw Clamp	Ultra SlimPak 90 x 17.7 x 112.7	Heak Sink	CSA, UL, CE
G418	UPAC RTD input, Analogue UniPolar Out	Screw Clamp	Ultra SlimPak 90 x 17.7 x 112.7	Heak Sink	CSA, UL, CE
8560700000	WAS5 WAVEPRO RTD	Screw Clamp	WaveSeries		
8560710000	WAZ5 WAVEPRO RTD	Tension Clamp	90.0 x 17.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CE, GL
8560700000C1D2	WAS5 WAVEPRO RTD C1D2	Screw Clamp	WaveSeries		
8560710000C1D2	WAZ5 WAVEPRO RTD C1D2	Tension Clamp	90.0 x 12.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CE, GL, CSA C1D2 Zone 2, UL Zone 2
8604430000	MCZ PT100/3 CLP -40 to +100	Tension Clamp	PicoPak (MCZ) 91.0x6.0x71.0 Add 1.5mm for end plate	see Accessories for MCZ	cURus, CE
8473000000	MCZ PT100/3 CLP -50 to +150	Tension Clamp	PicoPak (MCZ) 91.0x6.0x71.0 Add 1.5mm for end plate	see Accessories for MCZ	cURus, CE
8425720000	MCZ PT100/3 CLP 0-100C	Tension Clamp	PicoPak (MCZ) 91.0x6.0x71.0 Add 1.5mm for end plate	see Accessories for MCZ	cURus, CE
8594820000	MAS PT100 0...100C Output Select	Screw Clamp	MicroSeries		
8594850000	MAZ PT100 0-100C Output Select	Tension Clamp	88.0 x 6.1 x 98.0	ZQV Jumpers	cULus, CE
8483680000	MCZ PT100/3 CLP 0-120 DEG C	Tension Clamp	PicoPak (MCZ) 91.0x6.0x71.0 Add 1.5mm for end plate	see Accessories for MCZ	cURus, CE

Electronics - Analog Signal Conditioners

WaveSeries	Type	Input	Output	Aux. Supply	Configuration
	 RTD	Pt100 0 to +150° C	4-20mA	Output Loop Powered	
		Pt100 0 to +200° C	4-20mA	Output Loop Powered	
		Pt100 0 to +300° C	4-20mA	Output Loop Powered	
		Pt100 2 wire selectable -200 to +800 deg C	0(4)-20mA	19-30Vdc	
		Pt100 2 wire selectable -200 to +800 deg C	0-10Vdc	19-30Vdc	
		Pt100 3 wire selectable -200 to +800 deg C	0(4)-20mA	19-30Vdc	
		Pt100 3 wire selectable -200 to +800 deg C	0-10Vdc	19-30Vdc	
		Pt1004 wire selectable -200 to +800 deg C	0(4)-20mA	19-30Vdc	
		Pt100 4 wire selectable -200 to +800 deg C	0-10Vdc	19-30Vdc	
		Pt1000 -200°C to +850°C, Ni1000 -60°C to +250° configurable	0-20mA, 4-20mA, 0-10Vdc selectable	18-30Vdc	
		Cu10, Cu25, Cu50, Cu100 -200° to +260°C	0-20mA, 4-20mA, 0-10Vdc selectable	18-30Vdc	

Accessories	Description	Part Number	Type	Input	Output	Aux. Supply	Configuration	
Jumper Comb Red	2 Pole - ZQV 2.5N/2 RT	1717900000	 Thermocouple	Type K, J, E, N, R, S, B DIP switch selectable	0-20mA, 4-20mA, 0-10Vdc	18-30Vdc		
Jumper Comb Black	2 Pole - ZQV 2.5N/2 SW	1718080000		Type K, J, E, N, R, S, B DIP switch selectable	0-20mA, 4-20mA, 0-10Vdc	18-30Vdc		
Jumper Comb Blue	2 Pole - ZQV 2.5N/2 BL	1717990000		Type J: -210 to 780°C Type K: -270 to 1372°C Type E: -270 to 1000°C Type T: -270 to 390°C Type R: 0 to 1760°C Type S: 0 to 1750°C Type B: 0 to 1820°C selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA Selectable	9-30Vdc		
Jumper Comb Yellow	2 Pole - ZQV 2.5N/2 GE	1693800000		Type J: -210 to 780°C Type K: -270 to 1372°C Type E: -270 to 1000°C Type T: -270 to 390°C Type R: 0 to 1760°C Type S: 0 to 1750°C Type B: 0 to 1820°C selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA Selectable	9-30Vdc		
Marking Tag	White WS10/5	1635000000		Type J: -210 to 780°C Type K: -270 to 1372°C Type E: -270 to 1000°C Type T: -270 to 390°C Type R: 0 to 1760°C Type S: 0 to 1750°C Type B: 0 to 1820°C selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA Selectable	9-30Vdc		
DeciPak				Type J: -210 to 780°C Type K: -270 to 1372°C Type E: -270 to 1000°C Type T: -270 to 390°C Type R: 0 to 1760°C Type S: 0 to 1750°C Type B: 0 to 1820°C selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA Selectable	9-30Vdc		
				Type J: -210 to 780°C Type K: -270 to 1372°C Type E: -270 to 1000°C Type T: -270 to 390°C Type R: 0 to 1760°C Type S: 0 to 1750°C Type B: 0 to 1820°C selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA Selectable	9-30Vdc		
				Type J: -210 to 780°C Type K: -270 to 1372°C Type E: -270 to 1000°C Type T: -270 to 390°C Type R: 0 to 1760°C Type S: 0 to 1750°C Type B: 0 to 1820°C selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA Selectable	9-30Vdc		
				Type J: -210 to 780°C Type K: -270 to 1372°C Type E: -270 to 1000°C Type T: -270 to 390°C Type R: 0 to 1760°C Type S: 0 to 1750°C Type B: 0 to 1820°C selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA Selectable	9-30Vdc		
				Type J: -210 to 780°C Type K: -270 to 1372°C Type E: -270 to 1000°C Type T: -270 to 390°C Type R: 0 to 1760°C Type S: 0 to 1750°C Type B: 0 to 1820°C selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA Selectable	9-30Vdc		

Accessories	Description	Part Number	Type	Input	Output	Aux. Supply	Configuration
Marking Tag	Blank - White	DEK5/6.5	 Potentiometer	0-100Ω to 0-100kΩ 3 wire selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA selectable	9-30Vdc	
				<100kΩ 3 wire selectable 0-450Ω 2 wire selectable	0-20mA, 4-20mA, 0-10Vdc selectable	18-30Vdc	
				<100kΩ 3 wire selectable 0-450Ω 2 wire selectable	0-20mA, 4-20mA, 0-10Vdc selectable	18-30Vdc	
				>1kΩ 3 wire selectable <100kΩ 3 wire selectable 0-4500Ω 2 wire selectable	4-20mA 0-20mA, 4-20mA, 0-10Vdc selectable	Output Loop Powered 18-30Vdc	
				>1kΩ 3 wire selectable <100kΩ 3 wire selectable 0-4500Ω 2 wire selectable	4-20mA 0-20mA, 4-20mA, 0-10Vdc selectable	18-30Vdc	
				>1kΩ 3 wire selectable <100kΩ 3 wire selectable 0-4500Ω 2 wire selectable	4-20mA 0-20mA, 4-20mA, 0-10Vdc selectable	18-30Vdc	
Accessories	Description	Part Number	Type	Input	Output	Aux. Supply	Configuration
Marking Tag	Blank - White	DEK5/6.5	 Bridge/Strain	±5mV to ±200mVdc selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA selectable	18-30Vdc	
				0 to 200mV ±500mV selectable	0-5Vdc, 0-10Vdc, 0-20mA, 4-20mA selectable	18-30Vdc	

Electronics - Analog Signal Conditioners

Part Number	Description	Connection Type	Packing Style / Dimensions	Accessories	Approvals
8604420000	MCZ PT100/3 CLP 0-150	Tension Clamp	PicoPak (MCZ) 91.0x6.0x 71.0	see Accessories for MCZ	cURus, CE
	DEG C		Add 1.5mm for end plate		
8473010000	MCZ PT100/3 CLP 0-200	Tension Clamp	PicoPak (MCZ) 91.0x6.0x 71.0	see Accessories for MCZ	cURus, CE
	DEG C.		Add 1.5mm for end plate		
8473020000	MCZ PT100/3 CLP 0-300	Tension Clamp	PicoPak (MCZ) 91.0x6.0x 71.0	see Accessories for MCZ	cURus, CE
	DEG C		Add 1.5mm for end plate		
8432210000	WTS PT100/2 C	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE,
8432220000	WTZ PT100/2 C	Tension Clamp	90.0 x 17.5 x 113.0		
8432180000	WTS4 PT 100/2 V	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE,
8432190000	WTZ4 PT 100/2 V	Tension Clamp	90.0 x 17.5 x 113.0		
8432150000	WTS4 PT 100/3 C	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE,
8432160000	WTZ4 PT 100/3 C	Tension Clamp	90.0 x 17.5 x 113.0		
8432090000	WTS4 PT 100/3 V	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
8432130000	WTZ4 PT 100/3 V	Tension Clamp	90.0 x 17.5 x 113.0		
8432270000	WTS4 PT 100/4 C	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
8432280000	WTZ4 PT 100/4 C	Tension Clamp	90.0 x 17.5 x 113.0		
8432240000	WTZ4 PT 100/4 V	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
8432250000	WTZ4 PT 100/4 V	Tension Clamp	90.0 x 17.5 x 113.0		
8679490000	WAS PRO RTD PT1000	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
			90.0 x 17.5 x 113.0		
8638950000	WAS PRO RTD Cu	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
			90.0 x 17.5 x 113.0		
Part Number	Description	Connection Type	Packing Style / Dimensions	Accessories	Approvals
8560720000	WAS5 PRO Thermo	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
8560730000	WAZ5 PRO Thermo	Tension Clamp	90.0 x 17.5 x 113.0		
8560720000C1D2	WAS5 PRO Thermo C1D2	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
8560730000C1D2	WAZ5 PRO Thermo C1D2	Tension Clamp	90.0 x 17.5 x 113.0		
G128	UPAC Thermo input, Setpoint Relay Out	Screw Clamp	Ultra SlimPak	Heak Sink	CSA, UL, CE
			90 x 17.7 x 112.7		
G428	UPAC Thermo input, Analogue UniPolar Out	Screw Clamp	Ultra SlimPak	Heak Sink	CSA, UL, CE
			90 x 17.7 x 112.7		
8432300000	WTS4 Thermo Select	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
8432310000	WTZ4 Thermo Select	Tension Clamp	90.0 x 12.5 x 113.0	ZQV 2-Pole Jumpers	cULus, CE
8615210000	MAS Thermo-J Output Select	Screw Clamp	MicroSeries	ZQV Jumpers	cULus, CE
8615240000	MAZ Thermo-J Output Select	Tension Clamp	88.0 x 6.1 x 98.0	ZQV Jumpers	cULus, CE
8594830000	MAS Thermo-K Output Select	Screw Clamp	MicroSeries	ZQV Jumpers	cULus, CE
8594860000	MAZ Thermo-K Output Select	Tension Clamp	88.0 x 6.1 x 98.0	ZQV Jumpers	cULus, CE
Part Number	Description	Connection Type	Packing Style / Dimensions	Accessories	Approvals
G438	UPAC Potentiometer input, Analogue UniPolar Out	Screw Clamp	Ultra SlimPak	Heak Sink	CSA, UL, CE
			90 x 17.7 x 112.7		
8560700000	WAS5 WAVEPRO RTD	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE, GL
			90.0 x 12.5 x 113.0		
8560710000	WAZ5 WAVEPRO RTD	Tension Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE, GL, CSA C1D2
			90.0 x 12.5 x 113.0		
8560700000C1D2	WAS5 WAVEPRO RTD C1D2	Screw Clamp	PicoPak (DK5) 78.0 x 6.0 x 60.5	See Accessories DK5	Zone 2, UL Zone 2
			Add 1.5mm for end plate		
8560710000C1D2	WAZ5 WAVEPRO RTD C1D2	Tension Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
			90.0 x 17.5 x 113.0		
9908810000	PICOPAK 3	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
			90.0 x 17.5 x 113.0		
8679490000	WAS5 PRO RTD 1000	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
			90.0 x 17.5 x 113.0		
Part Number	Description	Connection Type	Packing Style / Dimensions	Accessories	Approvals
G448	UPAC Bridge input, Analogue UniPolar Out	Screw Clamp	Ultra SlimPak	Heak Sink	CSA, UL, CE
			90 x 17.7 x 112.7		
8581200000	WAS5 PRO Bridge	Screw Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
			90.0 x 17.5 x 113.0		
8581210000	WAZ5 PRO Bridge	Tension Clamp	WaveSeries	ZQV 2-Pole Jumpers	cULus, CE
			90.0 x 17.5 x 113.0		

Electronics - Analog Signal Conditioners

Ultra SlimPak (UPAC)



Type	Input	Output	Aux. Supply	Configuration
 Frequency	0-2Hz to 0-10kHz selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA selectable	18-30Vdc	
	0-1Hz to 0-1MHz	Frequency division 1 to 240 times	24Vdc	
	0-100kHz	0-20mA 4-20mA 0-10Vdc selectable	18-30Vdc	
	0 to 50Hz/100Hz/ 500Hz/1kHz/5kHz/ 10kHz/16kHz selectable	0-10Vdc	24Vdc	
	0 to 50Hz/100Hz/ 500Hz/1kHz/5kHz/ 10kHz/16kHz selectable	0(4)-20mA	24Vdc	

Accessories	Description	Part Number	Type	Input	Output	Aux. Supply	Configuration
Heat sink (1.6mm wide)	-	HS01-A	 AC Current	0-10mA to 0-100mA selectable	set point Relay 2x SPDT	18-30Vdc	
Shunt Resistor (for use with external current transformer)	-	C006		0-10mA to 0-100mA selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA Selectable	18-30Vdc	
Marking Tag				1/5/10A selectable	relay set point SPDT	18-30Vdc	
Blank Strips- White	DEK 5/5	0473360000		1/5/10A selectable	0-20mA, 4-20mA, 0-10Vdc selectable	18-30Vdc	
Preprinted for multi-purpose USP versions	DEK 5/5 (preprinted)	1609800000		1/5/10A selectable	4-20mA	Output Loop Powered	
				0-5A	4-20mA	Output Loop Powered	
				20/40/60A selectable	relay set point SPDT	18-30Vdc	
				0.25A-25A	relay set point SPDT	18-30Vdc	

Type	Input	Output	Aux. Supply	Configuration
 AC/DC Current	5A/10A selectable	0-20mA, 4-20mA, 0-10Vdc selectable	18-30Vdc	
	20A/25A/30A selectable	0-20mA, 4-20mA, 0-10Vdc selectable	18-30Vdc	
	40A/50A/60A selectable	0-20mA, 4-20mA, 0-10Vdc selectable	18-30Vdc	

Type	Input	Output	Aux. Supply	Configuration
 AC Voltage	0-100mV to 0-200V selectable	relay set point x2 SPDT	9-30Vdc	
	0-100mV to 0-200V selectable	0-5Vdc, 0-10Vdc, 0-1mA, 0-20mA, 4-20mA Selectable	9-30Vdc	
	0-30V/70V/130V/250V/450V selectable	0-20mA, 4-20mA	1	
	1 Phase	0-10Vdc selectable	8-30Vdc	
	0-70V/140V/210V/260V selectable	relay set point SPDT	1	
	3 Phase	Set point Relay	8-30Vdc	
	0-250V/400V selectable	2x SPDT	1	
			8-30Vdc	

Electronics

D

Electronics - Power Supplies

Single Phase	0.5A	1A	2.3A	6.5A	12.5
Advanced Features Power Supplies					
Input Voltage	85 - 264Vac / 120 - 300Vdc	85 - 264Vac / 120 - 300Vdc	85 - 264Vac / 120 - 300Vdc	85 - 138Vac / 195 - 250Vac Selectable	85 - 264Vac / 100 - 200Vdc
Output Voltage	24Vdc	24Vdc	24Vdc	24Vdc	24Vdc
Output Current	0.5A	1A	2.3A	6.5A	12.5A
Output Surge / Time	—	—	—	13A / 1 sec	18.5A / 300mS
Efficiency	80%	78%	80%	85%	80%
Operating Temp	-40°C - +50°C (-40°F - +122°F)	-20°C - +50°C (-4°F - +122°F)	-40°C - +50°C (-40°F - +122°F)	-20°C - +50°C (-4°F - +122°F)	-20°C - +50°C (-4°F - +122°F)
Features	Jumperable output, pluggable connectors	Plastic housing, output LED, compact size	Pluggable connectors, robust metal housing	Pluggable connectors, status relay, robust metal housing, built-in load sharing	Pluggable connectors, status relay, robust metal housing, analogue outputs, Active PFC, built-in load sharing
Dimensions (LxWxH)	90 x 18 x 112.5mm 3.54 x 0.71 x 4.43"	90.5 x 52 x 62.5mm 3.56 x 2.05 x 2.46"	98 x 57 x 131mm 3.86 x 2.24 x 5.16"	127 x 57 x 175mm 5 x 2.24 x 6.9"	104 x 240 x 155mm 4.1 x 9.45 x 6.1"
Part Number	9918840024	9928890024	9927480024	9925340024	9916250024
Type	CP SNT 12W	CP SNT 24W	CP SNT 55W	CP SNT 160W	CP SNT 300W
Approvals	CSA, UL 508 Listed, CE	CSA, UL 508 Listed, CE, UL 1310 (Class 2) for 992889 0024, CSA Class 1 Div. 2 and Zone 2 for 992889 0024 and 992889 0012	CSA, UL 508 Listed, CE, UL 1310 (Class 2) for 992748 0024, CSA Class 1 Div. 2 and Zone 2 for 992748 0024 and 992748 0012	CSA, UL 508 Listed, CE, CSA Class 1 Div. 2 and Zone 2 for 992534 0024 & 9925340012	CSA, UL 508 Listed, CE, CSA Class 1 Div 2 & Zone 2 pending
Other Voltage Variants		5Vdc @ 2A 9928890005 12Vdc @ 1.5A 9928890012 15Vdc @ 1.5A 9928890015 28Vdc @ 1A 9928890028	5Vdc @ 3A 9927480005 12-15Vdc @ 3A 9927480012 48Vdc @ 1.04A 9927480048	5Vdc @ 10A 9925340005 12-15Vdc @ 10A 9925340012 48Vdc @ 3.25A 9925340048	
Three Phase	2.3A	6.5A	12.5A	25A	40A
Advanced Features Power Supplies					
Input Voltage	342 - 528Vac Three phase	342 - 528Vac Three phase	342 - 528Vac Three phase	342 - 528Vac Three phase	342 - 528Vac Three phase
Output Voltage	24Vdc	24Vdc	24Vdc	24Vdc	24Vdc
Output Current	2.3A	6.5A	12.5A	25A	40A
Output Surge / Time	10A / 180mS	13A / 1sec	19A / 1sec	50A / 1sec	80A / 1 sec
Efficiency	85%	83%	80%	88%	90%
Operating Temp	-15°C - +50°C (5°F - +122°F)	-20°C - +50°C (-4°F - +122°F)	-0°C - +50°C (32°F - +122°F)	-10°C - +50°C (-14°F - +122°F)	-10°C - +50°C (-14°F - +122°F)
Features	Pluggable connectors, robust metal housing	Pluggable connectors, status relay, robust metal housing, built-in load sharing	Pluggable connectors, status relay, robust metal housing, built-in load sharing	Pluggable connectors, status relay, robust metal housing, analogue outputs, built-in load sharing	Pluggable connectors, status relay, robust metal housing, analogue outputs, built-in load sharing
Dimensions (LxWxH)	108 x 60 x 168mm 4.25 x 2.36 x 6.61"	138.2 x 58.4 x 177.8mm 5.44 x 2.3 x 7"	170 x 82 x 160mm 6.7 x 3.2 x 6.3"	173 x 238 x 135mm 6.8 x 9.4 x 5.3"	182 x 268 x 133mm 7.2 x 10.6 x 5.3"
Part Number	9917790324	9925340324	7924740324	7920210324	7918960324
Type	CP SNT 55W 2.3A 3 Phase	CP SNT 160W 6.5A 3 Phase	CP SNT 300W 12.5A 3 Phase	CP SNT 600W 25A 3 Phase	CP SNT 1000W 40A 3 Phase
Approvals	CSA, UL 508 Listed, CE	cULus 508 Listed, CE	cULus 508 Listed, CE	cULus 508 Listed, CE	cULus 508 Listed, CE


Single Phase	3A	5A	10A	20A	
ECO Line					
Input Voltage	85 - 264Vac / 120 - 300Vdc	85 - 138Vac / 195 - 250Vac Selectable	85 - 138Vac / 195 - 250Vac Selectable	85 - 138Vac / 195 - 250Vac Selectable	
Output Voltage	24Vdc	24Vdc	24Vdc	24Vdc	
Output Current	3A	5A	10A	20A	
Output Surege / Time	—	—	—	—	
Efficiency	80%	84%	84%	86%	
Operating Temp	-10°C - +55°C (-14°F - +131°F)	-10°C - +55°C (-14°F - +131°F)	-10°C - +55°C (-14°F - +131°F)	-10°C - +55°C (-14°F - +131°F)	
Features	Status relay, robust metal housing	Status relay, robust metal housing	Status relay, robust metal housing	Status relay, robust metal housing	
Dimensions (LxWxH)	125 x 55.5 x 110mm 4.9 x 2.2 x 4.3"	125 x 65.5 x 110mm 4.9 x 2.6 x 4.3"	125 x 125.5 x 110mm 4.9 x 4.9 x 4.3"	125 x 227.5 x 110mm 4.9 x 9 x 4.3"	
Part Number	8708660000	8708670000	8708680000	8778870000	
Type	CP SNT 70W 24V 3A	CP SNT 120W 24V 5A	CP SNT 250W 24V 10A	CP SNT 500W 24V 20A	
Approvals	cULus 508 Listed, CE, UR 60950	cULus 508 Listed, CE, UR 60950	cULus 508 Listed, CE, UR 60950	cULus 508 Listed, CE, UR 60950	
Other Voltage Variants					
Three Phase	10A	20A	40A		
ECO Line					
Input Voltage	340 - 575Vac Three phase	340 - 575Vac Three phase	340 - 575Vac Three phase		
Output Voltage	24Vdc	24Vdc	24Vdc		
Output Current	10A	20A	40A		
Output Surege / Time	—	—	—		
Efficiency	88%	88%	88%		
Operating Temp	-10°C - +55°C (-14°F - +131°F)	-10°C - +55°C (-14°F - +131°F)	-10°C - +55°C (-14°F - +131°F)		
Features	Status relay, robust metal housing	Status relay, robust metal housing	Status relay, robust metal housing		
Dimensions (LxWxH)	125 x 125.5 x 110mm 4.9 x 4.9 x 4.3"	125 x 227.5 x 110mm 4.9 x 9 x 4.3"	125 x 280 x 150mm 4.9 x 11 x 5.9"		
Part Number	8708700000	8708710000	870873 0000		
Type	CP SNT3 250W 24V 10A	CP SNT3 500W 24V 20A	CP SNT3 1000W 24V 40A		
Approvals	cULus 508 Listed, CE, UR 60950	cULus 508 Listed, CE, UR 60950	cULus 508 Listed, CE, UR 60950		

Electronics - Power Supplies

DC - DC Converters	12V - 5V	12V - 12V	12V - 15V	12V - 24V	
					
Input Voltage	10.2 - 13.8 Vdc	10.2 - 13.8 Vdc	10.2 - 13.8 Vdc	10.2 - 13.8 Vdc	
Output Voltage (Nominal)	5Vdc	12Vdc	15Vdc	24Vdc	
Output Voltage (Adj. Range)	4.6 - 5.5Vdc	10.5 - 14.5Vdc	13 - 18Vdc	20.5 - 29.5Vdc	
Output Current	8A	3A	3A	2A	
Efficiency	75%	80%	80%	80%	
Operating Temp	-10°C - +50°C (14°F - +122°F)	-10°C - +50°C (14°F - +122°F)	-10°C - +50°C (14°F - +122°F)	-10°C - +50°C (14°F - +122°F)	
Features	Pluggable connectors, robust metal housing	Pluggable connectors, robust metal housing	Pluggable connectors, robust metal housing	Pluggable connectors, robust metal housing	
Dimensions (LxWxH)	98 x 57 x 131mm 3.86 x 2.24 x 5.16"	98 x 57 x 131mm 3.86 x 2.24 x 5.16"	98 x 57 x 131mm 3.86 x 2.24 x 5.16"	98 x 57 x 131mm 3.86 x 2.24 x 5.16"	
Part Number	9919371205	9919371212	9919371215	9919371224	
Type	CP DCDC 12-5	CP DCDC 12-12	CP DCDC 12-15	CP DCDC 12-24	
Approvals	CSA, UL 508 Listed, CE, CSA Class 1 Div. 2 and Zone 2	CSA, UL 508 Listed, CE, CSA Class 1 Div. 2 and Zone 2	CSA, UL 508 Listed, CE, CSA Class 1 Div. 2 and Zone 2	CSA, UL 508 Listed, CE, CSA Class 1 Div. 2 and Zone 2	

DC - DC Converters	24V - 5V	24V - 12V	24V - 15V	24V - 24V	
					
Input Voltage	20.4 - 30Vdc	20.4 - 30Vdc	20.4 - 30Vdc	20.4 - 30Vdc	
Output Voltage (Nominal)	5Vdc	12Vdc	15Vdc	24Vdc	
Output Voltage (Adj. Range)	4.6 - 5.5Vdc	10.5 - 14.5Vdc	13 - 18Vdc	20.5 - 29.5Vdc	
Output Current	8A	3A	3A	2A	
Efficiency	75%	80%	80%	80%	
Operating Temp	-10°C - +50°C (14°F - +122°F)	-10°C - +50°C (14°F - +122°F)	-10°C - +50°C (14°F - +122°F)	-10°C - +50°C (14°F - +122°F)	
Features	Pluggable connectors, robust metal housing	Pluggable connectors, robust metal housing	Pluggable connectors, robust metal housing	Pluggable connectors, robust metal housing	
Dimensions (LxWxH)	98 x 57 x 131mm 3.86 x 2.24 x 5.16"	98 x 57 x 131mm 3.86 x 2.24 x 5.16"	98 x 57 x 131mm 3.86 x 2.24 x 5.16"	98 x 57 x 131mm 3.86 x 2.24 x 5.16"	
Part Number	9919372405	9919372412	9919372415	9919372424	
Type	CP DCDC 24-5	CP DCDC 24-12	CP DCDC 24-15	CP DCDC 24-24	
Approvals	CSA, UL 508 Listed, CE, CSA Class 1 Div. 2 and Zone 2	CSA, UL 508 Listed, CE, CSA Class 1 Div. 2 and Zone 2	CSA, UL 508 Listed, CE, CSA Class 1 Div. 2 and Zone 2	CSA, UL 508 Listed, CE, CSA Class 1 Div. 2 and Zone 2	

Battery Back-up Unit (BBU)	12Vdc	24Vdc
		
Input Voltage	85 - 264Vac / 120 - 300Vdc	85 - 264Vac / 120 - 300Vdc
Output Voltage	12Vdc	24Vdc
Output Current	15A Load	15A Load
Charge Current	3A bulk	2A bulk
Operating Temp	-20°C - +50°C (-4°F - +122°F)	-20°C - +50°C (-4°F - +122°F)
Features	Inputs for enable, drain cycle and drain reset. Relay outputs for battery status and fault. A variety of status LED's.	Inputs for enable, drain cycle and drain reset. Relay outputs for battery status and fault. A variety of status LED's.
Dimensions (LxWxH)	127.5 x 72.5 x 161mm 5.02 x 2.85 x 6.34"	125 x 65.5 x 110mm 4.9 x 2.6 x 4.3"
Part Number	9916280012	9916280024
Type	CP SNT BBU 12V	CP SNT BBU 24V
Approvals	CSA, UL 508 Listed, CE, CSA Class 1 Div. 2 and Zone 2	CSA, UL 508 Listed, CE, CSA Class 1 Div. 2 and Zone 2
Battery Size	3Ahr - Unlimited	2Ahr - Unlimited



Diode Modules	DM10	DM20	RS-2D	RSD-40A	
					
Input Voltage	40Vdc maximum	40Vdc maximum	24Vdc nominal	24Vdc nominal	
Input Current	2 x 10A max.	2 x 20A max.	2 x 15A max.	2 x 20A max.	
Output Voltage	V _{in} - 0.5Vdc (typical)	V _{in} - 0.5Vdc (typical)	V _{in} - 0.38 (typical)	V _{in} - 0.4V (typical)	
Output Current	20A max.	40A max.	30A max.	40A max.	
Operating Temp	-10°C - +50°C (14°F - +122°F)	-10°C - +50°C (14°F - +122°F)	0°C - +50°C (32°F - +122°F)	0°C - +40°C (32°F - +104°F)	
Features	Robust metal housing	Robust metal housing	Voltage sensing and status relay	Fan turns on at a heatsink temperature of 60°C (140°F) and its speed will raise proportionally as the heatsink temperature increases.	
Dimensions (LxWxH)	125 x 55.5 x 110mm 4.9 x 2.2 x 4.3"	125 x 55.5 x 110mm 4.9 x 2.2 x 4.3"	70 x 110 x 90mm 2.75 x 4.33 x 3.5"	109.2 x 109.2 x 99mm 4.3 x 4.3 x 3.9"	
Part Number	8710620000	8768650000	9987390000	7940005219	
Type	CP DM 10	CP DM 20	RS-2D/SC	RSD-40A	
Approvals	cULus 508 Listed, CE	cULus 508 Listed, CE	UL recognized	cULus 508 Listed	
Variations	-	-	9987860000 - Without voltage sensing	7940005218 - One input of 40A	

Notes






Tools






Tools	Cutting and stripping tools	E.2
	Crimpers	E.3
	Screwdrivers	E.4
	Ferrules	E.8

Tools

Cutters	KT 8	KT 12	KT 20	KT 36	KT 45
					
Part Number	9002650000	9002660000	9002300000	9001090000	9002000000
Solid mm ² /AWG	16/6	16/6	16/6	240/500	300/600
Stranded mm ² /AWG	16/6	25/3	35/2	240/500	300/600
Flexible mm ² /AWG	16/6	35/2	70/ 2/0	240/500	300/600

Strippers	Stripax	Stripax 16	AM12	AM25	AM35
					
Part Number	9005000000	9005610000	9030060000	9001540000	9001080000
Conductor cross-section mm ² /AWG	0.08...6/28-10AWG	6...16/10-6AWG	0.5...4/20-11AWG	-	-
Max. stripping length mm	20	20	-	-	-
Max. cutting performance mm ²	6	6	-	-	-
Length mm	190	190	97	135	140
Weight g	155	155	36	135	135
Cleaning brush	9005450000	9005450000	-	-	-
Spare stripping blade	9054030000	9054030000	-	9001530000	9001530000
Adjustable depth to cut mm	-	-	-	up to 4.5mm	up to 4.5mm


Crimpers	Stripax plus 2.5	PZ 1.5	PZ 6 HEX	PZ 4	PZ 6/5
					
					
Part Number	902000000	9005990000	9013650000	9012500000	9011460000
Crimping range mm ²	0.52...5	0.25...1.5	0.14...6	0.5...4	0.25...6
Wire range AWG	20...14	24...16	24...10	20...12	24...10
length mm	210	170	180	200	200
Weight g	260	170	380	448	423
Spare knife	9050340000				
Die Set					9011620000

Crimpers	PZ 3	PZ 6 Roto	PZ 16	PZ ZH16	PZ 50
					
					
Part Number	0567300000	9014350000	9012600000	9013600000	9006450000
Crimping range mm ²	0.5...6	0.14...6	6...16	6...16	25...50
Wire range AWG	20...10	26...10	10...6	10...6	3...1
length mm	200	200	200	260	260
Weight g	426	428	418	700	700
Spare knife					
Die Set	9011450000	9014480000	9012640000	9054580000	9006280000

Tools

VDE Insulated Screwdriver

VDE-insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC. DIN EN 60900, IEC 900. safety tested GS, checked individually. Blade made from high-alloy chromium-vanadium-molybdenum steel, through-hardened, browned



SDI S

VDE-insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, output acc. to DIN 5264, ISO 2380/1, SoftFinish-grip



Type	Size / SW	A	B	C	Order No.
SDI 0,4x2,5x75	0.4	2.5	80		9008370000
SDI 0,5x3,0x100	0.5	3	100		9008380000
SDI 0,6x3,5x100	0.6	3.5	100		9008390000
SDI 0,8x4,0x100	0.8	4	100		9008400000
SDI 1,0x4,5x125	1	4.5	125		9008910000
SDI 1,0x5,5x125	1	5.5	125		9008410000
SDI 1,2x6,5x150	1.2	6.5	150		9008420000
SDI 1,6x8,0x175	1.6	8	200		9008430000

SDIK PH

VDE-insulated crosshead screwdriver type Phillips, SDIK PH DIN 7438, ISO 8764/2-PH, output acc. to DIN 5260-PH, ISO 8764/1-PH, SoftFinish-grip



SDIK PH0	0	60	9008560000
SDIK PH1	1	80	9008570000
SDIK PH2	2	100	9008580000
SDIK PH3	3	150	9008590000

SDIK PZ

VDE-insulated crosshead screwdriver type Pozidriv SDIK PZ DIN 7438, ISO 8764/2-PZ, output acc. to DIN 5260-PZ, ISO 8764/1-PZ, SoftFinish-grip



SDIK PZ1	1	80	9008900000
SDIK PZ2	2	100	9008890000

SDIT

VDE-insulated Torx®-screwdriver, SDIT SoftFinish-grip



SDIT 8	8	60	9201940000
SDIT 10	10	80	9009640000
SDIT 15	15	80	9009650000
SDIT 20	20	80	9009660000
SDIT 25	25	80	9009670000
SDIT 30	30	100	9009680000
SDIT 40	40	150	9009690000

SKI

VDE-insulated hexagon socket wrench, SKI SoftFinish-grip




SKI 5,0x129	5	125	9009000000
SKI 5,5x128	5,5	125	9008990000
SKI 6,0x128	6	125	9008980000
SKI 7,0x127	7	125	9008970000
SKI 8,0x127	8	125	9008960000
SKI 9,0x126	9	125	9008950000
SKI 10,0x126	10	125	9008940000
SKI 11,0x125	11	125	9008930000
SKI 13,0x125	13	125	9008920000

Uninsulated Screwdriver

Weidmüller SoftFinish screwdriver for general uses, blade made from high-alloy chromium-vanadium-molybdenum steel, through-hardened, matte chrome finish.

SD S

Slot-head screwdriver with circular blade SD DIN 5265, ISO 2380/2, output acc. to DIN 5264, ISO 2380/1, point chromium top, SoftFinish-grip



Type	Size / SW	A	B	C	Order No.
SD 0,4x2,0x60		0.4	2	60	9037160000
SD 0,4x2,5x75		0.4	2.5	75	9009030000
SD 0,5X3,0X80		0.5	3	80	9008320000
SD 0,6X3,5X100		0.6	3.5	100	9008330000
SD 0,6X3,5X200		0.6	3.5	200	9010110000
SD 0,8X4,0X100		0.8	4	100	9008340000
SD 1,2x6,5x150		1.2	6.5	150	9009010000
SD 0,8x4,5x125		0.8	4.5	125	9009020000
SD 1,0x5,5x150		1	5.5	125	9008350000

SDK PH

Crosshead screwdriver Type Phillips, SDK PH DIN 5262, ISO 8764/2-PH, output acc. to DIN 5260-PH, ISO 8764/1-PH, point chromium top, SoftFinish-grip



SDK PH0	0	60	9008470000
SDK PH1	1	80	9008480000
SDK PH2	2	100	9008490000
SDK PH3	3	150	9008500000

SDK PZ

Crosshead screwdriver Type Pozidriv, SDK PZ DIN 5262, ISO 8764/2-PZ, output acc. to DIN 5260-PZ, ISO 8764/1-PZ, point chromium top, SoftFinish-grip



SDK PZ0	0	60	9008520000
SDK PZ1	1	80	9008530000
SDK PZ2	2	100	9008540000
SDK PZ3	3	150	9008550000

SDTR

Torx® TR-screwdriver with drill hole in the blade point (Tamper Resistant), SD TR for screwing of Torx® and Torx®-TR safety screws (centre pin in profile), point chromium top, SoftFinish-grip



SDTR 8	8	60	9009190000
SDTR 10	10	80	9009180000
SDTR 15	15	80	9009170000
SDTR 20	20	100	9009160000
SDTR 25	25	100	9009150000
SDTR 30	30	115	9009140000


SK

Hexagon socket wrench SK DIN 3125, output acc. to DIN 3125, SoftFinish-grip



SK 5,0x125	5	125	9009130000
SK 5,5x125	5,5	125	9009120000
SK 6,0x125	6	125	9009110000
SK 7,0x125	7	125	9009100000
SK 8,0x125	8	125	9009090000
SK 9,0x125	9	125	9009080000
SK 10,0x125	10	125	9009070000
SK 11,0x125	11	125	9009060000
SK 12,0x125	12	125	9009050000
SK 13,0x125	13	125	9009040000

Torque Screwdriver (non-insulated)
Torque-screwdriver Weidmüller SoftFinish



DMS manual

Torque-screwdriver



Type	Size / SW	A	B	C	Order No.
DMS manual 0,5-1,70.5 - 1.7 Nm					9918370000
DMS manual 2,0-8,02.0 - 8.0 Nm					9918380000

WK K S

Interchangeable blades for torque-screwdriver
output according to DIN 5264, ISO 2380/1



WK S 0,4 x 2,5	max. 0.6 Nm	0.4	2.5	175	9918520000
WK S 0,5 x 3,0	max. 0.6 Nm	0.5	3	175	9918530000
WK S 0,6 x 3,5	max. 1.1 Nm	0.6	3.5	175	9918540000
WK S 0,8 x 4,0	max. 2.5 Nm	0.8	4	175	9918550000
WK S 1,0 x 5,5	max. 3.8 Nm	1	5.5	175	9918560000

WK K PH

Interchangeable blades for torque-screwdriver
output according to DIN 5260-PH, ISO 8764/1 -PH



WK K PH 0	max. 0.9 Nm			175	9918570000
WK K PH 1	max. 3.8 Nm			175	9918580000
WK K PH 2	max. 5.5 Nm			175	9918590000

WK K PZ

Interchangeable blades for torque-screwdriver
output according to DIN 5260-PZ, ISO 8764/1 -PZ



WK K PZ 0	max. 0.9 Nm			175	9918600000
WK K PZ 1	max. 3.8 Nm			175	9918610000
WK K PZ 2	max. 5.5 Nm			175	9918620000

Set S 2.5/3.0/4.0/5.5/PH 1/2 (Screwdriver Set)


12-part set of interchangeable blades for slot-head,
cross-head PH screwdriver set with circular blades



SD 0,4x2,5x75		0.4	2.5	75	
SD 0,5x3,0x80		0.5	3	80	
SD 0,8x4,0x100		0.8	4	100	
SD 1,5x5,5x125		1	5.5	125	
SD PH 1	1			80	
SD PH 2	2			100	
SDS 2,5-5,5/PH1/2					9009740000

Tools

Wire end ferrules with plastic collars



Weidmüller standard

		Nominal cross-section (mm²)	AWG	Dimensions (mm)				Stripping length (mm)	Qty	Type	Colour	Order No.	Strip pack	Ferrules in strip form	Ferrules on reels
				L 1	L 2	D 1	D 2						Order No.	Order No.	Order No.
0.14		0.14	26	10	6	0.6	1.5	8	500	H 0.14/10	grey		9005180000		
		0.14	26	12	8	0.6	1.5	10	500	H 0.14/12	grey		9028240000		
0.25		0.25	24	10	6	0.8	1.8	8	500	H 0.25/10	light blue	9025740000	9026050000		
		0.25	24	12	8	0.8	1.8	10	500	H 0.25/12	light blue	9025760000	9025780000		
0.34		0.34	22	10	6	0.8	2	8	500	H 0.34/10	turquoise	9025750000	9026030000		
		0.34	22	12	8	0.8	2	10	500	H 0.34/12	turquoise	9025770000	9025790000		
0.5		0.5	20	10	6	1	2.6	8	500	H 0.5/10	orange		9028260000		
		0.5	20	12	6	1	2.6	8	500	H 0.5/12	orange	0409500000			
0.75		0.5	20	14	8	1	2.6	10	500	H 0.5/14	orange	0690700000	9026060000	9004270000	
		0.5	20	14	8	1	2.6	10	5000	H 0.5/14	orange				9005810000
1		0.5	20	16	10	1	2.6	12	500	H 0.5/16	orange	9025870000	9028270000		
		0.75	18	12	6	1.2	2.8	8	500	H 0.75/12	white	0409600000	9028280000		
1.5		0.75	18	14	8	1.2	2.8	10	500	H 0.75/14	white	0462900000	9026070000	9004290000	
		0.75	18	14	8	1.2	2.8	10	5000	H 0.75/14	white				9005820000
2.5		0.75	18	16	10	1.2	2.8	12	500	H 0.75/16	white	9025860000	9028290000		
		0.75	18	18	12	1.2	2.8	14	500	H 0.75/18	white	9025910000	9028300000		
4		1	17	12	6	1.4	3	8	500	H 1/12	yellow	0409700000	9028310000		
		1	17	14	8	1.4	3	10	500	H 1/14	yellow	0463000000	9026080000	9004320000	
6		1	17	14	8	1.4	3	11	5000	H 1/14	yellow				9005830000
		1	17	16	10	1.4	3	12	500	H 1/16	yellow	9025950000	9028320000		
10		1	17	18	12	1.4	3	15	500	H 1/18	yellow	9025930000	9028340000		
		1.5	16	14	8	1.7	3.2	10	500	H 1.5/14	red	0463100000	9026090000		
16		1.5	16	14	8	1.7	3.2	10	5000	H 1.5/14	red				9005840000
		1.5	16	14	8	1.7	3.2	10	500	H 1.5/14	red				
25		1.5	16	16	10	1.7	3.5	12	500	H 1.5/16	red	0635100000	9028350000		
		1.5	16	18	12	1.7	3.5	15	500						
35		1.5	16	24	18	1.7	3.5	20	500	H 1.5/24	red	0565600000			
		2.5	14	14	8	2.2	4.2	10	500	H 2.5/14 D	blue	9019160000	9026100000		
50 ...		2.5	14	14	8	2.2	4	11	3000	H 2.5/14 D	blue				9005850000
		2.5	14	14	8	2.2	4	11	500	H 2.5/14 D	blue			9004360000	
70		2.5	14	18	12	2.2	4.2	14	500	H 2.5/18 D	blue	9019170000			
		2.5	14	24	18	2.2	4.2	20	500	H 2.5/24 D	blue	9019180000			
95		4	12	17	10	2.8	4.8	12	500	H 4/17 D	grey	9019190000	9026010000*		
		4	12	20	12	2.8	4.8	14	500	H 4/20 D	grey	9019200000			
120		4	12	26	18	2.8	4.8	20	500	H 4/26 D	grey	9019210000			
		6	10	20	12	3.5	6.3	14	100	H 6/20	black	0533500000			
150		6	10	26	18	3.5	6.3	20	100	H 6/26	black	0565700000			
		10	7	22	12	4.5	7.6	15	100	H 10/22	ivory	0534200000			
200		10	7	28	18	4.5	7.6	21	100	H 10/28	ivory	0565800000			
		16	6	24	12	5.8	8.8	15	100	H 16/24	green	0565900000			
250		16	6	28	18	5.8	8.8	21	100	H 16/28	green	0566000000			
		25	3	30	16	7.3	11.2	18	50	H 25/30	brown	0317000000			
300		25	3	36	22	7.3	11.2	24	50	H 25/36	brown	0317100000			
		35	2	30	16	8.3	12.7	19	50	H 35/30	beige	0317200000			
400		35	2	30	18	8.3	12.7	21	50						
		35	2	39	25	8.3	12.7	28	50	H 35/39	beige	0317300000			
500		50	1	36	20	10.3	15	26	50	H 50/36	olive	0444200000			
		50	1	40	25	10.3	15	31	50						
600		70	2/0	37	20	12.7	16	26	25	H 70/40	yellow	9028200000			
		95	3/0	44	25	14.7	18	31	25	H 95/44	red	9028210000			
700		120	4/0	50	30	16.5	21	36	25	H 120/50	blue	9028220000			
		150	300 MCM	54	32	18.5	23.5	38	25	H 150/54	yellow	9028230000			

Strip pack 5 x 100 ferrules

* 5 x 50 ferrules

Wire end ferrules without plastic collars



		Nominal cross-section		Dimensions (mm)			Stripping length mm	Qty	Type	Order No.	
		(mm²)	AWG	L 1	D 1	D 2					
0.25		0.25	24	5	0.7	1.65	5	1000	H 0.25/5	9018910000	
0.5		0.5	20	6	1	2.1	6	1000	H 0.5/6	0282600000	
		0.5	20	10	1	2.1	10	1000	H 0.5/10	9004050000	
0.75		0.75	18	6	1.2	2.3	6	1000	H 0.75/6	0282700000	
		0.75	18	10	1.2	2.3	10	1000	H 0.75/10	0542500000	
1		1	17	6	1.4	2.5	6	1000	H 1/6	0372600000	
		1	17	10	1.4	2.5	10	1000	H 1/10	0282800000	
1.5		1.5	16	7	1.7	2.8	7	1000	H 1.5/7	0372700000	
		1.5	16	10	1.7	2.8	10	1000	H 1.5/10	0186500000	
		1.5	16	12	1.7	2.8	12	1000	H 1.5/12	9004060000	
		1.5	16	18	1.7	2.8	18	1000	H 1.5/18	9004070000	
2.5		2.5	14	7	2.2	3.4	7	1000	H 2.5/7	0373000000	
		2.5	14	10	2.2	3.4	10	1000	H 2.5/10	9004080000	
		2.5	14	12	2.2	3.4	12	1000	H 2.5/12	0186100000	
		2.5	14	18	2.2	3.4	18	1000	H 2.5/18	9004090000	
4		4	12	9	2.8	4	9	500	H 4/9	0373100000	
		4	12	12	2.8	4	12	1000	H 4/12	0244100000	
		4	12	15	2.8	4	15	500	H 4/15	9004100000	
		4	12	18	2.8	4	18	1000	H 4/18	9004110000	
6		6	10	10	3.5	4.7	10	500	H 6/10	9004120000	
		6	10	12	3.5	4.7	12	500	H 6/12	0191900000	
		6	10	15	3.5	4.7	15	500	H 6/15	0124700000	
		6	10	18	3.5	4.7	18	500	H 6/18	9004130000	
10		10	7	12	4.5	5.8	12	500	H 10/12	0282900000	
		10	7	15	4.5	5.8	15	500	H 10/15	0124800000	
		10	7	18	4.5	5.8	18	500	H 10/18	0379300000	
		16	6	12	5.8	7.5	12	500	H 16/12	0492500000	
		16	6	15	5.8	7.5	15	500	H 16/15	0124300000	
		16	6	18	5.8	7.5	18	100	H 16/18	0375200000	
		16	6	25	5.8	7.5	25	100	H 16/25	9004150000	
		16	6	32	5.8	7.5	32	100	H 16/32	9004160000	
25		25	3	15	7.3	9.5	15	250	H 25/15	0124400000	
		25	3	18	7.3	9.5	18	100	H 25/18	0375300000	
		25	3	25	7.3	9.5	25	100	H 25/25	9004170000	
		25	3	32	7.3	9.5	32	100	H 25/32	9004180000	
		35	2	18	8.3	11	18	100	H 35/18	0368900000	
		35	2	25	8.3	11	25	100	H 35/25	9004190000	
		35	2	30	8.3	11	30	500	H 35/30 S	9451000000	
		35	2	32	8.3	11	32	100	H 35/32	9004200000	
50 ...		50	1	18	10.3	13	18	100	H 50/18	9004210000	
		50	1	25	10.3	13	25	100	H 50/25	9025880000	
		50	1	32	10.3	13	32	100	H 50/32	9004220000	
		70	2/0	25	12.5	15	25	50	H 70/25	9004230000	
		70	2/0	32	12.5	15	32	50	H 70/32	9004240000	
		95	3/0	25	14.5	17	25	50	H 95/25	9004250000	
		95	3/0	32	14.5	17	32	50	H 95/32	9004260000	
		120	4/0	32	16.5	19	32	50	H 120/32	9036240000	
		150	300 MCM	32	18.5	21	32	50	H 150/32	9036250000	
		185	350 MCM	32	20	23.5	32	50	H 185/32	9036260000	

Tools

Crimping tools for ferrules

	PZ 1.5	stripax® plus 2.5	PZ 3	PZ 4	PZ 6 roto	PZ 6 HEX	PZ 6/5	PZ 16	PZ 50
Order No.									
	9005990000	9020000000	0567300000	9012500000	9014350000	9013650000	9011460000	9012600000	9006450000
AEH mm²									
H 0.25	●				●	●	●		
H 0.34	●				●	●	●		
H 0.5	●	●	●	●	●	●	●		
H 0.75	●	●	●	●	●	●	●		
H 1.0	●	●	●	●	●	●	●		
H 1.5	●	●	●	●	●	●	●		
H 2.5		●	●	●	●	●	●		
H 4.0			●	●	●	●	●		
H 6.0			●		●	●	●	●	
H 10.0								●	
H 16.0								●	
H 25.0									●
H 35.0									●
H 50.0									●

● = ferrules in strip form only

E

Twin wire end ferrules are to be crimped according to the following table:

Tool	Order No.	H 0,5	H 0,75	H 1,0	Ferrules		H 4,0	H 6,0	H 10,0	H 16,0
					H 1,5	H 2,5				
PZ 1.5	9005990000	●	●							
PZ 3	0567300000	●	●	●	●	●				
PZ 4	9012500000	●	●	●	●	●				
PZ 6 roto	9014350000	●	●	●	●	●	●			
PZ 6/5	9011460000		●	●	●	●	●			
PZZH16	9013600000							●	●	●


Weidmüller stocks a comprehensive range of wire end ferrules and insulated cable lugs for immediate supply.

Wire end ferrules

Wire end ferrules ensure the long-term quality of electrical connections. Another advantage is their usefulness during installation. The wide range of products embraces wire end ferrules with or without plastic collars and twin wire end ferrules in all the colours normally required by users.



Twin wire end ferrules with plastic collar



		Nominal cross-section		Dimensions (mm)				Stripping length	Qty
		(mm ²)	AWG	L 1	L 2	D 1	A/B		
0.5		0.5	20	15	8	1.4	5/3	11	500
		0.5	20	16	10	1.4	5/3	13	500
		0.5	20	19	12	1.4	5/3	15	500
0.75		0.75	18	15	8	1.7	5.5/3	11	500
		0.75	18	17	10	1.7	5.5/3	13	500
		0.75	18	24	18	1.7	5.5/3	21	500
1		1.0	17	16	8	2.2	6.5/3.6	12	500
		1.0	17	15	8	2.0	5.8/3.2	12	500
		1.0	17	19	12	2.0	5.8/3.2	16	500
		1.0	17	25	18	2.0	5.8/3.2	22	500
1.5		1.5	16	16	8	2.2	6.5/3.6	11	500
		1.5	16	20	12	2.2	6.5/3.6	15	500
		1.5	16	26	18	2.2	6.5/3.6	21	100
2.5		2.5	14	19	10	2.8	8/4.5	13	500
		2.5	14	19	10	2.8	8/4.5	13	250
		2.5	14	21	12	2.8	8/4.5	15	500
		2.5	14	21	12	2.8	8/4.5	15	250
		2.5	14	27	18	2.8	8/4.5	21	500
4		4.0	12	22	12	3.5	9/5.2	15	100
		4.0	12	28	18	3.5	9/5.2	21	100
6		6.0	10	25	12	4.5	11.4/6.2	20	100
		6.0	10	29	18	4.5	11.4/6.2	24	100
10		10.0	7	24	12	5.8	13.4/7.6	17	100
		10.0	7	30	18	5.8	13.4/7.6	23	100
		10.0	7	24	12	6.5	13.4/7.6	17	100
		10.0	7	30	18	6.5	13.4/7.6	23	100
16		16.0	6	29	16	8.3	17.2/9.5	20	50

Weidmüller standard

Type	Colour	Order No.	Strip pack Order No.
H 0.5/15	orange	9037200000	9004440000*
H 0.5/16.5	orange	9037210000	
H 0.5/18.5	orange	9037220000	
H 0.75/15	white	9037230000	9018510000***
H 0.75/17	white	9037240000	9004900000*
H 0.75/24.5	white	9037250000	
H 1/15S	yellow	9018690000	9018650000*
H 1/15	yellow	9037260000	9018530000*
H 1/20	yellow	9037270000	9004910000*
H 1/25.6	yellow	9037280000	
H 1.5/16	red	9037290000	9004410000*
H 1.5/20	red	9037300000	9004920000*
H 1.5/25.6	red	9037310000	
H 2.5/18.5D	blue	9037500000	
H 2.5/18.5D	blue		9004430000**
H 2.5/20.5D	blue	9037510000	
H 2.5/20.5D	blue		9004740000**
H 2.5/26.5D	blue	9037520000	
H 4/22D	grey	9037530000	9004730000***
H 4/28D	grey	9037540000	
H 6/25	black	9037320000	9004930000***
H 6/29	black	9037330000	
H 10/26	ivory	9037340000	9004940000***
H 10/30	ivory	9037350000	
H 10/24 S	ivory	9018860000	
H 10/30 S	ivory	9018870000	
H 16/29	green	9037360000	

* 5 x 100 ** 5 x 50 *** 5 x 20

Notes

Installation Products

Installation Products	Terminal Markers	F.2
	Wire and Cable Markers	F.4
	Protective Sleeves	F.16
	Equipment Markers	F.22
	Printers	F.28
	Software	F.30

Installation Products - Terminal Markers

Dekafix

Dekafix (DEK) markers are universal markers for all terminals and plug-in connectors as well as electronics modules. Including a wide range of ready-for-use prints, the system is particularly suitable for short sequences of digits.

Rapid strip mounting allows the markers to be clipped on in a single action. Available in five widths, the high-contrast print is easily legible.

- Large selection of ready-printed markers
- Rapid mounting in strips
- Terminal markers suitable for all Weidmüller terminal connectors



* NOTE: DEK 5/5 Plus MC eliminates carrier strip for easier mounting.

WS

WS markers have been optimised for W-Series terminal connectors. Thanks to their system compatibility, WS tags can be used for products from the I-Series and the Z-Series. The large marking surface is suitable for long sequences of characters as well as several lines of information.

WS markers are particularly suitable for marking lengthier, individually created sequences of characters. The proven MultiCard format means it is possible to print with the PrintJet and Plotter.

- Mount in strips or individually



* NOTE: WS 10/5 Middle and 10/6 Middle are equipped with a centred foot.

ZS

ZS markers – available in the proven MultiCard format – have been specially developed for the Z-Series. They offer a large marking surface. The hinged mechanism even allows access to cross-connectors without having to dismount the markers first. Snap-on attachment of individual tags in strips guarantees rapid mounting. The individual tags can easily be separated from the strips.

- Hinged marker surface
- Mount in strips or individually



Technical Data

Material: Polyamide - halogen-free
Flammability class to UL94 V2 (Unless specified V0 in product description)
Temperature range: -40 to 100°C

Possible printing systems: Plotter and PrintJet

Notes on mounting:

- Assemble in strips when the marker width = terminal width
- Assemble individually when the marker width < terminal width

Ordering data

Custom and standard pre-printed markers available.

Colour variations on request:

- | | | |
|----------|---------|----------|
| ● brown | ● red | ● orange |
| ● yellow | ● green | ● blue |
| ● violet | ● grey | ○ white |

Part Number (white)	Description	Dimensions	Qty. per box
1755270000	DEK 5/3.5 MC	5mm Length, 3.5mm Width	500
1609801044	DEK 5/5 MC	5mm Length, 5mm Width	1000
1854490000	DEK 5/5 Plus MC	5mm Length, 5mm Width	1000
1609820000	DEK 5/6 MC	5mm Length, 6mm Width	1000
1789590000	DEK 5/6 MC V0	5mm Length, 6mm Width	1000
1609840000	DEK 5/6.5 MC	5mm Length, 6.5mm Width	900
1720620000	DEK 5/7.5 MC	5mm Length, 7.5mm Width	320
1856740000	DEK 5/8 MC	5mm Length, 8mm Width	800
1640740000	WS 8/5 MC	8mm Length, 5mm Width	720
1635000000	WS 10/5 MC	10mm Length, 5mm Width	720
1792000000	WS 10/5 MC Middle	10mm Length, 5mm Width	720
1828450000	WS 10/6 MC	10mm Length, 6mm Width	600
1818400000	WS 10/6 MC Middle	10mm Length, 6mm Width	600
1905950000	WS 10/8 MC	10mm Length, 8mm Width	420
1905970000	WS 10/12 MC	10mm Length, 12mm Width	300
1854090000	WS 10/15 MC	10mm Length, 15mm Width	240
1778270000	WS 12/3.5 MC	12mm Length, 3.5mm Width	600
1609860000	WS 12/5 MC	12mm Length, 5mm Width	720
1609900000	WS 12/6 MC	12mm Length, 6mm Width	600
1609920000	WS 12/6.5 MC	12mm Length, 6.5mm Width	540
1906000000	WS 12/8 MC	12mm Length, 8mm Width	420
1768090000	WS 14/5 MC	14mm Length, 5mm Width	480
1609880000	WS 15/5 MC	15mm Length, 5mm Width	480
1610000000	ZS 10/5 MC	10mm Length, 5mm Width	480
1610020000	ZS 12/6 MC	12mm Length, 6mm Width	400
1646630000	ZS 15/5 MC	15mm Length, 5mm Width	480

Installation Products


F

Installation Products - Wire & Cable

SlimFix (SFX)

SlimFix are wire and cable markers featuring a space-saving design. The markers can also be attached to the wires after these have been installed. They are made from halogen-free material and fulfil flammability class VO requirements. SlimFix is an approved and listed marker for traffic engineering. Attaching even small markers is no problem when using the SF tool.

- Halogen-free material
- Flammability class VO/V2
- Approved and listed markers includes traffic engineering
- Attach to conductor cross-sections greater than 16.0 mm² with cable ties




* NOTE: SFX only - max. width of cable tie = 3.6 mm

Part Number	Description	Colour	Dimensions
1852490000	SFX 9/24	White	24mm Length, 9mm Width
1852460000	SFX 9/24	Yellow	24mm Length, 9mm Width
1852500000	SFX 9/24	Blue	24mm Length, 9mm Width
1852470000	SFX 9/24	Red	24mm Length, 9mm Width
1852390000	SFX 10/23	White	23mm Length, 10mm Width
1852360000	SFX 10/23	Yellow	23mm Length, 10mm Width
1852400000	SFX 10/23	Blue	23mm Length, 10mm Width
1852370000	SFX 10/23	Red	23mm Length, 10mm Width
1860120000	SFX 11/60	White	60mm Length, 11mm Width
1860150000	SFX 11/60	Yellow	60mm Length, 11mm Width
1860130000	SFX 11/60	Grey	60mm Length, 11mm Width
1852440000	SFX 14/23	White	23mm Length, 14mm Width
1852410000	SFX 14/23	Yellow	23mm Length, 14mm Width
1852450000	SFX 14/23	Blue	23mm Length, 14mm Width
1852420000	SFX 14/23	Red	23mm Length, 14mm Width

SlimFix V0 (SFX)

SlimFix are wire and cable markers featuring a space-saving design. The markers can also be attached to the wires after these have been installed. They are made from halogen-free material and fulfil flammability class VO requirements. SlimFix is an approved and listed marker for traffic engineering. Attaching even small markers is no problem when using the SF tool.


- Halogen-free material
- Flammability class VO/V2
- Approved and listed markers includes traffic engineering
- Attach to conductor cross-sections greater than 16.0 mm² with cable ties
- Markers available in the proven MultiCard format



* NOTE: SFX only - max. width of cable tie = 3.6 mm

1696140001	SFX V0 9/24	White	24mm Length, 9mm Width
1696140004	SFX V0 9/24	Yellow	24mm Length, 9mm Width
1696140002	SFX V0 9/24	Blue	24mm Length, 9mm Width
1696140003	SFX V0 9/24	Red	24mm Length, 9mm Width
1727750001	SFX V0 10/23	White	23mm Length, 10mm Width
1727750004	SFX V0 10/23	Yellow	23mm Length, 10mm Width
1727750002	SFX V0 10/23	Blue	23mm Length, 10mm Width
1727750003	SFX V0 10/23	Red	23mm Length, 10mm Width
1713660001	SFX V0 14/23	White	23mm Length, 14mm Width
1713660004	SFX V0 14/23	Yellow	23mm Length, 14mm Width
1713660002	SFX V0 14/23	Blue	23mm Length, 14mm Width
1713660003	SFX V0 14/23	Red	23mm Length, 14mm Width

SlimFix (SF)





1740830001	SF 00/12	White	12mm Length
1740830004	SF 00/12	Yellow	12mm Length
1740830002	SF 00/12	Blue	12mm Length
1740830003	SF 00/12	Red	12mm Length
1724050001	SF 0/12	White	12mm Length
1724050004	SF 0/12	Yellow	12mm Length
1724050002	SF 0/12	Blue	12mm Length
1724050003	SF 0/12	Red	12mm Length
1711320001	SF 1/12	White	12mm Length

Installation Products

F

Installation Products - Wire & Cable

SlimFix (SF) cont'd



Part Number	Description	Colour	Dimensions
1711320004	SF 1/12	Yellow	12mm Length
1711320002	SF 1/12	Blue	12mm Length
1711320003	SF 1/12	Red	12mm Length
1711350001	SF 2/12	White	12mm Length
1711350004	SF 2/12	Yellow	12mm Length
1711350002	SF 2/12	Blue	12mm Length
1711350003	SF 2/12	Red	12mm Length
1711370001	SF 3/12	White	12mm Length
1711370004	SF 3/12	Yellow	12mm Length
1711370002	SF 3/12	Blue	12mm Length
1711370003	SF 3/12	Red	12mm Length
1743490001	SF 4/12	White	12mm Length
1743490004	SF 4/12	Yellow	12mm Length
1743490002	SF 4/12	Blue	12mm Length
1743490003	SF 4/12	Red	12mm Length
1743500001	SF 5/12	White	12mm Length
1743500004	SF 5/12	Yellow	12mm Length
1743500002	SF 5/12	Blue	12mm Length
1743500003	SF 5/12	Red	12mm Length
1740840001	SF 00/21	White	21mm Length
1740840004	SF 00/21	Yellow	21mm Length
1740840002	SF 00/21	Blue	21mm Length
1740840003	SF 00/21	Red	21mm Length
1740850001	SF 0/21	White	21mm Length
1740850004	SF 0/21	Yellow	21mm Length
1740850002	SF 0/21	Blue	21mm Length
1740850003	SF 0/21	Red	21mm Length
1696090001	SF 1/21	White	21mm Length
1696090004	SF 1/21	Yellow	21mm Length
1696090002	SF 1/21	Blue	21mm Length
1696090003	SF 1/21	Red	21mm Length
1696100001	SF 2/21	White	21mm Length
1696100004	SF 2/21	Yellow	21mm Length
1696100002	SF 2/21	Blue	21mm Length
1696100003	SF 2/21	Red	21mm Length
1696110001	SF 3/21	White	21mm Length
1696110004	SF 3/21	Yellow	21mm Length
1696110002	SF 3/21	Blue	21mm Length

Installation Products - Wire & Cable

Qty. per box	Char. per tag using Font 10	Ext. diameter of wire (mm)	AWG	Cross-section (mm ²)	
400	5 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
400	5 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
400	5 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
400	5 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
400	5 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
400	5 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
400	5 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
320	5 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
320	5 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
320	5 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
320	5 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
128	5 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
128	5 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
128	5 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
128	5 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
160	5 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	6 mm ² - 10 mm ²	
160	5 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	6 mm ² - 10 mm ²	
160	5 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	6 mm ² - 10 mm ²	
160	5 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	6 mm ² - 10 mm ²	
400	10 Characters	1.0 mm - 1.3 mm	26 - 24 AWG	<0.25 mm ²	
400	10 Characters	1.0 mm - 1.3 mm	26 - 24 AWG	<0.25 mm ²	
400	10 Characters	1.0 mm - 1.3 mm	26 - 24 AWG	<0.25 mm ²	
400	10 Characters	1.0 mm - 1.3 mm	26 - 24 AWG	<0.25 mm ²	
400	10 Characters	1.3 mm - 1.6 mm	24 - 20 AWG	0.25 mm ² - 0.5 mm ²	
400	10 Characters	1.3 mm - 1.6 mm	24 - 20 AWG	0.25 mm ² - 0.5 mm ²	
400	10 Characters	1.3 mm - 1.6 mm	24 - 20 AWG	0.25 mm ² - 0.5 mm ²	
400	10 Characters	1.3 mm - 1.6 mm	24 - 20 AWG	0.25 mm ² - 0.5 mm ²	
400	10 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
400	10 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
400	10 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
400	10 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
400	10 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
400	10 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
400	10 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
400	10 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
320	10 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
320	10 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
320	10 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	

Installation Products - Wire & Cable

SlimFix (SF) cont'd



* NOTE: Attach to connected wires using SlimFix tool, see pg. F.12

Part Number	Description	Colour	Dimensions
1696110003	SF 3/21	Red	21mm Length
1696120001	SF 4/21	White	21mm Length
1696120004	SF 4/21	Yellow	21mm Length
1696120002	SF 4/21	Blue	21mm Length
1696120003	SF 4/21	Red	21mm Length
1740860001	SF 4.5/21	White	21mm Length
1740860004	SF 4.5/21	Yellow	21mm Length
1740860002	SF 4.5/21	Blue	21mm Length
1740860003	SF 4.5/21	Red	21mm Length
1696130001	SF 5/21	White	21mm Length
1696130004	SF 5/21	Yellow	21mm Length
1696130002	SF 5/21	Blue	21mm Length
1696130003	SF 5/21	Red	21mm Length
1740870001	SF 6/21	White	21mm Length
1740870004	SF 6/21	Yellow	21mm Length
1740870002	SF 6/21	Blue	21mm Length
1740870003	SF 6/21	Red	21mm Length

SlimFix V0 (VT-SF)

SlimFix are wire and cable markers featuring a space-saving design. The markers can also be attached to the wires after these have been installed. They are made from halogen-free material and fulfil flammability class V0 requirements. SlimFix is an approved and listed marker for traffic engineering. Attaching even small markers is no problem when using the SF tool.



- Halogen-free material
- Flammability class V0
- Approved and listed markers, includes traffic engineering
- Attach to wire cross-sections above 16.0 mm² with cable ties



1752200001	VT-SF V0 00/12	White	12mm Length
1752200004	VT-SF V0 00/12	Yellow	12mm Length
1752200002	VT-SF V0 00/12	Blue	12mm Length
1752200003	VT-SF V0 00/12	Red	12mm Length
1752110001	VT-SF V0 0/12	White	12mm Length
1752110004	VT-SF V0 0/12	Yellow	12mm Length
1752110002	VT-SF V0 0/12	Blue	12mm Length
1752110003	VT-SF V0 0/12	Red	12mm Length
1718470001	VT-SF V0 1/12	White	12mm Length
1718470004	VT-SF V0 1/12	Yellow	12mm Length
1718470002	VT-SF V0 1/12	Blue	12mm Length
1718470003	VT-SF V0 1/12	Red	12mm Length
1718480001	VT-SF V0 2/12	White	12mm Length
1718480004	VT-SF V0 2/12	Yellow	12mm Length
1718480002	VT-SF V0 2/12	Blue	12mm Length
1718480003	VT-SF V0 2/12	Red	12mm Length
1718490001	VT-SF V0 3/12	White	12mm Length
1718490004	VT-SF V0 3/12	Yellow	12mm Length
1718490002	VT-SF V0 3/12	Blue	12mm Length
1718490003	VT-SF V0 3/12	Red	12mm Length

* NOTE: Attach to connected wires using SlimFix tool, see pg. F.12

Installation Products - Wire & Cable

Qty. per box	Char. per tag using Font 10	Ext. diameter of wire (mm)	AWG	Cross-section (mm ²)	
320	10 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
192	10 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
192	10 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
192	10 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
192	10 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
96	10 Characters	4.1 mm - 4.9 mm	10 AWG	4 mm ² - 6 mm ²	
96	10 Characters	4.1 mm - 4.9 mm	10 AWG	4 mm ² - 6 mm ²	
96	10 Characters	4.1 mm - 4.9 mm	10 AWG	4 mm ² - 6 mm ²	
96	10 Characters	4.1 mm - 4.9 mm	10 AWG	4 mm ² - 6 mm ²	
160	10 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	6 mm ² - 10 mm ²	
160	10 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	6 mm ² - 10 mm ²	
160	10 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	6 mm ² - 10 mm ²	
160	10 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	6 mm ² - 10 mm ²	
160	10 Characters	5.8 mm - 7.0 mm	6 - 4 AWG	10 mm ² - 16 mm ²	
160	10 Characters	5.8 mm - 7.0 mm	6 - 4 AWG	10 mm ² - 16 mm ²	
160	10 Characters	5.8 mm - 7.0 mm	6 - 4 AWG	10 mm ² - 16 mm ²	
160	10 Characters	5.8 mm - 7.0 mm	6 - 4 AWG	10 mm ² - 16 mm ²	
800	5 Characters	1.0 mm - 1.3 mm	26 - 24 AWG	<0.25 mm ²	
800	5 Characters	1.0 mm - 1.3 mm	26 - 24 AWG	<0.25 mm ²	
800	5 Characters	1.0 mm - 1.3 mm	26 - 24 AWG	<0.25 mm ²	
800	5 Characters	1.0 mm - 1.3 mm	26 - 24 AWG	<0.25 mm ²	
800	5 Characters	1.3 mm - 1.6 mm	24 - 20 AWG	0.25 mm ² - 0.5 mm ²	
800	5 Characters	1.3 mm - 1.6 mm	24 - 20 AWG	0.25 mm ² - 0.5 mm ²	
800	5 Characters	1.3 mm - 1.6 mm	24 - 20 AWG	0.25 mm ² - 0.5 mm ²	
800	5 Characters	1.3 mm - 1.6 mm	24 - 20 AWG	0.25 mm ² - 0.5 mm ²	
800	5 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
800	5 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
800	5 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
800	5 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
800	5 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
800	5 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
800	5 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
800	5 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
640	5 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
640	5 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
640	5 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
640	5 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	

Installation Products - Wire & Cable

SlimFix V0 (VT-SF) cont'd



Part Number	Description	Colour	Dimensions
1746030001	VT-SF V0 4/12	White	12mm Length
1743490004	VT-SF V0 4/12	Yellow	12mm Length
1746030002	VT-SF V0 4/12	Blue	12mm Length
1746030003	VT-SF V0 4/12	Red	12mm Length
1746040001	VT-SF V0 5/12	White	12mm Length
1746040004	VT-SF V0 5/12	Yellow	12mm Length
1746040002	VT-SF V0 5/12	Blue	12mm Length
1746040003	VT-SF V0 5/12	Red	12mm Length
1730580001	VT-SF V0 00/21	White	21mm Length
1730580004	VT-SF V0 00/21	Yellow	21mm Length
1730580002	VT-SF V0 00/21	Blue	21mm Length
1730580003	VT-SF V0 00/21	Red	21mm Length
1730590001	VT-SF V0 0/21	White	21mm Length
1730590004	VT-SF V0 0/21	Yellow	21mm Length
1730590002	VT-SF V0 0/21	Blue	21mm Length
1730590003	VT-SF V0 0/21	Red	21mm Length
1689390001	VT-SF V0 1/21	White	21mm Length
1689390004	VT-SF V0 1/21	Yellow	21mm Length
1689390002	VT-SF V0 1/21	Blue	21mm Length
1689390003	VT-SF V0 1/21	Red	21mm Length
1689410001	VT-SF V0 2/21	White	21mm Length
1689410004	VT-SF V0 2/21	Yellow	21mm Length
1689410002	VT-SF V0 2/21	Blue	21mm Length
1689410003	VT-SF V0 2/21	Red	21mm Length
1689430001	VT-SF V0 3/21	White	21mm Length
1689430004	VT-SF V0 3/21	Yellow	21mm Length
1689430002	VT-SF V0 3/21	Blue	21mm Length
1689430003	VT-SF V0 3/21	Red	21mm Length
1689450001	VT-SF V0 4/21	White	21mm Length
1689450004	VT-SF V0 4/21	Yellow	21mm Length
1689450002	VT-SF V0 4/21	Blue	21mm Length
1689450003	VT-SF V0 4/21	Red	21mm Length
1730570001	VT-SF V0 4.5/21	White	21mm Length
1730570004	VT-SF V0 4.5/21	Yellow	21mm Length
1730570002	VT-SF V0 4.5/21	Blue	21mm Length
1730570003	VT-SF V0 4.5/21	Red	21mm Length
1689470001	VT-SF V0 5/21	White	21mm Length
1689470004	VT-SF V0 5/21	Yellow	21mm Length

Installation Products - Wire & Cable

Qty. per box	Char. per tag using Font 10	Ext. diameter of wire (mm)	AWG	Cross-section (mm ²)	
192	5 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
192	5 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
192	5 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
192	5 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
160	5 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	4 mm ² - 6 mm ²	
160	5 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	4 mm ² - 6 mm ²	
160	5 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	4 mm ² - 6 mm ²	
160	5 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	4 mm ² - 6 mm ²	
800	10 Characters	1.0 mm - 1.3 mm	26 - 24 AWG	<0.25 mm ²	
800	10 Characters	1.0 mm - 1.3 mm	26 - 24 AWG	<0.25 mm ²	
800	10 Characters	1.0 mm - 1.3 mm	26 - 24 AWG	<0.25 mm ²	
800	10 Characters	1.0 mm - 1.3 mm	26 - 24 AWG	<0.25 mm ²	
800	10 Characters	1.3 mm - 1.6 mm	24 - 20 AWG	0.25 mm ² - 0.5 mm ²	
800	10 Characters	1.3 mm - 1.6 mm	24 - 20 AWG	0.25 mm ² - 0.5 mm ²	
800	10 Characters	1.3 mm - 1.6 mm	24 - 20 AWG	0.25 mm ² - 0.5 mm ²	
800	10 Characters	1.3 mm - 1.6 mm	24 - 20 AWG	0.25 mm ² - 0.5 mm ²	
800	10 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
800	10 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
800	10 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
800	10 Characters	1.6 mm - 2.1 mm	20 - 16 AWG	0.5 mm ² - 0.75 mm ²	
800	10 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
800	10 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
800	10 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
800	10 Characters	2.1 mm - 2.9 mm	16 - 14 AWG	0.75 mm ² - 1.5 mm ²	
512	10 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
512	10 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
512	10 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
512	10 Characters	2.9 mm - 3.6 mm	14 - 10 AWG	1.5 mm ² - 2.5 mm ²	
288	10 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
288	10 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
288	10 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
288	10 Characters	3.6 mm - 4.5 mm	12 - 8 AWG	2.5 mm ² - 4 mm ²	
192	10 Characters	4.1 mm - 4.9 mm	10 AWG	4 mm ² - 6 mm ²	
192	10 Characters	4.1 mm - 4.9 mm	10 AWG	4 mm ² - 6 mm ²	
192	10 Characters	4.1 mm - 4.9 mm	10 AWG	4 mm ² - 6 mm ²	
192	10 Characters	4.1 mm - 4.9 mm	10 AWG	4 mm ² - 6 mm ²	
160	10 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	4 mm ² - 6 mm ²	
160	10 Characters	4.7 mm - 5.8 mm	8 - 6 AWG	4 mm ² - 6 mm ²	

Installation Products - Wire & Cable

SlimFix V0 (MT-SF) cont'd



SlimFix Tool



Technical data

Material: Polyamide / Wemid - halogen-free
Flammability class to UL94 V2 (Unless specified V0 in product description)
Temperature range V0: -50 to 120°C / V2: -40 to 100 °C

Possible printing systems: Plotter and PrintJet

Notes on mounting:

- SF: Slide onto unconnected wires attach to connected wires using SlimFix tool
- SFX: Attach using cable ties

Ordering data

Custom and standard pre-printed markers available.

[illegible]

Installation Products



F

Installation Products - Wire & Cable

SlimFix Clip (SFC)

The **SlimFix Clip (SFC)** unites the optimal combination of a secure fit and high flexibility during the marking process. The unique clip mechanism offers the security of a closed marker and the rapid fitting of an open marker in one. **SlimFix Clip** is available in 3 different sizes and in 12, 21 and 30 mm lengths. The blank conductor and cable markers in MultiCard format can be printed using various marking systems. Very long number combinations are possible, depending on the tag length.

- Halogen-free material with flammability rating V2
- Slim marker with compensating device for secure fitting
- Clip mechanism enables secure fitting even after the conductor is connected
- Rapid fitting without the use of additional tools
- Three sizes for conductor cross sections of 0.5 – 4.0 mm²
- Available in 12, 21 and 30 mm lengths.
- Additional marking space for exact project allocation
- Available as customized markers according to individual requirements



Technical data

Material: Polyamide - halogen-free
 Flammability class to UL94 V2 (Unless specified V0 in product description)
 Temperature range: -40 to 100°C

Possible printing systems: Plotter and PrintJet

Notes on mounting:

- Attach to unconnected wires and connected wires

Ordering data

Custom and standard pre-printed markers available.

Part Number	Description	Colour	Dimensions
1813130000	SFC 0/12	White	12mm Length
1813160000	SFC 0/12	Yellow	12mm Length
1813170000	SFC 0/12	Blue	12mm Length
1813150000	SFC 0/12	Red	12mm Length
1747320001	SFC 1/12	White	12mm Length
1747320004	SFC 1/12	Yellow	12mm Length
1747320002	SFC 1/12	Blue	12mm Length
1747320003	SFC 1/12	Red	12mm Length
1758320001	SFC 2/12	White	12mm Length
1758320004	SFC 2/12	Yellow	12mm Length
1758320002	SFC 2/12	Blue	12mm Length
1758320003	SFC 2/12	Red	12mm Length
1813190000	SFC 0/21	White	21mm Length
1813210000	SFC 0/21	Yellow	21mm Length
1813220000	SFC 0/21	Blue	21mm Length
1813200000	SFC 0/21	Red	21mm Length
1779080001	SFC 1/21	White	21mm Length
1779080004	SFC 1/21	Yellow	21mm Length
1779080002	SFC 1/21	Blue	21mm Length
1779080003	SFC 1/21	Red	21mm Length
1805810000	SFC 2/21	White	21mm Length
1805780000	SFC 2/21	Yellow	21mm Length
1805770000	SFC 2/21	Blue	21mm Length
1805790000	SFC 2/21	Red	21mm Length
1813240000	SFC 0/30	White	30mm Length
1813260000	SFC 0/30	Yellow	30mm Length
1813270000	SFC 0/30	Blue	30mm Length
1813250000	SFC 0/30	Red	30mm Length
1805760000	SFC 1/30	White	30mm Length
1805730000	SFC 1/30	Yellow	30mm Length
1805720000	SFC 1/30	Blue	30mm Length
1805740000	SFC 1/30	Red	30mm Length
1805870000	SFC 2/30	White	30mm Length
1805830000	SFC 2/30	Yellow	30mm Length
1805820000	SFC 2/30	Blue	30mm Length
1805850000	SFC 2/30	Red	30mm Length

Installation Products - Wire & Cable

Qty. per box	Char. per tag using Font 10	Ext. diameter of wire (mm)	AWG	Cross-section (mm ²)	
200	5 Characters	1.5 mm - 2.5 mm	20 - 16 AWG	0.5 mm ² - 1.0 mm ²	
200	5 Characters	1.5 mm - 2.5 mm	20 - 16 AWG	0.5 mm ² - 1.0 mm ²	
200	5 Characters	1.5 mm - 2.5 mm	20 - 16 AWG	0.5 mm ² - 1.0 mm ²	
200	5 Characters	1.5 mm - 2.5 mm	20 - 16 AWG	0.5 mm ² - 1.0 mm ²	
200	5 Characters	2.0 mm - 3.5 mm	18 - 12 AWG	0.75 mm ² - 2.5 mm ²	
200	5 Characters	2.0 mm - 3.5 mm	18 - 12 AWG	0.75 mm ² - 2.5 mm ²	
200	5 Characters	2.0 mm - 3.5 mm	18 - 12 AWG	0.75 mm ² - 2.5 mm ²	
200	5 Characters	2.0 mm - 3.5 mm	18 - 12 AWG	0.75 mm ² - 2.5 mm ²	
120	5 Characters	2.5 mm - 5.0 mm	12 - 10 AWG	2.5 mm ² - 4.0 mm ²	
120	5 Characters	2.5 mm - 5.0 mm	12 - 10 AWG	2.5 mm ² - 4.0 mm ²	
120	5 Characters	2.5 mm - 5.0 mm	12 - 10 AWG	2.5 mm ² - 4.0 mm ²	
120	5 Characters	2.5 mm - 5.0 mm	12 - 10 AWG	2.5 mm ² - 4.0 mm ²	
200	10 Characters	1.5 mm - 2.5 mm	20 - 16 AWG	0.5 mm ² - 1.0 mm ²	
200	10 Characters	1.5 mm - 2.5 mm	20 - 16 AWG	0.5 mm ² - 1.0 mm ²	
200	10 Characters	1.5 mm - 2.5 mm	20 - 16 AWG	0.5 mm ² - 1.0 mm ²	
200	10 Characters	1.5 mm - 2.5 mm	20 - 16 AWG	0.5 mm ² - 1.0 mm ²	
200	10 Characters	2.0 mm - 3.5 mm	18 - 12 AWG	0.75 mm ² - 2.5 mm ²	
200	10 Characters	2.0 mm - 3.5 mm	18 - 12 AWG	0.75 mm ² - 2.5 mm ²	
200	10 Characters	2.0 mm - 3.5 mm	18 - 12 AWG	0.75 mm ² - 2.5 mm ²	
200	10 Characters	2.0 mm - 3.5 mm	18 - 12 AWG	0.75 mm ² - 2.5 mm ²	
120	10 Characters	2.5 mm - 5.0 mm	12 - 10 AWG	2.5 mm ² - 4.0 mm ²	
120	10 Characters	2.5 mm - 5.0 mm	12 - 10 AWG	2.5 mm ² - 4.0 mm ²	
120	10 Characters	2.5 mm - 5.0 mm	12 - 10 AWG	2.5 mm ² - 4.0 mm ²	
120	10 Characters	2.5 mm - 5.0 mm	16 - 14 AWG	2.5 mm ² - 4.0 mm ²	
150	14 Characters	1.5 mm - 2.5 mm	20 - 16 AWG	0.5 mm ² - 1.0 mm ²	
150	14 Characters	1.5 mm - 2.5 mm	20 - 16 AWG	0.5 mm ² - 1.0 mm ²	
150	14 Characters	1.5 mm - 2.5 mm	20 - 16 AWG	0.5 mm ² - 1.0 mm ²	
150	14 Characters	1.5 mm - 2.5 mm	20 - 16 AWG	0.5 mm ² - 1.0 mm ²	
150	14 Characters	2.0 mm - 3.5 mm	18 - 12 AWG	0.75 mm ² - 2.5 mm ²	
150	14 Characters	2.0 mm - 3.5 mm	18 - 12 AWG	0.75 mm ² - 2.5 mm ²	
150	14 Characters	2.0 mm - 3.5 mm	18 - 12 AWG	0.75 mm ² - 2.5 mm ²	
150	14 Characters	2.0 mm - 3.5 mm	18 - 12 AWG	0.75 mm ² - 2.5 mm ²	
90	14 Characters	2.5 mm - 5.0 mm	12 - 10 AWG	2.5 mm ² - 4.0 mm ²	
90	14 Characters	2.5 mm - 5.0 mm	12 - 10 AWG	2.5 mm ² - 4.0 mm ²	
90	14 Characters	2.5 mm - 5.0 mm	12 - 10 AWG	2.5 mm ² - 4.0 mm ²	
90	14 Characters	2.5 mm - 5.0 mm	12 - 10 AWG	2.5 mm ² - 4.0 mm ²	

Installation Products - Protective Sleeves

TM-HF Sleeve

TM sleeves are halogen free and practically free from pollutants. The sleeves can be fitted with insert tags TM-I 12 or TM-I 18. They offer a wide range of applications for cables and wires. This system has proven particularly successful in traffic engineering. The slim design guarantees a secure attachment to the wire.

- Halogen-free
- Slim design guarantees secure attachment to the wire.



* NOTE: Use TM-I insert for marking

TMX-HF Sleeve

TMX rounds Weidmüller's extensive assortment of sleeves. By utilising cable ties, the transparent, halogen-free TMX sleeves can be fitted to any size of wire. The TMX sleeve is fitted with the insert tag TM-I 18. It is designed for a wide range of applications. The TMX sleeves are suitable for cables and wires with an external diameters from 15 mm and upwards. Cable ties guarantee secure attachment.

- Halogen-free
- Secure attachment with cable ties



* NOTE: Attach with cable ties - max. width of cable tie = 4.8 mm, use TM-I insert for marking

TM Twin Sleeve

Twin sleeves provide a two-side marking option of wires. They can be fitted with two TM-I 18 tags, so that input and output designations of a wire can be viewed from a single vantage point. The transparent, halogen-free sleeves can be used for external wire-insulation diameters from 1.3 to 4.0 mm.



* NOTE: Use TM-I insert for marking

WPT Sleeve

WPT wire and cable markers are high-quality, transparent markers available in various lengths for marking cables with cross-sections from 0.22 mm² to maximum 75 mm².

- Wider cross-section range per sleeve
- Wider application range thanks to special resilient bellow profile
- Marker tag inserts easily into marker pocket before and after wire is connected
- Available in five lengths and four sizes



* NOTE: Use TM-I insert for marking

Part Number	Description	Dimensions	Qty. per bag
1719760000	TM 0/12 HF	12mm Length	1000
1719780000	TM 1/12 HF	12mm Length	1000
1719800000	TM 2/12 HF	12mm Length	1000
1719820000	TM 3/12 HF	12mm Length	500
1719840000	TM 4/12 HF	12mm Length	500
1719860000	TM 5/12 HF	12mm Length	200
1719880000	TM 6/12 HF	12mm Length	200
1719770000	TM 0/18 HF	18mm Length	1000
1719790000	TM 1/18 HF	18mm Length	1000
1719810000	TM 2/18 HF	18mm Length	1000
1719830000	TM 3/18 HF	18mm Length	500
1719850000	TM 4/18 HF	18mm Length	500
1719870000	TM 5/18 HF	18mm Length	200
1719890000	TM 6/18 HF	18mm Length	200
1748820000	TMX	18mm Length	500
1841810000	TM 0/18 Twin HF/HB	18mm Length	500
1841780000	TM 1/18 Twin HF/HB	18mm Length	500
1764060000	WPT 02-12	12mm Length	200
1764070000	WPT 02-15	15mm Length	200
1764140000	WPT 02-18	18mm Length	200
1764150000	WPT 02-20	20mm Length	200
1889580000	WPT 02-30	30mm Length	200
1764190000	WPT 1-12	12mm Length	200
1764200000	WPT 1-15	15mm Length	200
1764210000	WPT 1-18	18mm Length	200
1764220000	WPT 1-20	20mm Length	200
1889560000	WPT 1-30	30mm Length	200
1764230000	WPT 2-12	12mm Length	200
1764240000	WPT 2-15	15mm Length	200
1764250000	WPT 2-18	18mm Length	200
1764260000	WPT 2-20	20mm Length	200
1889570000	WPT 2-30	30mm Length	200
1764270000	WPT 3-12	12mm Length	200
1764280000	WPT 3-15	15mm Length	200
1764290000	WPT 3-18	18mm Length	200
1764300000	WPT 3-20	20mm Length	200
1889550000	WPT 3-30	30mm Length	200

Installation Products - Protective Sleeves

Insert Tag *	Ext. diameter of wire (mm)	AWG	Cross-section (mm ²)		
TM-I 12	1.3 mm - 2.0 mm	20 AWG	0.22 mm ² - 0.5 mm ²		
TM-I 12	1.8 mm - 2.5 mm	18 - 14 AWG	0.5 mm ² - 1.5 mm ²		
TM-I 12	2.5 mm - 4.0 mm	16 - 12 AWG	0.75 mm ² - 2.5 mm ²		
TM-I 12	4.0 mm - 6.5 mm	12 - 8 AWG	2.5 mm ² - 6.0 mm ²		
TM-I 12	6.0 mm - 10.0 mm	6 - 1 AWG	10.0 mm ² - 35.0 mm ²		
TM-I 12	9.0 mm - 15.0 mm	2 - 0 AWG	25.0 mm ² - 70.0 mm ²		
TM-I 12	15.0 mm - 24.0 mm	1 - 0 AWG	35.0 mm ² - 150.0 mm ²		
TM-I 18	1.3 mm - 2.0 mm	20 AWG	0.22 mm ² - 0.5 mm ²		
TM-I 18	1.8 mm - 2.5 mm	18 - 14 AWG	0.5 mm ² - 1.5 mm ²		
TM-I 18	2.5 mm - 4.0 mm	16 - 12 AWG	0.75 mm ² - 2.5 mm ²		
TM-I 18	4.0 mm - 6.5 mm	12 - 8 AWG	2.5 mm ² - 6.0 mm ²		
TM-I 18	6.0 mm - 10.0 mm	6 - 1 AWG	10.0 mm ² - 35.0 mm ²		
TM-I 18	9.0 mm - 15.0 mm	2 - 0 AWG	25.0 mm ² - 70.0 mm ²		
TM-I 18	15.0 mm - 24.0 mm	1 - 0 AWG	35.0 mm ² - 150.0 mm ²		
TM-I 18	15 mm	4 - 1 AWG	up to 25 mm ²		
TM-I 18	1.3 mm - 2.6 mm	20 - 14 AWG	0.22 mm ² - 1.5 mm ²		
TM-I 18	2.4 mm - 4.0 mm	16 - 10 AWG	1.0 mm ² - 2.5 mm ²		
TM-I 12	1.3 mm - 3.0 mm	20 - 14 AWG	0.22 mm ² - 1.5 mm ²		
TM-I 15	1.3 mm - 3.0 mm	20 - 14 AWG	0.22 mm ² - 1.5 mm ²		
TM-I 18	1.3 mm - 3.0 mm	20 - 14 AWG	0.22 mm ² - 1.5 mm ²		
TM-I 20	1.3 mm - 3.0 mm	20 - 14 AWG	0.22 mm ² - 1.5 mm ²		
TM-I 30	1.3 mm - 3.0 mm	20 - 14 AWG	0.22 mm ² - 1.5 mm ²		
TM-I 12	2.5 mm - 5.0 mm	18 - 10 AWG	0.75 mm ² - 6.0 mm ²		
TM-I 15	2.5 mm - 5.0 mm	18 - 10 AWG	0.75 mm ² - 6.0 mm ²		
TM-I 18	2.5 mm - 5.0 mm	18 - 10 AWG	0.75 mm ² - 6.0 mm ²		
TM-I 20	2.5 mm - 5.0 mm	18 - 10 AWG	0.75 mm ² - 6.0 mm ²		
TM-I 30	2.5 mm - 5.0 mm	18 - 10 AWG	0.75 mm ² - 6.0 mm ²		
TM-I 12	4.0 mm - 10.0 mm	10 - 1 AWG	4.0 mm ² - 35.0 mm ²		
TM-I 15	4.0 mm - 10.0 mm	10 - 1 AWG	4.0 mm ² - 35.0 mm ²		
TM-I 18	4.0 mm - 10.0 mm	10 - 1 AWG	4.0 mm ² - 35.0 mm ²		
TM-I 20	4.0 mm - 10.0 mm	10 - 1 AWG	4.0 mm ² - 35.0 mm ²		
TM-I 30	4.0 mm - 10.0 mm	10 - 1 AWG	4.0 mm ² - 35.0 mm ²		
TM-I 12	8.0 mm - 16.0 mm	8 - 0 AWG	6.0 mm ² - 75.0 mm ²		
TM-I 15	8.0 mm - 16.0 mm	8 - 0 AWG	6.0 mm ² - 75.0 mm ²		
TM-I 18	8.0 mm - 16.0 mm	8 - 0 AWG	6.0 mm ² - 75.0 mm ²		
TM-I 20	8.0 mm - 16.0 mm	8 - 0 AWG	6.0 mm ² - 75.0 mm ²		
TM-I 30	8.0 mm - 16.0 mm	8 - 0 AWG	6.0 mm ² - 75.0 mm ²		

* See page F.20 for inserts

Installation Products

F

Installation Products - Protective Sleeves

ESG Insert

ESG is the proven marker in MultiCard format for many well-known electrical devices. The result is high-quality device markings with a contrast-rich appearance.

We offer versions for the devices produced by the following manufacturers:

- ABB
- Siemens
- Moeller
- Télémécanique
- For universal use, self-adhesive or clip-on tags are available (depending on the type)

ESG for clipping onto tag rails; suitable for devices mounted in rows, such as miniature circuit-breakers.



WPF Insert


WPF insert tags are made from a halogen-free polyester material. The perforated edges ensure the tags can easily be separated from the A4 sheets in which they are supplied. The pre-print treated material guarantees rapid and permanent marking by means of laser, matrix print.



TM-I Insert

Easy to fit and secure attachment thanks to the special contour of the TM-I. They are compatible with numerous commercially available sleeves. The MultiCard format means that the tags can be rapidly and easily printed with the printing systems, PrintJet, Plotter, or the STI pen. Thanks to the project marker surface of the MultiCard, they can easily be separated and then attached. There are five marker lengths available for custom prints with long sequences of characters.

- Project marker surface for easy separation & attachment
- Approved and listed markers for traffic engineering
- Top flexibility through advanced attachment of sleeve and retrospective fitting of tags



Technical Data

Material: ESG, TM-I - Polyamide - halogen-free, ESO - Paper or Polyester, WPF - Polyester foil - halogen-free
 Flammability class to UL94 V2 (Unless specified V0 in product description)
 Temperature range: ESG, TM-I -40 to 100°C, WPF -30 to 120°C, ESO -40 to 80°C.

Possible printing systems: ESO, WPF - Laser Printer, ESG, TM-I - Plotter and PrintJet

Notes on mounting:

- Insert into protective sleeve

Ordering data

Custom and standard pre-printed markers available.

Part Number	Description	Colour	Dimensions
1736181044	ESG 7/20	White	20mm Length, Width 7mm
1724760000	ESG 9/17	White	17mm Length, Width 9mm
1607720000	ESO 7 - Paper	White	6.3mm Length, Width 27mm
1634780000	ESO 7 - Paper	Yellow	6.3mm Length, Width 27mm
1670390000	ESO 7 - Polyester	White	6.3mm Length, Width 27mm
1670400000	ESO 7 - Polyester	Yellow	6.3mm Length, Width 27mm
1607710000	ESO 5 - Paper	White	16.5mm Length, Width 40mm
1631350000	ESO 5 - Paper	Yellow	16.5mm Length, Width 40mm
1670370000	ESO 5 - Polyester	White	16.5mm Length, Width 40mm
1670380000	ESO 5 - Polyester	Yellow	16.5mm Length, Width 40mm
1919890000	ESO 8/20 Paper	White	20mm Length, Width 7mm
1919900000	ESO 8/20 Paper	Yellow	20mm Length, Width 7mm
1919870000	ESO 8/20 Polyester	White	20mm Length, Width 7mm
1919880000	ESO 8/20 Polyester	Yellow	20mm Length, Width 7mm
1764050000	WPF 2/17.5	White	17.5mm Length
1600740000	WPF 1/20	White/Yellow	20mm Length
1718411044	TM-I 12	White	12mm Length, 4mm Width
1718411686	TM-I 12	Red	12mm Length, 4mm Width
1718411687	TM-I 12	Yellow	12mm Length, 4mm Width
1718411688	TM-I 12	Green	12mm Length, 4mm Width
1718411693	TM-I 12	Blue	12mm Length, 4mm Width
1609981044	TM-I 15	White	15mm Length, 4mm Width
1609981686	TM-I 15	Red	15mm Length, 4mm Width
1609981687	TM-I 15	Yellow	15mm Length, 4mm Width
1609981688	TM-I 15	Green	15mm Length, 4mm Width
1609981693	TM-I 15	Blue	15mm Length, 4mm Width
1718431044	TM-I 18	White	18mm Length, 4mm Width
1718431686	TM-I 18	Red	18mm Length, 4mm Width
1718431687	TM-I 18	Yellow	18mm Length, 4mm Width
1718431688	TM-I 18	Green	18mm Length, 4mm Width
1718431693	TM-I 18	Blue	18mm Length, 4mm Width
1680411044	TM-I 20	White	20mm Length, 4mm Width
1680411686	TM-I 20	Red	20mm Length, 4mm Width
1680411687	TM-I 20	Yellow	20mm Length, 4mm Width
1680411688	TM-I 20	Green	20mm Length, 4mm Width
1680411693	TM-I 20	Blue	20mm Length, 4mm Width
1876390000	TM-I 30	White	30mm Length, 4mm Width
1876380000	TM-I 30	Red	30mm Length, 4mm Width
1876370000	TM-I 30	Yellow	30mm Length, 4mm Width
1876400000	TM-I 30	Blue	30mm Length, 4mm Width

Installation Products - Protective Sleeves

Qty. per box	Char. per tag using Font 10	Fits Into		
200	10 Characters	WPM		
200	8 Characters	WPM		
1 Sheet (240 Tags)	4 Characters	WKM		
1 Sheet (240 Tags)	4 Characters	WKM		
1 Sheet (240 Tags)	4 Characters	WKM		
1 Sheet (240 Tags)	4 Characters	WKM		
1 Sheet (60 Tags)	8 Characters	WKM		
1 Sheet (60 Tags)	8 Characters	WKM		
1 Sheet (60 Tags)	8 Characters	WKM		
1 Sheet (60 Tags)	8 Characters	WKM		
1 Sheet (342 Tags)	5 Characters	WKM		
1 Sheet (342 Tags)	5 Characters	WKM		
1 Sheet (342 Tags)	5 Characters	WKM		
1 Sheet (342 Tags)	5 Characters	WKM		
1 Sheet (352 Tags)	8 Characters	WPT, WPM		
1 Sheet (594 Tags)	10 Characters	WPT, WPM		
320	5 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
320	5 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
320	5 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
320	5 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
320	5 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
400	7 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
400	7 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
400	7 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
400	7 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
400	7 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
320	8 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
320	8 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
320	8 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
320	8 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
320	8 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
400	9 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
400	9 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
400	9 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
400	9 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
400	9 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
300	14 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
300	14 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
300	14 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		
300	14 Characters	TM-HF, TMX-HF TM Twin Sleeve, WPT, WPM		

Installation Products - Equipment Markers


ESG

ESG is the proven marker in MultiCard format for many well-known electrical devices. The result is high-quality device markings with a contrast-rich appearance.

We offer versions for the devices produced by the following manufacturers:

- ABB
- Siemens
- Moeller
- Télémécanique
- For universal use, self-adhesive or clip-on tags are available (depending on the type)

ESG for clipping onto tag rails; suitable for devices mounted in rows, such as miniature circuit-breakers.



Tag Rail



Part Number	Description	Colour	Dimensions
1919940000	ESG 5/10 MC	White	10mm Length, 5mm Width
1880130000	ESG 6/15 K MC	Yellow	15mm Length, 6mm Width
1880100000	ESG 6/15 K MC	White	15mm Length, 6mm Width
1881280000	ESG 6/15 K MC - RIDERSERIES	White	15mm Length, 6mm Width
1880110000	ESG 6/17 K MC	Yellow	17mm Length, 6mm Width
1880120000	ESG 6/17 K MC	White	17mm Length, 6mm Width
1736181687	ESG 7/20 SIRIUS MC	Yellow	20mm Length, 7mm Width
1736181044	ESG 7/20 SIRIUS MC	White	20mm Length, 7mm Width
1736181696	ESG 7/20 SIRIUS MC	Turquoise	20mm Length, 7mm Width
1736190000	ESG 8/10 ASI	White	10mm Length, 8mm Width
1674740000	ESG 8/17 MC	White	17mm Length, 8mm Width
1755340000	ESG 8/17 SYS PRO M	White	17mm Length, 8mm Width
1720610000	ESG 8/17 SCHS MC	White	17mm Length, 8mm Width
1890470000	ESG 8/17 L MC	White	17mm Length, 8mm Width
1652220000	ESG 8/19 MC	White	19mm Length, 8mm Width
1775910000	ESG 9/10 MC	White	10mm Length, 9mm Width
1857440000	ESG 9/11 K MC	White	11mm Length, 9mm Width
1753500000	ESG 9/17 K MC	Yellow	17mm Length, 9mm Width
1674760000	ESG 9/17 K MC	White	17mm Length, 9mm Width
1856700000	ESG 10/17 MC	White	17mm Length, 10mm Width
1890460000	ESG 9/20 L MC	White	20mm Length, 9mm Width
1766160000	ESG 9/20 K MC	Yellow	20mm Length, 9mm Width
1609940000	ESG 9/20 K MC	White	20mm Length, 9mm Width
1856720000	ESG 9/20 MC Universal	Transparent	20mm Length, 9mm Width
0138900000	Tag rail SchS1	Black	1m Length
0337400000	Tag rail SchS2	Black	1m Length
1720600000	Tag rail SchS2, self-adhesive	Black	1m Length
1753480000	Tag rail SchS3 , self-adhesive	White	1m Length
1753460000	Tag rail SchS3, self-adhesive	Grey	1m Length
0139000000	ESO/SCHS1	White	0.5m Length, 12.5mm Width
0139200000	STR SCHS1	Transparent	0.5m Length, 12.5mm Width

Installation Products - Equipment Markers

Qty. per box	Char. per tag using Font 10	Application		
400	5 Characters	Turck/Beckhoff SAI distributor		
200	7 Characters	Self-adhesive		
200	7 Characters	Self-adhesive		
200	7 Characters	Riderseries SCM/SRC		
200	8 Characters	Self-adhesive		
200	8 Characters	Self-adhesive		
200	9 Characters	Siemens 3R / tag rail SchS3/4		
200	9 Characters	Siemens 3R / tag rail SchS3/4		
200	9 Characters	Siemens 3R / tag rail SchS3/4		
200	4 Characters	Siemens AS-interface		
200	8 Characters	Télemécanique		
200	8 Characters	GE power Controls (AEG) ABB-Stotz		
200	8 Characters	Tag rail SchS2		
200	8 Characters	Lumberg distributor (SAI)		
200	9 Characters	AEG		
200	4 Characters			
200	4 Characters	Self-adhesive		
200	8 Characters	Self-adhesive		
200	8 Characters	Self-adhesive		
200	8 Characters	Allen Bradley / Festo MT		
200	9 Characters	Lumberg distributor		
200	9 Characters	Siemens + Moeller+WI SAI distributor		
200	9 Characters	Siemens + Moeller+WI SAI distributor		
200	9 Characters	Siemens + Moeller+WI and		
1m		for ESO with protective strip		
1m		for ESG 18/17 S DEK WS		
1m		for ESG 18/17 S DEK WS		
1m		for ESG 7/20		
1m		for ESG 7/20		
0.5m		Insert strips for SCHS1		
0.5m		Protective strip for SCHS1		

Installation Products - Equipment Markers

SwitchMark (SM)

SwitchMark (SM) markers are used to identify command and signalling devices. The tags are either snapped into the holder or secured by means of the self-adhesive foil on their rear. Individual custom prints can be created using the printing system, PrintJet or Plotter.

- Create individual custom prints utilising Weidmüller's marking system for MultiCards.
- Fast production of custom prints to in-house specifications.
- No need to store expensive standard tags.
- Extremely resistant print quality with PrintJet instead of engraving.
- We recommend the protective foil ETO SM for extreme conditions.



SwitchMark Accessories - Holders (SM-H)

The device and installation markers are either snapped into the holder or secured by means of the self-adhesive foil on their rear.

- For example: insert the SM 27/18 into the holder that we offer as well as the markers
- We recommend that the transparent protective foil ETO SM be used if the print is subjected to extreme demands with respect to their wipe and scratch resistance in the presence of chemicals



*Note: For ø22mm push buttons

SwitchMark Accessories - Protective Foils (ETO-SM)



*Note: Details in round brackets indicate the number of markers per sheet

ClipCard (CC)

ClipCard device markers in MultiCard format offer an interesting alternative to **engraving**. This assortment is used to mark electrical installations and switchgear. The proven MultiCard format means it is possible to print with any of the PrintJet and Plotter printers.

- Extremely resilient print quality with PrintJet instead of engraving
- Universal attachment
 - Holder (screw attachment or with cable tie)
 - Tag rail (self-adhesive and screw attachment)
 - or self-adhesive markers

Part Number	Description	Colour	Dimensions
1699840000	SM 27/12.5	White	27mm Length, 12.5mm Width
1713700000	SM 27/12.5	Silver	27mm Length, 12.5mm Width
1699860000	SM 27/18	White	27mm Length, 18mm Width
1713740000	SM 27/18	Silver	27mm Length, 18mm Width
1773220000	SM 27/27	White	27mm Length, 27mm Width
1773230000	SM 27/27	Silver	27mm Length, 27mm Width
1812630000	SM 27/8 K	White	27mm Length, 8mm Width
1771930000	SM 27/8 K	Silver	27mm Length, 8mm Width
1699880000	SM 27/12.5 K	White	27mm Length, 12.5mm Width
1713720000	SM 27/12.5 K	Silver	27mm Length, 12.5mm Width
1707270000	SM 27/18 K	White	27mm Length, 18mm Width
1713760000	SM 27/18 K	Silver	27mm Length, 18mm Width
1877570000	SM 22/22 K	White	22mm Length, 22mm Width
1877590000	SM 22/22 K	Silver	22mm Length, 22mm Width
1783000000	SM 27/27 K	White	27mm Length, 27mm Width
1782990000	SM 27/27 K	Silver	27mm Length, 27mm Width
1716640000	SM-H 27/12.5		41.6mm Length, 29.5mm Width
1716630000	SM-H 27/18		49.8mm Length, 29.5mm Width
1782710000	SM-H 27/27		59.3mm Length, 29.5mm Width
1812630000	ETO SM 27/8		27mm Length, 8mm Width
1699880000	ETO SM 27/12.5		27mm Length, 12.5mm Width
1707270000	ETO SM 27/18		27mm Length, 18mm Width
1877570000	ETO SM 22/22		22mm Length, 22mm Width
1783000000	ETO SM 27/27		27mm Length, 27mm Width
1876570000	CC 15/17 MC	White	17mm Length, 15mm Width
1876610000	CC 15/17 MC	Silver	17mm Length, 15mm Width
1876770000	CC 15/27 MC	White	27mm Length, 15mm Width
1876760000	CC 15/27 MC	Silver	27mm Length, 15mm Width
1877260000	CC 15/49 MC	White	49mm Length, 15mm Width
1877240000	CC 15/49 MC	Silver	49mm Length, 15mm Width

Installation Products -Equipment Markers

Qty. per box	Char. per tag using Font 10	Application		
80		SM-H 27/12.5		
80		SM-H 27/12.5		
80		SM-H 27/18		
80		SM-H 27/18		
60		SM-H 27/27		
60		SM-H 27/27		
80		Self-adhesive		
80		Self-adhesive		
80		Self-adhesive		
80		Self-adhesive		
80		Self-adhesive		
80		Self-adhesive		
80		Self-adhesive		
80		Self-adhesive		
80		Self-adhesive		
60		Self-adhesive		
60		Self-adhesive		
25		SM 27/12.5		
25		SM 27/18		
20		SM 27/27		
1 (165)		SM 27/8, SM 27/8 K		
1 (100)		SM 27/12.5, SM 27/12.5 K		
1 (112)		SM 27/18, SM 27/18 K		
1 (112)		SM 22/22 K		
1 (70)		SM 27/27, SM 27/27 K		
80		CC-H 15/17		
80		CC-H 15/17		
80		CC-H 15/27		
80		CC-H 15/27		
40		CC-H 15/49		
40		CC-H 15/49		

Installation Products - Equipment Markers

ClipCard (CC) - continued

- For extreme conditions, we recommend:
 - Protective strips (holder)
 - Protective rail (CC-Rail)
 - Protective foil for markers



Part Number	Description	Colour	Dimensions
1877350000	CC 15/60 MC	White	60mm Length, 15mm Width
1877340000	CC 15/60 MC	Silver	60mm Length, 15mm Width
1934420000	CC 30/60 MC	White	60mm Length, 30mm Width
1934400000	CC 30/60 MC	Silver	60mm Length, 30mm Width
1876590000	CC 15/17 K MC	White	17mm Length, 15mm Width
1876580000	CC 15/17 K MC	Silver	17mm Length, 15mm Width
1876640000	CC 15/27 K MC	White	27mm Length, 15mm Width
1876780000	CC 15/27 K MC	Silver	27mm Length, 15mm Width
1877220000	CC 15/49 K MC	White	49mm Length, 15mm Width
1877270000	CC 15/49 K MC	Silver	49mm Length, 15mm Width
1877310000	CC 15/60 K MC	White	60mm Length, 15mm Width
1877360000	CC 15/60 K MC	Silver	60mm Length, 15mm Width
1934390000	CC 30/60 K MC	White	60mm Length, 30mm Width
1934330000	CC 30/60 K MC	Silver	60mm Length, 30mm Width

F

ClipCard - Holders (CC-H)

Universal attachment options with the possibility of being mounted either in a holder, per cable tie or screw as well as by utilising CC-Rail tag rails.

- Universal attachment options: per holder, cable tie or screw as well as by means of a tag rail
- For extreme conditions, we recommend:
 - Protective strips (holder)
 - Protective rail (CC-Rail)
 - Protective foil for markers



1790430000	CC-H 15/17	Black	
1790410000	CC-H 15/27	Black	
1790420000	CC-H 15/49	Black	
1878910000	CC-H 15/60	Black	
1934430000	CC-H 30/60	Black	

ClipCard - Protective Strips (STR CC)



1888310000	STR CC 15/17	Transparent	17mm Length, 15mm Width
1888290000	STR CC 15/27	Transparent	27mm Length, 15mm Width
1888300000	STR CC 15/49	Transparent	49mm Length, 15mm Width
1888280000	STR CC 15/60	Transparent	60mm Length, 15mm Width
1934450000	STR CC 30/60	Transparent	60mm Length, 30mm Width

ClipCard - Protective Foils & Tag Rail (ETO CC)



*NOTE: Details in round brackets indicate the number of markers per sheet

1880850000	ETO CC 15/17	Transparent	17mm Length, 15mm Width
1880810000	ETO CC 15/27	Transparent	27mm Length, 15mm Width
1880830000	ETO CC 15/49	Transparent	49mm Length, 15mm Width
1880840000	ETO CC 15/60	Transparent	60mm Length, 15mm Width
1934440000	ETO CC 30/60	Transparent	60mm Length, 30mm Width

Technical Data

Material: ESG - Polyamide halogen-free, SwitchMark - Polyamide 66 halogen-free, ClipCard - Polyamide 66 halogen-free
 Flammability class to UL94 V2 (Unless specified V0 in product description)
 Temperature range: -40 to 100°C
 Adhesive force on stainless steel: K = normal adhesive 22 N/m
 Possible printing systems: Plotter and PrintJet

Ordering data

Custom and standard pre-printed markers available.

1790150000	CC-Rail 1000	Black	1m Length
1790160000	CC-Rail 1000	Transparent	1m Length

Installation Products - Equipment Markers

Qty. per box	Char. per tag using Font 10	Application		
40	27 Characters	CC-H 15/60		
40	27 Characters	CC-H 15/60		
30	27 Characters	CC-H 30/60		
30	27 Characters	CC-H 30/60		
80	8 Characters	Self-adhesive		
80	8 Characters	Self-adhesive		
80	12 Characters	Self-adhesive		
80	12 Characters	Self-adhesive		
40	20 Characters	Self-adhesive		
40	20 Characters	Self-adhesive		
40	27 Characters	Self-adhesive		
40	27 Characters	Self-adhesive		
30	27 Characters	Self-adhesive		
30	27 Characters	Self-adhesive		
75		CC 15/17 MC		
45		CC 15/27 MC		
25		CC 15/49 MC		
25		CC 15/60 MC		
10		CC 30/60 MC		
80		CC 15/17 MC, CC-H 15/17		
80		CC 15/27 MC, CC-H 15/27		
40		CC 15/49 MC, CC-H 15/49		
40		CC 15/60 MC, CC-H 15/60		
10		CC 30/60 MC, CC-H 30/60		
1 (228)		CC 15/17 MC		
1 (133)		CC 15/27 MC		
1 (76)		CC 15/49 MC		
1 (57)		CC 15/60 MC		
1 (27)		CC 30/60 MC		
1		CC 15/17 MC, CC 15/27 MC, CC 15/49 MC, CC 15/60 MC		
1		CC-Rail 1000		

Installation Products - Printers

PrintJet II

The **PrintJet** printer allows you to print customised marker prints for terminal blocks, switchgear, cables, wires and circuit-breakers at your convenience.

- Sharp print contours
- High-contrast typeface
- Extremely resilient lettering
- Permanently readable identification
- Fast and user friendly
- Compatible with all MultiCards
- The PrintJet-Loader holds up to 20 MultiCards



Technical data

Type	PrintJet II
Application	Prints MultiCard markers
Technology	Ink-jet process
Print quality	2880 dpi
Printer drivers	Win 9X, Win NT, Windows 2000
Print software	Recommended: M-Print 1.60
System requirements	Windows 95/98/NT/2000/XP
Feed	Manual or with optional loader
Fusing	Thermal fusing
Interface	Centronics and USB
Connection	AC 230 V/AC 115 V
Location	Office conditions
Ambient temperature	20 °C – 35 °C
Dimensions (L x W x H)	800 x 450 x 200 mm
Cartridge system	Ink cartridge, black (210 000 characters, Arial font size 6); average print performance per day: 20 MultiCards; max. print performance per day: 100 MultiCards
Range of supply	PrintJet printer, power cable, printer drivers, manuals (CD), cleaning unit, Centronics cable, software M-Print

PrintJet-Loader

System requirements	PrintJet printer
Marker types	MultiCard format
Operating voltage	12 V/DC
Current input	approx. 1 A
Interface	Connection via plug-in connector
Location	Office conditions
Ambient temperature	20 °C – 35 °C
Dimensions (L x W x H)	345 x 305 x 155 mm
Weight	4 kg

Ordering data


Type	PrintJet II Order No.
PrintJet II 115 V	1858980000
PrintJet-Loader	1813090000
Accessories	
Ink cartridge PrintJet II	1858920000
Clean Unit PrintJet II	1858950000

MCP Plus

Plotter complements the Weidmüller MultiCard concept. It is suitable for smaller quantities of markers and when only part of a MultiCard is to be printed on. The special positioning frame for five MultiCards increases productivity by 20 % over comparable systems. With the positioning frame for SlimFix markers sizes 4 to 6, printing on more than 120 MultiCard types for terminals, cables, wires and equipment is possible. Labels are printed with the MCP-Label positioning frame. Suitable for use with the Weidmüller **M-Print® PRO** software.

- 2 positioning frames for more than 120 MultiCard types
- MultiCards easily fitted into the frame
- Easy to use with partly used MultiCards
- Automatic pen activation function
- Safe storage of the plotter pens

Plotter



MCP Plus

Technical data

Type	Plotter
Application	printing of MultiCard markers and labels
Technology	plotting technique
Print software	M-Print® PRO
System requirements	Windows 95/98/NT/2000/XP
Interface	Parallel Centronics, USB
Power supply	230/115 V AC
Feed	manual
Location	office conditions
Ambient	temperature 10 °C – 35 °C
Dimensions (L x W x H)	660 x 440 x 125 mm
Weight	approx. 8 kg
Scope of supply	MCP Plus with Centronics cable, power pack (100-240 V AC/ 50-60 Hz), Euro and US plugs, MultiCard positioning frame, 0.25 mm plotter pen, M-Print® PRO software and manual

Ordering data

Type	MCP Plus
MCP Plus plotter set	Order no. 1925000000

Ordering data

Type	For	Qty	MCP positioning frames
MCP pos. frame	MultiCards	1	Order no. 1924360000
MCP pos. frame	SF 4-6 SlimFix sizes 4 to 6	1	Order no. 1924310000
MCP pos. frame	Labels	1	Order no. 1924370000

Ordering data

Type	For	Qty	MCP plotter pens
Plotter pen 0.18	Reusable pen	1	Order no. 1768570000
Plotter pen 0.25	Reusable pen	1	Order no. 1768540000
Plotter pen 0.25	P ink Disposable pen 8 ml	1	Order no. 1920640000
Plotter pen 0.35	Reusable pen	1	Order no. 1768550000
Plotter pen 0.35	P ink Disposable pen 8 ml	1	Order no. 1920650000
Plotter pen 0.50	Reusable pen	1	Order no. 1768560000

Ordering data

Type	Qty	Order no.	MCP ink
P ink	22 ml	1	Order no. 1924340000
MCD ink	22 ml	1	Order no. 1684470000

Ordering data

Type	Qty	Order no.	MCP miscellaneous
P cleaner	22 ml	1	Order no. 1924330000
MCD cleaner	22 ml	1	Order no. 1684460000
MCP cover		1	Order no. 1924350000

Ordering data

Type	Qty	Order no.
Adapter aluminium STI pen	1	17624400000
STI pen SW	10	05084000000

Adapter for STI-S




STI-S pen with adapter

Installation Products - Software


M-Print®

M-Print® PRO Label Designer



Print and ordering software for markers and labels.

M-Print® PRO is a professional software for printing and ordering Weidmüller markers and labels under Windows®. This software helps you to optimise your processes for marking electrical equipment. You can design, print and order your marking material effortlessly, professionally and quickly: texts, frames, lines, graphics, barcodes, serial numbers and photos.



M-Print

- The software solution for labelling markers or labels and for cutting own label formats. .

M-Print is the universal labelling program for plotters and printers.

F

In conjunction with the MCP Plus Plotter and the PrintJet, all MultiCard varieties can be printed.

All configurations are clearly divided into 3 different areas. There is a choice of conductor markers, equipment markers and terminal markers. Data input is simplified through the MC mat, presented in its original form. All TrueType fonts can be used if the text information output is on a Windows printer.

The most up-to-date versions of the program may be found on the Internet at www.m-print.de

M-Print makes marking easy.

Ordering data

Type	Order No.
M-Print (multilingual version)	1784560000

Only software available in 16 bit format for use on old operating Windows systems. (Administrative rights reserved for NT and above versions).

Here is an overview of the main functions:

- Integrated product catalogue for all labels and markers, including images and links to the relevant web pages and product data sheets
- Markers and labels can be designed in as many levels as required
- Custom formatting of individual text characters (RTF)
- Perform copy-and-paste functions with texts and their formats
- Supports UNICODE for foreign-language texts, such as Russian, Chinese, Polish, etc.
- Enter data in labels and table sheet
- Permanent print preview: see how the printout will look during design phase
- Alphanumeric counts and sequences
- Extensive range of image formats (*.bmp, *.wmf, *.png, *.ico, *.jpeg, *.tif, *.gif)
- Image library including all of the important symbols used in electrical engineering
- Assign product to specific printer; for example, ESG 9/20 to PrintJet, LaserMark to laser printer, etc.
- Supported output devices: PrintJet II, ThermoCard, THM as well as standard printers with Windows drivers
- Optimum and rapid adjustment of the output devices
- Online update service via Internet
- Interface to RailDesigner®
- Import assistant to create your own import filter for numerous file formats (*.txt, *.asc, *.mak, *.wei, *.tmf, etc.)
- Integrates data from CAE systems

Supported operating systems:

WINDOWS® 98 SE, ME, NT, 2000, XP

System requirements:

- RAM: > 64 MB
- Processor: > Pentium III or comparable model
- Graphic: > 800 x 600 pixels with 256 colours optimum: 1024 x 768 with 16-bit High Colour
- Hard disk: > 90 MB free storage
- Miscellaneous: mouse, keyboard, CD-ROM drive (to install the software)

M-Print® PRO is available in two editions:

M-Print® PRO Standard Edition for professional printing results with all of Weidmüller's marking materials

M-Print® PRO Advanced Edition for professional printing results with all of Weidmüller's marking materials and customer specific labels

Ordering data

Type	Order No.
M-Print® PRO	1905490000

RailDesigner™ Software

For planning and ordering rail assemblies.



When it comes to optimizing planning and ordering terminal rail assemblies, Weidmüller's RailDesigner software has proven itself to be a real time saver. True-to-detail display of products and an easy-to-use graphic user interface distinguish Weidmüller's RailDesigner software from other packages.


RailDesigner software provides you with:

- Complete product information and search functions that enable the user to quickly and easily select the necessary products through intelligent database queries and product libraries.
- Product libraries that can be customized to contain products Weidmüller offers for your specific requirements.
- Product images in flat and expanded views; add them to the rail assembly with the click of a mouse or the touch of a button.

And with the RailDesigner software, you won't make a mistake because errors are quickly detected and brought to the user's attention via the "Installation" function. Weidmüller's RailDesigner software is easy to learn and comes with a multimedia tutorial.


Advantages:

- Graphics user guidance and true-to-detail user interface
- On-line updates and service
- Intuitive commands through Windows® standard functions and clear menu structure
- Quick article selection through intelligent database queries and article libraries
- Ordering of terminal rails directly by email
- Multimedia tutorial for self-instruction
- Export/import interface to standard file formats (i.e. DXF, ASCII, Bitmap, etc.)
 - Bitmap export allows anyone to view a design with standard photo editing software




1. First Select

- Over 5,000 parts to select from
- Print out data sheet of selected parts




2. Then Build

- Assign products to the rail
- Jumper
- Insert customer specific components (i.e. contactors, interface boards, etc.)



3. Now Order

- Contact local authorized Weidmüller distributor



Notes

Industrial Ethernet

Industrial Ethernet	
Unmanaged Switches	G.2
Media Converters	G.3
Managed Switches	G.4
Routers	G.5
Connectivity	G.5

Industrial Ethernet - Unmanaged Switches

Unmanaged Switches					
					
Number of Ports	5x RJ45	5 x RJ45	8 x RJ45	8 x RJ45	4 x RJ45, 2 SC
Data Rate	10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps
Segment Length	100m	100m	100m	100m	100m RJ45, 2km Fibre
Input Voltage	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac
Input Power	5 watts dc, 5VA ac	5 watts dc, 5VA ac	5 watts dc, 5VA ac	6 watts dc, 6VA ac	6 watts dc, 6VA ac
Operating Temp	0°C - +60°C	0°C - +60°C	0°C - +60°C	0°C - +60°C	0°C - +60°C
Dimensions (LxWxH)	116 x 25.4 x 70mm	100 x 90 x 24.6mm	116 x 44.1 x 98mm	156 x 44 x 164.5mm	156 x 44 x 164.5mm
Part Number	8808230000	8833790000	8829430000	8808240000	8808250000
Type	IE-SW5-ECO	IE-SW5-ECO-FLAT	IE-SW8-ECO	IE-SW8	IE-SW4/2SC
Approvals	cULus, CE	cULus, CE	cULus, CE	cULus, CE	cULus, CE
Features	Auto MDIX Auto Negociation	Auto MDIX Auto Negociation	Auto MDIX Auto Negociation Redundant Power Supply	4K Mac addresses Auto Negociation Redundant Power Supply	4K Mac addresses Auto Negociation Redundant Power Supply

Unmanaged Switches					
					
Number of Ports	24 x RJ45	22 x RJ45, 2 SC	22 x RJ45, 2 ST		
Data Rate	10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps		
Segment Length	100m	100m RJ45, 2km Fibre	100m RJ45, 2km Fibre		
Input Voltage	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac		
Input Power	20 watts dc, 20VA ac	20 watts dc, 20VA ac	20 watts dc, 20VA ac		
Operating Temp	-40°C - +75°C	-40°C - +75°C	-40°C - +75°C		
Dimensions (LxWxH)	140 x 44 x 156mm	140 x 44 x 156mm	140 x 44 x 156mm		
Part Number	8808300000	8808310000	8808320000		
Type	IE-SW24	IE-SW22/2SC	IE-SW22/2ST		
Approvals	cULus, CE	cULus, CE	cULus, CE		
Features	4K Mac addresses / 8 ports Auto Negociation, Auto MDIX Redundant Power Supply Status Relay	4K Mac addresses / 8 ports Auto Negociation, Auto MDIX Redundant Power Supply Status Relay	4K Mac addresses / 8 ports Auto Negociation, Auto MDIX Redundant Power Supply Status Relay		

Industrial Ethernet - Unmanged Switches & Media Converters

Unmanaged Switches					
					
4 x RJ45, 2 ST	16 x RJ45	14 x RJ45, 2 SC	14 x RJ45, 2 ST		
10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps		
100m RJ45, 2km Fibre	100m	100m RJ45, 2km Fibre	100m RJ45, 2km Fibre		
10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac		
6 watts dc, 6VA ac	20 watts dc, 20VA ac	20 watts dc, 20VA ac	20 watts dc, 20VA ac		
0°C - +60°C	-40°C - +75°C	-40°C - +75°C	-40°C - +75°C		
156 x 44 x 164.5mm	156 x 44 x 164.5mm	156 x 44 x 164.5mm	156 x 44 x 164.5mm		
8808260000	8808270000	8808280000	8808290000		
IE-SW4/2ST	IE-SW16	IE-SW14/2SC	IE-SW14/2ST		
cULus, CE	cULus, CE	cULus, CE	cULus, CE		
4K Mac addresses Auto Negociation Redundant Power Supply	4K Mac addresses / 8 ports Auto Negociation, Auto MDIX Redundant Power Supply Status Relay	4K Mac addresses / 8 ports Auto Negociation, Auto MDIX Redundant Power Supply Status Relay	4K Mac addresses / 8 ports Auto Negociation, Auto MDIX Redundant Power Supply Status Relay		
Media Converters					
					
Number of Ports	2 x RJ45, 1 x SC	2 x RJ45, 1 x ST			
Data Rate	10 / 100 Mbps	10 / 100 Mbps			
Segment Length	100m RJ45, 2 km Fibre	100m RJ45, 2 km Fibre			
Input Voltage	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac			
Input Power	4 watts dc, 4VA ac	4 watts dc, 4VA ac			
Operating Temp	0°C - +60°C	0°C - +60°C			
Dimensions (LxWxH)	79 x 40 x 85mm	79 x 40 x 85mm			
Part Number	8808220000	8808190000			
Type	IE-MC-SC	IE-MC-ST			
Approvals	cULus, CE	cULus, CE			
Features	MDI and MDIX RJ45 Inputs Auto Negotiation Redundant power supply inputs Invisible to other network components Full / Half duplex configurable	MDI and MDIX RJ45 Inputs Auto Negotiation Redundant power supply inputs Invisible to other network components Full / Half duplex configurable			




Industrial Ethernet - Managed Switches

Managed Switches					
Number of Ports	8x RJ45	6 x RJ45, 2 x SC	6 x RJ45, 2 x ST	16 x RJ45	14 x RJ45, 2 SC
Data Rate	10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps
Segment Length	100m	100m RJ45, 2 km Fibre	100m RJ45, 2 km Fibre	100m	100m RJ45, 2km Fibre
Input Voltage	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac
Input Power	20 watts dc, 20VA ac	20 watts dc, 20VA ac	20 watts dc, 20VA ac	20 watts dc, 20VA ac	20 watts dc, 20VA ac
Operating Temp	-40°C - +75°C	-40°C - +75°C	-40°C - +75°C	-40°C - +75°C	-40°C - +75°C
Dimensions (LxWxH)	156 x 44 x 164.5mm	156 x 44 x 164.5mm	156 x 44 x 164.5mm	156 x 44 x 164.5mm	156 x 44 x 164.5mm
Part Number	8845740000	8845840000	8845850000	8845800000	8845780000
Type	IE-SW8-M	IE-SW6/2SC-M	IE-SW6/2ST-M	IE-SW16-M	IE-SW14/2SC-M
Approvals	cULus, CE	cULus, CE	cULus, CE	cULus, CE	cULus, CE
Features	SNMP V1, Rapid Ring, IGMP Snooping Port Mirroring, Port Filtering, Trunking, VLAN, QoS, TOS 4K Mac addresses per 8 ports Auto MDIX, Auto Negotiation	SNMP V1, Rapid Ring, IGMP Snooping Port Mirroring, Port Filtering, Trunking, VLAN, QoS, TOS 4K Mac addresses per 8 ports Auto MDIX, Auto Negotiation	SNMP V1, Rapid Ring, IGMP Snooping Port Mirroring, Port Filtering, Trunking, VLAN, QoS, TOS 4K Mac addresses per 8 ports Auto MDIX, Auto Negotiation	SNMP V1, Rapid Ring, IGMP Snooping Port Mirroring, Port Filtering, Trunking, VLAN, QoS, TOS 4K Mac addresses per 8 ports Auto MDIX, Auto Negotiation	SNMP V1, Rapid Ring, IGMP Snooping Port Mirroring, Port Filtering, Trunking, VLAN, QoS, TOS 4K Mac addresses per 8 ports Auto MDIX, Auto Negotiation





Managed Switches					
Number of Ports	14 x RJ45, 2 ST	24 x RJ45	22 x RJ45, 2 SC	22 x RJ45, 2 ST	
Data Rate	10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps	
Segment Length	100m RJ45, 2km Fibre	100m	100m RJ45, 2km Fibre	100m RJ45, 2km Fibre	
Input Voltage	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	
Input Power	20 watts dc, 20VA ac	20 watts dc, 20VA ac	20 watts dc, 20VA ac	20 watts dc, 20VA ac	
Operating Temp	-40°C - +75°C	-40°C - +75°C	-40°C - +75°C	-40°C - +75°C	
Dimensions (LxWxH)	156 x 44 x 164.5mm	156 x 44 x 164.5mm	156 x 44 x 164.5mm	156 x 44 x 164.5mm	
Part Number	8845790000	8845830000	8845810000	8845820000	
Type	IE-SW14/2ST-M	IE-SW24-M	IE-SW22/2SC-M	IE-SW22/2ST-M	
Approvals	cULus, CE	cULus, CE	cULus, CE	cULus, CE	
Features	SNMP V1, Rapid Ring, IGMP Snooping Port Mirroring, Port Filtering, Trunking, VLAN, QoS, TOS 4K Mac addresses per 8 ports Auto MDIX, Auto Negotiation	SNMP V1, Rapid Ring, IGMP Snooping Port Mirroring, Port Filtering, Trunking, VLAN, QoS, TOS 4K Mac addresses per 8 ports Auto MDIX, Auto Negotiation	SNMP V1, Rapid Ring, IGMP Snooping Port Mirroring, Port Filtering, Trunking, VLAN, QoS, TOS 4K Mac addresses per 8 ports Auto MDIX, Auto Negotiation	SNMP V1, Rapid Ring, IGMP Snooping Port Mirroring, Port Filtering, Trunking, VLAN, QoS, TOS 4K Mac addresses per 8 ports Auto MDIX, Auto Negotiation	






Industrial Ethernet - Routers & Connectivity

Routers					
					
Number of Ports	2 x RJ45, 1 x RS232	1 x RJ45, 2 x RS232	1 x RJ45 Ethernet, 1 x RJ45 Modem, 2 x RS-232	1 x RJ45 Ethernet, 1 x RJ45 ISDN, 2 x RS-232	
Data Rate	10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps	10 / 100 Mbps	
Segment Length	100m	100m	100m	100m	
Input Voltage	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	10-36Vdc / 8-24Vac	
Input Power	4 watts dc, 4VA ac	4 watts dc, 4VA ac	6 watts dc, 6VA ac	6 watts dc, 6VA ac	
Operating Temp	0°C - +60°C	0°C - +60°C	0°C - +60°C	0°C - +60°C	
Dimensions (LxWxH)	79 x 40 x 85mm	79 x 40 x 85mm	156 x 44 x 164.5mm	156 x 44 x 164.5mm	
Part Number	8845760000	8845770000	8845860000	8845750000	
Type	IE-ARM-E	IE-ARM-U	IE-AR-10T	IE-AR-10T-ISDN	
Approvals	cULus, CE	cULus, CE	cULus, CE	cULus, CE	
Features	Configurable Firewall Port forwarding, DND/DynDNS Dial on Demand, Call back Webserver / console programmable RS-232 for Console or ext. modem	Configurable Firewall Port forwarding, DND/DynDNS Dial on Demand, Call back Webserver / console programmable RS-232 for Console or ext. modem	Analog Modem, Firewall Port forwarding, DND/DynDNS Dial on Demand, Call back Webserver / console programmable RS-232 for Console or ext. modem	ISDN Modem, Firewall Port forwarding, DND/DynDNS Dial on Demand, Call back Webserver / console programmable RS-232 for Console or ext. modem	

Connectivity					
					
Mechanical					
Description	Terminal block for RJ45 with IDC on the back end	Terminal block for ST fibre optic cables	Terminal block for RJ45 with RJ45 on the back end		
Category Rating	Cat. 6e		Cat. 6e		
IRating	IP 20	IP 20	IP 20		
Front Connector	RJ45 Female	ST	RJ45 Female		
Back Connector	IDC	ST	RJ45 Female		
Standard Pack	1	1	1		
Part Number	8808360000	8808340000	8879050000		
Type	IE-XM-RJ45/IDC	IE-XM-ST/ST	IE-XM-RJ45/RJ45		

Industrial Ethernet - Connectivity

Connectivity					
					
Mechanical					
Description	IP 67 screw down Ethernet cable coupler	IP 67 Ethernet cable coupler	IP67 mating plug	Adapter for putting 2 ethernet networks on one 4 pair cable. Comes in pairs of 2.	
Category Rating	Cat. 6e	Cat. 6e	Cat. 6e	Cat. 5e	
IIP Rating	IP 67	IP 67	IP67	IP20	
Front Connector	RJ45 Female	RJ45 Female	RJ45 Male	1 x RJ45 Male	
Back Connector	IDC	IDC	IDC	2 x RJ45 female	
Standard Pack	1	1	1	2	
Part Number	8808370000	8813090000	8808380000	8808400000	
Type	IE-S-IP67	IE-C-IP67	IE-P-IP67	IE-CSM 1 Set	


Connectivity					
					
Mechanical					
Description	Chasis mount flange with RJ45 insert (RJ45 to IDC)	Chasis mount flange with RJ45 insert (RJ45 to RJ45)	Chasis mount flange with RJ45 insert (90° downward RJ45 to RJ45)	Chasis mount flange with RJ45 insert (90° upward RJ45 to RJ45)	Ethernet IDC connection box used for extending or repairing Ethernet cables
Category Rating	Cat. 6e	Cat. 5e	Cat. 5e	Cat. 5e	Cat. 7
IRating	IP67	IP67	IP67	IP67	IP 20
Front Connector	RJ45 Female	RJ45 Female	RJ45 Female	RJ45 Female	IDC
Back Connector	IDC	RJ45 Female	RJ45 Female	RJ45 Female	IDC
Standard Pack	1	1	1	1	1
Part Number	8808440000	8808450000	8829450000	8829440000	8808410000
Type	IE-XM-RJ45/IDC-IP67	IE-XM-RJ45/RJ45-IP67	IE-XM-6D-RJ45/RJ45-IP67	IE-XM-6U-RJ45/RJ45-IP67	IE-CCM

Accessories					
Functionality	Device for testing ethernet cables for: crossed wires, short cuts, line & core interruptions etc.	Punch down tool for ethernet cables AWG20 - AWG28 (0.08-0.34mm²)	Crimping tool for 8-pole shielded RJ45 plugs AWG27 - AWG24 (0.09-0.20mm²)	Sheathing stripper for shielded data lines AWG20 - AWG11 (0.5 - 3.9mm²)	
Supply	9V battery				
Dimensions (LxWxH)	70x140x36mm (basic) 30x68x23mm (test box)				
Part Number	8808420000	9013970000	9202800000	9030060000	
Type	IE-CT	PDT	TT 8RJ MP8	AM12	
Features/Accessories	9V battery included	PD blade (standard) 9014000000 PD blade (scissors) 9014050000			


Patch Cables and Fiber Optics

True to the idea of "one-stop shopping", Weidmüller can also supply Ethernet copper as well as fibre optic connecting cables.

- Copper cables available in Cat 5, Cat 5e, Cat 6, Cat7 1:1 versions or crossover.
- Patch cables have a molded RJ45 plug that provides kink protection and provides good strain relief.
- Extended temp range pur: -40°C to +70°C



- All the FO cables from Weidmüller can be supplied with SC duplex or ST connectors.
- Available as PVC zip-cord
- Resistant to oils, acids, electrolytes



FO breakout cable

* Contact Weidmuller for more detailed information and part numbers.

Notes

Index

Index	Index by Description	X.2
	Index by Part Number	X.8

Appendix	Index
	Search according to description or part number

Description	Part Number	Page
-------------	-------------	------

A

AC OUTLET EUROPEAN FOR TS35	8734580000	D.4
ADAPTOR FOOT	9102100000	B.5
ADAPTOR PG 11/NPT 3/8	1712340000	C.3
ADAPTOR PG13.5 - NPT 1/2	1712350000	C.3
ADAPTOR PG36 - NPT 1 1/4	1712380000	C.3
AEH 0.75/18	9025910000	E.8
AEH 1.0/16 FERRULES (YELLOW)	9025950000	E.8
AEH 1.0/18 FERRULES	9025930000	E.8
AM 1/25/35 REPLACEMENT BLADE	9001530000	E.2
AM 12 GRAY	9030060000	E.2
AM 12 GRAY	9030060000	G.7
AM 25 STRIP TOOL	9001540000	E.2
AM 35 STRIPPING TOOL	9001080000	E.2
ANALOG ISOLATOR W/BIPOLAR VOLT	G408-1000	D.19
ANALOG ISOLATOR W/BIPOLAR VOLT	G408-1000	D.21
AP DK5 END PLATE	C9039986	D.6
AP DK5 END PLATE	C9039986	D.10
AP DK5 END PLATE	C9039986	D.18
AP DK6 END PLATE	C9040396	D.18
AP FOR DKT 4,PA,BG	0687560000	D.10
AP FOR DKT 4,PA,BG	0687560000	D.6
AP FOR MCZ PRODUCTS	8389030000	D.6
AP FOR MCZ PRODUCTS	8389030000	D.12
AP FOR MCZ PRODUCTS	8389030000	D.20
ASK 1 EN, NO LED, PA, BG	0474560000	A.8
ASK1EN/SMT10-60VUC BFI H-	0222760001	A.8
ASK1EN/SMT10-60VUC BFI H+	9123140001	A.8
ASK1EN/SMT100-250VUC BFI H-	0225560001	A.8
ASK1EN/SMT100-250VUC BFI H+	9118290001	A.8

B

BLADE SET NEW STRIPAX 6	9054030000	E.2
BLUE STRIP FERRULES	9004360000	E.8
BLUE TWIN FERRULES	9004430000	E.11
BRUSH FOR STRIPAX	9005450000	E.2
BS M5X8 HEX F.TST/TSTW,ST	0295900000	A.17
BS M6X12 HEX F.TST/TSTW,ST	0353500000	A.17
BS M6X8 HEX F.TST/TSTW,ST	0642600000	A.17

C

CB 80VDC, 10A, CURVE U2, 1P	9926251910	B.2
CB 80VDC, 15A, CURVE U2, 1P	9926251915	B.2
CB 80VDC, 1A, CURVE U2, 1P	9926251901	B.2
CB 80VDC, 20A, CURVE U2, 1P	9926251920	B.2
CB 80VDC, 2A, CURVE U2, 1P	9926251902	B.2
CB 120V, 1A, CURVE KM, 1 POLE	9926251001	B.2
CB 120V, 2A, CURVE KM, 1 POLE	9926251002	B.2
CB 120V, 5A, CURVE KM, 1 POLE	9926251005	B.2
CB 120V,10A, CURVE KM, 1 POLE	9926251010	B.2
CB 120V,15A, CURVE KM, 1 POLE	9926251015	B.2
CB 120V,20A, CURVE KM, 1 POLE	9926251020	B.2
CB 120V,25A, CURVE KM, 1 POLE	9926251025	B.2
CB 240V, 1A, CURVE KM, 2 POLE	9926252001	B.2
CB 240V, 2A, CURVE KM, 2 POLE	9926252002	B.2
CB 240V, 5A, CURVE KM, 2 POLE	9926252005	B.2
CB 240V,10A, CURVE KM, 2 POLE	9926252010	B.2
CB 240V,15A, CURVE KM, 2 POLE	9926252015	B.2
CB 240V,20A, CURVE KM, 2 POLE	9926252020	B.2
CB 240V,25A, CURVE KM, 2 POLE	9926252025	B.2
CC 15/17 K MC NEUTRAL SILVER	1876580000	F.26
CC 15/17 K MC NEUTRAL WHITE	1876590000	F.26
CC 15/17 MC NEUTRAL SILVER	1876610000	F.24
CC 15/17 MC NEUTRAL WHITE	1876570000	F.24
CC 15/27 K MC NEUTRAL SILVER	1876780000	F.26
CC 15/27 K MC NEUTRAL WHITE	1876640000	F.26
CC 15/27 MC NEUTRAL SILVER	1876760000	F.24
CC 15/27 MC NEUTRAL WHITE	1876770000	F.24
CC 15/49 K MC NEUTRAL SILVER	1877270000	F.26
CC 15/49 K MC NEUTRAL WHITE	1877220000	F.26
CC 15/49 MC NEUTRAL SILVER	1877240000	F.24
CC 15/49 MC NEUTRAL WHITE	1877260000	F.24
CC 15/60 K MC NEUTRAL SILVER	1877360000	F.26
CC 15/60 K MC NEUTRAL WHITE	1877310000	F.26
CC 15/60 MC NEUTRAL SILVER	1877340000	F.26
CC 15/60 MC NEUTRAL WHITE	1877350000	F.26
CC 30/60 K MC NEUTRAL SI	1934330000	F.26
CC 30/60 K MC NEUTRAL WS	1934390000	F.26
CC 30/60 MC NEUTRAL SI	1934400000	F.26
CC 30/60 MC NEUTRAL WS	1934420000	F.26
CC-H 15/17 BLACK HOLDER	1790430000	F.26
CC-H 15/27 BLACK HOLDER	1790410000	F.26
CC-H 15/49 BLACK HOLDER	1790420000	F.26
CC-H 15/60 BLACK HOLDER	1878910000	F.26
CC-H 30/60	1934430000	F.26
CC-RAIL 1000 BLACK CARRIER	1790150000	F.26
CC-RAIL 1000 TRANSPARENT COVER	1790160000	F.26
CIRCUIT BREAKER 1P .1A	9911010000	B.4
CIRCUIT BREAKER 1P .2A	9911020000	B.4
CIRCUIT BREAKER 1P .3A	9911030000	B.4
CIRCUIT BREAKER 1P .4A	9911040000	B.4
CIRCUIT BREAKER 1P .5A	9911050000	B.4
CIRCUIT BREAKER 1P .6A	9911060000	B.4
CIRCUIT BREAKER 1P .8A	9911080000	B.4
CIRCUIT BREAKER 1P 1.0A	9911100000	B.4
CIRCUIT BREAKER 1P 1.5A	9911150000	B.4
CIRCUIT BREAKER 1P 10.A	9921100000	B.4
CIRCUIT BREAKER 1P 12.A	9921120000	B.4
CIRCUIT BREAKER 1P 15.A	9921150000	B.4
CIRCUIT BREAKER 1P 16.A	9921160000	B.4
CIRCUIT BREAKER 1P 18.A	9921180000	B.4
CIRCUIT BREAKER 1P 2.0A	9921120000	B.4

Description	Part Number	Page
-------------	-------------	------

CIRCUIT BREAKER 1P 2.5A	9911250000	B.4
CIRCUIT BREAKER 1P 20.A	9921200000	B.4
CIRCUIT BREAKER 1P 25.A	9921250000	B.4
CIRCUIT BREAKER 1P 3.0A	9911300000	B.4
CIRCUIT BREAKER 1P 32.A	9921320000	B.4
CIRCUIT BREAKER 1P 4.0A	9911400000	B.4
CIRCUIT BREAKER 1P 5.0A	9911500000	B.4
CIRCUIT BREAKER 1P 6.0A	9911600000	B.4
CIRCUIT BREAKER 1P 8.0A	9911800000	B.4
CIRCUIT BREAKER 2P .1A	9912010000	B.4
CIRCUIT BREAKER 2P .2A	9912020000	B.4
CIRCUIT BREAKER 2P .3A	9912030000	B.4
CIRCUIT BREAKER 2P .4A	9912040000	B.4
CIRCUIT BREAKER 2P .5A	9912050000	B.4
CIRCUIT BREAKER 2P .6A	9912060000	B.4
CIRCUIT BREAKER 2P .8A	9912080000	B.4
CIRCUIT BREAKER 2P 1.0A	9912100000	B.4
CIRCUIT BREAKER 2P 1.5A	9912150000	B.4
CIRCUIT BREAKER 2P 10.A	9922100000	B.4
CIRCUIT BREAKER 2P 12.A	9922120000	B.4
CIRCUIT BREAKER 2P 15.A	9922150000	B.4
CIRCUIT BREAKER 2P 16.A	9922160000	B.4
CIRCUIT BREAKER 2P 18.A	9922180000	B.4
CIRCUIT BREAKER 2P 2.0A	9922200000	B.4
CIRCUIT BREAKER 2P 2.5A	9912250000	B.4
CIRCUIT BREAKER 2P 20.A	9922200000	B.4
CIRCUIT BREAKER 2P 25.A	9922250000	B.4
CIRCUIT BREAKER 2P 3.0A	9912300000	B.4
CIRCUIT BREAKER 2P 32.A	9922320000	B.4
CIRCUIT BREAKER 2P 4.0A	9912400000	B.4
CIRCUIT BREAKER 2P 5.0A	9912500000	B.4
CIRCUIT BREAKER 2P 6.0A	9912600000	B.4
CIRCUIT BREAKER 2P 8.0A	9912800000	B.4
CIRCUIT BREAKER 3P .1A	9913010000	B.4
CIRCUIT BREAKER 3P .2A	9913020000	B.4
CIRCUIT BREAKER 3P .3A	9913030000	B.4
CIRCUIT BREAKER 3P .4A	9913040000	B.4
CIRCUIT BREAKER 3P .5A	9913050000	B.4
CIRCUIT BREAKER 3P .6A	9913060000	B.4
CIRCUIT BREAKER 3P .8A	9913080000	B.4
CIRCUIT BREAKER 3P 1.0A	9913100000	B.4
CIRCUIT BREAKER 3P 1.5A	9913150000	B.4
CIRCUIT BREAKER 3P 10.A	9923100000	B.4
CIRCUIT BREAKER 3P 12.A	9923120000	B.4
CIRCUIT BREAKER 3P 15.A	9923150000	B.4
CIRCUIT BREAKER 3P 16.A	9923160000	B.4
CIRCUIT BREAKER 3P 18.A	9923180000	B.4
CIRCUIT BREAKER 3P 2.0A	9913200000	B.4
CIRCUIT BREAKER 3P 2.5A	9913250000	B.4
CIRCUIT BREAKER 3P 25.A	9923200000	B.4
CIRCUIT BREAKER 3P 20.A	9923250000	B.4
CIRCUIT BREAKER 3P 3.0A	9913300000	B.4
CIRCUIT BREAKER 3P 32.A	9923320000	B.4
CIRCUIT BREAKER 3P 4.0A	9913400000	B.4
CIRCUIT BREAKER 3P 5.0A	9913500000	B.4
CIRCUIT BREAKER 3P 6.0A	9913600000	B.4
CIRCUIT BREAKER 3P 8.0A	9913800000	B.4
CP DM 20A DIODE MODULE	8768650000	D.29
CP-BBU 12VDC	9916280012	D.29
CP-BBU 24VDC	9916280024	D.29
CP-DCDC 12VDC IN/ 5VDC, 8A OUT	9919371205	D.28
CP-DCDC 12VDC IN/12VDC, 3A OUT	9919371212	D.28
CP-DCDC 12VDC IN/15VDC, 3A OUT	9919371215	D.28
CP-DCDC 12VDC IN/24VDC, 2A OUT	9919371224	D.28
CP-DCDC 24VDC IN/ 5VDC, 8A OUT	9919372405	D.28
CP-DCDC 24VDC IN/12VDC, 3A OUT	9919372412	D.28
CP-DCDC 24VDC IN/15VDC, 3A OUT	9919372415	D.28
CP-DCDC 24VDC IN/24VDC, 2A OUT	9919372424	D.28
CP-SNT 115,230VAC/ 5V,2A	9928890005	D.26
CP-SNT 115,230VAC/12-15VDC 3A	9927480012	D.26
CP-SNT 115,230VAC/12V,1.5A	9928890012	D.26
CP-SNT 115,230VAC/15V,1.5A	9928890015	D.26
CP-SNT 115,230VAC/24-28V,2.3A	9927480024	D.26
CP-SNT 115,230VAC/24V,1.0A	9928890024	D.26
CP-SNT 115,230VAC/28V,1.0A	9928890028	D.26
CP-SNT 115,230VAC/48VDC,1.0A	9927480048	D.26
CP-SNT 115,230VAC/5VDC, 3A	9927480005	D.26
CP-SNT 120V 24V 5A	8708670000	D.27
CP-SNT 240V 24V 10A	8708680000	D.27
CP-SNT 360-480V 3PH/24VDC,2.3A	9917790324	D.26
CP-SNT 360-500V 3PH/24VDC,12.5	7924740324	D.26
CP-SNT 360-500V 3PH/24VDC,6.5A	9925340324	D.26
CP-SNT 380-480V 3PH/24VDC,25A	7920210324	D.26
CP-SNT 380-480V 3PH/24VDC,40A	9918960324	D.26
CP-SNT 70W 24V 3A	8708660000	D.27
CP-SNT 100 PARALLEL	8710620000	D.29
CP-SNT ECM 500W 24V 20A	8778870000	D.27
CP-SNT120W 115,230VAC/12V,10A	9925340012	D.26
CP-SNT12W 115,230VAC/24V,0.5A	9918840024	D.26
CP-SNT156W 115,230VAC/48V,3.25A	9925340048	D.26
CP-SNT160W 115,230VAC/24-28,6.5A	9925340024	D.26
CP-SNT3 1000W 24V 40A 3 PHASE	8708730000	D.27
CP-SNT3 250W 24V 10A 3 PHASE	8708700000	D.27
CP-SNT3 500W 24V 20A 3 PHASE	8708710000	D.27
CP-SNT300W 115-230V/24VDC,12.5A	9916250024	D.26
CP-SNT50W 115,230VAC/ 5V,10A	9925340005	D.26
CSR CUR. SENS. RELAY RS45 HOUS	9916090000	D.25
CUTTING BLADE FOR STRIPAX PLUS	9050340000	E.3

D

DC BRANCH CB 25A 1 POLE	9926251925	B.2
DC BRANCH CB 30A 1 POLE	9926251930	B.2
DC BRANCH CB 35A 1 POLE	9926251935	B.2
DC BRANCH CB 40A 1 POLE	9926251940	B.2
DC BRANCH CB 45A 1 POLE	9926251945	B.2

Description	Part Number	Page
-------------	-------------	------

DC BRANCH CB 50A 1 POLE	9926251950	B.2
DC BRANCH CB 55A 1 POLE	9926251955	B.2
DC BRANCH CB 5A 1 POLE	9926251905	B.2
DC BRANCH CB 60A 1 POLE	9926251960	B.2
DC CURRENT SENSOR + AMP	9916450000	D.21
DECIPAK 0-100MV/4-20MA/24V 2W	7940005531	D.21
DECIPAK 0-10MV/4-20MA/24V 2W	7940005529	D.21
DECIPAK 0-10V/0-5V/24V 4W	7940005508	D.21
DECIPAK 0-10V/4-20MA/24V 2W	7940005528	D.21
DECIPAK 0-10V/4-20MA/24V 4W	7940005499	D.21
DECIPAK 0-1MA/4-20MA/24V 2W	7940005523	D.19
DECIPAK 0-20MA/0-20MA/24V 4W	7940005488	D.19
DECIPAK 0-20MA/4-20MA/24V 2W	7940005524	D.19
DECIPAK 0-20MA/4-20MA/24V 4W	7940005485	D.19
DECIPAK 4-20/4-20/LOOP POWERED	7940005521	D.19
DECIPAK 4-20MA/0-10V/240V 4W	7940005478	D.19
DECIPAK 4-20MA/0-20MA/24V 4W	7940005476	D.19
DECIPAK 4-20MA/0-5V/24V 4W	7940005482	D.19
DECIPAK 4-20MA/4-20MA/120V 4W	7940005471	D.19
DECIPAK 4-20MA/4-20MA/24V 2W	7940005522	D.19
DECIPAK 4-20MA/4-20MA/24V 4W	7940005473	D.19
DEK 5/3.5 MC NEUTRAL WHITE	1755270000	F.2
DEK 5/5 MC-10 BLANK WHITE	1609801044	F.2
DEK 5/5 MC-10 NEUT. VAR	1609800000	D.24
DEK 5/5 PLUS MC NEUTRAL	1854490000	F.2
DEK 5/6 MC NEUTRAL WHITE	1609820000	D.6
DEK 5/6 MC NEUTRAL WHITE	1609820000	D.10
DEK 5/6 MC NEUTRAL WHITE	1609820000	D.12
DEK 5/6 MC NEUTRAL WHITE	1609820000	D.18
DEK 5/6 MC NEUTRAL WHITE	1609820000	D.20
DEK 5/6 MC NEUTRAL WHITE	1609820000	F.2
DEK 5/6 MC V0 NEUTRAL	1789590000	F.2
DEK 5/6.5 MC NEUTRAL WHITE	1609840000	D.22
DEK 5/6.5 MC NEUTRAL WHITE	1609840000	F.2
DEK 5/7.5 MC BLANK WHITE	1720620000	F.2
DEK 5/8 MC WHITE BLANK	1856740000	D.18
DEK 5/8 MC WHITE BLANK	1856740000	F.2
DEKAFIX 5MM BLANK - WHITE	0473360000	D.24
DELCON 5VDC IN/0-240VAC OUT,1.2A	SLO5IRA	D.14
DELCON 5VDC IN/0-240VAC OUT,3A	SLO5TR	D.14
DELCON 5VDC IN/0-24VDC OUT 10A	SLO5CRX	D.14
DELCON 5VDC IN/0-60VDC,3A OUT	SLO5OCR	D.14
DELCON 5VDC IN/0-300VDC, 1.8 OUT	SLO5CRA	D.14
DELCON 12VDC IN/60VDC OUT 50MA	SLI12CRI	D.14
DELCON 12VDC IN/NC 60VDC OUT 30MA	SLI12CRI	D.14
DELCON 12VDC IN/0-24VDC OUT 10A	SLO12CRX	D.14
DELCON 12VDC IN/0-250VDC OUT 1.8A	SLO12CRA	D.14
DELCON 12VDC IN/0-250VDC OUT 4A	SLO12CRA4	D.14
DELCON 12VDC IN/0-60VDC OUT 3A	SLO12CR	D.14
DELCON 24VAC IN/60VDC OUT 30MA	SLI125CRI	D.14
DELCON 24VAC IN/60VDC OUT 50MA	SLI25CR	D.14
DELCON 24VAC IN/NC 60VDC OUT 30MA	SLI25CRI	D.14
DELCON 24VDC 2MA IN/0-240VAC OUT 3A	SLO24TL	D.14
DELCON 24VDC 2MA IN/0-60VDC OUT 3A	SLO24CL	D.14
DELCON 24VDC IN/250VAC OUT 3A	SLO24TH	D.14
DELCON 24VDC IN/250VAC OUT 3A	SLO24TR	D.14
DELCON 24VDC IN/32VDC OUT 10A	SLO24CRX	D.14
DELCON 24VDC IN/60 VDC OUT 3A	SLO24CR	D.14
DELCON 24VDC IN/60VDC OUT 50MA	SLI24CR	D.14
DELCON 24VDC IN/NC 60VDC OUT 30MA	SLI24CRI	D.14
DELCON 24VDC IN/250VAC OUT1.2A	SLO24IRA	D.14
DELCON 24VDC IN/300VDC OUT1.8A	SLO24CRA	D.14
DELCON 24VDC IN/300VDC OUT4.0A	SLO24CRA4	D.14
DELCON 24VDC IN/60VDC OUT 50MA	SLI24CLR	D.14
DELCON 24VDCIN/60VDC OUT 50MA	SLI24CRF	D.14
DELCON 48VAC IN/60VDC OUT 50MA	SLI48CR	D.14
DELCON 48VAC IN/NC 60VDC OUT 30MA	SLI48CRI	D.14
DELCON 48VDC IN/60VDC OUT 50MA	SLI48CR	D.14
DELCON 48VDC IN/NC 60VDC OUT 30MA	SLI48CRI	D.14
DELCON 48VDC IN/0-250VDC OUT 1.8A	SLO48CRA	D.14
DELCON 48VDC IN/0-250VDC OUT 4A	SLO48CRA4	D.14
DELCON 120VAC IN/60VDC OUT 50MA	SLI120CH	D.14
DELCON 120VAC IN/60VDC OUT 50MA	SLI120CR	D.14
DELCON 120VAC IN/60VDC OUT 50MA	SLI120CRP	D.14
DELCON 120VAC IN/NC 60VDC OUT 30MA	SLI120CRI	D.14
DELCON 120VAC IN/0-240VAC OUT,1A	SLOP120TR	D.14
DELCON 120VAC IN/0-240VAC OUT3A	SLOA120TR	D.14
DELCON 120VDC IN/0-250VDC OUT 1.8A	SLO120CRA	D.14
DELCON 120VDC IN/0-250VDC OUT 4A	SLO120CRA4	D.14
DELCON 125VDC IN/60VDC OUT 50MA	SLI125CH	D.14
DELCON 125VDC IN/60VDC OUT 50MA	SLI125CR	D.14
DELCON 220VDC IN/0-250VDC OUT 1.8A	SLO220CRA	D.14
DELCON 220VDC IN/0-250VDC OUT 4A	SLO220CRA4	D.14
DELCON 230VAC IN/60VDC 50MA	SLI230CR	D.14
DELCON 230VAC IN/60VDC OUT 50MA	SLI230CH	D.14
DELCON 230VAC IN/60VDC OUT 50MA	SLI230CR	D.14
DELCON 230VAC IN/60VDC OUT 50MA	SLI230CRP	D.14
DELCON 230VAC IN/NC 60VDC OUT 30MA	SLI230CRI	D.14
DELCON 230VAC IN/0-240VAC OUT 1A	SLOA230TR	D.14
DELCON 230VAC IN/0-240VAC OUT 3A	SLOP230TR	D.14
DELCON 250VDC IN/60VDC OUT 50MA	SLI250CR	D.14
DELCON 250VDC IN/NC 60VDC OUT 30MA	SLI250CRI	D.14
DELCON 250VDC IN/60VDC OUT 50MA	SLI250CH	D.14
DIE SET FOR PZ 16, 10-6 AWG	9012640000	E.3
DIE SET FOR PZ PZ 3	9011450000	E.3
DIE SET FOR PZ 6/5	9011620000	E.3
DIE SET FOR PZ ZH 16	9054580000	E.3
DIE SET FOR PZ6 ROTO	9011480000	E.3
DIN RAIL MOUNTABLE UTILITY BOX	79174760001	D.25
DK F-1 DK5 0-16KHZ	8311870001	D.25
DK F-U DK5 0-16KHZ 24V	82838110001	D.25
DK U-F DK5 0-10V E315A	8224040000	D.21
DK50 24VDC 50KHZ/5V TTL OUT	8228260000	D.10
DKO 24V DC/O	8019590000	D.10
DKO 35 OPTO COUPLER 24 VDC	8028300000	D.10
DKO DK5 5VTT/L-5-48VDC,100MA	8228650000	D.12
DKSC 0-10V IN/2 SET POINT OUT	8019640000	D.10

Description	Part Number	Page
-------------	-------------	------

DKT 4/32,PA,BG 0687360000 A.10
 DKT 4/35,PA,BG 0687460000 A.10
 DMS MANUAL 0.5-1.7NM TORQUE 9918370000 E.7
 DMS MANUAL 2.0-8.0NM TORQUE 9918380000 E.7
 DMSI MANUAL 0.5-1.7NM TORQUE 9918390000 E.6
 DMSI MANUAL 2.0-8.0NM TORQUE 9918400000 E.6

E

EK 10/32,PA,GN/YL 0354660000 A.8
 EK 10/35,PA,GN/YL 0661360000 A.8
 EK 16/32,PA,GN/YL 0374660000 A.8
 EK 16/35,PA,GN/YL 0190160000 A.8
 EK 2.5 N/32,PA,GN/YL 0473630000 A.8
 EK 2.5/35,PA,GN/YL 0661060000 A.8
 EK 35/32,PA,GN/YL 0354760000 A.8
 EK 35/35,PA,GN/YL 0661460000 A.8
 EK 4/32,PA,GN/YL 0354560000 A.8
 EK 4/35,PA,GN/YL 0661160000 A.8
 EK 6/35,PA,GN/YL 0661260000 A.8
 ESG 10/17 MC NEUTRAL 1856700000 F.22
 ESG 5/10 MC NEUTRAL WS 1919940000 F.22
 ESG 6/15 K MC NEUTR. GE 1880130000 F.22
 ESG 6/15 K MC NEUTR. WS 1880100000 F.22
 ESG 6/15 MC RIDERSERIES 1881280000 F.22
 ESG 6/17 K MC NEUTR. GE 1880110000 F.22
 ESG 6/17 K MC NEUTR. WS 1880120000 F.22
 ESG 7/20 1736181044 F.20
 ESG 7/20 1736181044 F.22
 ESG 7/20 SIRIUS TUEKIS 1736181696 F.22
 ESG 7/20 SIRIUS YELLOW 1736181687 F.22
 ESG 8/10 1736190000 F.22
 ESG 8/17 F/MTG BAR SCH5 NEUTR 1720610000 F.22
 ESG 8/17 L MC NEUTRAL 1890470000 F.22
 ESG 8/17 MULTICARD NEUTRAL 1674740000 F.22
 ESG 8/17 SYS PRO M 1755340000 F.22
 ESG 8/19 MULTICARD NEUTRAL 1652220000 F.22
 ESG 9/10 MC NEUTRAL WS 1775910000 F.22
 ESG 9/11K MC NEUTRAL 1857440000 F.22
 ESG 9/17 K NEUTRAL/GE 1753500000 F.22
 ESG 9/17 WHITE BLANK NO ADHES. 1724760000 F.20
 ESG 9/17K UNIVERSAL MULTICARD 1724760000 F.22
 ESG 9/20 L MC NEUTRAL 1890460000 F.22
 ESG 9/20 MC NEUTRAL GE 1866160000 F.22
 ESG 9/20 MC UNIVERSAL 1756720000 F.22
 ESG 9/20 MULTICARD 1609940000 F.22
 ESO 5 (POLYESTER WHITE) 1670370000 F.20
 ESO 5 POLYESTER YELLOW A4 1670380000 F.20
 ESO 5 YELLOW 1631350000 F.20
 ESO 7 A4 PAPER YELLOW 1634780000 F.20
 ESO 7 A4 PAPER, WHITE 240PCS. 1607720000 F.20
 ESO 7 POLYESTER WHITE 1670390000 F.20
 ESO 7 POLYESTER YELLOW A4 1670400000 F.20
 ESO 8/20 GE 1919900000 F.20
 ESO 8/20 WS 1919890000 F.20
 ESO 8/20P GE 1919880000 F.20
 ESO 8/20P WS 1919870000 F.20
 ESO FGPR MARK CARRIER 0139000000 F.22
 ESO5 FOR SHT5 (60 PER SHEET) 1607710000 A.17
 ESO5 FOR SHT5 (60 PER SHEET) 1607710000 F.20
 ESO5S F. SHT5S(140 PER SHEET) 1631920000 A.17
 ETO CC 15/17 TRANSPARENT LABEL 1880850000 F.26
 ETO CC 15/27 TRANSPARENT LABEL 1880810000 F.26
 ETO CC 15/49 TRANSPARENT LABEL 1880830000 F.26
 ETO CC 15/60 TRANSPARENT LABEL 1880840000 F.26
 ETO CC 30/60 TRANSPARENT 1934440000 F.26
 EW 35 FOR TS 35,PA,BG 0383560000 A.16
 EW 35 FOR TS 35,PA,BG 0383560000 A.18
 EWK 1 FOR TS 32 SLOT,PA,BG 0495160000 A.16
 EWK 1 FOR TS 32 SLOT,PA,BG 0495160000 A.18
 EWK 1 FOR TS 32,PA,BG 0206160000 A.16
 EWK 1 FOR TS 32,PA,BG 0206160000 A.18
 EWK 2 FOR TS 32,PA,BG 0199360000 A.16
 EWK 2 FOR TS 32,PA,BG 0199360000 A.18

F

FM 4 MOUNTING FOOT FOR TS 35 0687900000 A.17
 FM5 (M5) 0636800000 A.17
 FM6 (M6) FOR TS 35 0636900000 A.17

G

GFI OUTLET, 15A,LPZF TERMINALS 7940000037 D.4
 GFI OUTLET, 20A, LLP TERMINALS 7940000036 D.4

H

H 0.14/10 GREY STRIP PACK 9005180000 E.8
 H 0.14/12 GREY STRIP PACK 9028240000 E.8
 H 0.25/10 LIGHT BLUE 9025740000 E.8
 H 0.25/10,24AWG,INS,LIGHT BLUE 9026050000 E.8
 H 0.25/12 LIGHT BLUE FERRULES 9025760000 E.8
 H 0.25/12 LIGHT BLUE STRIP PKG 9025780000 E.8
 H 0.25/5 UNINSULATED FERRULES 9018910000 E.9
 H 0.34/10 TURQUOISE FERRULES 9025750000 E.8
 H 0.34/12 FERRULES STRIP PCK 9025790000 E.8
 H 0.34/12 TURQUOISE FERRULES 9025770000 E.8
 H 0.34/12 TURQUOISE ON REELS 9004390000 E.8
 H 0.5/10 FERRULES 9004050000 E.9
 H 0.5/10 ORANGE STRIP PKG 9028260000 E.8
 H 0.5/12,20 AWG,INS, ORANGE 0409500000 E.8
 H 0.5/14 ORANGE REEL FERRULES 9005810000 E.8

Description	Part Number	Page
-------------	-------------	------

H 0.5/14,20AWG,INS,ORANGE 0690700000 E.8
 H 0.5/15 ORANGE TWIN FERRULES 9004440000 E.11
 H 0.5/15 ZH ORANGE 9037200000 E.11
 H 0.5/16 OR SV 9028270000 E.8
 H 0.5/16 ORANGE FERRULES 9025870000 E.8
 H 0.5/16 ORANGE FERRULES 9026060000 E.8
 H 0.5/16.5 ZH ORANGE FERRULES 9037210000 E.11
 H 0.5/18.5 ZH ORANGE TWIN 9037220000 E.11
 H 0.5/6,26-22AWG,UNINSULATED 0282600000 E.9
 H 0.75/10,20AWG,UNINSULATED 0542500000 E.9
 H 0.75/12 WHITE STRIP PKG 9028280000 E.8
 H 0.75/12,18AWG,INS,WHITE 0409600000 E.8
 H 0.75/14 WHITE 9026070000 E.8
 H 0.75/14 WHITE REEL FERRULES 9005870000 E.8
 H 0.75/14,18AWG,INS,WHITE 0462900000 E.8
 H 0.75/15 ZH WHITE TWIN FERR 9037230000 E.11
 H 0.75/15 ZH WHITE TWIN FERRULE 9018510000 E.11
 H 0.75/16 WHITE 9025860000 E.8
 H 0.75/16 WHITE FERRULES 9028290000 E.8
 H 0.75/17 WHITE STRIP PACKAGE 9004900000 E.11
 H 0.75/17 ZH WHITE 9037240000 E.11
 H 0.75/18 W SV 9028300000 E.8
 H 0.75/24, 5 ZH WHITE FERRULES 9037250000 E.11
 H 0.75/6,20AWG,UNINSULATED 0282700000 E.9
 H 1/14 YELLOW 9026080000 E.8
 H 1/15 S ZH YELLOW 9018690000 E.11
 H 1.0/10,18AWG,UNINSULATED 0282800000 E.9
 H 1.0/12 GE SV 9028310000 E.8
 H 1.0/12,18AWG,INS,YELLOW 0409700000 E.8
 H 1.0/14 YELLOW FERRULES 9004320000 E.8
 H 1.0/14 YELLOW REEL FERRULES 9005830000 E.8
 H 1.0/14,18AWG,INS,YELLOW 0463000000 E.8
 H 1.0/15 ZH YELLOW FERRULES 9037260000 E.11
 H 1.0/15S ZH GE SV 9018650000 E.11
 H 1.0/16 YELLOW STRIP PCK 9028320000 E.8
 H 1.0/18 GE SV 9028340000 E.8
 H 1.0/20 ZH GE SV 9004910000 E.11
 H 1.0/20 ZH YELLOW 9037270000 E.11
 H 1.0/25, 6 ZH YELLOW 9037280000 E.11
 H 1.0/6,18AWG,UNINSULATED 9037260000 E.9
 H 1.5/10,16AWG,UNINSULATED 0188500000 E.9
 H 1.5/12 NON-INSULATED 9004060000 E.9
 H 1.5/14 9026090000 E.8
 H 1.5/14 RED REEL FERRULES 9005840000 E.8
 H 1.5/14,16AWG,INS,RED 0463100000 E.8
 H 1.5/16 RED FERRULES STRIP PK 9028350000 E.8
 H 1.5/16 RED TWIN FERRULES 9004410000 E.11
 H 1.5/16 ZH RED FERRULES 9037290000 E.11
 H 1.5/16,16AWG,INS,RED 0635100000 E.8
 H 1.5/18 NON-INSULATED FERRULE 9004070000 E.9
 H 1.5/20 ZH R SV 9004920000 E.11
 H 1.5/20 ZH RED FERRULES 9037300000 E.11
 H 1.5/24,16AWG,INS,RED 0565600000 E.8
 H 1.5/25 6 ZH RED FERRULES 9037310000 E.11
 H 1.5/7,16AWG,UNINSULATED 9037270000 E.9
 H 2.5 FERRULES 14 9026100000 E.8
 H 2.5/10 FERRULES 9004080000 E.9
 H 2.5/12,14AWG,UNINSULATED 0186100000 E.9
 H 2.5/14D 9019160000 E.8
 H 2.5/14D BLUE REEL FERRULES 9005850000 E.8
 H 2.5/18 D BLUE FERRULES 9019170000 E.8
 H 2.5/18 FERRULES 9004090000 E.9
 H 2.5/18 D ZH BLUE 9037500000 E.11
 H 2.5/20.5 D ZH BLUE FERRULES 9004740000 E.11
 H 2.5/20.5 D ZH BLUE 9037510000 E.11
 H 2.5/25,14AWG, INS, BLUE 9019180000 E.8
 H 2.5/26, 5D ZH BLUE FERRULES 9037520000 E.11
 H 2.5/7,14AWG,UNINSULATED 0373000000 E.9
 H 4/0/25, 12AWG, INS, GREY 9019210000 E.8
 H 4/15 FERRULES 9004100000 E.9
 H 4/17 D GREY FERRULE 9019190000 E.8
 H 4/17 D GREY FERRULES 9026010000 E.8
 H 4/18 NON-INSULATED FERRULE 9004110000 E.9
 H 4/20D GREY FERRULES 9019200000 E.8
 H 4/22 D GREY 9004730000 E.11
 H 4.0/12,12AWG,UNINSULATED 0244100000 E.9
 H 4.0/22D ZH GREY 9037530000 E.11
 H 4.0/28D ZH GREY FERRULES 9037540000 E.11
 H 4.0/9,12AWG,UNINSULATED 0373100000 E.9
 H 6/10 FERRULES 9004120000 E.9
 H 6/18 FERRULES W/O COLLAR 9004130000 E.9
 H 6.0/12,10AWG,UNINSULATED 0191900000 E.9
 H 6.0/15,10AWG,UNINSULATED 0124700000 E.9
 H 6.0/20,10AWG,INS,BLACK 0533500000 E.8
 H 6.0/25 ZH BLACK FERRULES 9037320000 E.11
 H 6.0/25 ZH BLACK SV FERRULES 9004930000 E.11
 H 6.0/26,10AWG,INS,BLACK 0565700000 E.8
 H 6.0/29 ZH BLACK FERRULES 9037330000 E.11
 H 10/24 ZH IVORY STRIP PACK 9018860000 E.11
 H 10/30S ZH EB 9018870000 E.11
 H 10.0/12,8AWG,UNINSULATED 0282900000 E.9
 H 10.0/15,8AWG,UNINSULATED 0124800000 E.9
 H 10.0/18,8AWG,UNINSULATED 0379300000 E.9
 H 10.0/21,8AWG,INS,IVORY 0534200000 E.8
 H 10.0/26 ZH IVORY FERRULES 9037340000 E.11
 H 10.0/26 ZH IVORY STRIP PACK 9004940000 E.11
 H 10.0/27,8AWG,INS,IVORY 0565800000 E.8
 H 10.0/30 ZH EB 9037350000 E.11
 H 16/18 6 AWG UNINSULATED 0375200000 E.9
 H 16/25 FERRULE 9004150000 E.9
 H 16.0/12,6AWG,UNINSULATED 0492500000 E.9
 H 16.0/15,6AWG,UNINSULATED 0124300000 E.9
 H 16.0/22,6AWG,INS, GREEN 0565900000 E.8
 H 16.0/28,6AWG,INS, GREEN 0566000000 E.8
 H 16.0/29 TWIN GREEN FERRULE 9037360000 E.11
 H 16.0/32 9004160000 E.9
 H 25/25 3 AWG UNINSULATED 9004170000 E.9

Description	Part Number	Page
-------------	-------------	------

H 25.0/15,4AWG,UNINSULATED 0124400000 E.9
 H 25.0/18,2AWG,UNINSULATED 0375300000 E.9
 H 25.0/29,4AWG,INS,BROWN 0317000000 E.8
 HDC-KIT HA 03.300M 1802470000 C.2
 HDC-KIT HA 04.402 M 1802700000 C.2
 H 25.0/32 9004180000 E.9
 H 25.0/35,4AWG,INS,BROWN 0317100000 E.8
 H 35/32 2 AWG UNINSULATED 9004190000 E.9
 H 35/32 2 AWG UNINSULATED 9004200000 E.9
 H 35.0/18,2AWG,UNINSULATED 0368900000 E.9
 H 35.0/30,2AWG,INS,BEIGE 0317200000 E.8
 H 35.0/30S 9451000000 E.8
 H 35.0/39,2AWG,INS,BEIGE 0317300000 E.8
 H 50/18 FERRULES 9004210000 E.9
 H 50/32 FERRULES W/O COLLAR 9004220000 E.9
 H 50.0 FERRULES 9025880000 E.9
 H 50.0/37, 1/O AWG INS. OLIVE 0444200000 E.8
 H 70/25 FERRULES 9004230000 E.9
 H 70/32 FERRULES 9004240000 E.9
 H 70.0/40 YELLOW 9028200000 E.8
 H 95/25 FERRULES 9004250000 E.9
 H 95/32 FERRULE W/O COLLAR 9004260000 E.9
 H 95/44 RED FERRULES 3/0 AWG 9028210000 E.8
 H 120/32 FERRULES W/O COLLARS 9036240000 E.9
 H 120/50 BLUE 9028220000 E.8
 H 150.0/32 9036250000 E.9
 H 150/54 YELLOW 9028230000 E.8
 H 185.0/32 9036260000 E.9
 HDC-KIT-HA 03.300 1712560000 C.2
 HDC-KIT-HA 03.301 1712570000 C.2
 HDC-KIT-HA 03.301 M 1802460000 C.2
 HDC-KIT-HA 03.302 1712580000 C.2
 HDC-KIT-HA 03.302 M 1802450000 C.2
 HDC-KIT-HA 03.404 1712630000 C.2
 HDC-KIT-HA 04.400 1712590000 C.2
 HDC-KIT-HA 04.400M 1802440000 C.2
 HDC-KIT-HA 04.401 1712600000 C.2
 HDC-KIT-HA 04.401 M 1802430000 C.2
 HDC-KIT-HA 04.402 1712610000 C.2
 HDC-KIT-HA 04.406 1712650000 C.2
 HDC-KIT-HE 06 100M 1802730000 C.2
 HDC-KIT-HE 06.100 1712460000 C.2
 HDC-KIT-HE 06.101 1712660000 C.2
 HDC-KIT-HE 06.101 M 1802740000 C.2
 HDC-KIT-HE 06.200 1712700000 C.2
 HDC-KIT-HE 06.COUPLER 7940000440 C.3
 HDC-KIT-HE 06.200 SIDE 7940000447 C.3
 HDC-KIT-HE 06.201 TOP 7940000446 C.3
 HDC-KIT-HE 10.110 1712510000 C.2
 HDC-KIT-HE 10.110M 1802420000 C.2
 HDC-KIT-HE 10.111 1712670000 C.2
 HDC-KIT-HE 10.111M 1802410000 C.2
 HDC-KIT-HE 10.210 1712710000 C.2
 HDC-KIT-HE 10.310 1/2 NPT 1763870000 C.2
 HDC-KIT-HE 10.311 1/2 NPT 1763910000 C.2
 HDC-KIT-HE 10.COUPLER 7940000441 C.3
 HDC-KIT-HE 10.210 SIDE 7940000449 C.3
 HDC-KIT-HE 10.211 TOP 7940000448 C.3
 HDC-KIT-HE 16.120 1712520000 C.2
 HDC-KIT-HE 16.120 M 1802400000 C.2
 HDC-KIT-HE 16.121 1712680000 C.2
 HDC-KIT-HE 16.121M 1802390000 C.2
 HDC-KIT-HE 16.220 1712720000 C.2
 HDC-KIT-HE 16.320 3/4 NPT 1763880000 C.2
 HDC-KIT-HE 16.321 3/4 NPT 1763920000 C.2
 HDC-KIT-HE 16.COUPLER 7940000442 C.3
 HDC-KIT-HE 16.220 SIDE 7940000451 C.3
 HDC-KIT-HE 16.221 TOP 7940000450 C.3
 HDC-KIT-HE 24 130M 1802380000 C.2
 HDC-KIT-HE 24.130 1712530000 C.2
 HDC-KIT-HE 24.131 1712690000 C.2
 HDC-KIT-HE 24.131 M 1802480000 C.2
 HDC-KIT-HE 24.230 1712730000 C.2
 HDC-KIT-HE 24.330 3/4 NPT 1763890000 C.2
 HDC-KIT-HE 24.331 3/4 NPT 1763930000 C.2
 HDC-KIT-HE 24.COUPLER 7940000443 C.3
 HDC-KIT-HE 24.230 SIDE 7940000453 C.3
 HDC-KIT-HE 24.231 TOP 7940000452 C.3
 HDC-KIT-HE 32.140M 1712540000 C.2
 HDC-KIT-HE 32.140M 1802370000 C.2
 HDC-KIT-HE 32.340 1 NPT 1763900000 C.2
 HDC-KIT-HE 32.COUPLER 7940000444 C.3
 HDC-KIT-HE 32.240 SIDE 7940000454 C.3
 HDC-KIT-HE 48. 150M 1802360000 C.2
 HDC-KIT-HE 48.150 1712550000 C.2
 HDC-KIT-HSB 06.500 1724000000 C.2
 HDC-KIT-HSB6 COUPLER 7940000445 C.3
 HEAT SINK FOR ULTRA SLIMPAK HS01-A D.24
 HO 34/10 TURQUOISE 9026030000 E.8
 HVDC 24VAC/DC 9906310000 D.6

I

IDK 1.5N PE, WEIMID GREEN/YELLOW 1792690000 A.14
 IDK 1.5N, WEIMID BEIGE 1792650000 A.14
 IDU 1.5N, WEIMID BEIGE 1792540000 A.14
 IDU 1.5N/3AN, WEIMID BEIGE 1792570000 A.14
 IDU 1.5N/3AN/ZB 1806170000 A.14
 IDU 1.5N/3AN/ZF 1806150000 A.14
 IDU 1.5N/4AN, WEIMID BEIGE 1792600000 A.14
 IDU 1.5N/ZB SCREW, WM BEIGE 1792730000 A.14
 IDU 1.5N/ZF TENSION, WM BEIGE 1792700000 A.14
 IDU 2.5N 1812900000 A.14
 IDU 2.5N/3AN 1812930000 A.14
 IDU 2.5N/3AN/ZB 1848300000 A.14
 IDU 2.5N/4N 1812960000 A.14

Description	Part Number	Page
IDU 2.5N/ZB	1821290000	A.14
IDU 2.5N/ZF	1821260000	A.14
IE-AR-10T	8845860000	G.5
IE-AR-10T-ISDN	8845750000	G.5
IE-ARM-E	8845760000	G.5
IE-ARM-U	8845770000	G.5
IE-CM CABLE CONNECTING MODULE	8808410000	G.6
IE-C-IP67 RJ45 IDC CABLE COUPL	8811309000	G.6
IE-CSM CABLE SHARING MODULE	8808400000	G.6
IE-CT ETHERNET TESTER	8808420000	G.7
IE-MC-SC FIBER CONVERTER	8808220000	G.3
IE-MC-ST FIBER CONVERTER	8808190000	G.3
IE-P-IP67	8808380000	G.6
IE-S-IP67 RJ45 IDC SOCKET MOD	8808370000	G.6
IE-SW14/2/SC-M	8845780000	G.4
IE-SW14/2SC ETHERNET SWITCH	8808280000	G.3
IE-SW14/2ST ETHERNET SWITCH	8808290000	G.3
IE-SW14/2ST-M	8845790000	G.4
IE-SW16 ETHERNET SWITCH	8808270000	G.3
IE-SW16-M	8845800000	G.4
IE-SW22 2ST ETHERNET SWITCH	8808320000	G.2
IE-SW22/2SC SWITCH	8808310000	G.2
IE-SW22/2SC-M	8845810000	G.4
IE-SW22/2ST-M	8845820000	G.4
IE-SW24 ETHERNET SWITCH	8808300000	G.2
IE-SW24-M	8845830000	G.4
IE-SW4/2SC ETHERNET SWITCH	8808250000	G.2
IE-SW4/2ST ETHERNET SWITCH	8808260000	G.3
IE-SW5-ECO 5 PORT SWITCH	8808230000	G.2
IE-SW5-ECO-FLAT ETHERNETSWITCH	8833790000	G.2
IE-SW6/2SC-M	8845840000	G.4
IE-SW6/2ST-M	8845850000	G.4
IE-SW8 8 PORT SWITCH	8808240000	G.2
IE-SW8-ECO 8 PORT SWITCH	8829430000	G.2
IE-SW8-M	8845740000	G.4
IE-X1M-RJ45/RJ45-IP67	8808450000	G.6
IE-XM ETHERNET OUTLET	8808360000	G.5
IE-XM-6D-RJ45/RJ45-IP67	8829450000	G.6
IE-XM-6U-RJ45/RJ45-IP67	8829440000	G.6
IE-XM-RJ45/IDC-IP67	8808440000	G.6
IE-XM-RJ45/RJ45	8879050000	G.5
IE-XM-ST ST ETHERNET OUTLET	8808340000	G.5
INK CARTRIDGE FOR PRINTJET II	1858920000	F.28
IP 58 FOR QB 58,58 POLE,8MM	0546000000	D.18
IP 75 FOR QB 75,75 POLE,6MM	0526700000	D.10
IP 75 FOR QB 75,75 POLE,6MM	0526700000	D.6
IP 75 FOR QB 75,75 POLE,6MM	0526700000	D.18
IPE 1.5N, WEMID YELLOW/GREEN	1792590000	A.14
IPE 1.5N/3AN, WM YELLOW/GREEN	1792590000	A.14
IPE 1.5N/3AN/ZB	1806160000	A.14
IPE 1.5N/3AN/ZF	1806140000	A.14
IPE 1.5N/4AN	1792620000	A.14
IPE 1.5N/ZB	1792750000	A.14
IPE 1.5N/ZF	1792720000	A.14
IPE 2.5N	1812920000	A.14
IPE 2.5N/3AN	1812950000	A.14
IPE 2.5N/3AN/ZB	1848320000	A.14
IPE 2.5N/4AN	1812980000	A.14
IPE 2.5N/ZB	1821310000	A.14
IPE 2.5N/ZF	1821280000	A.14
ITR 1.5N	1792630000	A.14
ITR 1.5N SI, WEMID BEIGE,SIHA3	1792640000	A.14
ITR 1.5N/3AN	1812510000	A.14
ITR 1.5N/3AN SI	1820390000	A.14
ITR 2.5N SI 5X20	1813010000	A.14
ITR 2.5N, WM, BG	1812990000	A.14

K

KDKS 1 EN MBB PA BG	1836770000	D.5
KDKS 1 EN/35 NO LED, WM, BEIGE	9503350000	A.8
KDKS 1 EN/SMT10-60VUC BFI H-	9802720001	A.8
KDKS 1 EN/SMT10-60VUC BFI H+	9808510001	A.8
KDKS 1 EN/SMT100-250VUC BFI H-	9802760001	A.8
KDKS 1 EN/SMT100-250VUC BFI H+	9515820001	A.8
KDKS 1 PE/35 NO LED, WM, BG	9528110000	A.8
KDKS 1 PE/SMT10-60VUC BFI H-	9158330001	A.8
KDKS 1 PE/SMT10-60VUC BFI H+	9158340001	A.8
KDKS 1 PE/SMT100-250VUC BFI H-	9158350001	A.8
KDKS 1 PE/SMT100-250VUC BFI H+	9915150001	A.8
KT 12 CABLE/WIRE CUTTER	9002660000	E.2
KT 35 BLADE	9002580000	E.3
KT 36 CABLE CUTTER 35MM	9001090000	E.2
KT 45 CABLE CUTTER 45MM DIA	9002000000	E.2
KT 8 CABLE CUTTER UP TO 6AWG	9002650000	E.2
KT20 UP TO AWG2/0 CABLE CUTTER	9002300000	E.2

M

MAGAZINE PRINTJET 115V(FEEDER)	1813090000	F.28
MAS DC/DC SELECT	8594810000	D.19
MAS PT100 0...100C	8594820000	D.21
MAS RPS W/O HART 4-20MA/4-20MA	8721150000	D.19
MAS RPSH HART 4-20MA/SELEC.OUT	8721170000	D.19
MAS THERMO J 0...700 OUTPUT	8615210000	D.23
MAS THERMO K 0...1000C OUT SEL	8594830000	D.23
MAZ DC/DC SELECT	8594840000	D.19
MAZ PT100 0-100C OUTPUT SELECT	8594850000	D.21
MAZ THERMO-J 0...700°C OUTPUT SELECT	8615240000	D.23
MAZ THERMO-K 0...1000°C OUTPUT SELECT	8594860000	D.23
MB FOR TS 32, M3/M5, CREAM	0053050000	A.17
MB FOR TS32, M5/M3, BLACK	0553400000	A.17
MB FOR TS32, M6/M4, GREY	0334900000	A.17
MC50 24VDC/5-34VDC 10A RES	7901690001	D.10
MC5R 115VAC IN 3.5MA/OUT 4A	7901600000	D.8

Description	Part Number	Page
MC5R 12/24VAC/DC IN15MA,OUT 4A	7901560000	D.6
MC5R 12V/24VDC IN 14MA,OUT 4A	7901540000	D.6
MC5R 24/48VAC/DC IN 7MA,OUT 4A	7901570000	D.8
MC5R 24V/48VDC IN 7MA,OUT 4A	7901550000	D.8
MC5R 24VDC,7MA/1 FORM C, 6A	7901620000	D.6
MC5RL 5-15L LOG/24 VAC/DC	7901590000	D.6
MC5RL 5-15VIN/AUX 24VDC,OUT 4A	7901580000	D.6
MC6 INS MAKE BEFORE BREAK TB	9917841000	D.5
MC6 NON-INCENDIVE BARRIER(ANG)	9918010000	D.5
MC6 NON-INCENDIVE BARRIER(DIG)	9916290000	D.5
MC6RF 120VACIN/SPST NO 5A FUSE	7923450120	D.8
MC6RF 24VUC IN/SPST NO 5A FUSE	7923450024	D.6
MCB 0.05 AMP;1 POLE	9124080000	B.5
MCB 0.08 AMP;1 POLE	9104650000	B.5
MCB 0.1 AMP;1 POLE	9104170000	B.5
MCB 0.2 AMP;1 POLE	9104180000	B.5
MCB 0.3 AMP;1 POLE	9129810000	B.5
MCB 0.4 AMP;1 POLE	9124090000	B.5
MCB 0.5 AMP;1 POLE	9101000000	B.5
MCB 0.6 AMP;1 POLE	9124110000	B.5
MCB 0.7 AMP;1 POLE	9129560000	B.5
MCB 0.8 AMP;1 POLE	9101100000	B.5
MCB 1.0 AMP;1 POLE	9101200000	B.5
MCB 1.2 AMP;1 POLE	9101300000	B.5
MCB 1.3 AMP;1 POLE	9124120000	B.5
MCB 1.4 AMP;1 POLE	9124130000	B.5
MCB 1.5 AMP;1 POLE	9101400000	B.5
MCB 1.8 AMP;1 POLE	9124140000	B.5
MCB 10.0 AMP;1 POLE	9101900000	B.5
MCB 11.0 AMP;1 POLE	9124180000	B.5
MCB 12.0 AMP;1 POLE	9107840000	B.5
MCB 13.0 AMP;1 POLE	9124190000	B.5
MCB 14.0 AMP;1 POLE	9107850000	B.5
MCB 15.0 AMP;1 POLE	9102000000	B.5
MCB 16.0 AMP;1 POLE	9124210000	B.5
MCB 2.0 AMP;1 POLE	9101500000	B.5
MCB 2.5 AMP;1 POLE	9101600000	B.5
MCB 3.0 AMP;1 POLE	9101700000	B.5
MCB 3.5 AMP;1 POLE	9124160000	B.5
MCB 4.0 AMP;1 POLE	9104350000	B.5
MCB 4.5 AMP;1 POLE	9124170000	B.5
MCB 5.0 AMP;1 POLE	9101800000	B.5
MCB 5.5 AMP;1 POLE	9107830000	B.5
MCB 6.0 AMP;1 POLE	9103810000	B.5
MCB 6.5 AMP;1 POLE	9120040000	B.5
MCB 7.0 AMP;1 POLE	9104150000	B.5
MCB 8.0 AMP;1 POLE	9103000000	B.5
MCB 9.0 AMP;1 POLE	9104610000	B.5
MCBD 0.05 AMP;2 POLE	9124220000	B.5
MCBD 0.1 AMP;2 POLE	9120350000	B.5
MCBD 0.2 AMP;2 POLE	9124240000	B.5
MCBD 0.3 AMP;2 POLE	9124260000	B.5
MCBD 0.4 AMP;2 POLE	9124270000	B.5
MCBD 0.5 AMP;2 POLE	9129580000	B.5
MCBD 0.6 AMP;2 POLE	9124280000	B.5
MCBD 0.7 AMP;2 POLE	9124290000	B.5
MCBD 0.8 AMP;2 POLE	9129590000	B.5
MCBD 1.0 AMP;2 POLE	9129610000	B.5
MCBD 1.2 AMP;2 POLE	9129620000	B.5
MCBD 1.3 AMP;2 POLE	9124310000	B.5
MCBD 1.4 AMP;2 POLE	9124320000	B.5
MCBD 1.5 AMP;2 POLE	9129630000	B.5
MCBD 1.8 AMP;2 POLE	9124330000	B.5
MCBD 10.0 AMP;2 POLE	9129680000	B.5
MCBD 11.0 AMP;2 POLE	9124430000	B.5
MCBD 12.0 AMP;2 POLE	9124440000	B.5
MCBD 13.0 AMP;2 POLE	9124450000	B.5
MCBD 14.0 AMP;2 POLE	9124460000	B.5
MCBD 15.0 AMP;2 POLE	9129690000	B.5
MCBD 16.0 AMP;2 POLE	9124470000	B.5
MCBD 2.0 AMP;2 POLE	9129640000	B.5
MCBD 2.5 AMP;2 POLE	9129650000	B.5
MCBD 3.0 AMP;2 POLE	9129660000	B.5
MCBD 3.5 AMP;2 POLE	9124340000	B.5
MCBD 4.0 AMP;2 POLE	9129710000	B.5
MCBD 4.5 AMP;2 POLE	9124350000	B.5
MCBD 5.0 AMP;2 POLE	9129670000	B.5
MCBD 5.5 AMP;2 POLE	9124360000	B.5
MCBD 6.0 AMP;2 POLE	9124370000	B.5
MCBD 6.5 AMP;2 POLE	9124380000	B.5
MCBD 7.0 AMP;2 POLE	9124390000	B.5
MCBD 8.0 AMP;2 POLE	9104670000	B.5
MCBD 9.0 AMP;2 POLE	9124420000	B.5
MCBD 0.08 AMP;2 POLE	9124230000	B.5
MCP AP	1924360000	F.29
MCP AP LABELS	1924370000	F.29
MCP AP SF 4-6	1924310000	F.29
MCP PLOTTER COVER	1924350000	F.29
MCP PLUS	1925000000	F.29
MCZ CCC 0-20MA/0-20MA LOOP PWR	8411190000	D.19
MCZ CFC 0-20MA	8461480000	D.19
MCZ CFC 4-20MACLP TO FREQUENCY	8461490000	D.19
MCZ O 24VDC/5V TTL OUT 50KHZ	8324610000	D.10
MCZ O 5V TTL IN/5-48VDC, 100MA	8398940000	D.12
MCZ OPTO 24VAC/DC/5-48VDC@20MA	8365940000	D.10
MCZ PT100/3 CLP 0 TO +150	8604420000	D.23
MCZ PT100/3 CLP 0-100C	8425720000	D.21
MCZ PT100/3 CLP 0-120 DEG C	8483680000	D.21
MCZ PT100/3 CLP 0-200C.	8473010000	D.23
MCZ PT100/3 CLP 0-300C	8473020000	D.23
MCZ PT100/3 CLP -40 TO +100	8604430000	D.21
MCZ PT100/3 CLP -50-150	8473000000	D.21
MCZ SC 0-10VDC SET POINT	8260280000	D.21
MCZ VFC 0-10V	8461470000	D.21
MCZSO 24VDC/5-34VDC 10A RES	7940000063	D.10
MOFU 35	0495660000	A.17
MOS 5VDC/24VDC 0.1A	8633020000	D.12

Description	Part Number	Page
MOS 5VDC/24VDC 2A	8633000000	D.12
MOS 24VDC/24VDC 0.1A	8607340000	D.10
MOS 24VDC/24VDC 2A	8607350000	D.10
MOS 24VDC/24VDC ACT	8676250000	D.10
MOS 24VDC/230VAC 1A	8652010000	D.10
MOS 120VUC/230VDC 1A	8651930000	D.12
MOS 120VUC/24VDC 0.1A	8607690000	D.12
MOS 120VUC/24VDC 2A	8607700000	D.12
MOS 230VAC/230VAC 1A	8561990000	D.12
MOS 230VAC/24VDC 0.1A	8607710000	D.12
MOS 230VAC/24VDC 2A	8607720000	D.12
MOUNTING FOOT, TS 35	0646260000	A.17
MOZ 5VDC/24VDC 0.1A	8633010000	D.12
MOZ 5VDC/24VDC 2A	8632990000	D.12
MOZ 24VDC/ 24VDC 0.1A	8607360000	D.10
MOZ 24VDC/24VDC 2A	8607370000	D.10
MOZ 24VDC/24VDC ACT	8676230000	D.10
MOZ 24VDC/230VAC 1A	8652020000	D.10
MOZ 120VUC / 24VDC 0,1A	8607730000	D.12
MOZ 120VUC / 24VDC 2A	8607740000	D.12
MOZ 120VUC/230VDC 1A	8651950000	D.12
MOZ 230VAC / 24VDC 0,1A	8607750000	D.12
MOZ 230VAC/230VAC 1A	8651970000	D.12
MOZ 230VAC/24VDC 2A	8607760000	D.12
M-PRINT 1.6 CD MULTILINGUAL	1784560000	F.30
M-PRINT PRO SOFTWARE CD	1905490000	F.30
MRS 5VDC 1CO 6A INRUSH	8556080000	D.6
MRS 12VDC 1CO 6A INRUSH	8556070000	D.6
MRS 12VDC C1D2 SECURED LEVER	7940004779	D.8
MRS 24VDC 1CO AU 6A INRUSH	8596060000	D.6
MRS 24VUC 1C 6A INRUSH	8556050000	D.6
MRS 24VDC 1CO 6A INRUSH	8533640000	D.6
MRS 24VDC ACTUATOR, 1NO+CC	8660920000	D.6
MRS 24VDC C1D2 SECURED LEVER	7940004781	D.6
MRS 48VUC 1CO 6A INRUSH	8556040000	D.8
MRS 60VDC 1CO 6A INRUSH	8556060000	D.8
MRS 120VUC 1CO 6A INRUSH	8556030000	D.8
MRS 120VUC 1CO AU 6A INRUSH	8652030000	D.8
MRS 120VAC C1D2 SECURED LEVER	7940004783	D.8
MRS 120VAC RC C1D2	7940023882	D.8
MRS 120VUC 1CO RC	8825970000	D.8
MRS 230VAC 1CO 5UAU	8596050000	D.8
MRS 230VAC 1CO 6A INRUSH	8556020000	D.8
MRZ 5VDC 1CO 6A INRUSH	8556150000	D.6
MRZ 12VDC 1CO 6A INRUSH	8556140000	D.6
MRZ 12VDC C1D2 SECURED LEVER	7940004780	D.6
MRZ 24 VDC 1CO 6A INRUSH	8533660000	D.6
MRZ 24 VDC 1CO AU 6A INRUSH	8596080000	D.6
MRZ 24VDC ACTUATOR, 1NO+CC	8660910000	D.6
MRZ 24VDC C1D2 SECURED LEVER	7940004782	D.6
MRZ 24VUC 1CO 6A INRUSH	8556120000	D.6
MRZ 48VUC 1CO 6A INRUSH	8556110000	D.8
MRZ 60 VDC 1CO 6A INRUSH	8556130000	D.8
MRZ 120 VUC 1CO 6A INRUSH	8556100000	D.8
MRZ 120 VUC 1CO AU 6A INRUSH	8652040000	D.8
MRZ 120VAC C1D2 SECURED LEVER	7940004784	D.8
MRZ 120VAC RC C1D2	7940023881	D.8
MRZ 120VUC 1CO RC	8825960000	D.8
MRZ 230VAC 1CO 5MICRON AU	8596070000	D.8
MRZ 230VAC 1CO 6A INRUSH	8556090000	D.8

O

OPTO W/O INPUT CURRENT LIMIT	9906660000	D.12
ORANGE STRIP FERRULES	9004270000	E.8

P

PAS CMR 0.5 TO 2.5A DC	8742610000	D.21
PAS CMR 2 TO 5A DC	8742620000	D.21
PAS CMR 4.5 TO 10A DC	8742630000	D.21
P-CLEANER	1924330000	F.29
PCS ADAPTOR FOR STI-S PEN	1762440000	F.29
PCS MCD CLEANER 25ML	1684460000	F.29
PCS MCD INK 22ML	1684477000	F.29
PCS PLOTTER PM 0.18 RED	1768570000	F.29
PCS PLOTTER PM 0.25 WHITE	1768540000	F.29
PCS PLOTTER PM 0.35 YELLOW	1768550000	F.29
PCS PLOTTER PM 0.50 BROWN	1768560000	F.29
PDU 2.5/4	1896110000	A.16
PDU 2.5/4/3AN	1896120000	A.16
PDU 2.5/4/4AN	1896130000	A.16
PG16-NPT 1/2	1712360000	C.3
PG21 - NPT 3/4	1712370000	C.3
PG29 - NPT 1	1712390000	C.3
PICOPAK 3 WIRE POTENTIOMETER	9908810000	D.23
PICOPAK DK6RELAY 24VDC/120VAC	9910590000	D.8
PICOPAK FREQUENCY DIVIDER DK5	9806370000	D.25
PICOPAK I TO I / DK6 WITH AP	9908800000	D.19
PICOPAK MC6/0-5AAC/4-20MA 2W	9916240000	D.25
PICOPAK MCZ II/	9916010000	D.10
PICOPAK OPT024/120 C/W LEAKAGE	9915700000	D.10
P-INK	1924340000	F.29
PLOTTER PM 0.25 P-INK	1920640000	F.29
PLOTTER PM 0.35 P-INK	1920650000	F.29
PLUG SERIES BLOCKER	1836880000	D.12
PLUG SERIES BLOCKER	1836880000	D.8
POS 24VDC/24VUC 1A	8610890000	D.10
POS 24VDC/24VDC 2A COMPLETE	8610840000	D.10
POS 24VDC/24VDC 5A	8610900000	D.10
POS 24VDC/230VAC 2A	8610860000	D.10
POS 24VDC/230VAC 4A	8610910000	D.10
POZ 24VDC/24VUC 1A	8610960000	D.10
POZ 24VDC/24VDC 2A	8610920000	D.10
POZ 24VDC/24VDC 5A	8610970000	D.10

Description	Part Number	Page
-------------	-------------	------

POZ 24VDC/230VAC 2A	8610930000	D.10
POZ 24VDC/230VAC 4A	8610980000	D.10
PPE 2.5/4	1896170000	A.16
PPE 2.5/4/3AN	1896200000	A.16
PPE 2.5/4/4AN	1896160000	A.16
PRC RETAINING CLIP PRS/PRZ	8536700000	D.8
PRC RETAINING CLIP PRS/PRZ	8536700000	D.12
PRINTJET II 115VAC	1858980000	F.28
PRINTJET II CLEANING UNIT	1858950000	F.28
PRS 12VDC LD 1CO COMPLETE	8536471001	D.6
PRS 12VDC LD 2CO COMPLETE	8536501001	D.6
PRS 24VAC LD 1CO COMPLETE	8536530000	D.8
PRS 24VAC LD 2CO COMPLETE	8536560000	D.8
PRS 24VDC LD 1CO COMPLETE	8536621001	D.6
PRS 24VDC LD 2CO COMPLETE	8536631001	D.6
PRS 115VDC LD 1CO COMPLETE	8536510000	D.8
PRS 115VDC LD 2CO COMPLETE	8536520000	D.8
PRS 120VAC LD 1CO COMPLETE	8536641001	D.8
PRS 120VAC LD 2CO COMPLETE	8536661001	D.8
PRS 230VAC LD 1CO COMPLETE	8536671001	D.8
PRS 230VAC LD 2CO COMPLETE	8536681001	D.8
PRZ 24VAC LD 1CO COMPLETE	8536651001	D.8
PRZ 24VAC LD 2CO COMPLETE	8536681001	D.8
PRZ 24VDC LD 1CO COMPLETE	8536691001	D.6
PRZ 24VDC LD 2CO COMPLETE	8536701001	D.6
PRZ 115VDC LD 1CO COMPLETE	8536610000	D.8
PRZ 115VDC LD 2CO COMPLETE	8536630000	D.8
PRZ 120VAC LD 1CO COMPLETE	8530710000	D.8
PRZ 120VAC LD 2CO COMPLETE	8530720000	D.8
PRZ 12VDC LD 1CO COMPLETE	8536571001	D.6
PRZ 12VDC LD 2CO COMPLETE	8536591001	D.6
PRZ 230VAC LD 1CO COMPLETE	8530731001	D.8
PRZ 230VAC LD 2CO COMPLETE	8530741001	D.8
PUNCH/DOWN TOOL PDT	9013970000	G.7
PZ 1.5	9005990000	E.10
PZ 1.5	9005990000	E.3
PZ 3 CRIMP TOOL,22-10AWG	0567300000	E.10
PZ 3 CRIMP TOOL,22-10AWG	0567300000	E.3
PZ 4 FERRULE CRIMPER 0.5-4MM2	9012500000	E.10
PZ 4 FERRULE CRIMPER 0.5-4MM2	9012500000	E.3
PZ 50 CRIMP TOOL,4-1/0AWG	9006450000	E.10
PZ 50 CRIMP TOOL,4-1/0AWG	9006450000	E.3
PZ 6 HEX	9013650000	E.10
PZ 6 HEX	9013650000	E.3
PZ 6 ROTO	9014350000	E.10
PZ 6 ROTO	9014350000	E.3
PZ 6/5 FERRULE CRIMPER	9011460000	E.10
PZ 6/5 FERRULE CRIMPER	9011460000	E.3
PZ ZH16 FOR TWIN FERRULES	9013600000	E.10
PZ ZH16 FOR TWIN FERRULES	9013600000	E.3
PZ16 CRIMP TOOL/METRIC CABLES	9012600000	E.10
PZ16 CRIMP TOOL/METRIC CABLES	9012600000	E.3

Q

QB 2 FOR 6/6.5MM TB,2 POLE	0482700000	D.10
QB 2 FOR 6/6.5MM TB,2 POLE	0482700000	D.6
QB 2 FOR 6/6.5MM TB,2 POLE	0482700000	D.18
QB 2 FOR 8MM TB,2 POLE	0461100000	D.18
QB 3 FOR 6/6.5MM TB,3 POLE	0482800000	D.10
QB 3 FOR 6/6.5MM TB,3 POLE	0482800000	D.6
QB 3 FOR 6/6.5MM TB,3 POLE	0482800000	D.18
QB 3 FOR 8MM TB,3 POLE	0461200000	D.18
QB 4 FOR 6/6.5MM TB,4 POLE	0482900000	D.10
QB 4 FOR 6/6.5MM TB,4 POLE	0482900000	D.18
QB 4 FOR 8MM TB,4 POLE	0461300000	D.18
QB 58 FOR 8MM TB,58 POLE,ANGLE	0545300000	D.18
QB 58 FOR 8MM TB,58 POLE,STRAI	0545400000	D.18
QB 75 FOR 6MM TB,75 POLE,ANGLE	0526400000	D.10
QB 75 FOR 6MM TB,75 POLE,ANGLE	0526400000	D.18
QB 75 FOR 6MM TB,75 POLE,ANGLE	0526400000	D.18
QB 75 FOR 6MM TB,75 POLE,STRAI	0535200000	D.10
QB 75 FOR 6MM TB,75 POLE,STRAI	0535200000	D.6
QB 75 FOR 6MM TB,75 POLE,STRAI	0535200000	D.18

R

RCM KIT 115VAC 4CO LED RED	8810150000	D.8
RCM KIT 24VDC 4CO LED	8798740000	D.6
RCM KIT 24VDC 4CO LED GREEN	7940007063	D.6
RCM KIT Z 115VAC 4 CO LDRT	8810080000	D.8
RED STRIP FERRULES	9004340000	E.8
RS 30 110VAC;SPST NO;GRN CSA	1102111001	D.8
RS 30 24VDC;SPDT;GRN LE CSA	1100210000	D.6
RS 30 24VDC;SPST NC;GRN CSA	1100911001	D.6
RS 30 24VDC;SPST NO;GRN CSA	1101611001	D.6
RS 30 24VDC SDT 250V 4A FUSE	37SM400F	D.6
RS-2D/SC FOR 24VDC P/S, 30A	9987390000	D.29
RS70-12V-C1D2-2C	330075	D.6
RS-AC/CB 120V SINGLE OUTLET	951480001	D.4
RS2 2X20A DIO W/FAN&TEMPMONI.	7940005219	D.29
RS2-40A DIODE W/FAN&TEMPMONI.	7940005218	D.27
RS-DUAL DIODE ARRAY 30A	9987860000	D.27
RS-DUPLEX 120VAC DUAL OUTLET	9915490000	D.4
RS-F10 IDC LP2N	0224961001	D.3
RS-F10 LPK 2H/12	8155610000	D.3
RS-F10 LPK 3/12	8012850000	D.3
RS-F14 IDC LP2N	0225061001	D.3
RS-F14 LPK 2H/16	8258980000	D.3
RS-F14 LPK 3/21	8012860000	D.3
RS-F20 IDC LP2N	0224261001	D.3
RS-F20 LPK 2H/22	8155600000	D.3
RS-F20 LPK 3/21	8012910000	D.3
RS-F34 IDC LP2N	0224361001	D.3

Description	Part Number	Page
-------------	-------------	------

RS-F34 LPK 2H/36	8155590000	D.3
RS-F34 LPK 3/36	8012930000	D.3
RS-F40	8155580000	D.3
RS-F40 IDC LP2N	0224461001	D.3
RS-F40 LPK 3/42	8012940000	D.3
RSHV AC, 110V W/O LED	9902860000	D.8
RS-SD 9B FEMALE LP2N	8003911001	D.3
RS-SD 9S MALE LP2N	8003901001	D.3
RS-SD 15B FEMALE LP2N	8005211001	D.3
RS-SD 15S MALE LP2N	8005201001	D.3
RS-SD 25B FEMALE LP2N	8005191001	D.3
RS-SD 25S MALE LP2N	8005181001	D.3
RS-SD 37B FEMALE LP2N	8003891001	D.3
RS-SD 37S MALE LP2N	8003881001	D.3
RS-SD 50B FEMALE LP2N	8005171001	D.3
RS-SD 50S MALE LP2N	8005161001	D.3

S

SAK 2.5 EN, PA, BEIGE	0218660000	A.6
SAK 2.5/32,KRG,BN	0279620000	A.6
SAK 2.5/32,PA,BG PLASTIC FOOT	0279660000	A.6
SAK 2.5/35,KRG,BN	0380420000	A.6
SAK 2.5/35,PA,BG	0380460000	A.6
SAK 4 EN, PA, BEIGE	0467460000	A.6
SAK 4/32,KRG,BN	0128320000	A.6
SAK 4/32,STEEL SPRING	1716240000	A.6
SAK 4/35,KRG,BN	0443620000	A.6
SAK 4/35,PA,BG	0443660000	A.6
SAK 6 EN, PA, BEIGE	0212860000	A.6
SAK 6 N/32,KRG,BN	0193220000	A.6
SAK 6 N/32,PA,BG	0193260000	A.6
SAK 6/35,KRG,BN	0380520000	A.6
SAK 6/35,PA,BG	0380560000	A.6
SAK 10 EN, PA, BEIGE	0337660000	A.6
SAK 10/32,KRG,BN	0110020000	A.6
SAK 10/32,PA,BG	0110060000	A.6
SAK 10/35,KRG,BN	0443720000	A.6
SAK 10/35,PA,BG	0443760000	A.6
SAK 16 EN, PA, BEIGE	0339760000	A.6
SAK 16/32,KRG,BN	0271020000	A.6
SAK 16/32,PA,BG	0271060000	A.6
SAK 16/35,KRG,BN	0380620000	A.6
SAK 16/35,PA,BG	0380660000	A.6
SAK 35 EN, PA, BEIGE	0339860000	A.6
SAK 35 N/32,SLOT HEAD,PA,BG	0550660000	A.6
SAK 35 N/35,SLOT HEAD,KRG,BN	0608220000	A.6
SAK 35 N/35,SLOT HEAD,PA,BG	0608260000	A.6
SAK 35/32,SLOT HEAD,KRG,BN	0303520000	A.6
SAKC 4/32,NO STB,KRG,BN	0340720000	A.10
SAKC 4/35,NO STB,KRG,BN	0357520000	A.10
SAKC 10/32, 2 STB,KRG,BN	0324120000	A.10
SAKC 10/35, 2 STB,KRG,BN	1404620000	A.10
SAKR/32,NO STB,KRG,BN	0412120000	A.10
SAKR/32,NO STB,PA,BG	0412160000	A.10
SAKR/35,NO STB,PA,BG	0172160000	A.10
SAKS 1/32,5X20,KRG,BN	0191220000	A.8
SAKS 1/35/5X20, KRG, BROWN	0501620000	A.8
SAKS 1/35/5X20, KRG, WM BEIGE	0501600000	A.8
SAKS 3 G/5X30 500V	0297520000	A.8
SAKS 3/35,5X30,KRG,BN	0328920000	A.8
SAKS 6/32, 1-1/4X1/4,KRG,BN	0531820000	A.8
SCHS 2 F.BS CARR. STRIP	0337400000	F.22
SCHS GROUP MARK,CARRIER	0138900000	F.22
SCHS2 ADHESIVE MARKING STRIP	1720600000	F.22
SCHS3 K	1753480000	F.22
SCHS4 K	1753460000	F.22
SCHT 5	0292460000	A.17
SCHT 5S	1631930000	A.17
SD 0.4X2.5X75, NON-INSUL,FLAT	9009030000	E.5
SD 0.4X2.0X60, NON-INSUL,FLAT	9037160000	E.5
SD 0.5X3.0X80, NON-INSUL,FLAT	9008320000	E.5
SD 0.6X3.5X100, NON-INSUL,FLAT	9008330000	E.5
SD 0.8X4.0X100, NON-INSUL,FLAT	9008340000	E.5
SD 0.8X4.5X125, NON-INSUL,FLAT	9009020000	E.5
SD 1.0X5.5X150, NON-INSUL,FLAT	9008350000	E.5
SD 1.2X6.5X150, NON-INSUL,FLAT	9009010000	E.5
SD TH30	9009140000	E.5
SD2S 0.6X3.5X200, NON-INSUL,FLAT	9010110000	E.5
SDI 0.4 X 2.5 X 75	9008370000	E.4
SDI 1,INSUL,FLAT,0.5X3.0X100	9008380000	E.4
SDI 1.0X4.5X125	9008910000	E.4
SDI 1.2X6.5X150	9008420000	E.4
SDI 2,INSUL,FLAT,0.6X3.5X100	9008390000	E.4
SDI 3,INSUL,FLAT,0.8X4.0X100	9008400000	E.4
SDI 4,INSUL,FLAT,1.0X5.5X125	9008410000	E.4
SDI 6,INSUL,FLAT,1.6X8.0X175	9008430000	E.4
SDI T8	9201940000	E.4
SDI T10	9009640000	E.4
SDI T15	9009650000	E.4
SDI T20	9009660000	E.4
SDI T25	9009670000	E.4
SDI T30	9009680000	E.4
SDI T40	9009690000	E.4
SDIK PZ1 SCREWDRIVER	9008900000	E.4
SDIK PHILIPS SIZE 1 INSULATED	9008570000	E.4
SDIK PHILIPS SIZE 2 INSULATED	9008580000	E.4
SDIK PHILIPS SIZE 3 INSULATED	9008590000	E.4
SDIK PZ2 SCREWDRIVER	9008890000	E.4
SDIS 2.55-5.5/PH1/2 SET	9009730000	E.6
SDK PHILIPS SIZE 0 NON-INSUL.	9008470000	E.5
SDK PHILIPS SIZE 1 NON-INSUL.	9008480000	E.5
SDK PHILIPS SIZE 2 NON-INSUL.	9008490000	E.5
SDK PHILIPS SIZE 3 NON-INSUL.	9008500000	E.5
SDP PZ0	9008520000	E.5
SDP PZ1	9008530000	E.5

Description	Part Number	Page
-------------	-------------	------

SDP PZ2	9008540000	E.5
SDP PZ3	9008550000	E.5
SDS 2.5-5.5/PH1/2	9009740000	E.7
SDTR 25 TORX HEAD SCREWDRIVER	9009150000	E.5
SDTR 8 TORX SCREWDRIVER	9009190000	E.5
SDTR TORX 10 SCREWDRIVER	9009180000	E.5
SDTR TORX 15 SCREWDRIVER	9009170000	E.5
SDTR TORX 20 SCREWDRIVER	9009160000	E.5
SF 0/12 NEUTRAL BL V0	1724050002	F.4
SF 0/12 NEUTRAL GE V0	1724050004	F.4
SF 0/12 NEUTRAL RT V0	1724050003	F.4
SF 0/12 NEUTRAL WS	1724050001	F.4
SF 0/21 NEUTRAL BL V0	1740850002	F.6
SF 0/21 NEUTRAL GE V0	1740850004	F.6
SF 0/21 NEUTRAL RT V0	1740850003	F.6
SF 0/21 NEUTRAL WS	1740850001	F.6
SF 00/12 NEUTRAL BL V0	1740830002	F.4
SF 00/12 NEUTRAL GE V0	1740830004	F.4
SF 00/12 NEUTRAL RT V0	1740830003	F.4
SF 00/12 NEUTRAL WS	1740830001	F.4
SF 00/21 NEUTRAL BL V0	1740840002	F.6
SF 00/21 NEUTRAL GE V0	1740840004	F.6
SF 00/21 NEUTRAL RT V0	1740840003	F.6
SF 00/21 NEUTRAL WS	1740840001	F.6
SF 1/12 NEUTRAL BLUE	1711320002	F.6
SF 1/12 NEUTRAL RED	1711320003	F.6
SF 1/12 NEUTRAL YELLOW	1711320004	F.6
SF 1/12 WHITE	1711320001	F.4
SF 1/21 BLUE (80 MARKERS/CARD)	1696090002	F.6
SF 1/21 RED (80 MARKERS /CARD)	1696090003	F.6
SF 1/21 WHITE (80MARKERS/CARD)	1696090001	F.6
SF 1/21 YELLOW 80 MARKERS/CARD	1696090004	F.6
SF 2/12 BLANK WHITE	1711350001	F.6
SF 2/12 NEUTRAL BLUE	1711350002	F.6
SF 2/12 NEUTRAL RED	1711350003	F.6
SF 2/12 NEUTRAL YELLOW	1711350004	F.6
SF 2/21 BLUE 80 MARKERS/CARD	1696100002	F.6
SF 2/21 RED 80 MARKERS/CARD	1696100003	F.6
SF 2/21 WHITE 80 MARKERS/CARD	1696100001	F.6
SF 2/21 YELLOW 80 MARKERS/CARD	1696100004	F.6
SF 3/12 BLANK WHITE	1711370001	F.6
SF 3/12 NEUTRAL BLUE	1711370002	F.6
SF 3/12 NEUTRAL RED	1711370003	F.6
SF 3/12 NEUTRAL YELLOW	1711370004	F.6
SF 3/21 BLANK WHITE	1696110001	F.6
SF 3/21 BLUE (64 MARKERS/CARD)	1696110002	F.6
SF 3/21 RED 64 MARKERS/CARD	1696110003	F.8
SF 3/21 YELLOW 64 MARKERS/CARD	1696110004	F.6
SF 4,5/21 NEUTRAL BL V0	1740860002	F.8
SF 4,5/21 NEUTRAL GE V0	1740860004	F.8
SF 4,5/21 NEUTRAL RT V0	1740860003	F.8
SF 4,5/21 NEUTRAL WHITE	1740860001	F.8
SF 4/12 NEUTRAL BL V0	1743490002	F.6
SF 4/12 NEUTRAL RT V0	1743490003	F.6
SF 4/12 NEUTRAL WS	1743490001	F.6
SF 4/12 NEUTRAL YELLOW	1743490004	F.10
SF 4/12 NEUTRAL YELLOW	1743490004	F.6
SF 4/21 BLUE	1696120002	F.8
SF 4/21 NEUTRAL GE V0	1696120004	F.8
SF 4/21 RED	1696120003	F.8
SF 4/21 WHITE	1696120001	F.8
SF 5/12 NEUTRAL BL V0	1743500002	F.6
SF 5/12 NEUTRAL RT V0	1743500003	F.6
SF 5/12 NEUTRAL WS	1743500001	F.6
SF 5/12 NEUTRAL YELLOW	1743500004	F.6
SF 5/21 NEUTRAL BL V0	1696130002	F.8

Description	Part Number	Page
SFC 2/30 NEUTRAL WHITE	1805870000	F.14
SFC 2/30 NEUTRAL YELLOW	1805830000	F.14
SF-TOOL 00-6	19050820000	F.12
SF-TOOL 1 (SLIMFIX)	1782970000	F.12
SF-TOOL 2-3 (SLIMFIX)	1782960000	F.12
SF-TOOL 4-5 (SLIMFIX)	1782980000	F.12
SF-TOOL COLLECTION (SLIMFIX)	1770080000	F.12
SFX 10/23 NEUTRAL BL	1727750002	F.4
SFX 10/23 NEUTRAL BL V2	1852400000	F.4
SFX 10/23 NEUTRAL GE	1727750004	F.4
SFX 10/23 NEUTRAL GE V2	1852360000	F.4
SFX 10/23 NEUTRAL RT V2	1852370000	F.4
SFX 10/23 NEUTRAL WS	1727750001	F.4
SFX 10/23 NEUTRAL WS V2	1852390000	F.4
SFX 10/23 RED	1727750003	F.4
SFX 11/60 MC NEUTRAL GR	1860130000	F.4
SFX 11/60 MC NEUTRAL WHITE	1860120000	F.4
SFX 11/60 MC NEUTRAL YELLOW	1860150000	F.4
SFX 14/23 NEUTRAL BL V2	1852450000	F.4
SFX 14/23 NEUTRAL BLUE	1713660002	F.4
SFX 14/23 NEUTRAL GE V2	1852410000	F.4
SFX 14/23 NEUTRAL RED	1713660003	F.4
SFX 14/23 NEUTRAL RT V2	1852420000	F.4
SFX 14/23 NEUTRAL WHITE	1713660001	F.4
SFX 14/23 NEUTRAL WS V2	1852440000	F.4
SFX 14/23 NEUTRAL YELLOW	1713660004	F.4
SFX 9/24 BLUE 32 MARKERS/CARD	1696140002	F.4
SFX 9/24 NEUTRAL BL V2	1852500000	F.4
SFX 9/24 NEUTRAL GE V2	1852460000	F.4
SFX 9/24 NEUTRAL RT V2	1852470000	F.4
SFX 9/24 NEUTRAL WS V2	1852490000	F.4
SFX 9/24 RED 32 (MARKERS/CARD)	1696140003	F.4
SFX 9/24 WHITE 32 MARKERS/CARD	1696140001	F.4
SFX 9/24 YELLOW 32 MARKERS/CARD	1696140004	F.4
SH 1 SOCKET BASE ONLY	0401460000	A.17
SH 1 BUSBAR SUPPORT,PA,BG	0299860000	A.17
SH 1 CLIP ONLY (BULK PACKAGING)	0635900000	A.17
SH 2 RAIL HOLDER,KRG,BN	0494920000	A.17
SH 2 S	0641720000	A.17
SHUNT RESISTOR 0.1OHM,5WATT,1%	C006	D.24
SIHA 3/G20/LD 10-36V	7921570000	A.12
SIHA 3/G20/LD 140-250V	7921600000	A.12
SIHA 3/G20/LD 35-70V	7921580000	A.12
SIHA 3/G20/LD 60-150V	7921590000	A.12
SK 10,0X125 SCREWDRIVER	9009070000	E.5
SK 11,0X125 SCREWDRIVER	9009060000	E.5
SK 12,0X125 SCREWDRIVER	9009050000	E.5
SK 13,0X125 SCREWDRIVER	9009040000	E.5
SK 5,0X125 SCREWDRIVER	9009130000	E.5
SK 5,5X125 ALLEN KEY	9009120000	E.5
SK 6,0X125 SCREWDRIVER	9009110000	E.5
SK 7,0X125 SCREWDRIVER	9009100000	E.5
SK 8,0X125 SCREWDRIVER	9009090000	E.5
SK 9,0X125 SCREWDRIVER	9009080000	E.5
SKI 10.0 X 126 BOX SPANNER	9009840000	E.4
SKI 11,0X125 HEXAGONAL SPANNER	9009830000	E.4
SKI 13,0X125 HEXAGONAL SPANNER	9009820000	E.4
SKI 5,0X129 HEXAGONAL SPANNER	9009000000	E.4
SKI 5,5X128 HEXAGONAL SPANNER	9009890000	E.4
SKI 6,0X128 HEXAGONAL SPANNER	9009880000	E.4
SKI 7,0X127 HEXAGONAL SPANNER	9008970000	E.4
SKI 8,0X127 HEXAGONAL SPANNER	9009860000	E.4
SKI 9,0X126 HEXAGONAL SPANNER	9008950000	E.4
SL-SMT3.5/17/90G 3.2SN SW BOX	1841780000	F.16
SL-SMT3.5/20/90G 3.2 SN BL BOX	1841810000	F.16
SM 22/22 K MC NEUTR. SI	1877590000	F.24
SM 22/22 K MC NEUTR. WS	1877570000	F.24
SM 27/12 5K NEUTRAL SI	1713720000	F.24
SM 27/12.5 K WS BLANK	1699880000	F.24
SM 27/12.5 NEUTRAL SILVER	1713700000	F.24
SM 27/12.5 WHITE	1699840000	F.24
SM 27/18 K NEUTRAL SILVER	1713760000	F.24
SM 27/18 NEUTRAL SILVER	1713740000	F.24
SM 27/18 WHITE	1699860000	F.24
SM 27/18K NEUTRAL WHITE	1707270000	F.24
SM 27/27 NEUTRAL SILVER	1773230000	F.24
SM 27/27 NEUTRAL WHITE	1773220000	F.24
SM 27/27K NEUTRAL	1783000000	F.24
SM 27/27K NEUTRAL SILVER	1782990000	F.24
SM 27/8 K SILVER NEUTRAL	1771930000	F.24
SM 27/8 K WHITE NEUTRAL	1812630000	F.24
SM-H 27/12.5 BLACK HOLDER	1716640000	F.24
SM-H 27/18 BLACK	1716630000	F.24
SM-H 27/27 HOLDER BLACK	1782710000	F.24
SST F.GRP MARK CARRIER	0139200000	F.22
STI-S FINE PEN BLK FOR PLOTTER	0508400000	F.29
STR CC 15/17 TRANSPARENT COVER	1888310000	F.26
STR CC 15/27 TRANSPARENT COVER	1888290000	F.26
STR CC 15/49 TRANSPARENT COVER	1888300000	F.26
STR CC 15/60 TRANSPARENT COVER	1888280000	F.26
STR CC 30/60 TRANSPARENT	1934450000	F.26
STR5 FOR SCHT5	0294000000	A.17
STR5S FOR SCHT5S	1631940000	A.17
STRIPAX 16	9005610000	E.2
STRIPAX PLUS	9020000000	E.10
STRIPAX PLUS	9020000000	E.3
STRIPAX PROFESSIONAL STRIPPER	9005000000	E.2

T

TM 0/12 HF/HB LABELS	1719760000	F.16
TM 0/18 HF/HB LABELS	1719770000	F.16
TM 1/12 HF/HB	1719780000	F.16
TM 1/18 HF/HB	1719790000	F.16
TM 2/12 HF LABELS	1719800000	F.16
TM 2/18 HF/HB LABEL	1719810000	F.16

Part Number	Description	Page
TM 3/12 HF/HB	1719820000	F.16
TM 3/18 HF/HB	1719830000	F.16
TM 4/12 HF/HB	1719840000	F.16
TM 4/18 HF/HB	1719850000	F.16
TM 5/12 HF/HB	1719860000	F.16
TM 5/18 HF/HB	1719870000	F.16
TM 6/12 HF/HB	1719880000	F.16
TM 6/18 HF/HB	1719890000	F.16
TM-1 12 NEUTRAL BL	1718411693	F.20
TM-1 12 NEUTRAL GN	1718411688	F.20
TM-1 12 NEUTRAL RT	1718411686	F.20
TM-1 12 NEUTRAL WHITE	1718411044	F.20
TM-1 12 NEUTRAL YELLOW	1718411687	F.20
TM-1 15 BLANK WHITE	1609981044	F.20
TM-1 15 BLANK YELLOW	1609981687	F.20
TM-1 15 NEUTRAL BL	1609981693	F.20
TM-1 15 NEUTRAL GN	1609981688	F.20
TM-1 15 NEUTRAL RT	1609981686	F.20
TM-1 18 NEUTRAL BL	1718431693	F.20
TM-1 18 NEUTRAL GN	1718431688	F.20
TM-1 18 NEUTRAL RT	1718431686	F.20
TM-1 18 NEUTRAL WHITE	1718431044	F.20
TM-1 18 NEUTRAL YELLOW	1718431687	F.20
TM-1 20 NEUTRAL BL	1680411688	F.20
TM-1 20 NEUTRAL GN	1680411688	F.20
TM-1 20 NEUTRAL RED	1680411686	F.20
TM-1 20 WHITE MC	1680411044	F.20
TM-1 20 YELLOW TAGS	1680411687	F.20
TM-1 30 MC NEUTRAL BL	1876400000	F.20
TM-1 30 MC NEUTRAL RT	1876380000	F.20
TM-1 30 MC NEUTRAL WHITE	1876390000	F.20
TM-1 30 MC NEUTRAL YELLOW	1876370000	F.20
TMX LABELS	1748820000	F.16
TS 32X15X1.5 2M STEEL M5 SLOT	0514400000	A.16
TS 32X15X1.5 2M STEEL M6 SLOT	0676100000	A.16
TS 32X15X1.5 2M STEEL SOLID	0122800000	A.16
TS 35X15X1.5 2M STEEL M5 SLOT	0236500000	A.16
TS 35X15X1.5 2M STEEL SOLID	0236400000	A.16
TS 35X15X2.3 2M STEEL SOLID	0498000000	A.16
TS 35X7.5X1.0 2M STEEL M5 SLOT	0514500000	A.16
TS 35X7.5X1.0 2M STEEL M6 SLOT	0676200000	A.16
TS 35X7.5X1.0 2M STEEL SOLID	0383400000	A.16
TST M5,PARALLEL,STEEL	1286600000	A.17
TST M6 ANGLED 49MM HIGH	7924273549	A.17
TST M6 ANGLED 58MM HIGH	7924273558	A.17
TST M6 ANGLED 68MM HIGH	7924273568	A.17
TST M6 ANGLED 88MM HIGH	7924273588	A.17
TST M6 ANGLED 98MM HIGH	7924273598	A.17
TST M6 STRAIGHT 30MM HIGH	7924270030	A.17
TST M6 STRAIGHT 40MM HIGH	7924270040	A.17
TST M6 STRAIGHT 50MM HIGH	7924270050	A.17
TST M6 STRAIGHT 70MM HIGH	7924270070	A.17
TST M6 STRAIGHT 90MM HIGH	7924270090	A.17
TST M6,PARALLEL,STEEL	0101700000	A.17
TST MG ANGLED 78MM HIGH	7924273578	A.17
TSTW 5/M5 2N	1779100000	A.17
TSTW M5,ANGLED,STEEL	0178100000	A.17
TSTW M6,ANGLED,STEEL	0164000000	A.17
TT 8 RS MP 8	9202800000	G.7

U

ULTRA SLIMPAK AC - DC ISOLATOR	G468	D.25
ULTRA SLIMPAK AC IN DUAL SET POINT OUT	G168	D.25
ULTRA SLIMPAK DC - DC ISOLATOR	G408	D.19
ULTRA SLIMPAK DC - DC ISOLATOR	G408	D.21
ULTRA SLIMPAK DC IN DUAL SET POINT OUT	G108	D.19
ULTRA SLIMPAK DC IN DUAL SET POINT OUT	G108	D.21
ULTRA SLIMPAK FREQUENCY ISOLATOR	G478	D.25
ULTRA SLIMPAK POTENTIOMETER	G438	D.23
ULTRA SLIMPAK RTD IN DUAL SETPOINT OUT	G118	D.21
ULTRA SLIMPAK RTD ISOLATOR	G418	D.21
ULTRA SLIMPAK STRAIN GAUGE ISOLATOR	G448	D.23
ULTRA SLIMPAK T/C IN DUAL SETPOINT OUT	G128	D.23
ULTRA SLIMPAK THERMO ISOLATOR	G428	D.23
UNI.OB 2M CABLE 18 CONDUCTOR	7940000628	D.3
UNIVERSAL I/O MODULE 1 FUSE	7940000602	D.3
UNIVERSAL I/O MODULE 2 FUSES	7940000604	D.3

V

VT SF 0/12 NEUTRAL BL V0	1752110002	F.8
VT SF 0/12 NEUTRAL GE V0	1752110004	F.8
VT SF 0/12 NEUTRAL RT V0	1752110003	F.8
VT SF 0/12 NEUTRAL WS V0	1752110001	F.8
VT SF 0/21 NEUTRAL BL V0	1730590002	F.10
VT SF 0/21 NEUTRAL GE V0	1730590004	F.10
VT SF 0/21 NEUTRAL RT V0	1730590003	F.10
VT SF 0/21 NEUTRAL WS V0	1730590001	F.10
VT SF 00/12 NEUTRAL BL V0	1752200002	F.8
VT SF 00/12 NEUTRAL GE V0	1752200004	F.8
VT SF 00/12 NEUTRAL RT V0	1752200003	F.8
VT SF 00/12 NEUTRAL WS V0	1752200001	F.8
VT SF 00/21 NEUTRAL BL V0	1730580002	F.10
VT SF 00/21 NEUTRAL GE V0	1730580004	F.10
VT SF 00/21 NEUTRAL RT V0	1730580003	F.10
VT SF 00/21 NEUTRAL WS V0	1730580001	F.10
VT SF 1/12 NEUTRAL BL V0	1718470002	F.8
VT SF 1/12 NEUTRAL GE V0	1718470004	F.8
VT SF 1/12 NEUTRAL RT V0	1718470003	F.8
VT SF 1/12 NEUTRAL WS V0	1718470001	F.8
VT SF 1/21 NEUTRAL BL V0	1689390002	F.10
VT SF 1/21 NEUTRAL GE V0	1689390004	F.10
VT SF 1/21 NEUTRAL RT V0	1689390003	F.10
VT SF 1/21 NEUTRAL WS V0	1689390001	F.10

Description	Part Number	Page
VT SF 2/12 NEUTRAL BL V0	1718480002	F.8
VT SF 2/12 NEUTRAL GE V0	1718480004	F.8
VT SF 2/12 NEUTRAL RT V0	1718480003	F.8
VT SF 2/12 NEUTRAL WS V0	1718480001	F.8
VT SF 2/21 NEUTRAL BL V0	1689410002	F.10
VT SF 2/21 NEUTRAL GE V0	1689410004	F.10
VT SF 2/21 NEUTRAL RT V0	1689410003	F.10
VT SF 2/21 NEUTRAL WS V0	1689410001	F.10
VT SF 3/12 NEUTRAL BL V0	1718490002	F.8
VT SF 3/12 NEUTRAL GE V0	1718490004	F.8
VT SF 3/12 NEUTRAL RT V0	1718490003	F.8
VT SF 3/12 NEUTRAL WS V0	1718490001	F.8
VT SF 3/21 NEUTRAL BL V0	1689430002	F.10
VT SF 3/21 NEUTRAL GE V0	1689430004	F.10
VT SF 3/21 NEUTRAL RT V0	1689430003	F.10
VT SF 3/21 NEUTRAL WS V0	1689430001	F.10
VT SF 4,5/21 NEUTRAL BL V0	1730570002	F.10
VT SF 4,5/21 NEUTRAL GE V0	1730570004	F.10
VT SF 4,5/21 NEUTRAL RT V0	1730570003	F.10
VT SF 4,5/21 NEUTRAL WS V0	1730570001	F.10
VT SF 4/12 NEUTRAL BL V0	1746030002	F.10
VT SF 4/12 NEUTRAL RT V0	1746030003	F.10
VT SF 4/12 NEUTRAL WS V0	1746030001	F.10
VT SF 4/21 NEUTRAL BL V0	1689450002	F.10
VT SF 4/21 NEUTRAL GE V0	1689450004	F.10
VT SF 4/21 NEUTRAL RT V0	1689450003	F.10
VT SF 4/21 NEUTRAL WS V0	1689450001	F.10
VT SF 5/12 NEUTRAL BL V0	1746040002	F.10
VT SF 5/12 NEUTRAL GE V0	1746040004	F.10
VT SF 5/12 NEUTRAL RT V0	1746040003	F.10
VT SF 5/12 NEUTRAL WS V0	1746040001	F.10
VT SF 5/21 NEUTRAL BL V0	1689470002	F.12
VT SF 5/21 NEUTRAL GE V0	1689470004	F.12
VT SF 5/21 NEUTRAL RT V0	1689470003	F.12
VT SF 5/21 NEUTRAL WS V0	1689470001	F.12
VT SF 6/21 NEUTRAL BL V0	1730560002	F.12
VT SF 6/21 NEUTRAL GE V0	1730560004	F.12
VT SF 6/21 NEUTRAL RT V0	1730560003	F.12
VT SF 6/21 NEUTRAL WS V0	1730560001	F.12

W

WAS 2 VMR 3 PHASE	8705630000	D.25
WAS 5 CCC LP 0-20/0-20MA	8444950000	D.19
WAS 5 CCC LP 0-20/0-20MA C1D2	8444950000C1D2	D.19
WAS1 CMA 1/5/10A AC	8523400000	D.25
WAS1 CMA LP 1/5/10A AC	8528650000	D.25
WAS2 CMA 20/25/30A UC	8545830000	D.25
WAS2 CMA 40/50/60 A UC	8513330000	D.25
WAS2 CMA 5/10A UC	8526610000	D.25
WAS2 CMR 1/5/10A AC	8516560000	D.25
WAS2 CMR 20/40/60A AC	8513340000	D.25
WAS2 VMR 1PHASE	8705640000	D.25
WAS2 WAVECONTROL VMA VAC	8581220000	D.25
WAS4 CCC DC 0-20/0-20MA	8445070000	D.19
WAS4 CCC DC 4-20/4-20MA	8444980000	D.19
WAS4 CCVC DC 4-20/0-10V	8445040000	D.19
WAS4 VCC DC 0-10/4-20MA	8447100000	D.21
WAS4 VVC DC 0-10/0-10V	8447130000	D.21
WAS4 WAVEPRO DC/DC	8560740000	D.19
WAS4 WAVEPRO DC/DC	8560740000	D.21
WAS4 WAVEPRO FREQUENCY	8581180000	D.25
WAS5 CCC 20LP	8581160000	D.19
WAS5 CCC DC 0(4)-20/0(4)-20MA	8540180000	D.19
WAS5 CCC HF 0-20/0-20MA	8447160000	D.19
WAS5 CCC LP 2CH. 0-20MA/0-20MA	8463580000	D.19
WAS5 CCC LP 2CH. 0-20MA/0-20MA	8463580000	D.19
WAS5 CVC DC 4-20MA/0-10V	8540230000	D.19
WAS5 CVC HF 4-20/0-10V	8447280000	D.19
WAS5 PRO RTD 1000	8679490000	D.23
WAS5 PRO RTD C/C	8638950000	D.23
WAS5 VCC DC 0-10V/4-20MA	8540290000	D.21
WAS5 VCC HF 0-10/4-20MA	8447340000	D.21
WAS5 VVC DC 0-10V/0-10V	8540330000	D.21
WAS5 VVC HF 0-10/0-10V	8447370000	D.21
WAS5 WAVEANALOG DC/ALARM	8543820000	D.19
WAS5 WAVEANALOG DC/ALARM	8543820000	D.21
WAS5 WAVEANALOG OUTPUT LOOP 2W	8543720000	D.19
WAS5 WAVEPRO BRIDGE	8581200000	D.23
WAS5 WAVEPRO RTD	8560700000	D.21
WAS5 WAVEPRO RTD	8560700000	D.23
WAS5 WAVEPRO RTD C1D2	8560700000C1D2	D.21
WAS5 WAVEPRO RTD C1D2	8560700000C1D2	D.23
WAS5 WAVEPRO THERMO	8560720000	D.23
WAS5 WAVEPRO THERMO C1D2	8560720000C1D2	D.23
WAVEPAK 0-300VDC/4-20MA/24V 3W	9916340000	D.21
WAVEPAK LOOP SPLITTER C1D2,Z2	7920400000	D.19
WAVEPAK MPI-OPTO	9916080000	D.10
WAZ 5 CCC 20LP	8581170000	D.19
WAZ 5 CCC LP 0-20/0-20MA	8444960000	D.19
WAZ 5 CCC LP 0-20/0-20MA C1D2	8444960000C1D2	D.19
WAZ1 CMA 1/5/10A AC	8523410000	D.25
WAZ1 CMA LP 1/5/10A AC	8528660000	D.25
WAZ2 CMA 20/25/30A UC	8545840000	D.25
WAZ2 CMA 40/60/60A UC	8526590000	D.25
WAZ2 CMA 5/10A UC	8526620000	D.25
WAZ2 CMR 1/5/10A AC	8516570000	D.25
WAZ2 CMR 20/40/60A AC	8526600000	D.25
WAZ2 WAVECONTROL VMA VAC	8581230000	D.25
WAZ4 CCC DC 0-20/0-20MA	8445080000	D.19
WAZ4 CCC DC 4-20/4-20MA	8444990000	D.19
WAZ4 CCVC DC 4-20/0-10V	8445050000	D.19
WAZ4 VCC DC 0-10/4-20MA	8447110000	D.21
WAZ4 VVC DC 0-10/0-10V	8447140000	D.21
WAZ4 WAVEPRO DC/DC	8560750000	D.19
WAZ4 WAVEPRO DC/DC	8560750000	D.21

X.7

Part Number	Description	Page
-------------	-------------	------

0100000000

0101700000	TST M6,PARALLEL,STEEL	A.17
0110020000	SAK 10/32,KRG,BN	A.6
0110060000	SAK 10/32,PA,BG	A.6
0122800000	TS 32X15X1.5 2M STEEL SOLID	A.16
0124300000	H 16.0/15,6AWG,UNINSULATED	E.9
0124400000	H 25.0/15,4AWG,UNINSULATED	E.9
0124700000	H 6.0/15,10AWG,UNINSULATED	E.9
0124800000	H 10.0/15,8AWG,UNINSULATED	E.9
0128320000	SAK 4/32,KRG,BN	A.6
0138900000	SCHS GROUP MARK,CARRIER	F.22
0139000000	ESO F.GRP MARK CARRIER	F.22
0139200000	SST F.GRP MARK CARRIER	F.22
0164000000	TSTW M6,ANGLED,STEEL	A.17
0172160000	SAKR/35,NO STB,PA,BG	A.10
0178100000	TSTW M5,ANGLED,STEEL	A.17
0186100000	H 2.5/12,14AWG,UNINSULATED	E.9
0186500000	H 1.5/10,16AWG,UNINSULATED	E.9
0190160000	EK 16/35,PA,GN/YL	A.8
0191220000	SAKS 1/32,5X20,KRG,BN	A.8
0191900000	H 6.0/12,10AWG,UNINSULATED	E.9
0193220000	SAK 6 N/32,KRG,BN	A.6
0193260000	SAK 6 N/32,PA,BG	A.6
0199360000	EWK 2 FOR TS 32,PA,BG	A.16
0199360000	EWK 2 FOR TS 32,PA,BG	A.18

0200000000

0206160000	EWK 1 FOR TS 32,PA,BG	A.16
0206160000	EWK 1 FOR TS 32,PA,BG	A.18
0212860000	SAK 6 EN, PA, BEIGE	A.6
0218660000	SAK 2.5 EN, PA, BEIGE	A.6
0222760001	ASK1EN/SMT100-60VUC BFI H-	A.8
0224261001	RS-F20 IDC LP2N	D.3
0224361001	RS-F34 IDC LP2N	D.3
0224461001	RS-F40 IDC LP2N	D.3
0224961001	RS-F10 IDC LP2N	D.3
0225061001	RS-F14 IDC LP2N	D.3
0225560001	ASK1EN/SMT100-250VUC BFI H-	A.8
0236400000	TS 35X15X1.5 2M STEEL SOLID	A.16
0236500000	TS 35X15X1.5 2M STEEL M5 SLOT	A.16
0244100000	H 4.0/12,12AWG,UNINSULATED	E.9
0271020000	SAK 16/32,KRG,BN	A.6
0271060000	SAK 16/32,PA,BG	A.6
0279620000	SAK 2.5/32,KRG,BN	A.6
0279660000	SAK 2.5/32,PA,BG PLASTIC FOOT	A.6
0282600000	H 0.5/6,26-22AWG,UNINSULATED	E.9
0282700000	H 0.75/6,20AWG,UNINSULATED	E.9
0282800000	H 1.0/10,18AWG,UNINSULATED	E.9
0282900000	H 10.0/12,8AWG,UNINSULATED	E.9
0292460000	SCHT 5	A.17
0294000000	STR5 FOR SCHT5	A.17
0295900000	BS M5X8 HEX F.TST/TSTW,ST	A.17
0297520000	SAKS 3 G/5X30 500V	A.8
0299860000	SH1 BUSBAR SUPPORT,PA,BG	A.17

0300000000

0303520000	SAK 35/32,SLOT HEAD,KRG,BN	A.6
0317000000	H 25.0/29,4AWG,INS,BROWN	E.8
0317100000	H 25.0/35,4AWG,INS,BROWN	E.8
0317200000	H 35.0/30,2AWG,INS,BEIGE	E.8
0317300000	H 35.0/39,2AWG,INS,BEIGE	E.8
0324120000	SAKC 10/32,2 STB,KRG,BN	A.10
0328920000	SAKS 3/35,5X30,KRG,BN	A.8
0334900000	MB FOR TS32, M6/M4, GREY	A.17
0337400000	SCHS 2 FBS CARR. STRIP	F.22
0337660000	SAK 10 EN, PA, BEIGE	A.6
0339760000	SAK 16 EN, PA, BEIGE	A.6
0339860000	SAK 35 EN, PA, BEIGE	A.6
0340720000	SAKC 4/32,NO STB,KRG,BN	A.10
0353500000	BS M6X12 HEX F.TST/TSTW,ST	A.17
0354560000	EK 4/32,PA,GN/YL	A.8
0354660000	EK 10/32,PA,GN/YL	A.8
0354760000	EK 35/32,PA,GN/YL	A.8
0357520000	SAKC 4/35,NO STB,KRG,BN	A.10
0368900000	H 35.0/18,2AWG,UNINSULATED	E.9
0372600000	H 1.0/6,18AWG,UNINSULATED	E.9
0372700000	H 1.5/7,16AWG,UNINSULATED	E.9
0373000000	H 2.5/7,14AWG,UNINSULATED	E.9
0373100000	H 4.0/9,12AWG,UNINSULATED	E.9
0374660000	EK 16/32,PA,GN/YL	A.8
0375200000	H 16/18 6 AWG UNINSULATED	E.9
0375300000	H 25.0/18,2AWG,UNINSULATED	E.9
0379300000	H 10.0/18,8AWG,UNINSULATED	E.9
0380420000	SAK 2.5/35,KRG,BN	A.6
0380460000	SAK 2.5/35,PA,BG	A.6
0380520000	SAK 6/35,KRG,BN	A.6
0380560000	SAK 6/35,PA,BG	A.6
0380620000	SAK 16/35,KRG,BN	A.6
0380660000	SAK 16/35,PA,BG	A.6
0383400000	TS 35X7.5X1.0 2M STEEL SOLID	A.16
0383560000	EW 35 FOR TS 35,PA,BG	A.16
0383560000	EW 35 FOR TS 35,PA,BG	A.18

0400000000

0401460000	SH 1 SOCKET BASE ONLY	A.17
0409500000	H 0.5/12,20 AWG,INS, ORANGE	E.8

Part Number	Description	Page
-------------	-------------	------

0409600000	H 0.75/12,18AWG,INS,WHITE	E.8
0409700000	H 1.0/12,18AWG,INS,YELLOW	E.8
0412120000	SAKR/32,NO STB,KRG,BN	A.10
0412160000	SAKR/32,NO STB,PA,BG	A.10
0443620000	SAK 4/35,KRG,BN	A.6
0443660000	SAK 4/35,PA,BG	A.6
0443720000	SAK 10/35,KRG,BN	A.6
0443760000	SAK 10/35,PA,BG	A.6
0444200000	H 50.0/37,1/0 AWG INS. OLIVE	E.8
0461100000	QB 2 FOR 8MM TB,2 POLE	D.18
0461200000	QB 3 FOR 8MM TB,3 POLE	D.18
0461300000	QB 4 FOR 8MM TB,4 POLE	D.18
0462900000	H 0.75/14,18AWG,INS,WHITE	E.8
0463000000	H 1.0/14,18AWG,INS,YELLOW	E.8
0463100000	H 1.5/14,16AWG,INS,RED	E.8
0467460000	SAK 4 EN, PA, BEIGE	A.6
0473360000	DEKAFIX 5MM BLANK - WHITE	D.24
0474360000	EK 2.5 N/32,PA,GN/YL	A.8
0474560000	ASK 1 EN, NO LED, PA, BG	A.8
0482700000	QB 2 FOR 6/6.5MM TB,2 POLE	D.6
0482700000	QB 2 FOR 6/6.5MM TB,2 POLE	D.10
0482700000	QB 2 FOR 6/6.5MM TB,2 POLE	D.18
0482800000	QB 3 FOR 6/6.5MM TB,3 POLE	D.6
0482800000	QB 3 FOR 6/6.5MM TB,3 POLE	D.10
0482800000	QB 3 FOR 6/6.5MM TB,3 POLE	D.18
0482900000	QB 4 FOR 6/6.5MM TB,4 POLE	D.6
0482900000	QB 4 FOR 6/6.5MM TB,4 POLE	D.10
0482900000	QB 4 FOR 6/6.5MM TB,4 POLE	D.18
0492500000	H 16.0/12,6AWG,UNINSULATED	E.9
0494920000	SH 2 RAIL HOLDER,KRG,BN	A.17
0495160000	EWK 1 FOR TS 32 SLOT,PA,BG	A.18
0495160000	EWK 1 FOR TS 32 SLOT,PA,BG	A.16
0495660000	MOFU 35	A.17
0498000000	TS 35X15X2.3 2M STEEL SOLID	A.16

0500000000

0501600000	SAKS 1/35/5X20, KRG, WM BEIGE	A.8
0501620000	SAKS 1/35/5X20, KRG, BROWN	A.8
0503500000	MB FOR TS 32, M3/M5, CREAM	A.17
0508400000	STI-S FINE PEN BLK FOR PLOTTER	F.29
0514400000	TS 32X15X1.5 2M STEEL M5 SLOT	A.16
0514500000	TS 35X7.5X1.0 2M STEEL M5 SLOT	A.16
0526400000	QB 75 FOR 6MM TB,75 POLE,ANGLE	D.6
0526400000	QB 75 FOR 6MM TB,75 POLE,ANGLE	D.10
0526400000	QB 75 FOR 6MM TB,75 POLE,ANGLE	D.18
0526700000	IP 75 FOR QB 75,75 POLE,6MM	D.6
0526700000	IP 75 FOR QB 75,75 POLE,6MM	D.10
0526700000	IP 75 FOR QB 75,75 POLE,6MM	D.18
0531820000	SAKS 6/32,1-1/4X1/4,KRG,BN	A.8
0533500000	H 6.0/20,10AWG,INS,BLACK	E.8
0534200000	H 10.0/21,8AWG,INS,IVORY	E.8
0535200000	QB 75 FOR 6MM TB,75 POLE,STRAI	D.6
0535200000	QB 75 FOR 6MM TB,75 POLE,STRAI	D.10
0535200000	QB 75 FOR 6MM TB,75 POLE,STRAI	D.18
0535200000	H 0.75/10,20AWG,UNINSULATED	E.9
0535200000	QB 58 FOR 8MM TB,58 POLE,ANGLE	D.18
0535200000	QB 58 FOR 8MM TB,58 POLE,STRAI	D.18
0535200000	IP 58 FOR QB 58,58 POLE,8MM	D.18
0550660000	SAK 35 N/32,SLOT HEAD,PA,BG	A.6
0553400000	MB FOR TS32, M5/M3, BLACK	A.17
0565600000	H 1.5/24,16AWG,INS,RED	E.8
0565700000	H 6.0/26,10AWG,INS,BLACK	E.8
0565800000	H 10.0/27,8AWG,INS,IVORY	E.8
0565900000	H 16.0/22,6AWG,INS,GREEN	E.8
0566000000	H 16.0/28,6AWG,INS,GREEN	E.8
0567300000	PZ 3 CRIMP TOOL,22-10AWG	E.10
0567300000	PZ 3 CRIMP TOOL,22-10AWG	E.3

0600000000

0608220000	SAK 35 N/35,SLOT HEAD,KRG,BN	A.6
0608260000	SAK 35 N/35,SLOT HEAD,PA,BG	A.6
0635100000	H 1.5/16,16AWG,INS,RED	E.8
0635900000	SH1 CLIP ONLY (BULK PACKAGING)	A.17
0636800000	FM5 (M5)	A.17
0636900000	FM6 (M6) FOR TS 35	A.17
0641720000	SH 2 S	A.17
0642600000	BS M6X8 HEX F.TST/TSTW,ST	A.17
0642600000	MOUNTING FOOT, TS 35	A.17
0661060000	EK 2.5/35,PA,GN/YL	A.8
0661160000	EK 4/35,PA,GN/YL	A.8
0661260000	EK 6/35,PA,GN/YL	A.8
0661360000	EK 10/35,PA,GN/YL	A.8
0661460000	EK 35/35,PA,GN/YL	A.8
0676100000	TS 32X15X1.5 2M STEEL M6 SLOT	A.16
0676200000	TS 35X7.5X1.0 2M STEEL M6 SLOT	A.16
0687360000	DKT 4/32,PA,BG	A.10
0687460000	DKT 4/35,PA,BG	A.10
0687560000	AP FOR DKT 4,PA,BG	D.10
0687560000	AP FOR DKT 4,PA,BG	D.6
0687900000	FM 4 MOUNTING FOOT FOR TS 35	A.17
0690700000	H 0.5/14,20AWG,INS,ORANGE	E.8

1000000000

1010000000	WPE 2.5,WM,GN/YL	A.2
1010100000	WPE 4,WM,GN/YL	A.2
1010200000	WPE 6,WM,GN/YL	A.2
1010300000	WPE 10,WM,GN/YL	A.2
1010400000	WPE 16,WM,GN/YL	A.2
1010500000	WPE 35,FLAT HEAD,WM,GN/YL	A.2
1011000000	WSI 6 WM NO LED FOR 5x20	A.2
1011300000	WSI 6/LD 10-36VAC/DC WM BG	A.2

Part Number	Description	Page
-------------	-------------	------

1012200000	WSI 6/LD 30-70VAC/DC, WM, BG	A.2
1012300000	WSI 6/LD 60-150VAC/DC WM BG	A.2
1012400000	WSI 6/LD 140-250VACDC, WM BG	A.2
1014000000	WSI 6/2,1/4,NO LED	A.2
1014100000	WSI 6/2/LD 10-36VAC/DC, WM BG	A.2
1014200000	WSI 6/2/LD 30-70VAC/DC, WM, BG	A.2
1014300000	WSI 6/2/LD 60-150VAC/DC WM BG	A.2
1014400000	WSI 6/2/LD 140-250VAC/DC WM BG	A.2
1019700000	WPE 120	A.2
1020000000	WDU 2.5,WM,BG	A.2
1020100000	WDU 4,WM,BG	A.2
1020200000	WDU 6,WM,BG	A.2
1020300000	WDU 10,WM,BG	A.2
1020400000	WDU 16,WM,BG	A.2
1020500000	WDU 35,FLAT HEAD,WM,BG	A.2
1021500000	WDK 2.5,WM,BG	A.2
1022300000	WDK 2.5V,WM,BG	A.2
1024500000	WDU 120,ALLEN HEAD,WM,BG	A.2
1024600000	WDU 70/95,ALLEN HEAD,WM,BG	A.2
1036300000	WDK 2.5 PE	A.2
1037300000	WPE 70/95	A.2
1041100000	WDK 2.5 W/ 2 ZOV PER LEVEL	A.2
1041600000	WDK 2.5N, BG WM	A.2
1041610000	WDK 2.5N V, BG, WM	A.2
1041620000	WDK 2.5N PE YL/GE WM	A.2
1041900000	WDK 4N BG WM	A.2
1041910000	WDK 4N V, BG WM	A.2
1041920000	WDK 4N PE YL/GE WM	A.2
1059000000	WEW 35/1,GF PA, DB	A.16
1059000000	WEW 35/1,GF PA, DB	A.18
1061200000	WEW 35/2,GF PA, DB	A.16
1061200000	WEW 35/2,GF PA, DB	A.18
1067600000	WEW 32/1	A.16

1100000000

1100210000	RS 30 24VDC;SPDT;GRN LE	CSA	D.6
1100911001	RS 30 24VDC;SPST NC;GRN	CSA	D.6
1101611001	RS 30 24VDC;SPST NO;GRN	CSA	D.6
1102111001	RS 30 110VAC;SPST NO;GR	CSA	D.8

1200000000

1288600000	TST M5,PARALLEL,STEEL	A.17
------------	-----------------------	------

1400000000

1404620000	SAKC 10/35,2 STB,KRG,BN	A.10
------------	-------------------------	------

1600000000

1600740000	WPF 1-20 WS/GE NEUTRAL	F.20
1607710000	ES05 FOR SCHT5 (60 PER SHEET)	A.17
1607710000	ES05 FOR SCHT5 (60 PER SHEET)	F.20
1607720000	ES0 7 A4 PAPER, WHITE 240PCS.	F.20
1608510000	ZDU 2.5	A.10
1608620000	ZDU 6	A.10
1608640000	ZPE 2.5	A.10
1608670000	ZPE 6	A.10
1608950000	ZQV 4/2	D.12
1608950000	ZQV 4/2	D.20
1608960000	ZQV 4/3	D.12
1608960000	ZQV 4/3	D.20
1608970000	ZQV 4/4	D.6
1608970000	ZQV 4/4	D.12
1608970000	ZQV 4/4	D.20
1608980000	ZQV 4/5	D.20
1608990000	ZQV 4/6	D.20
1609000000	ZQV 4/7	D.20
1609010000	ZQV 4/8	D.20
1609020000	ZQV 4/9	D.20
1609030000	ZQV 4/10	D.6
1609030000	ZQV 4/10	D.12
1609030000	ZQV 4/10	D.20
1609800000	DEK 5/5 MC-10 NEUT. VAR	D.24
1609801044	DEK 5/5 MC-10 BLANK WHITE	F.2
1609820000	DEK 5/6 MC NEUTRAL WHITE	D.6
1609820000	DEK 5/6 MC NEUTRAL WHITE	D.10
1609820000	DEK 5/6 MC NEUTRAL WHITE	D.12
1609820000	DEK 5/6 MC NEUTRAL WHITE	D.18
1609820000	DEK 5/6 MC NEUTRAL WHITE	D.20
1609820000	DEK 5/6 MC NEUTRAL WHITE	F.2
1609840000	DEK 5/6.5 MC NEUTRAL WHITE	D.22
1609840000	DEK 5/6.5 MC NEUTRAL WHITE	F.2
1609860000	WS 12/5 MULTICARD	F.2
1609888000	WS 15/5 MULTICARD	D.8
1609888000	WS 15/5 MULTICARD	D.12
1609880000	WS 15/5 MULTICARD	F.2
1609900000	WS 12/6 MULTICARD	D.6
1609900000	WS 12/6 MULTICARD	F.2
1609920000	WS 12/6.5 MC WHITE BLANK	F.2
1609940000	ESC 9/20 MULTICARD	F.22
1609981044	TM-1 15 BLANK WHITE	F.20
1609981686	TM-1 15 NEUTRAL RT	F.20
1609981687	TM-1 15 BLANK YELLOW	F.20
1609981688	TM-1 15 NEUTRAL GN	F.20
1609981693	TM-1 15 NEUTRAL BL	F.20

Part Number	Description	Page
-------------	-------------	------

1616400000	ZSI 2.5	A.12
1616410000	ZSI 2.5/LD 60-150VDC140-250VAC	A.12
1616420000	ZSI 2.5/LD 60-150VAC/DC	A.12
1616430000	ZSI 2.5/LD 30-70VAC/DC	A.12
1616440000	ZSI 2.5/LD 10-36VAC/DC	A.12
1616460000	ZSI 2.5/2 500AC	A.12
1616470000	ZSI 2.5/2/LD 10-36VAC/DC	A.12
1616480000	ZSI 2.5/2/LD 30-70VAC/DC	A.12
1616490000	ZSI 2.5/2/LD 60-150VAC/DC	A.12
1616500000	ZSI 2.5/2/LD60-150VDC/140-250VA	A.12

1630000000

1631350000	ESO 5 YELLOW	F.20
1631910000	WKM 8/30	F.18
1631920000	ESOS5 F. SCHT5S(140 PER SHEET)	A.17
1631930000	SCHT 5S	A.17
1631940000	STR5S FOR SCHT5S	A.17
1632050000	ZDU 4	A.10
1632080000	ZPE 4	A.10
1634780000	ESO 7 A4 PAPER YELLOW	F.20
1635000000	WS 10/5 MULTICARD	D.12
1635000000	WS 10/5 MULTICARD	D.8
1635000000	WS 10/5 MULTICARD	D.22
1635000000	WS 10/5 MULTICARD	F.2

1640000000

1640740000	WS 8/5 FOR MULTICARD SYSTEM	F.2
1646630000	ZS 15/5 WHITE	F.2

1650000000

1652220000	ESG 8/19 MULTICARD NEUTRAL	F.22
------------	----------------------------	------

1670000000

1670370000	ESO 5 (POLYESTER WHITE)	F.20
1670380000	ESO 5 POLYESTER YELLOW A4	F.20
1670390000	ESO 7 POLYESTER WHITE	F.20
1670400000	ESO 7 POLYESTER YELLOW A4	F.20
1674740000	ESG 8/17 MULTICARD NEUTRAL	F.22
1674760000	ESG 9/17K UNIVERSAL MULTICARD	F.22

1680000000

1680411044	TM-I 20 WHITE MC	F.20
1680411686	TM-I 20 NEUTRAL RED	F.20
1680411687	TM-I 20 YELLOW TAGS	F.20
1680411688	TM-I 20 NEUTRAL GN	F.20
1680411693	TM-I 20 NEUTRAL BL	F.20
1684460000	PCS MCD CLEANER 25ML	F.29
1684470000	PCS MCD INK 22ML	F.29
1689390001	VT SF 1/21 NEUTRAL WS V0	F.10
1689390002	VT SF 1/21 NEUTRAL BL V0	F.10
1689390003	VT SF 1/21 NEUTRAL RT V0	F.10
1689390004	VT SF 1/21 NEUTRAL GE V0	F.10
1689410001	VT SF 2/21 NEUTRAL WS V0	F.10
1689410002	VT SF 2/21 NEUTRAL BL V0	F.10
1689410003	VT SF 2/21 NEUTRAL RT V0	F.10
1689410004	VT SF 2/21 NEUTRAL GE V0	F.10
1689430001	VT SF 3/21 NEUTRAL WS V0	F.10
1689430002	VT SF 3/21 NEUTRAL BL V0	F.10
1689430003	VT SF 3/21 NEUTRAL RT V0	F.10
1689430004	VT SF 3/21 NEUTRAL GE V0	F.10
1689450001	VT SF 4/21 NEUTRAL WS V0	F.10
1689450002	VT SF 4/21 NEUTRAL BL V0	F.10
1689450003	VT SF 4/21 NEUTRAL RT V0	F.10
1689450004	VT SF 4/21 NEUTRAL GE V0	F.10
1689470001	VT SF 5/21 NEUTRAL WS V0	F.10
1689470002	VT SF 5/21 NEUTRAL BL V0	F.12
1689470003	VT SF 5/21 NEUTRAL RT V0	F.12
1689470004	VT SF 5/21 NEUTRAL GE V0	F.10

1690000000

1693800000	ZQV 2.5N/2	D.12
1693800000	ZQV 2.5N/2	D.22
1696090001	SF 1/21 WHITE (80MARKERS/CARD)	F.6
1696090002	SF 1/21 BLUE (80 MARKERS/CARD)	F.6
1696090003	SF 1/21 RED (80 MARKERS /CARD)	F.6
1696090004	SF 1/21 YELLOW 80 MARKERS/CARD	F.6
1696100001	SF 2/21 WHITE 80 MARKERS/CARD	F.6
1696100002	SF 2/21 BLUE 80 MARKERS/CARD	F.6
1696100003	SF 2/21 RED 80 MARKERS/CARD	F.6
1696100004	SF 2/21 YELLOW 80 MARKERS/CARD	F.6
1696110001	SF 3/21 BLANK WHITE	F.6
1696110002	SF 3/21 BLUE (64 MARKERS/CARD)	F.6
1696110003	SF 3/21 RED 64 MARKERS/CARD	F.8
1696110004	SF 3/21 YELLOW 64 MARKERS/CARD	F.6
1696120001	SF 4/21 WHITE	F.8
1696120002	SF 4/21 BLUE	F.8
1696120003	SF 4/21 RED	F.8
1696120004	SF 4/21 NEUTRAL GE V0	F.8
1696130001	SF 5/21 NEUTRAL WS	F.8
1696130002	SF 5/21 NEUTRAL BL V0	F.8
1696130003	SF 5/21 NEUTRAL RT V0	F.8
1696130004	SF 5/21 NEUTRAL GE V0	F.8
1696140001	SFX 9/24 WHITE 32 MARKERS/CARD	F.4
1696140002	SFX 9/24 BLUE 32 MARKERS/CARD	F.4
1696140003	SFX 9/24 RED 32 (MARKERS/CARD)	F.4
1696140004	SFX 9/24 YELLOW 32MARKERS/CARD	F.4

Part Number	Description	Page
-------------	-------------	------

1699840000	SM 27/12.5 WHITE	F.24
1699860000	SM 27/18 WHITE	F.24
1699880000	SM 27/12.5 K WS BLANK	F.24

1700000000

1707270000	SM 27/18K NEUTRAL WHITE	F.24
------------	-------------------------	------

1710000000

1711320001	SF 1/12 WHITE	F.4
1711320002	SF 1/12 NEUTRAL BLUE	F.6
1711320003	SF 1/12 NEUTRAL RED	F.6
1711320004	SF 1/12 NEUTRAL YELLOW	F.6
1711350001	SF 2/12 BLANK WHITE	F.6
1711350002	SF 2/12 NEUTRAL BLUE	F.6
1711350003	SF 2/12 NEUTRAL RED	F.6
1711350004	SF 2/12 NEUTRAL YELLOW	F.6
1711370001	SF 3/12 BLANK WHITE	F.6
1711370002	SF 3/12 NEUTRAL BLUE	F.6
1711370003	SF 3/12 NEUTRAL RED	F.6
1711370004	SF 3/12 NEUTRAL YELLOW	F.6
1712340000	ADAPTOR PG 11/NPT 3/8	C.3
1712350000	ADAPTOR PG13.5 - NPT 1/2	C.3
1712360000	PG16-NPT 1/2	C.3
1712370000	PG21 - NPT 3/4	C.3
1712380000	ADAPTOR PG36 - NPT 1 1/4	C.3
1712390000	PG29 - NPT 1	C.3
1712460000	HDC-KIT-HE 06.100	C.2
1712510000	HDC-KIT-HE-10.110	C.2
1712520000	HDC-KIT-HE 16.120	C.2
1712530000	HDC-KIT-HE 24.130	C.2
1712540000	HDC-KIT-HE 32.140	C.2
1712550000	HDC-KIT-HE 48.150	C.2
1712560000	HDC-KIT-HA 03.300	C.2
1712570000	HDC-KIT-HA 03.301	C.2
1712580000	HDC-KIT-HA 03.302	C.2
1712590000	HDC-KIT-HA 04.400	C.2
1712600000	HDC-KIT-HA 04.401	C.2
1712610000	HDC-KIT-HA 04.402	C.2
1712630000	HDC-KIT-HA 03.404	C.2
1712650000	HDC-KIT-HA 04.406	C.2
1712660000	HDC-KIT-HE 06.101	C.2
1712670000	HDC-KIT-HE 10.111	C.2
1712680000	HDC-KIT-HE 16.121	C.2
1712690000	HDC-KIT-HE 24.131	C.2
1712700000	HDC-KIT-HE 06.200	C.2
1712710000	HDC-KIT-HE 10.210	C.2
1712720000	HDC-KIT-HE 16.220	C.2
1712730000	HDC-KIT-HE 24.230	C.2
1713660001	SFX 14/23 NEUTRAL WHITE	F.4
1713660002	SFX 14/23 NEUTRAL BLUE	F.4
1713660003	SFX 14/23 NEUTRAL RED	F.4
1713660004	SFX 14/23 NEUTRAL YELLOW	F.4
1713700000	SM 27/12.5 NEUTRAL SILVER	F.24
1713720000	SM 27/12 5K NEUTRAL SI	F.24
1713740000	SM 27/18 NEUTRAL SILVER	F.24
1713760000	SM 27/18 K NEUTRAL SILVER	F.24
1716240000	SAK 4/32,STEEL SPRING	A.6
1716630000	SM-H 27/18 BLACK	F.24
1716640000	SM-H 27/12.5 BLACK HOLDER	F.24
1717900000	ZQV 2.5N/2 RT (RED)	D.12
1717900000	ZQV 2.5N/2 RT (RED)	D.12
1717990000	ZQV 2.5N/2 BL	D.12
1717990000	ZQV 2.5N/2 BL	D.12
1718080000	ZQV 2.5N/2 SW (BLACK)	D.12
1718080000	ZQV 2.5N/2 SW (BLACK)	D.22
1718411044	TM-I 12 NEUTRAL WHITE	F.20
1718411686	TM-I 12 NEUTRAL RT	F.20
1718411687	TM-I 12 NEUTRAL YELLOW	F.20
1718411688	TM-I 12 NEUTRAL GN	F.20
1718411693	TM-I 12 NEUTRAL BL	F.20
1718431044	TM-I 18 NEUTRAL WHITE	F.20
1718431686	TM-I 18 NEUTRAL RT	F.20
1718431687	TM-I 18 NEUTRAL YELLOW	F.20
1718431688	TM-I 18 NEUTRAL GN	F.20
1718431693	TM-I 18 NEUTRAL BL	F.20
1718470001	VT SF 1/12 NEUTRAL WS V0	F.8
1718470002	VT SF 1/12 NEUTRAL BL V0	F.8
1718470003	VT SF 1/12 NEUTRAL RT V0	F.8
1718470004	VT SF 1/12 NEUTRAL GE V0	F.8
1718480001	VT SF 2/12 NEUTRAL WS V0	F.8
1718480002	VT SF 2/12 NEUTRAL BL V0	F.8
1718480003	VT SF 2/12 NEUTRAL RT V0	F.8
1718480004	VT SF 2/12 NEUTRAL GE V0	F.8
1718490001	VT SF 3/12 NEUTRAL WS V0	F.8
1718490002	VT SF 3/12 NEUTRAL BL V0	F.8
1718490003	VT SF 3/12 NEUTRAL RT V0	F.8
1718490004	VT SF 3/12 NEUTRAL GE V0	F.8
1719760000	TM 0/12 HF/HB LABELS	F.16
1719770000	TM 0/18 HF/HB LABELS	F.16
1719780000	TM 1/12 HF/HB	F.16
1719790000	TM 1/18 HF/HB	F.16
1719800000	TM 2/12 HF LABELS	F.16
1719810000	TM 2/18 HF/HB LABEL	F.16
1719820000	TM 3/12 HF/HB	F.16
1719830000	TM 3/18 HF/HB	F.16
1719840000	TM 4/12 HF/HB	F.16
1719850000	TM 4/18 HF/HB	F.16
1719860000	TM 5/12 HF/HB	F.16
1719870000	TM 5/18 HF/HB	F.16
1719880000	TM 6/12 HF/HB	F.16
1719890000	TM 6/18 HF/HB	F.16

Part Number	Description	Page
-------------	-------------	------

1720000000

1720600000	SCHS2 ADHESIVE MARKING STRIP	F.22
1720610000	ESG 8/17 F/MTG BAR SCH5 NEUTR	F.22
1720620000	DEK 5/7.5 MC BLANK WHITE	F.2
1724000000	HDC-KIT-HSB 06.500	C.2
1724050001	SF 0/12 NEUTRAL WS	F.4
1724050002	SF 0/12 NEUTRAL BL V0	F.4
1724050003	SF 0/12 NEUTRAL RT V0	F.4
1724050004	SF 0/12 NEUTRAL GE V0	F.4
1724760000	ESG 9/17 WHITE BLANK NO ADHES.	F.20
1727750001	SFX 10/23 NEUTRAL WS	F.4
1727750002	SFX 10/23 NEUTRAL BL	F.4
1727750003	SFX 10/23 RED	F.4
1727750004	SFX 10/23 NEUTRAL GE	F.4

1730000000

1730560001	VT SF 6/21 NEUTRAL WS V0	F.12
1730560002	VT SF 6/21 NEUTRAL BL V0	F.12
1730560003	VT SF 6/21 NEUTRAL RT V0	F.12
1730560004	VT SF 6/21 NEUTRAL GE V0	F.12
1730570001	VT SF 4,5/21 NEUTRAL WS V0	F.10
1730570002	VT SF 4,5/21 NEUTRAL BL V0	F.10
1730570003	VT SF 4,5/21 NEUTRAL RT V0	F.10
1730570004	VT SF 4,5/21 NEUTRAL GE V0	F.10
1730580001	VT SF 00/21 NEUTRAL WS V0	F.10
1730580002	VT SF 00/21 NEUTRAL BL V0	F.10
1730580003	VT SF 00/21 NEUTRAL RT V0	F.10
1730580004	VT SF 00/21 NEUTRAL GE V0	F.10
1730590001	VT SF 0/21 NEUTRAL WS V0	F.10
1730590002	VT SF 0/21 NEUTRAL BL V0	F.10
1730590003	VT SF 0/21 NEUTRAL RT V0	F.10
1730590004	VT SF 0/21 NEUTRAL GE V0	F.10
1730900000	ZSI 2.5/5X25	A.12
1736181044	ESG 7/20	F.20
1736181044	ESG 7/20	F.22
1736181687	ESG 7/20 SIRIUS YELLOW	F.22
1736181696	ESG 7/20 SIRIUS TUEKIS	F.22
1736190000	ESG 8/10	F.22
1739620000	ZDU 35	A.10
1739650000	ZPE 35	A.10

1740000000

1740830001	SF 00/12 NEUTRAL WS	F.4
1740830002	SF 00/12 NEUTRAL BL V0	F.4
1740830003	SF 00/12 NEUTRAL RT V0	F.4
1740830004	SF 00/12 NEUTRAL GE V0	F.4
1740840001	SF 00/21 NEUTRAL WS	F.6
1740840002	SF 00/21 NEUTRAL BL V0	F.6
1740840003	SF 00/21 NEUTRAL RT V0	F.6
1740840004	SF 00/21 NEUTRAL GE V0	F.6
1740850001	SF 0/21 NEUTRAL WS	F.6
1740850002	SF 0/21 NEUTRAL BL V0	F.6
1740850003	SF 0/21 NEUTRAL RT V0	F.6
1740850004	SF 0/21 NEUTRAL GE V0	F.6
1740860001	SF 4.5/21 NEUTRAL WHITE	F.8
1740860002	SF 4.5/21 NEUTRAL BL V0	F.8
1740860003	SF 4.5/21 NEUTRAL RT V0	F.8
1740860004	SF 4.5/21 NEUTRAL GE V0	F.8
1740870001	SF 6/21 NEUTRAL WS	F.8
1740870002	SF 6/21 NEUTRAL BL V0	F.8
1740870003	SF 6/21 NEUTRAL RT V0	F.8
1740870004	SF 6/21 NEUTRAL GE V0	F.8
1743490001	SF 4/12 NEUTRAL WS	F.6
1743490002	SF 4/12 NEUTRAL BL V0	F.6
1743490003	SF 4/12 NEUTRAL RT V0	F.6
1743490004	SF 4/12 NEUTRAL YELLOW	F.10
1743490004	SF 4/12 NEUTRAL YELLOW	F.6
1743500001	SF 5/12 NEUTRAL WS	F.6
1743500002	SF 5/12 NEUTRAL BL V0	F.6
1743500003	SF 5/12 NEUTRAL RT V0	F.6
1743500004	SF 5/12 NEUTRAL YELLOW	F.6
1745230000	ZDU 16	A.10
1745250000	ZPE 16	A.10
1745400000	ZDTR 2.5	A.12
1746030001	VT SF 4/12 NEUTRAL WS V0	F.10
1746030002	VT SF 4/12 NEUTRAL BL V0	F.10
1746030003	VT SF 4/12 NEUTRAL RT V0	F.10
1746040001	VT SF 5/12 NEUTRAL WS V0	F.10

Part Number	Description	Page
1753490000	WKM 8/20	F.18
1753500000	ESG 9/17 K NEUTRAL/GE	F.22
1755270000	DEK 5/3.5 MC NEUTRAL WHITE	F.2
1755340000	ESG 8/17 SYS PRO M	F.22
1758320001	SFC 2/12 NEUTRAL WHITE MC	F.14
1758320002	SFC 2/12 NEUTRAL BLUE MC	F.14
1758320003	SFC 2/12 NEUTRAL RED MC	F.14
1758320004	SFC 2/12 NEUTRAL YELLOW MC	F.14

1760000000

1762440000	PCS ADAPTOR FOR STI-S PEN	F.29
1763270000	WPM 10-33	F.18
1763280000	WPM 20-33	F.18
1763390000	WPM 20-66	F.18
1763870000	HDC-KIT HE 10.310 1/2 NPT	C.2
1763880000	HDC-KIT HE 16.320 3/4 NPT	C.2
1763890000	HDC-KIT HE 24.330 3/4 NPT	C.2
1763900000	HDC-KIT HE.32.340 1 NPT	C.2
1763910000	HDC-KIT HE 10.311 1/2 NPT	C.2
1763920000	HDC-KIT HE 16.321 3/4 NPT	C.2
1763930000	HDC-KIT HE 24.331 3/4 NPT	C.2
1764050000	WPF 2-17.5 WS/GE NEUTRAL	F.20
1764060000	WPT 02-12	F.16
1764070000	WPT 02-15	F.16
1764140000	WPT 02-18	F.16
1764150000	WPT 02-20 WIRE MARKERS	F.16
1764190000	WPT 1-12	F.16
1764200000	WPT 1-15 WIRE MARKERS	F.16
1764210000	WPT 1-18	F.16
1764220000	WPT 1-20	F.16
1764230000	WPT 2-12	F.16
1764240000	WPT 2-15	F.16
1764250000	WPT 2-18	F.16
1764260000	WPT 2-20	F.16
1764270000	WPT 3-12	F.16
1764280000	WPT 3-15	F.16
1764290000	WPT 3-18	F.16
1764300000	WPT 3-20 WIRE MARKERS	F.16
1766160000	ESG 9/20 MC NEUTRAL GE	F.22
1767690000	ZDU 10/3AN	A.10
1768090000	WS 14/5 MC NEUTRAL	F.2
1768320000	ZDU 16/3AN	A.10
1768540000	PCS PLOTTER PEN 0.25 WHITE	F.29
1768550000	PCS PLOTTER PEN 0.35 YELLOW	F.29
1768560000	PCS PLOTTER PEN 0.50 BROWN	F.29
1768570000	PCS PLOTTER PEN 0.18 RED	F.29

1770000000

1770080000	SF-TOOL COLLECTION (SLIMFIX)	F.12
1770370000	ZDU4-2/2AN BEIGE WEMID	A.10
1770380000	ZPE 4-2/2AN	A.10
1771370000	ZPE 6-2/2AN	A.10
1771380000	ZDU 6-2/2AN	A.10
1771930000	SM 27/8 K SILVER NEUTRAL	F.24
1772060000	ZDU 2.5-2	A.10
1772090000	ZPE 2.5-2	A.10
1773220000	SM 27/27 NEUTRAL WHITE	F.24
1773230000	SM 27/27 NEUTRAL SILVER	F.24
1775480000	ZDU 1.5, WM, BG	A.10
1775510000	ZPE 1.5, WM, YL/GN	A.10
1775530000	ZDU 1.5/3AN WM BG	A.10
1775910000	ESG 9/10 MC NEUTRAL WS	F.22
1778270000	WS 12/3.5 MC NEUTRAL	F.2
1779080001	SFC 1/21 NEUTRAL WHITE	F.14
1779080002	SFC 1/21 NEUTRAL BLUE	F.14
1779080003	SFC 1/21 NEUTRAL RED	F.14
1779080004	SFC 1/21 NEUTRAL YELLOW	F.14
1779100000	TSTW 5/MS ZN	A.17

1780000000

1782710000	SM-H 27/27 HOLDER BLACK	F.24
1782960000	SF-TOOL 2-3 (SLIMFIX)	F.12
1782970000	SF-TOOL 1 (SLIMFIX)	F.12
1782980000	SF-TOOL 4-5 (SLIMFIX)	F.12
1782990000	SM 27/27K NEUTRAL SILVER	F.24
1783000000	SM 27/27K NEUTRAL	F.24
1784270000	ZQV 2.5N 1/4-2 SW BLACK	D.8
1784270000	ZQV 2.5N 1/4-2 SW BLACK	D.12
1784280000	ZQV 2.5N 1/42- RT RED	D.8
1784280000	ZQV 2.5N 1/42- RT RED	D.12
1784290000	ZQV 2.5N 1/4-2 BLUE	D.8
1784290000	ZQV 2.5N 1/4-2 BLUE	D.12
1784560000	M-PRINT 1.6 CD MULTILINGUAL	F.30
1789590000	DEK 5/6 MC V0 NEUTRAL	F.2

1790000000

1790150000	CC-RAIL 1000 BLACK CARRIER	F.26
1790160000	CC-RAIL 1000 TRANSPARENT COVER	F.26
1790410000	CC-H 15/27 BLACK HOLDER	F.26
1790420000	CC-H 15/49 BLACK HOLDER	F.26
1790430000	CC-H 15/17 BLACK HOLDER	F.26
1791010000	ZDK 2.5-2 PE	A.10
1792000000	WS 10/5 MC MIDD. NEUTR.	F.2
1792540000	IDU 1.5N, WEMID BEIGE	A.14
1792560000	IPE 1.5N, WEMID YELLOW/GREEN	A.14
1792570000	IDU 1.5N/3AN, WEMID BEIGE	A.14
1792590000	IPE 1.5N/3AN, WM YELLOW/GREEN	A.14
1792600000	IDU 1.5N/4AN, WEMID BEIGE	A.14
1792620000	IPE 1.5N/4AN	A.14

Part Number	Description	Page
1792630000	ITR 1.5N	A.14
1792640000	ITR 1.5N SI, WEMID BEIGE,SIHA3	A.14
1792650000	IDK 1.5N, WEMID BEIGE	A.14
1792690000	IDK 1.5N PE,WEMID GREEN/YELLOW	A.14
1792700000	IDU 1.5N/ZF TENSION, WM BEIGE	A.14
1792720000	IPE 1.5N/ZF	A.14
1792730000	IDU 1.5N/ZB SCREW, WM BEIGE	A.14
1792750000	IPE 1.5N/ZB	A.14
1793950000	ZQV 4N/2 RED	D.6
1793950000	ZQV 4N/2 RED	D.20
1793960000	ZQV 4N/2 BLUE	D.6
1793960000	ZQV 4N/2 BLUE	D.20
1793970000	ZQV 4N/2 BLACK	D.6
1793980000	ZQV 4N/3 RED	D.6
1793980000	ZQV 4N/3 RED	D.20
1793990000	ZQV 4N/3 BLUE	D.6
1793990000	ZQV 4N/3 BLUE	D.20
1794000000	ZQV 4N/3 BLACK	D.6
1794010000	ZQV 4N/4 RED	D.20
1794020000	ZQV 4N/4 BLUE	D.20
1794040000	ZQV 4N/10 RED	D.20
1794050000	ZQV 4N/10 BLUE	D.20
1794070000	ZQV 4N/41 RED	D.6
1794070000	ZQV 4N/41 RED	D.20
1794080000	ZQV 4N/41 BLUE	D.6
1794080000	ZQV 4N/41 BLUE	D.20
1794090000	ZQV 4N/41 BLACK	D.6

1793950000	ZQV 4N/2 RED	D.6
1793950000	ZQV 4N/2 RED	D.20
1793960000	ZQV 4N/2 BLUE	D.6
1793960000	ZQV 4N/2 BLUE	D.20
1793970000	ZQV 4N/2 BLACK	D.6
1793980000	ZQV 4N/3 RED	D.6
1793980000	ZQV 4N/3 RED	D.20
1793990000	ZQV 4N/3 BLUE	D.6
1793990000	ZQV 4N/3 BLUE	D.20
1794000000	ZQV 4N/3 BLACK	D.6
1794010000	ZQV 4N/4 RED	D.20
1794020000	ZQV 4N/4 BLUE	D.20
1794040000	ZQV 4N/10 RED	D.20
1794050000	ZQV 4N/10 BLUE	D.20
1794070000	ZQV 4N/41 RED	D.6
1794070000	ZQV 4N/41 RED	D.20
1794080000	ZQV 4N/41 BLUE	D.6
1794080000	ZQV 4N/41 BLUE	D.20
1794090000	ZQV 4N/41 BLACK	D.6

1800000000

1802360000	HDC-KIT HE 48. 150M	C.2
1802370000	HDC-KIT-HE 32.140M	C.2
1802380000	HDC-KIT HE 24 130M	C.2
1802390000	HDC-KIT-HE 16.121M	C.2
1802400000	HDC-KIT-HE 16.120 M	C.2
1802410000	HDC-KIT-HE 10.111M	C.2
1802420000	HDC-KIT-HE 10.110M	C.2
1802430000	HDC-KIT-HA 04.401 M	C.2
1802440000	HDC-KIT-HA 04.400M	C.2
1802450000	HDC-KIT-HA 03.302 M	C.2
1802460000	HDC-KIT-HA 03.301 M	C.2
1802470000	HDC-KIT HA 03.300M	C.2
1802480000	HDC-KIT-HE 24.131 M	C.2
1802700000	HDC-KIT HA 04.402 M	C.2
1802730000	HDC-KIT HE.06 100M	C.2
1802740000	HDC-KIT HE 06.101 M	C.2
1802780000	WDU 240, WEMID BEIGE	A.2
1805720000	SFC 1/30 NEUTRAL BLUE	F.14
1805730000	SFC 1/30 NEUTRAL YELLOW	F.14
1805740000	SFC 1/30 NEUTRAL RED	F.14
1805760000	SFC 1/30 NEUTRAL WHITE	F.14
1805770000	SFC 2/21 NEUTRAL WHITE	F.14
1805770000	SFC 2/21 NEUTRAL BLUE	F.14
1805780000	SFC 2/21 NEUTRAL YELLOW	F.14
1805790000	SFC 2/21 NEUTRAL RED	F.14
1805810000	SFC 2/21 NEUTRAL WHITE	F.14
1805820000	SFC 2/30 NEUTRAL BLUE	F.14
1805830000	SFC 2/30 NEUTRAL YELLOW	F.14
1805850000	SFC 2/30 NEUTRAL RED	F.14
1805870000	SFC 2/30 NEUTRAL WHITE	F.14
1806140000	IPE 1.5N/3AN/ZF	A.14
1806150000	IDU 1.5N/3AN/ZF	A.14
1806160000	IPE 1.5N/3AN/ZB	A.14
1806170000	IDU 1.5N/3AN/ZB	A.14

1810000000

1812510000	ITR 1.5N/3AN	A.14
1812630000	SM 27/8 K WHITE NEUTRAL	F.24
1812900000	IDU 2.5N	A.14
1812920000	IPE 2.5N	A.14
1812930000	IDU 2.5N/3AN	A.14
1812950000	IPE 2.5N/3AN	A.14
1812960000	IDU 2.5N/4N	A.14
1812980000	IPE 2.5N/4AN	A.14
1812990000	ITR 2.5N, WM, BG	A.14
1813010000	ITR 2.5N SI 5X20	A.14
1813090000	MAGAZINE PRINTJET 115V(FEEDER)	F.28
1813130000	SFC 0/12 NEUTRAL WHITE	F.14
1813150000	SFC 0/12 NEUTRAL RED	F.14
1813160000	SFC 0/12 NEUTRAL YELLOW	F.14
1813170000	SFC 0/12 NEUTRAL BLUE	F.14
1813190000	SFC 0/21 NEUTRAL WHITE	F.14
1813200000	SFC 0/21 NEUTRAL RED	F.14
1813210000	SFC 0/21 NEUTRAL YELLOW	F.14
1813220000	SFC 0/21 NEUTRAL BLUE	F.14
1813240000	SFC 0/30 NEUTRAL WHITE	F.14
1813250000	SFC 0/30 NEUTRAL RED	F.14
1813260000	SFC 0/30 NEUTRAL YELLOW	F.14
1813270000	SFC 0/30 NEUTRAL BLUE	F.14
1814690000	ZSI 6-2/FC, WM BLACK	A.12
1818400000	WS 10/6MC MIDDLE NEUTRAL WHITE	F.2

1821000000

1820390000	ITR 1.5N/3AN SI	A.14
1820930000	ZSI 6-2 2X2.5/G20	A.12
1821260000	IDU 2.5N/ZF	A.14
1821280000	IPE 2.5N/ZF	A.14
1821290000	IDU 2.5N/ZB	A.14
1821310000	IPE 2.5N/ZB	A.14
1828450000	WS 10/6MC OFFSET NEUTRAL WHITE	D.20
1828450000	WS 10/6MC OFFSET NEUTRAL WHITE	F.2

Part Number	Description	Page
1831130000	ZTR 2.5/O.TNHE	A.12
1831280000	ZTR 2.5	A.12
1836880000	PLUG SERIES BLOCKER	D.8
1836880000	PLUG SERIES BLOCKER	D.12

1840000000

1841780000	SL-SMT3.5/17/90G 3.2SN SW BOX	F.16
1841810000	SL-SMT3.5/20/90G 3.2 SN BL BOX	F.16
1848300000	IDU 2.5N/3AN/ZB	A.14
1848320000	IPE 2.5N/3AN/ZB	A.14

1850000000

1852360000	SFX 10/23 NEUTRAL GE V2	F.4
1852370000	SFX 10/23 NEUTRAL RT V2	F.4
1852390000	SFX 10/23 NEUTRAL WS V2	F.4
1852400000	SFX 10/23 NEUTRAL BL V2	F.4
1852410000	SFX 14/23 NEUTRAL GE V2	F.4
1852420000	SFX 14/23 NEUTRAL RT V2	F.4
1852440000	SFX 14/23 NEUTRAL WS V2	F.4
1852450000	SFX 14/23 NEUTRAL BL V2	F.4
1852460000	SFX 9/24 NEUTRAL GE V2	F.4
1852470000	SFX 9/24 NEUTRAL RT V2	F.4
1852490000	SFX 9/24 NEUTRAL WS V2	F.4
1852500000	SFX 9/24 NEUTRAL BL V2	F.4
1854090000	WS 10/15 MC NEUTR.	F.2
1854490000	DEK 5/5 PLUS MC NEUTRAL	F.2
1855610000	WTR 2.5/ZQV BEIGE	A.4
1855620000	WTR 2.5/ZQV STB 2.3 BEIGE	A.4
1856700000	ESG 10/17 MC NEUTRAL	F.22
1856720000	ESG 9/20 MC UNIVERSAL	F.22
1856740000	DEK 5/8 MC WHITE BLANK	D.18
1856740000	DEK 5/8 MC WHITE BLANK	F.2
1857440000	ESG 9/11K MC NEUTRAL	F.22
1858920000	INK CARTRIDGE FOR PRINTJET II	F.28
1858950000	PRINTJET II CLEANING UNIT	F.28
1858980000	PRINTJET II 115VAC	F.28

1860000000

1860120000	SFX 11/60 MC NEUTRAL WHITE	F.4
1860130000	SFX 11/60 MC NEUTRAL GR	F.4
1860150000	SFX 11/60 MC NEUTRAL YELLOW	F.4

1870000000

1876370000	TM-I 30 MC NEUTRAL YELLOW	F.20
1876380000	TM-I 30 MC NEUTRAL RT	F.20
1876390000	TM-I 30 MC NEUTRAL WHITE	F.20
1876400000	TM-I 30 MC NEUTRAL BL	F.20
1876570000	CC 15/17 MC NEUTRAL WHITE	F.24
1876580000	CC 15/17 K MC NEUTRAL SILVER	F.26
1876590000	CC 15/17 K MC NEUTRAL WHITE	F.26
1876610000	CC 15/17 MC NEUTRAL SILVER	F.24
1876640000	CC 15/27 K MC NEUTRAL WHITE	F.26
1876760000	CC 15/27 MC NEUTRAL SILVER	F.24
1876770000	CC 15/27 MC NEUTRAL WHITE	F.24
1876780000	CC 15/27 K MC NEUTRAL SILVER	F.26
1877220000	CC 15/49 K MC NEUTRAL WHITE	F.26
1877240000	CC 15/49 MC NEUTRAL SILVER	F.24
1877260000	CC 15/49 MC NEUTRAL WHITE	F.24
1877270000	CC 15/49 K MC NEUTRAL SILVER	F.26
1877310000	CC 15/60 K MC NEUTRAL WHITE	F.26
1877340000	CC 15/60 MC NEUTRAL SILVER	F.26
1877350000	CC 15/60 MC NEUTRAL WHITE	F.26
1877360000	CC 15/60 K MC NEUTRAL SILVER	F.26
1877570000	SM 22/22 K MC NEUTR. WS	F.24
1877590000	SM 22/22 K MC NEUTR. SI	F.24
1878910000	CC-H 15/60 BLACK HOLDER	F.26

1880000000

1880100000	ESG 6/15 K MC NEUTR. WS	F.22
1880110000	ESG 6/17 K MC NEUTR. GE	F.22
1880120000	ESG 6/17 K MC NEUTR. WS	F.22
1880130000	ESG 6/15 K MC NEUTR. GE	F.22
1880390000	WSI 4/2 LD 140-250V AC/DC	A.4
1880410000	WSI 4/2 LD 10-36V AC/DC	A.4
1880420000	WSI 4/2 LD 60-150V AC/DC	A.4
1880430000	WSI 4/2	A.4
1880440000	WSI 4/2 LD 30-70V AC/DC	A.4
1880810000	ETO CC 15/27 TRANSPARENT LABEL	F.26
1880830000	ETO CC 15/49 TRANSPARENT LABEL	F.26
1880840000	ETO CC 15/60 TRANSPARENT LABEL	F.26
1880850000	ETO CC 15/17 TRANSPARENT LABEL	F.26
1881280000	ESG 6/15 MC RIDERSERIES	F.22
1888280000	STR CC 15/60 TRANSPARENT COVER	F.26
1888290000	STR CC 15/27 TRANSPARENT COVER	F.26
1888300000	STR CC 15/49 TRANSPARENT COVER	F.26
1888310000	STR CC 15/17 TRANSPARENT COVER	F.26
1889550000	WPT 3-30	F.16
1889560000	WPT 1-30	F.16
1889570000	WPT 2-30	F.16
1889580000	WPT 02-30	F.16

Part Number	Description	Page
-------------	-------------	------

1890470000	ESG 8/17 L MC NEUTRAL	F.22
1896110000	PDU 2.5/4	A.16
1896120000	PDU 2.5/4/3AN	A.16
1896130000	PDU 2.5/4/4AN	A.16
1896160000	PPE 2.5/4/4AN	A.16
1896170000	PPE 2.5/4	A.16
1896200000	PPE 2.5/4/3AN	A.16

1900000000

1905490000	M-PRINT PRO SOFTWARE CD	F.30
1905950000	WS 10/8 MC NEUTRAL	F.2
1905970000	WS 10/12 MC NEUTRAL	F.2
1906000000	WS 12/8 MC NEUTRAL	F.2

1910000000

1919870000	ESO 8/20P WS	F.20
1919880000	ESO 8/20P GE	F.20
1919890000	ESO 8/20 WS	F.20
1919900000	ESO 8/20 GE	F.20
1919940000	ESG 5/10 MC NEUTRAL WS	F.22

1920000000

1920640000	PLOTTER PEN 0.25 P-INK	F.29
1920650000	PLOTTER PEN 0.35 P-INK	F.29
1924310000	MCP AP SF 4-6	F.29
1924330000	P-CLEANER	F.29
1924340000	P-INK	F.29
1924350000	MCP PLOTTER COVER	F.29
1924360000	MCP AP	F.29
1924370000	MCP AP LABELS	F.29
1925000000	MCP PLUS	F.29

1930000000

1934330000	CC 30/60 K MC NEUTRAL SI	F.26
1934390000	CC 30/60 K MC NEUTRAL WS	F.26
1934400000	CC 30/60 MC NEUTRAL SI	F.26
1934420000	CC 30/60 MC NEUTRAL WS	F.26
1934430000	CC-H 30/60	F.26
1934440000	ETO CC 30/60 TRANSPARENT	F.26
1934450000	STR CC 30/60 TRANSPARENT	F.26

1950000000

1950820000	SF-TOOL 00-6	F.12
------------	--------------	------

3000000000

330075	RS70-12V-C1D2-2C	D.6
37SM400F	RS30 24VDC SDT 250V 4A FUSE	D.6

7900000000

7901540000	MC5R 12V/24VDC IN 14MA,OUT 4A	D.6
7901550000	MC5R 24V/48VDC IN 7MA,OUT 4A	D.6
7901560000	MC5R 12/24VAC/DC IN15MA,OUT 4A	D.8
7901570000	MC5R 24/48VAC/DC IN 7MA,OUT 4A	D.8
7901580000	MC5RL 5-15VIN/AUX 24VDC,OUT 4A	D.6
7901590000	MC5RL 5-15L LOG/24 VAC/DC	D.6
7901600000	MC5R 115VAC IN 3.5MA/OUT 4A	D.8
7901620000	MC5R 24VDC,7MA/1 FORM C, 6A	D.6
7901690001	MC5O 24VDC/5-34VDC 10A RES	D.10
7904180000	ZDU 4/3AN	A.10
7907410000	ZDU 6 / 3AN	A.10

7910000000

7910210000	WTR 4 STB, BEIGE WEMID	A.4
7914760001	DIN RAIL MOUNTABLE UTILITY BOX	D.4
7918960324	CP-SNT 380-480V 3PH/24VDC,40A	D.26

7920000000

7920210324	CP-SNT 380-480V 3PH/24VDC,25A	D.26
7920400000	WAVEPAK LOOP SPLITTER C1D2,Z2	D.19
7920900000	ZTR 2.5/4AN	A.12
7921570000	SIHA 3/G20/LD 10-36V	A.12
7921580000	SIHA 3/G20/LD 35-70V	A.12
7921590000	SIHA 3/G20/LD 60-150V	A.12
7921600000	SIHA 3/G20/LD 140-250V	A.12
7923450024	MC6RF 24VUC IN/SPST NO 5A FUSE	D.6
7923450120	MC6RF 120VACIN/SPST NO 5A FUSE	D.8
7924270030	TST M6 STRAIGHT 30MM HIGH	A.17
7924270040	TST M6 STRAIGHT 40MM HIGH	A.17
7924270050	TST M6 STRAIGHT 50MM HIGH	A.17
7924270070	TST M6 STRAIGHT 70MM HIGH	A.17
7924270090	TST M6 STRAIGHT 90MM HIGH	A.17
7924273549	TST M6 ANGLED 49MM HIGH	A.17
7924273558	TST M6 ANGLED 58MM HIGH	A.17
7924273568	TST M6 ANGLED 68MM HIGH	A.17
7924273578	TST M6 ANGLED 78MM HIGH	A.17
7924273588	TST M6 ANGLED 88MM HIGH	A.17
7924273598	TST M6 ANGLED 98MM HIGH	A.17
7924740324	CP-SNT 360-500V 3PH/24VDC,12.5	D.26

Part Number	Description	Page
-------------	-------------	------

7940000000

7940000036	GFI OUTLET, 230, LLP TERMINALS	D.4
7940000037	GFI OUTLET, 15A,LPZF TERMINALS	D.4
7940000063	MC250 24VDC/5-34VDC 10A RES	D.10
7940000440	HDC-KIT-HE06.COUPLER	C.3
7940000441	HDC-KIT-HE10.COUPLER	C.3
7940000442	HDC-KIT-HE16.COUPLER	C.3
7940000443	HDC-KIT-HE24.COUPLER	C.3
7940000444	HDC-KIT-HE32.COUPLER	C.3
7940000445	HDC-KIT-HSB6.COUPLER	C.3
7940000446	MRZ KIT-HE06.Z01 TOP	C.3
7940000447	HDC-KIT-HE06.Z00 SIDE	C.3
7940000448	HDC-KIT-HE10.Z11 TOP	C.3
7940000449	HDC-KIT-HE10.Z10 SIDE	C.3
7940000450	HDC-KIT-HE16.Z21 TOP	C.3
7940000451	HDC-KIT-HE16.Z20 SIDE	C.3
7940000452	HDC-KIT-HE24.Z31 TOP	C.3
7940000453	HDC-KIT-HE24.Z30 SIDE	C.3
7940000454	HDC-KIT-HE32.Z40 SIDE	C.3
7940000602	UNIVERSAL I/O MODULE 1 FUSE	D.3
7940000604	UNIVERSAL I/O MODULE 2 FUSES	D.3
7940000628	UNI.QB 2M CABLE 18 CONDUCTOR	D.3
7940004779	MRS 12VDC C1D2 SECURED LEVER	D.6
7940004780	MRZ 12VDC C1D2 SECURED LEVER	D.6
7940004781	MRS 24VDC C1D2 SECURED LEVER	D.6
7940004782	MRZ 24VDC C1D2 SECURED LEVER	D.6
7940004783	MRS 120VAC C1D2 SECURED LEVER	D.8
7940004784	MRZ 120VAC C1D2 SECURED LEVER	D.8
7940005218	RS-D 40A DIODE W/FAN&TEMP.MONI.	D.29
7940005219	RS-D 2X20A DIO W/FAN&TEMP.MONI.	D.29
7940005471	DECIPAK 4-20MA/4-20MA/120V 4W	D.19
7940005473	DECIPAK 4-20MA/4-20MA/24V 4W	D.19
7940005476	DECIPAK 4-20MA/0-20MA/24V 4W	D.19
7940005478	DECIPAK 4-20MA/0-10V/240V 4W	D.19
7940005482	DECIPAK 4-20MA/0-5V/24V 4W	D.19
7940005485	DECIPAK 0-20MA/4-20MA/24V 4W	D.19
7940005488	DECIPAK 0-20MA/0-20MA/24V 4W	D.19
7940005499	DECIPAK 0-10V/4-20MA/24V 4W	D.21
7940005508	DECIPAK 0-10V/0-5V/24V 4W	D.21
7940005521	DECIPAK 4-20/4-20/LOOP POWERED	D.19
7940005522	DECIPAK 4-20MA/4-20MA/24V 2W	D.19
7940005523	DECIPAK 0-1MA/4-20MA/24V 2W	D.19
7940005524	DECIPAK 0-20MA/4-20MA/24V 2W	D.19
7940005528	DECIPAK 0-10V/4-20MA/24V 2W	D.21
7940005529	DECIPAK 0-10MV/4-20MA/24V 2W	D.21
7940005531	DECIPAK 0-100MV/4-20MA/24V 2W	D.21
7940007063	RCM KIT 24VDC 4CO LED GREEN	D.6
7940023881	MRZ 120VAC RC C1D2	D.8
7940023882	MRS 120VAC RC C1D2	D.8

8000000000

8003881001	RS-SD 37S MALE LP2N	D.3
8003891001	RS-SD 37B FEMALE LP2N	D.3
8003901001	RS-SD 9S MALE LP2N	D.3
8003911001	RS-SD 9B FEMALE LP2N	D.3
8005161001	RS-SD 50S MALE LP2N	D.3
8005171001	RS-SD 50B FEMALE LP2N	D.3
8005181001	RS-SD 25S MALE LP2N	D.3
8005191001	RS-SD 25B FEMALE LP2N	D.3
8005201001	RS-SD 15S MALE LP2N	D.3
8005211001	RS-SD 15B FEMALE LP2N	D.3
8012850000	RS-F10 LPK 3/12	D.3
8012860000	RS-F14 LPK 3/1	D.3
8012910000	RS-F20 LPK 3/24	D.3
8012930000	RS-F34 LPK 3/36	D.3
8012940000	RS-F40 LPK 3/42	D.3
8019590000	DKO 24V DC/O	D.10
8019640000	DKSC 0-10V IN/2 SET POINT OUT	D.21
8028300000	DKO 35 OPTO COUPLER 24 VDC	D.10

8100000000

8155580000	RS-F40	D.3
8155590000	RS-F34 LPK 2H/36	D.3
8155600000	RS-F20 LPK 2H/22	D.3
8155610000	RS-F10 LPK 2H/12	D.3

8200000000

8228640000	DK5O 24VDC 50KHZ/5V TTL OUT	D.10
8228650000	DKO DK5 5VTTL/5-48VDC,100MA	D.12
8237730000	WOS1 15-60VDC/0.5ADC	D.12
8242040000	DK U-F DK5 0-10V E315A	D.21
8258980000	RS-F14 LPK 2H/16	D.3
8259950000	WOS2 115VUC/2AAC	D.12
8260280000	MC2 SC 0-10VDC SET POINT	D.21
8275390000	WOS1 3.5-15VDC/100MADC	D.10
8275440000	WOS2 15-60VUC/24-250VAC,3.0A	D.12
8283810001	DK F-U DK5 0-16KHZ 24V	D.25
8296250000	WOS2 115VUC/3ADC	D.12

8300000000

8311870001	DK F-1 DK5 0-16KHZ	D.25
8324610000	MC2 O 24VDC/5V TTL OUT 50KHZ	D.10
8365940000	MC2 OPTO 24VAC/DC/5-48VDC @20MA	D.10
8389030000	AP FOR MCZ PRODUCTS	D.6
8389030000	AP FOR MCZ PRODUCTS	D.12
8389030000	AP FOR MCZ PRODUCTS	D.10
8389940000	MCZ O 5VTTL IN/5-48VDC,100MA	D.12

Part Number	Description	Page
-------------	-------------	------

8400000000

8411190000	MCZ CCC 0-20MA/0-20MA LOOP PWR	D.19
8425720000	MCZ PT100/3 CLP 0-100C	D.21
8432090000	WTS4 PT100/3 DIP SWITCH/0-10V	D.23
8432130000	WTZ4 PT100/3 V 0-10V	D.23
8432150000	WTS4 PT100/3 C 0/4-20MA	D.23
8432160000	WTZ4 PT 100/3 C 0/4-20MA	D.23
8432180000	WTS4 PT 100/2 V 0C/0-10V	D.23
8432190000	WTZ4 PT 100/2 V 0C/0-10V	D.23
8432210000	WTS4 PT100/2 C 0/4-20MA	D.23
8432220000	WTZ4 PT100/2 C 0/4-20MA	D.23
8432240000	WTS4 PT100/4 V 0-10V	D.23
8432250000	WTS4 PT100/4 V 0C/0-10V	D.23
8432270000	WTS4 PT100/4 C 0/4-20MA	D.23
8432280000	WTZ4 PT100/4 C 0/4-20MA	D.23
8432300000	WTS4 THERMO	D.23
8432310000	WTZ4 THERMO	D.23
8444950000	WAS 5 CCC LP 0-20/0-20MA	D.19
8444950000c1D2	WAS 5 CCC LP 0-20/0-20MA C1D2	D.19
8444960000	WAZ 5 CCC LP 0-20/0-20MA	D.19
8444960000c1D2	WAZ 5 CCC LP 0-20/0-20MA C1D2	D.19
8444980000	WAS4 CCC DC 4-20/4-20MA	D.19
8444990000	WAZ4 CCC DC 4-20/4-20MA	D.19
8445040000	WAS4 CCVC DC 4-20/0-10V	D.19
8445050000	WAZ4 CVC DC 4-20/0-10V	D.19
8445070000	WAS4 CCC DC 0-20/0-20MA	D.19
8445080000	WAZ4 CCC DC 0-20/0-20MA	D.19
8447100000	WAS4 VCC DC 0-10/4-20MA	D.21
8447110000	WAZ4 VCC DC 0-10/4-20MA	D.21
8447130000	WAS4 VVC DC 0-10/0-10V	D.21
8447140000	WAZ4 VVC DC 0-10/0-10V	D.21
8447160000	WAS5 CCC HF 0-20/0-20MA	D.19
8447170000	WAZ5 CCC HF 0-20/0-20MA	D.19
8447280000	WAS5 CVC HF 4-20/0-10V	D.19
8447290000	WAZ5 CVC HF 4-20/0-10V	D.19
8447340000	WAS5 VCC HF 0-10/4-20MA	D.21
8447350000	WAZ5 VCC HF 0-10/4-20MA	D.21
8447370000	WAS5 VVC HF 0-10/0-10V	D.21
8447380000	WAZ5 VVC HF 0-10/0-10V	D.21
8461470000	MCZ VFC 0-10V	D.21
8461480000	MCZ CFC 0-20MA	D.19
8461490000	MCZ CFC 4-20MACLP TO FREQUENCY	D.19
8463580000	WAS5 CCC LP 2CH. 0-20MA/0-20MA	D.19
8463580000	WAS5 CCC LP 2CH. 0-20MA/0-20MA	D.19
8463590000	WAZ5 CCC LP 2CH. 0-20MA/0-20MA	D.19
8463590000c1D2	WAZ5 CCC LP 2CH. 0-20MA C1D2	D.19
8473000000	MCZ PT100/3 CLP -50/+150	D.21
8473010000	MCZ PT100/3 CLP 0-200C	D.23
8473020000	MCZ PT100/3 CLP 0-300C	D.23
8483680000	MCZ PT100/3 CLP 0-120 DEG C	D.21

8500000000

8513330000	WAS2 CMA 40/50/60 A UC	D.25
8513340000	WAS2 CMR 20/40/60A AC	D.25
8516560000	WAS2 CMR 1/5/10A AC	D.25
8516570000	WAZ2 CMR 1/5/10A AC	D.25
8523400000	WAS1 CMA 1/5/10A AC	D.25
8523410000	WAZ1 CMA 1/5/10A AC	D.25
8526590000	WAZ2 CMA 40/60/60A UC	D.25
8526600000	WAZ2 CMR 20/40/60A AC	D.25
8526610000	WAS2 CMA 5/10A UC	D.25
8526620000	WAZ2 CMA 5/10A UC	D.25
8528650000	WAS1 CMA LP 1/5/10A AC	D.25
8528660000	WAZ1 CMA LP 1/5/10A AC	D.25
8530621001	PRS 24VDC LD 1CO COMPLETE	D.6
8530631001	PRS 24 VDC LD 2CO COMPLETE	D.6
8530641001	PRS 120VAC LD 1CO COMPLETE	D.8
8530651001	PRS 120VAC LD 2CO COMPLETE	D.8
8530671001	PRS 230VAC LD 1CO COMPLETE	D.8
8530681001	PRS 230VAC LD 2CO COMPLETE	D.8
8530691001	PRZ 24VDC LD 1CO COMPLETE	D.6
8530701001	PRZ 24VDC LD 2CO COMPLETE	D.6
8530710000	PRZ 120VAC LD 1CO COMPLETE	D.8
8530720000	PRZ 120VAC LD 2CO COMPLETE	D.8
8530731001	PRZ 230VAC LD 1CO COMPLETE	D.8
8530741001	PRZ 230VAC LD 2CO COMPLETE	D.8
8533640000	MRS 24VDC 1CO 6A INRUSH	D.6
8533660000	MRZ 24 VDC 1CO 6A INRUSH	D.6
8536471001	PRS 12VDC LD 1CO COMPLETE	D.6
8536501001	PRS 12VDC LD 2CO COMPLETE	D.6
8536510000	PRS 115VDC LD 1CO COMPLETE	D.8
8536520000	PRS 115VDC LD 2CO COMPLETE	D.8
8536530000	PRS 24VAC LD 1CO COMPLETE	D.8
8536560000	PRS 24VAC LD 2CO COMPLETE	D.8
8536571001	PRZ 12VDC LD 1CO COMPLETE	D.6
8536581001	PRZ 12VDC LD 2CO COMPLETE	D.6
8536591001	PRZ 115VDC LD 1CO COMPLETE	D.8
8536610000	PRZ 115VDC LD 2CO COMPLETE	D.8
8536630000	PRZ 24VAC LD 1CO COMPLETE	D.8
8536651001	PRZ 24VAC LD 2CO COMPLETE	D.8
8536681001	PRC RETAINING CLIP PRS/PRZ	D.12
8536700000	PRC RETAINING CLIP PRS/PRZ	D.12
8540180000	WASS CCC DC 0(4)-20(0(4))-20MA	D.19
8540190000	WAZS CCC 0-20(0)-20MA	D.19
8540230000	WASS CVC DC 4-20MA/0-10V	D.19
8540240000	WAZS CVC 4-20MA/0-10V	D.19
8540290000	WASS VCC DC 0-10V/4-20MA	D.21
8540300000	WAZS VCC DC 0-10V/4-20MA	D.21
8540330000	WASS VVC DC 0-10V/0-10V	D.21
8540340000	WAZS VVC 0-10V/0-10V	D.21
8543720000	WASS WAVEANALOG OUTPUT LOOP 2W	D.19
8543730000	WAZS WAVEANALOG OUTPUT LOOP 2W	D.19
8543820000	WASS WAVEANALOG DC/ALARM	D.19
8543820000	WASS WAVEANALOG DC/ALARM	D.21

Part Number	Description	Page
8543880000	WAZ5 WAVEANALOG DC/ALARM	D.19
8543880000	WAZ5 WAVEANALOG DC/ALARM	D.21
8545830000	WAS2 CMA 20/25/30A UC	D.25
8545840000	WAZ2 CMA 20/25/30A UC	D.25
8556020000	MRS 230VAC 1CO 6A INRUSH	D.8
8556030000	MRS 120 VUC 1CO 6A INRUSH	D.8
8556040000	MRS 48VUC 1CO 6A INRUSH	D.8
8556050000	MRS 24 VUC 1C 6A INRUSH	D.6
8556060000	MRS 60VDC 1CO 6A INRUSH	D.8
8556070000	MRS 12 VDC 1CO 6A INRUSH	D.6
8556080000	MRS 5VDC 1CO 6A INRUSH	D.6
8556090000	MRZ 230VAC 1CO 6A INRUSH	D.8
8556100000	MRZ 120 VUC 1CO 6A INRUSH	D.8
8556110000	MRZ 48VUC 1CO 6A INRUSH	D.8
8556120000	MRZ 24VUC 1CO 6A INRUSH	D.6
8556130000	MRZ 60 VDC 1CO 6A INRUSH	D.8
8556140000	MRZ 12VDC 1CO 6A INRUSH	D.6
8556150000	MRZ 5VDC 1CO 6A INRUSH	D.6
8560700000	WASS WAVEPRO RTD	D.21
8560700000c102	WASS WAVEPRO RTD C1D2	D.21
8560700000	WASS WAVEPRO RTD	D.23
8560700000c102	WASS WAVEPRO RTD C1D2	D.23
8560710000	WAZ5 WAVEPRO RTD	D.21
8560710000c102	WAZ5 WAVEPRO RTD C1D2	D.21
8560710000	WAZ5 WAVEPRO RTD	D.23
8560710000c102	WAZ5 WAVEPRO RTD C1D2	D.23
8560720000	WASS WAVEPRO THERMO	D.23
8560720000c102	WASS WAVEPRO THERMO C1D2	D.23
8560730000	WAZ5 WAVEPRO THERMO	D.23
8560730000c102	WAZ5 WAVEPRO THERMO C1D2	D.23
8560740000	WAS4 WAVEPRO DC/DC	D.19
8560740000	WAS4 WAVEPRO DC/DC	D.21
8560750000	WAZ4 WAVEPRO DC/DC	D.19
8560750000	WAZ4 WAVEPRO DC/DC	D.21
8561990000	MOS 230VAC/230VAC 1A	D.12
8581160000	WASS CCC 20LP	D.19
8581170000	WAZ 5 CCC 20LP	D.19
8581180000	WAS4 WAVEPRO FREQUENCY	D.25
8581190000	WAZ4 WAVEPRO FREQUENCY	D.25
8581200000	WASS WAVEPRO BRIDGE	D.23
8581210000	WAZ5 WAVEPRO BRIDGE	D.23
8581220000	WAS2 WAVECONTROL VMA VAC	D.25
8581230000	WAZ2 WAVECONTROL VMA VAC	D.25
8594810000	MAS DC/DC SELECT	D.19
8594820000	MAS PT100 0...100C	D.21
8594830000	MAS THERMO K 0...1000C OUT SEL	D.23
8594840000	MAZ DC/DC SELECT	D.19
8594850000	MAZ PT100 0-100C OUTPUT SELECT	D.23
8594860000	MAZ THERMO K 0...1000°C OUTPUT SELECT	D.23
8596050000	MRS 230VAC 1CO 5UAU	D.8
8596060000	MRS 24 VDC 1CO AU 6A INRUSH	D.6
8596070000	MRZ 230VAC 1CO 5MICRON AU	D.8
8596080000	MRZ 24 VDC 1CO AU 6A INRUSH	D.6

8600000000

8604420000	MCZ PT100/3 CLP 0 TO +150	D.23
8604430000	MCZ PT100/3 CLP -40 TO +100	D.21
8607340000	MOS 24VDC/24VDC 0.1A	D.10
8607350000	MOS 24VDC/24VDC 2A	D.10
8607360000	MOZ 24VDC/ 24VDC 0.1A	D.10
8607370000	MOZ 24VDC/24VDC 2A	D.10
8607690000	MOS 120VUC/24VDC 0.1A	D.12
8607700000	MOS 120VUC/24VDC 2A	D.12
8607710000	MOS 230VAC/24VDC 0.1A	D.12
8607720000	MOS 230VAC/24VDC 2A	D.12
8607730000	MOZ 120VUC/24VDC 0.1A	D.12
8607740000	MOZ 120VUC/24VDC 2A	D.12
8607750000	MOZ 230VAC/24VDC 0.1A	D.12
8607760000	MOZ 230VAC/24VDC 2A	D.12
8610840000	POS 24 VDC/24VDC 2A COMPLETE	D.10
8610860000	POS 24VDC/230VAC 2A	D.10
8610890000	POS 24VDC/24VUC 1A	D.10
8610900000	POS 24VDC/24VDC 5A	D.10
8610910000	POS 24VDC/230VAC 4A	D.10
8610920000	POZ 24VDC/24VDC 2A	D.10
8610930000	POZ 24VDC/230VAC 2A	D.10
8610960000	POZ 24VDC/24VUC 1A	D.10
8610970000	POZ 24VDC/24VDC 5A	D.10
8610980000	POZ 24VDC/230VAC 4A	D.10
8615210000	MAS THERMO J 0...700 OUTPUT	D.23
8615240000	MAZ THERMO-J 0...700°C OUTPUT SELECT	D.23
8630740000	ZEW 35/2 SCREWLESS END BRACKET	A.16
8630740000	ZEW 35/2 SCREWLESS END BRACKET	A.18
8632990000	MOZ 5VDC/24VDC 2A	D.12
8633000000	MOS 5VDC/24VDC 2A	D.12
8633010000	MOZ 5VDC/24VDC 0.1A	D.12
8633020000	MOS 5VDC/24VDC 0.1A	D.12
8638950000	WASS PRO RTD CU	D.23
8651930000	MOS 120VUC/230VDC 1A	D.12
8651950000	MOZ 120VUC/230VDC 1A	D.12
8651970000	MOZ 230VAC/230VAC 1A	D.12
8652010000	MOS 24VDC/230VAC 1A	D.10
8652020000	MOZ 24VDC/230VAC 1A	D.10
8652030000	MRS 120 VUC 1CO AU 6A INRUSH	D.8
8652040000	MRZ 120 VUC 1CO AU 6A INRUSH	D.8
8660910000	MRZ 24VDC ACTUATOR, 1NO+CC	D.6
8660920000	MRS 24VDC ACTUATOR, 1NO+CC	D.6
8676230000	MOZ 24VDC/24VDC ACT	D.10
8676250000	MOS 24VDC/24VDC ACT	D.10
8679490000	WASS PRO RTD 1000	D.23

8700000000

8705630000	WAS 2 VMR 3 PHASE	D.25
------------	-------------------	------

Part Number	Description	Page
8705640000	WAS2 VMR 1PHASE	D.25
8708660000	CP-SNT 70W 24V 3A	D.27
8708670000	CP-SNT 120W 24V 5A	D.27
8708680000	CP-SNT 240W 24V 10A	D.27
8708700000	CP-SNT3 250W 24V 10A 3 PHASE	D.27
8708710000	CP-SNT3 500W 24V 20A 3 PHASE	D.27
8708730000	CP-SNT3 1000W 24V 40A 3 PHASE	D.27
8710620000	CP-SNT DM 10 PARALLEL	D.29
8721150000	MAS RPS W/O HART 4-20MA/4-20MA	D.19
8721170000	MAS RPSH HART 4-20MA/SELEC.OUT	D.19
8731720000	ZTR 2.5/3AN	A.12
8734580000	AC OUTLET EUROPEAN FOR TS35	D.4
8742610000	PAS CMR 0.5 TO 2.5A DC	D.21
8742620000	PAS CMR 2 TO 5A DC	D.21
8742630000	PAS CMR 4.5 TO 10A DC	D.21
8768650000	CP DM 20A DIODE MODULE	D.29
8778870000	CP-SNT ECO 500W 24V 20A	D.27
8798740000	RCM KIT 24VDC 4CO LED	D.6

8800000000

8808190000	IE-MC-ST FIBER CONVERTER	G.3
8808220000	IE-MC-SC FIBER CONVERTER	G.3
8808230000	IE-SW5-ECO 5 PORT SWITCH	G.2
8808240000	IE-SW8 8 PORT SWITCH	G.2
8808250000	IE-SW4/2SC ETHERNET SWITCH	G.2
8808260000	IE-SW4/2ST ETHERNET SWITCH	G.3
8808270000	IE-SW16 ETHERNET SWITCH	G.3
8808280000	IE-SW14/2SC ETHERNET SWITCH	G.3
8808290000	IE-SW14/2ST ETHERNET SWITCH	G.3
8808300000	IE-SW24 ETHERNET SWITCH	G.2
8808310000	IE-SW22/2SC SWITCH	G.2
8808320000	IE-SW22 2ST ETHERNET SWITCH	G.2
8808340000	IE-XM-ST ETHERNET OUTLET	G.5
8808360000	IE-XM ETHERNET OUTLET	G.5
8808370000	IE-S-IP67 RJ45 IDC SOCKET MOD	G.6
8808380000	IE-P-IP67	G.6
8808400000	IE-CSM CABLE SHARING MODULE	G.6
8808410000	IE-CCM CABLE CONNECTING MODULE	G.6
8808420000	IE-CT ETHERNET TESTER	G.7
8808440000	IE-XM-RJ45/IDC-IP67	G.6
8808450000	IE-X1M-RJ45/RJ45-IP67	G.6
8810080000	RCM KIT Z 115VAC 4 CO LDRT	D.8
8810150000	RCM KIT 115VAC 4CO LED REU	D.8
8813090000	IE-C-IP67 RJ45 IDC CABLE COUPL	G.6
8825960000	MRZ 120VUC 1CO RC	D.8
8825970000	MRS 120VUC 1CO RC	D.8
8829430000	IE-SW8-ECO 8 PORT SWITCH	G.2
8829440000	IE-XM-6U-RJ45/RJ45-IP67	G.6
8829450000	IE-XM-6D-RJ45/RJ45-IP67	G.6
8833790000	IE-SW5-ECO-FLAT ETHERNETSWITCH	G.2
8845740000	IE-SW8-M	G.4
8845750000	IE-AR-10T-ISDN	G.5
8845760000	IE-ARM-E	G.5
8845770000	IE-ARM-U	G.5
8845780000	IE-SW14/2/SC-M	G.4
8845790000	IE-SW14/2ST-M	G.4
8845800000	IE-SW16-M	G.4
8845810000	IE-SW22/2SC-M	G.4
8845820000	IE-SW22/2ST-M	G.4
8845830000	IE-SW24-M	G.4
8845840000	IE-SW6/2SC-M	G.4
8845850000	IE-SW6/2ST-M	G.4
8845860000	IE-AR-10T	G.5
8879050000	IE-XM-RJ45/RJ45	G.5

9000000000

9001080000	AM 35 STRIPPING TOOL	E.2
9001090000	KT 36 CABLE CUTTER 35MM	E.2
9001530000	AM 1/25/35 REPLACEMENT BLADE	E.2
9001540000	AM 25 STRIP TOOL	E.2
9002000000	KT 45 CABLE CUTTER 45MM DIA	E.2
9002300000	KT20 UP TO AWG2/0 CABLE CUTTER	E.2
9002580000	KT 35 BLADE	E.3
9002650000	KT 8 CABLE CUTTER UP TO 6AWG	E.2
9002660000	KT 12 CABLE/WIRE CUTTER	E.2
9004050000	H 0.5/10 FERRULES	E.9
9004060000	H 1.5/12 NON-INSULATED	E.9
9004070000	H 1.5/18 NON-INSULATED FERRULE	E.9
9004080000	H 2.5/10 FERRULES	E.9
9004090000	H 2.5/18 FERRULES	E.9
9004100000	H 4/15 FERRULES	E.9
9004110000	H 4/18 NON-INSULATED FERRULE	E.9
9004120000	H 6/10 FERRULES	E.9
9004130000	H 6/18 FERRULES W/O COLLAR	E.9
9004150000	H 16/25 FERRULE	E.9
9004160000	H 16,0/32	E.9
9004170000	H 25/25 3 AWG UNINSULATED	E.9
9004180000	H 25,0/32	E.9
9004190000	H 35/32 2 AWG UNINSULATED	E.9
9004200000	H 35/32 2 AWG UNINSULATED	E.9
9004210000	H 50/18 FERRULES	E.9
9004220000	H 50/32 FERRULES W/O COLLAR	E.9
9004230000	H 70/25 FERRULES	E.9
9004240000	H 70/32 FERRULES	E.9
9004250000	H 95/25 FERRULES	E.9
9004260000	H 95/32 FERRULE W/O COLLAR	E.9
9004270000	ORANGE STRIP FERRULES	E.8
9004290000	WHITE FERRULES 0.75/14 .75/8N	E.8
9004320000	H 1.0/14 YELLOW FERRULES	E.8
9004340000	RED STRIP FERRULES	E.8
9004360000	BLUE STRIP FERRULES	E.8
9004390000	H 0.34/12 TURQUOISE ON REELS	E.8
9004410000	H 1.5/16 RED TWIN FERRULES	E.11

Part Number	Description	Page
9004430000	BLUE TWIN FERRULES	E.11
9004440000	H 0.5/15 ORANGE TWIN FERRULES	E.11
9004730000	H 4/22 D GREY	E.11
9004740000	H 2.5/20.5 D ZH BLUE FERRULES	E.11
9004900000	H 0.75/17 WHITE STRIP PACKAGE	E.11
9004910000	H 1.0/20 ZH GE SV	E.11
9004920000	H 1.5/20 ZH R SV	E.11
9004930000	H 6.0/25 ZH BLACK SV FERRULES	E.11
9004940000	H 10.0/26 ZH IVORY STRIP PACK	E.11
9005000000	STRIPAX PROFESSIONAL STRIPPER	E.2
9005180000	H 014/10 GREY STRIP PACK	E.8
9005450000	BRUSH FOR STRIPAX	E.2
9005610000	STRIPAX 16	E.8
9005810000	H 0.5/14 ORANGE REEL FERRULES	E.2
9005820000	H 0.75/14 WHITE REEL FERRULES	E.8
9005830000	H 1.0/14 YELLOW REEL FERRULES	E.8
9005840000	H 1.5/14 RED REEL FERRULES	E.8
9005850000	H 2.5/14D BLUE REEL FERRULES	E.8
9005990000	PZ 1.5	E.3
9005990000	PZ 1.5	E.10
9006450000	PZ 50 CRIMP TOOL,4-1/0AWG	E.10
9006450000	PZ 50 CRIMP TOOL,4-1/0AWG	E.3
9008320000	SD 0.5X3.0X80,NON-INSUL,FLAT	E.5
9008330000	SD 0.6X3.5X100, NON-INSUL,FLAT	E.5
9008340000	SD 0.8X4.0X100,NON-INSUL,FLAT	E.5
9008350000	SD 1.0X5.5X150,NON-INSUL,FLAT	E.5
9008370000	SDI 0.4 X 2.5 X 75	E.4
9008380000	SDI 1,INSUL,FLAT,0.5X3.0X100	E.4
9008390000	SDI 2,INSUL,FLAT,0.6X3.5X100	E.4
9008400000	SDI 3,INSUL,FLAT,0.8X4.0X100	E.4
9008410000	SDI 4,INSUL,FLAT,1.0X5.5X125	E.4
9008420000	SDI 1.2X6.5X150	E.4
9008430000	SDI 6,INSUL,FLAT,1.6X8.0X175	E.4
9008470000	SDK PHILIPS SIZE 0 NON-INSUL.	E.5
9008480000	SDK PHILIPS SIZE 1 NON-INSUL.	E.5
9008490000	SDK PHILIPS SIZE 2 NON-INSUL.	E.5
9008500000	SDK PHILIPS SIZE 3 NON-INSUL.	E.5
9008520000	SDP P20	E.5
9008530000	SDP P21	E.5
9008540000	SDP P22	E.5
9008550000	SDP P23	E.5
9008570000	SDIK PHILIPS SIZE 1 INSULATED	E.4
9008580000	SDIK PHILIPS SIZE 2 INSULATED	E.4
9008590000	SDIK PHILIPS SIZE 3 INSULATED	E.4
9008900000	SDIK PZ2 SCREWDRIVER	E.4
9008900000	SDIK PZ1 SCREWDRIVER	E.4
9008910000	SDI 1.0X4.5X125	E.4
9008920000	SKI 13.0X125 HEXAGONAL SPANNER	E.4
9008930000	SKI 11.0X125 HEXAGONAL SPANNER	E.4
9008940000	SKI 10.0 X 126 BOX SPANNER	E.4
9008950000	SKI 9.0X126 HEXAGONAL SPANNER	E.4
9008960000	SKI 8.0X127 HEXAGONAL SPANNER	E.4
9008970000	SKI 7.0X127 HEXAGONAL SPANNER	E.4
9008980000	SKI 6.0X128 HEXAGONAL SPANNER	E.4
9008990000	SKI 5.5X128 HEXAGONAL SPANNER	E.4
9009000000	SKI 5.0X129 HEXAGONAL SPANNER	E.4
9009010000	SD 1.2X6.5X150,NON-INSUL,FLAT	E.5
9009020000	SD 0.8X4.5X125,NON-INSUL,FLAT	E.5
9009030000	SD 0.4X2.5X75,NON-INSUL,FLAT	E.5
9009040000	SK 13.0X125 SCREWDRIVER	E.5
9009050000	SK 12.0X125 SCREWDRIVER	E.5
9009060000	SK 11.0X125 SCREWDRIVER	E.5
9009070000	SK 10.0X125 SCREWDRIVER	E.5
9009080000	SK 9.0X125 SCREWDRIVER	E.5
9009090000	SK 8.0X125 SCREWDRIVER	E.5
9009100000	SK 7.0X125 SCREWDRIVER	E.5
9009110000	SK 6.0X125 SCREWDRIVER	E.5
9009120000	SK 5.5X125 ALLEN KEY	E.5
9009130000	SK 5.0X125 SCREWDRIVER	E.5
9009140000	SD TH30	E.5
9009150000	SDTR 25 TORX HEAD SCREWDRIVER	E.5
9009160000	SDTR TORX 20 SCREWDRIVER	E.5
9009170000	SDTR TORX 15 SCREWDRIVER	E.5
9009180000	SDTR TORX 10 SCREWDRIVER	E.5
9009190000	SDTR 8 TORX SCREWDRIVER	E.5
9009640000	SDI T10	E.4
9009650000	SDI T15	E.4
9009660000	SDI T20	E.4
9009670000	SDI T25	E.4
9009680000	SDI T30	E.4
9009690000	SDI T40	E.4
9009730000	SDIS 2.55-.5/PH1/2 SET	E.5
9009740000	SDS 2.5-.5/PH1/2	E.5

Part Number	Description	Page
-------------	-------------	------

9018650000	H 1,0/15S ZH GE SV	E.11
9018690000	H 1/15 S ZH YELLOW	E.11
9018860000	H 10/24 ZH IVORY STRIP PACK	E.11
9018870000	H 10/30S ZH EB	E.11
9018910000	H 0.25/5 UNINSULATED FERRULES	E.9
9019160000	H 2.5/14D	E.8
9019170000	H 2.5/18 D BLUE FERRULES	E.8
9019180000	H 2.5/25, 14AWG, INS, BLUE	E.8
9019190000	H 4/17 D GREY FERRULE	E.8
9019200000	H 4/20D GREY FERRULES	E.8
9019210000	H 4/0/25, 12AWG, INS, GREY	E.8

9020000000

9020000000	STRIPAX PLUS	E.3
9020000000	STRIPAX PLUS	E.10
9025740000	H 0.25/10 LIGHT BLUE	E.8
9025750000	H 0.34/10 TURQUOISE FERRULES	E.8
9025760000	H 0.25/12 LIGHT BLUE FERRULES	E.8
9025770000	H 0.34/12 TURQUOISE FERRULES	E.8
9025780000	H 0.25/12 LIGHT BLUE STRIP PKG	E.8
9025790000	H 0.34/12 FERRULES STRIP PKG	E.8
9025860000	H 0.75/16 WHITE	E.8
9025870000	H 0.5/16 ORANGE FERRULES	E.8
9025880000	H 50.0 FERRULES	E.9
9025910000	AEH 0.75/18	E.8
9025930000	AEH 1.0/18 FERRULES	E.8
9025950000	AEH 1.0/16 FERRULES (YELLOW)	E.8
9026010000	H 4/17 D GREY FERRULES	E.8
9026030000	HO 34/10 TURQUOISE	E.8
9026050000	H 0.25/10,24AWG,INS,LIGHT BLUE	E.8
9026060000	H 0.5/16 ORANGE FERRULES	E.8
9026070000	H 0.75/14 WHITE	E.8
9026080000	H 1/14 YELLOW	E.8
9026090000	H 1.5/14	E.8
9026100000	H 2.5 FERRULES 14	E.8
9028200000	H 70.0/40 YELLOW	E.8
9028210000	H 95/44 RED FERRULES 3/0 AWG	E.8
9028220000	H 120/50 BLUE	E.8
9028230000	H 150/54 YELLOW	E.8
9028240000	H 0.14/12 GREY STRIP PACK	E.8
9028260000	H 0.5/10 ORANGE STRIP PKG	E.8
9028270000	H 0.5/16 OR SV	E.8
9028280000	H 0.75/12 WHITE STRIP PKG	E.8
9028290000	H 0.75/16 WHITE FERRULES	E.8
9028300000	H 0.75/18 W SV	E.8
9028310000	H 1,0/12 GE SV	E.8
9028320000	H 1,0/16 YELLOW STRIP PKG	E.8
9028340000	H 1,0/18 GE SV	E.8
9028350000	H 1.5/16 RED FERRULES STRIP PK	E.8

9030000000

9030060000	AM 12 GRAY	E.2
9030060000	AM 12 GRAY	G.7
9036240000	H 120/32 FERRULES W/O COLLARS	E.9
9036250000	H 150,0/32	E.9
9036260000	H 185,0/32	E.9
9037160000	SD 0.4X2.0X60, NON-INSUL, FLAT	E.5
9037200000	H 0.5/15 ZH ORANGE	E.11
9037210000	H 0.5/16.5 ZH ORANGE FERRULES	E.11
9037220000	H 0.5/18.5 ZH ORANGE TWIN	E.11
9037230000	H 0.75/15 ZH WHITE TWIN FERR	E.11
9037240000	H 0.75/17 ZH WHITE	E.11
9037250000	H 0.75/24, 5 ZH WHITE FERRULES	E.11
9037260000	H 1.0/15 ZH YELLOW FERRULES	E.11
9037270000	H 1.0/20 ZH YELLOW	E.11
9037280000	H 1.0/25.6 ZH YELLOW	E.11
9037290000	H 1.5/16 ZH RED FERRULES	E.11
9037300000	H 1.5/20 ZH RED FERRULES	E.11
9037310000	H 1.5/25 6 ZH RED FERRULES	E.11
9037320000	H 6.0/25 ZH BLACK FERRULES	E.11
9037330000	H 6.0/29 ZH BLACK FERRULES	E.11
9037340000	H 10.0/26 ZH IVORY FERRULES	E.11
9037350000	H 10.0/30 ZH EB	E.11
9037360000	H 16.0/29 TWIN GREEN FERRULE	E.11
9037500000	H 2.5/18 SD 2H BLUE	E.11
9037510000	H 2.5/20.5D ZH BLUE	E.11
9037520000	H 2.5/26, 5D ZH BLUE FERRULES	E.11
9037530000	H 4.0/22D ZH GREY	E.11
9037540000	H 4.0/28D ZH GREY FERRULES	E.11

9050000000

9050340000	CUTTING BLADE FOR STRIPAX PLUS	E.3
9054030000	BLADE SET NEW STRIPAX 6	E.2
9054580000	DIE SET FOR PZ ZH 16	E.3

9100000000

9101000000	MCB 0.5 AMP,1 POLE	B.5
9101100000	MCB 0.8 AMP,1 POLE	B.5
9101200000	MCB 1.0 AMP,1 POLE	B.5
9101300000	MCB 1.2 AMP,1 POLE	B.5
9101400000	MCB 1.5 AMP,1 POLE	B.5
9101500000	MCB 2.0 AMP,1 POLE	B.5
9101600000	MCB 2.5 AMP,1 POLE	B.5
9101700000	MCB 3.0 AMP,1 POLE	B.5
9101800000	MCB 5.0 AMP,1 POLE	B.5
9101900000	MCB 10.0 AMP,1 POLE	B.5
9102000000	MCB 15.0 AMP,1 POLE	B.5
9102100000	ADAPTOR FOOT	B.5
9103000000	MCB 8.0 AMP,1 POLE	B.5

Part Number	Description	Page
-------------	-------------	------

9103810000	MCB 6.0 AMP,1 POLE	B.5
9104150000	MCB 7.0 AMP,1 POLE	B.5
9104170000	MCB 0.1 AMP,1 POLE	B.5
9104180000	MCB 0.2 AMP,1 POLE	B.5
9104350000	MCB 4.0 AMP,1 POLE	B.5
9104610000	MCB 9.0 AMP,1 POLE	B.5
9104650000	MCB 0.08 AMP,1 POLE	B.5
9104670000	MCBD 8.0 AMP,2 POLE	B.5
9107830000	MCB 5.5 AMP,1 POLE	B.5
9107840000	MCB 12.0 AMP,1 POLE	B.5
9107850000	MCB 14.0 AMP,1 POLE	B.5

9110000000

9118290001	ASK1EN/SMT100-250VUC BFI H+	A.8
------------	-----------------------------	-----

9120000000

9120040000	MCB 6.5 AMP,1 POLE	B.5
9120350000	MCBD 0.1 AMP,2 POLE	B.5
9123140001	ASK1EN/SMT10-60VUC BFI H+	A.8
9124080000	MCB 0.05 AMP,1 POLE	B.5
9124090000	MCB 0.4 AMP,1 POLE	B.5
9124110000	MCB 0.6 AMP,1 POLE	B.5
9124120000	MCB 1.3 AMP,1 POLE	B.5
9124130000	MCB 1.4 AMP,1 POLE	B.5
9124140000	MCB 1.8 AMP,1 POLE	B.5
9124160000	MCB 3.5 AMP,1 POLE	B.5
9124170000	MCB 4.5 AMP,1 POLE	B.5
9124180000	MCB 11.0 AMP,1 POLE	B.5
9124190000	MCB 13.0 AMP,1 POLE	B.5
9124210000	MCB 16.0 AMP,1 POLE	B.5
9124220000	MCBD 0.05 AMP,2 POLE	B.5
9124230000	MCBD 0.08 AMP,2 POLE	B.5
9124240000	MCBD 0.2 AMP,2 POLE	B.5
9124260000	MCBD 0.3 AMP,2 POLE	B.5
9124270000	MCBD 0.4 AMP,2 POLE	B.5
9124280000	MCBD 0.6 AMP,2 POLE	B.5
9124290000	MCBD 0.7 AMP,2 POLE	B.5
9124310000	MCBD 1.3 AMP,2 POLE	B.5
9124320000	MCBD 1.4 AMP,2 POLE	B.5
9124330000	MCBD 1.8 AMP,2 POLE	B.5
9124340000	MCBD 3.5 AMP,2 POLE	B.5
9124350000	MCBD 4.5 AMP,2 POLE	B.5
9124360000	MCBD 5.5 AMP,2 POLE	B.5
9124370000	MCBD 6.0 AMP,2 POLE	B.5
9124380000	MCBD 6.5 AMP,2 POLE	B.5
9124390000	MCBD 7.0 AMP,2 POLE	B.5
9124420000	MCBD 9.0 AMP,2 POLE	B.5
9124430000	MCBD 11.0 AMP,2 POLE	B.5
9124440000	MCBD 12.0 AMP,2 POLE	B.5
9124450000	MCBD 13.0 AMP,2 POLE	B.5
9124460000	MCBD 14.0 AMP,2 POLE	B.5
9124470000	MCBD 16.0 AMP,2 POLE	B.5
9129560000	MCB 0.7 AMP,1 POLE	B.5
9129580000	MCBD 0.5 AMP,2 POLE	B.5
9129590000	MCBD 0.8 AMP,2 POLE	B.5
9129610000	MCBD 1.0 AMP,2 POLE	B.5
9129620000	MCBD 1.2 AMP,2 POLE	B.5
9129630000	MCBD 1.5 AMP,2 POLE	B.5
9129640000	MCBD 2.0 AMP,2 POLE	B.5
9129650000	MCBD 2.5 AMP,2 POLE	B.5
9129660000	MCBD 3.0 AMP,2 POLE	B.5
9129670000	MCBD 5.0 AMP,2 POLE	B.5
9129680000	MCBD 10.0 AMP,2 POLE	B.5
9129690000	MCBD 15.0 AMP,2 POLE	B.5
9129710000	MCBD 4.0 AMP,2 POLE	B.5
9129810000	MCB 0.3 AMP,1 POLE	B.5

9150000000

9158330001	KDKS1PE/SMT10-60VUC BFI H-	A.8
9158340001	KDKS1PE/SMT10-60VUC BFI H+	A.8
9158350001	KDKS1PE/SMT100-250VUC BFI H-	A.8

9200000000

9201940000	SDI T8	E.4
9202800000	TT 8 RS MP 8	G.7

9400000000

9451000000	H 35,0/30S	E.9
------------	------------	-----

9500000000

9503350000	KDKS 1 EN/35 NO LED, WM, BEIGE	A.8
9528110000	KDKS 1 PE/35 NO LED, WM, BG	A.8
9540000000	ZEW TS35 SCREWLESS BRACKET	A.16
9540000000	ZEW TS35 SCREWLESS BRACKET	A.18

9800000000

9806370000	PICOPAK FREQUENCY DIVIDER DK5	D.25
9802720001	KDKS1EN/SMT10-60VUC BFI H-	A.8
9802760001	KDKS1EN/SMT100-250VUC BFI H-	A.8

Part Number	Description	Page
-------------	-------------	------

9900000000

9902860000	RSHV AC, 110V W/O LED	D.8
9906310000	HVDC 24VAC/DC	D.6
9906660000	OPTO W/O INPUT CURRENT LIMIT	D.12
9908510001	KDKS1EN/SMT10-60VUC BFI H+	A.8
9908800000	PICOPAK I TO I / DK6 WITH AP	D.19
9908810000	PICOPAK 3 WIRE POTENTIOMETER	D.23

9910000000

9910590000	PICOPAK DK6RELAY 24VDC/120VAC	D.8
9911010000	CIRCUIT BREAKER 1P .1A	B.4
9911020000	CIRCUIT BREAKER 1P .2A	B.4
9911030000	CIRCUIT BREAKER 1P .3A	B.4
9911040000	CIRCUIT BREAKER 1P .4A	B.4
9911050000	CIRCUIT BREAKER 1P .5A	B.4
9911060000	CIRCUIT BREAKER 1P .6A	B.4
9911080000	CIRCUIT BREAKER 1P .8A	B.4
9911100000	CIRCUIT BREAKER 1P 1.0A	B.4
9911150000	CIRCUIT BREAKER 1P 1.5A	B.4
9911200000	CIRCUIT BREAKER 1P 2.0A	B.4
9911250000	CIRCUIT BREAKER 1P 2.5A	B.4
9911300000	CIRCUIT BREAKER 1P 3.0A	B.4
9911400000	CIRCUIT BREAKER 1P 4.0A	B.4
9911500000	CIRCUIT BREAKER 1P 5.0A	B.4
9911600000	CIRCUIT BREAKER 1P 6.0A	B.4
9911800000	CIRCUIT BREAKER 1P 8.0A	B.4
9912010000	CIRCUIT BREAKER 2P .1A	B.4
9912020000	CIRCUIT BREAKER 2P .2A	B.4
9912030000	CIRCUIT BREAKER 2P .3A	B.4
9912040000	CIRCUIT BREAKER 2P .4A	B.4
9912050000	CIRCUIT BREAKER 2P .5A	B.4
9912060000	CIRCUIT BREAKER 2P .6A	B.4
9912080000	CIRCUIT BREAKER 2P .8A	B.4
9912100000	CIRCUIT BREAKER 2P 1.0A	B.4
9912150000	CIRCUIT BREAKER 2P 1.5A	B.4
9912200000	CIRCUIT BREAKER 2P 2.0A	B.4
9912250000	CIRCUIT BREAKER 2P 2.5A	B.4
9912300000	CIRCUIT BREAKER 2P 3.0A	B.4
9912400000	CIRCUIT BREAKER 2P 4.0A	B.4
9912500000	CIRCUIT BREAKER 2P 5.0A	B.4
9912600000	CIRCUIT BREAKER 2P 6.0A	B.4
9912800000	CIRCUIT BREAKER 2P 8.0A	B.4
9913010000	CIRCUIT BREAKER 3P .1A	B.4
9913020000	CIRCUIT BREAKER 3P .2A	B.4
9913030000	CIRCUIT BREAKER 3P .3A	B.4
9913040000	CIRCUIT BREAKER 3P .4A	B.4
9913050000	CIRCUIT BREAKER 3P .5A	B.4
9913060000	CIRCUIT BREAKER 3P .6A	B.4
9913080000	CIRCUIT BREAKER 3P .8A	B.4
9913100000	CIRCUIT BREAKER 3P 1.0A	B.4
9913150000	CIRCUIT BREAKER 3P 1.5A	B.4
9913200000	CIRCUIT BREAKER 3P 2.0A	B.4
9913250000	CIRCUIT BREAKER 3P 2.5A	B.4
9913300000	CIRCUIT BREAKER 3P 3.0A	B.4
9913400000	CIRCUIT BREAKER 3P 4.0A	B.4
9913500000	CIRCUIT BREAKER 3P 5.0A	B.4
9913600000	CIRCUIT BREAKER 3P 6.0A	B.4
9913800000	CIRCUIT BREAKER 3P 8.0A	B.4
9915150001	KDKS1PE/SMT100-250VUC BFI H+	A.8
9915480001	RS-AC/CB 120V SINGLE OUTLET	D.4
9915490000	RS-DUPLEX 120VAC DUAL OUTLET	D.4
9915700000	PICOPAK OPTO24/120 C/W LEAKAGE	D.10
9915820001	KDKS1EN/SMT100-250VUC BFI H+	A.8
9916010000	PICOPAK MCZ I/I	D.19
9916080000	WAVEPAK MPI-OPTO	D.10
9916090000	CSR CUR. SENS. RELAY RS45 HOUS	D.25
9916240000	PICOPAK MC6/0-5AAC/4-20MA 2W	D.25
9916250024	CP-SNT300W 115-230V/24VDC, 12.5A	D.26
9916280012	CP-BBU 12VDC	D.29
9916280024	CP-BBU 24VDC	D.29
9916290000	MC6 NON-INCENDIVE BARRIER(DIG)	D.5
9916340000	WAVEPAK 0-300VDC/4-20MA/24V 3W	D.21
9916450000	DC CURRENT SENSOR + AMP	D.21
9917790324	CP-SNT 360-480V 3PH/24VDC,2.3A	D.26
9917841000	MC6 INS MAKE BEFORE BREAK TB	D.5
9918010000	MC6 NON-INCENDIVE BARRIER(ANG)	D.5
9918370000	DMS MANUAL 0.5-1.7NM TORQUE	E.7
9918380000	DMS MANUAL 2.0-8.0NM TORQUE	E.7
9918390000	DMSI MANUAL 0.5-1.7NM TORQUE	E.6
9918400000	DMSI MANUAL 2.0-8.0NM TORQUE	E.6
9918410000	WK SI 0.4X2.5 FOR DMSI MANUAL	E.6
9918420000	WK SI 0.5X3.0 FOR DMSI MANUAL	E.6
9918430000	WK SI0.1X3.5 FOR DMSI MANUAL	E.6
9918440000	WK SI 0.8X4.0 FOR DMSI MANUAL	E.6
9918450000	WK SI 1.0X5.5 FOR DMSI MANUAL	E.6
9918460000	WK IK PH 0 FOR DMSI MANUAL	E.6
9918470000	WK IK PH 1 FOR DMSI MANUAL	E.6
9918480000	WK IK PH 2 FOR DMSI MANUAL	E.6
9918490000	WK IK PZ 0 FOR DMSI MANUAL	E.6
9918500000	WK IK PZ 1 FOR DMSI MANUAL	E.6
9918510000	WK IK PZ 2 FOR DMSI MANUAL	E.6
9918520000	WK S 0.4X2.5 FOR DMS MANUAL	E.7
9918530000	WK S 0.5X3.0 FOR DMS MANUAL	E.7
9918540000	WK S 0.6X3.5 FOR DMS MANUAL	E.7
9918550000	WK S 0.8X4.0 FOR DMS MANUAL	E.7
9918560000	WK S 1.0X5.5 FOR DMS MANUAL	E.7
9918570000	WK K PH 0 FOR DMS MANUAL	E.7
9918580000	WK K PH 1 FOR DMS MANUAL	E.7
9918590000	WK K PH 2 FOR DMS MANUAL	E.7
9918600000	WK K PZ 0 FOR DMS MANUAL	E.7
9918610000	WK K PZ 1 FOR DMS MANUAL	E.7
9918620000	WK K PZ 2 FOR DMS MANUAL	E.7
9918840024	CP-SNT12W 115.230VAC/24V,0.5A	D.26
9919371205	CP-DCDC 12VDC IN/ 5VDC, 8A OUT	D.20

Part Number	Description	Page
9919371212	CP-DCDC 12VDC IN/12VDC, 3A OUT	D.28
9919371215	CP-DCDC 12VDC IN/15VDC, 3A OUT	D.28
9919371224	CP-DCDC 12VDC IN/24VDC, 2A OUT	D.28
9919372405	CP-DCDC 24VDC IN/ 5VDC, 8A OUT	D.28
9919372412	CP-DCDC 24VDC IN/12VDC, 3A OUT	D.28
9919372415	CP-DCDC 24VDC IN/15VDC, 3A OUT	D.28
9919372424	CP-DCDC 24VDC IN/24VDC, 2A OUT	D.28

9920000000

9921100000	CIRCUIT BREAKER 1P 10.A	B.4
9921120000	CIRCUIT BREAKER 1P 12.A	B.4
9921150000	CIRCUIT BREAKER 1P 15.A	B.4
9921160000	CIRCUIT BREAKER 1P 16.A	B.4
9921180000	CIRCUIT BREAKER 1P 18.A	B.4
9921200000	CIRCUIT BREAKER 1P 20.A	B.4
9921250000	CIRCUIT BREAKER 1P 25.A	B.4
9921320000	CIRCUIT BREAKER 1P 32.A	B.4
9922100000	CIRCUIT BREAKER 2P 10.A	B.4
9922120000	CIRCUIT BREAKER 2P 12.A	B.4
9922150000	CIRCUIT BREAKER 2P 15.A	B.4
9922160000	CIRCUIT BREAKER 2P 16.A	B.4
9922180000	CIRCUIT BREAKER 2P 18.A	B.4
9922200000	CIRCUIT BREAKER 2P 20.A	B.4
9922250000	CIRCUIT BREAKER 2P 25.A	B.4
9922320000	CIRCUIT BREAKER 2P 32.A	B.4
9923100000	CIRCUIT BREAKER 3P 10.A	B.4
9923120000	CIRCUIT BREAKER 3P 12.A	B.4
9923150000	CIRCUIT BREAKER 3P 15.A	B.4
9923160000	CIRCUIT BREAKER 3P 16.A	B.4
9923180000	CIRCUIT BREAKER 3P 18.A	B.4
9923200000	CIRCUIT BREAKER 3P 20.A	B.4
9923250000	CIRCUIT BREAKER 3P 25.A	B.4
9923320000	CIRCUIT BREAKER 3P 32.A	B.4
9925340005	CP-SNT50W 115,230VAC/ 5V,10A	D.26
9925340012	CP-SNT120W 115,230VAC/12V,10A	D.26
9925340024	CP-SNT160W 115,230V/24-28,6.5A	D.26
9925340324	CP-SNT 360-500V 3PH/24VDC,6.5A	D.26
9925340048	CP-SNT156W 115,230VA/48V,3.25A	D.26
9925350000	91H12-0.5	B.3
9925360000	91H12-1	B.3
9925380000	91H12-2	B.3
9925390000	91H12-3	B.3
9925400000	91H12-4	B.3
9925410000	91H12-6	B.3
9925430000	91H12-10	B.3
9925440000	91H12-16	B.3
9925450000	91H12-20	B.3
9925460000	91H12-25	B.3
9925470000	91H12-32	B.3
9925480000	91H12-40	B.3
9925490000	91H12-50	B.3
9925500000	91H12-63	B.3
9925650000	91H22-0.5	B.3
9925660000	91H22-1	B.3
9925680000	91H22-2	B.3
9925690000	91H22-3	B.3
9925700000	91H22-4	B.3
9925710000	91H22-6	B.3
9925730000	91H22-10	B.3
9925740000	91H22-16	B.3
9925750000	91H22-20	B.3
9925760000	91H22-25	B.3
9925770000	91H22-32	B.3
9925780000	91H22-40	B.3
9925790000	91H22-50	B.3
9925800000	91H22-63	B.3
9925810000	91H32-0.5	B.3
9925820000	91H32-1	B.3
9925840000	91H32-2	B.3
9925850000	91H32-3	B.3
9925860000	91H32-4	B.3
9925870000	91H32-6	B.3
9925890000	91H32-10	B.3
9925900000	91H32-16	B.3
9925910000	91H32-20	B.3
9925920000	91H32-25	B.3
9925930000	91H32-32	B.3
9925940000	91H32-40	B.3
9925950000	91H32-50	B.3
9925960000	91H32-63	B.3
9926251001	CB 120V, 1A, CURVE KM, 1 POLE	B.2
9926251002	CB 120V, 2A, CURVE KM, 1 POLE	B.2
9926251005	CB 120V, 5A, CURVE KM, 1 POLE	B.2
9926251010	CB 120V,10A, CURVE KM, 1 POLE	B.2
9926251015	CB 120V,15A, CURVE KM, 1 POLE	B.2
9926251020	CB 120V,20A, CURVE KM, 1 POLE	B.2
9926251025	CB 120V,25A, CURVE KM, 1 POLE	B.2
9926251901	CB 80VDC, 1A, CURVE U2, 1P	B.2
9926251902	CB 80VDC, 2A, CURVE U2, 1P	B.2
9926251905	DC BRANCH CB 5A 1 POLE	B.2
9926251910	CB 80VDC, 10A, CURVE U2, 1P	B.2
9926251915	CB 80VDC, 15A, CURVE U2, 1P	B.2
9926251920	CB 80VDC, 20A, CURVE U2, 1P	B.2
9926251925	DC BRANCH CB 25A 1 POLE	B.2
9926251930	DC BRANCH CB 30A 1 POLE	B.2
9926251935	DC BRANCH CB 35A 1 POLE	B.2
9926251940	DC BRANCH CB 40A 1 POLE	B.2
9926251945	DC BRANCH CB 45A 1 POLE	B.2
9926251950	DC BRANCH CB 50A 1 POLE	B.2
9926251955	DC BRANCH CB 55A 1 POLE	B.2
9926251960	DC BRANCH CB 60A 1 POLE	B.2
9926252001	CB 240V, 1A, CURVE KM, 2 POLE	B.2
9926252002	CB 240V, 2A, CURVE KM, 2 POLE	B.2
9926252005	CB 240V, 5A, CURVE KM, 2 POLE	B.2
9926252010	CB 240V,10A, CURVE KM, 2 POLE	B.2

Part Number	Description	Page
9926252015	CB 240V,15A, CURVE KM, 2 POLE	B.2
9926252020	CB 240V,20A, CURVE KM, 2 POLE	B.2
9926252025	CB 240V,25A, CURVE KM, 2 POLE	B.2
9928890005	CP-SNT 115,230VAC/ 5V,2A	D.26
9928890012	CP-SNT 115,230VAC/12V,1.5A	D.26
9928890015	CP-SNT 115,230VAC/15V,1.5A	D.26
9927480005	CP-SNT 115,230VAC/5VDC, 3A	D.26
9927480012	CP-SNT 115,230VAC/12-15VDC 3A	D.26
9927480024	CP-SNT 115,230VAC/24-28V,2.3A	D.26
9927480048	CP-SNT 115,230VAC/48VDC,1.0A	D.26
9928890028	CP-SNT 115,230VAC/28V,1.0A	D.26
9928890024	CP-SNT 115,230VAC/24V,1.0A	D.26
9929820000	91H12-13	B.3
9929830000	91H22-13	B.3
9929840000	91H32-13	B.3

9980000000

9987390000	RS-2D/SC FOR 24VDC P/S, 30A	D.29
9987860000	RS-DUAL DIODE ARRAY 30A	D.29

C

C006	SHUNT RESISTOR 0.1OHM,5WATT,1%	D.24
C9039986	AP DK5 END PLATE	D.10
C9039986	AP DK5 END PLATE	D.6
C9039986	AP DK5 END PLATE	D.18
C9040396	AP DK6 END PLATE	D.18

G

G108	ULTRA SLIMPAK DC IN DUAL SETPOINT	D.19
G108	ULTRA SLIMPAK DC IN DUAL SETPOINT	D.21
G118	ULTRA SLIMPAK RTD IN DUAL SETPOINT	D.21
G128	ULTRA SLIMPAK T/C IN DUAL SETPOINT	D.23
G168	ULTRA SLIMPAK AC IN DUAL SETPOINT	D.25
G408	ULTRA SLIMPAK DC - DC ISOLATOR	D.19
G408	ULTRA SLIMPAK DC - DC ISOLATOR	D.21
G408-1000	ANALOG ISOLATOR W/BIPOLAR VOLT	D.19
G408-1000	ANALOG ISOLATOR W/BIPOLAR VOLT	D.21
G418	ULTRA SLIMPAK RTD ISOLATOR	D.21
G428	ULTRA SLIMPAK THERMO ISOLATOR	D.23
G438	ULTRA SLIMPAK POTENTIOMETER	D.23
G448	ULTRA SLIMPAK BRIDGE ISOLATOR	D.23
G468	ULTRA SLIMPAK AC - DC ISOLATOR	D.25
G478	ULTRA SLIMPAK FREQUENCY ISOLATOR	D.25

HS

HS01-A	HEAT SINK FOR ULTRA SLIMPAK	D.24
--------	-----------------------------	------

SL

SLI120CH	DELCON 120VAC IN/60VDC OUT 50MA	D.14
SLI120CR	DELCON 120VAC IN/60VDC OUT 50MA	D.14
SLI120CRI	DELCON 120VAC IN/NC 60VDC OUT 30MA	D.14
SLI120CRP	DELCON 120VAC IN/60VDC OUT 50MA	D.14
SLI125CH	DELCON 125VDC IN/60VDC OUT 50MA	D.14
SLI125CR	DELCON 125VDC/60VDC OUT 50MA	D.14
SLI125CRI	DELCON 24VAC IN/60VDC OUT 30MA	D.14
SLI12CR	DELCON 12VDC IN/60VDC OUT 50MA	D.14
SLI12CRI	DELCON 12VDC IN/NC 60VDC OUT 30MA	D.14
SLI230CH	DELCON 230VAC IN/60VDC OUT 50MA	D.14
SLI230CR	DELCON 230VAC IN/60VDC OUT 50MA	D.14
SLI230CRI	DELCON 230VAC IN/NC 60VDC OUT 30MA	D.14
SLI230CRP	DELCON 230VAC IN/60VDC OUT 50MA	D.14
SLI230CRH	DELCON 230VAC IN/60VDC 50MA	D.14
SLI24CR	DELCON 24VDC IN/60VDC OUT 50MA	D.14
SLI24CRF	DELCON 24VDCIN/60VDC OUT 50MA	D.14
SLI24CRI	DELCON 24VDC IN/NC 60VDC OUT 30MA	D.14
SLI24CRL	DELCON 24VDC IN/60VDC OUT 50MA	D.14
SLI250CH	DELCON 250VDC IN/60VDC OUT 50MA	D.14
SLI250CR	DELCON 250VDC IN/60VDC OUT 50MA	D.14
SLI250CRI	DELCON 250VDC IN/NC 60VDC OUT 30MA	D.14
SLI25CR	DELCON 24VAC IN/60VDC OUT 50MA	D.14
SLI25CRI	DELCON 24VAC IN/NC 60VDC OUT 30MA	D.14
SLI48CR	DELCON 48VDC IN/60VDC OUT 50MA	D.14
SLI48CRI	DELCON 48VDC IN/NC 60VDC OUT 30MA	D.14
SLI49CR	DELCON 48VAC IN/60VDC OUT 50MA	D.14
SLI49CRI	DELCON 48VAC IN/NC 60VDC OUT 30MA	D.14
SLO120CRA	DELCON 120VDC IN/0-250VDC OUT 1.8A	D.14
SLO120CRA4	DELCON 120VDC IN/0-250VDC OUT 4A	D.14
SLO12CR	DELCON 12VDC IN/0-60VDC OUT 3A	D.14
SLO12CRA	DELCON 12VDC IN/0-250VDC OUT 1.8A	D.14
SLO12CRA4	DELCON 12VDC IN/0-250VDC OUT 4A	D.14
SLO12CRX	DELCON 12VDC IN/0-24VDC OUT 10A	D.14
SLO220CRA	DELCON 220VDC IN/0-250VDC OUT 1.8A	D.14
SLO220CRA4	DELCON 220VDC IN/0-250VDC OUT 4A	D.14
SLO24CL	DELCON 24VDC 2MA IN/0-60VDC OUT 3A	D.14
SLO24CR	DELCON 24VDC IN/60 VDC OUT 3A	D.14
SLO24CRA	DELCON 24VDC IN/300VDC OUT1.8A	D.14
SLO24CRA4	DELCON 24VDC IN/300VDC OUT4.0A	D.14
SLO24CRX	DELCON 24VDC IN/32VDC OUT 10A	D.14
SLO24IRA	DELCON 24VDC IN/250VAC OUT1.2A	D.14
SLO24TH	DELCON 24VDC IN/250VAC OUT 3A	D.14
SLO24TL	DELCON 24VDC 2MA IN/0-240VAC OUT 3A	D.14
SLO24TR	DELCON 24VDC IN/250VAC OUT 3A	D.14
SLO48CRA	DELCON 48VDC IN/0-250VDC OUT 1.8A	D.14
SLO48CRA4	DELCON 48VDC IN/0-250VDC OUT 4A	D.14
SLO5CR	DELCON 5VDC IN/0-60VDC,3A OUT	D.14
SLO5CRA	DELCON 5VDC IN/0-300VDC, 1.8 OUT	D.14
SLO5CRX	DELCON 5VDC IN/0-24VDC OUT 10A	D.14
SLO5IRA	DELCON 5VDC IN/0-240VAC OUT,1.2A	D.14

Part Number	Description	Page
SLO5TR	DELCON 5VDC IN/0-240VAC OUT,3A	D.14
SLOA120TR	DELCON 120VAC IN/0-240VAC OUT1A	D.14
SLOA230TR	DELCON 230VAC IN/0-240VAC OUT 1A	D.14
SLOP120TR	DELCON 120VAC IN/0-240VAC OUT,3A	D.14
SLOP230TR	DELCON 230VAC IN/0-240VAC OUT 3A	D.14

Notes

Lined area for notes.

www.weidmuller.ca

Argentina	Ireland	Slovenia
Australia	Israel	South Africa
Austria	Italy	South Korea
Azerbaijan	Japan	Spain
Bahrain	Jordan	Sweden
Belarus	Kazakhstan	Switzerland
Belgium	Kuwait	Syria
Bosnia	Latvia	Taiwan
-Herzegovina	Lebanon	Thailand
Brazil	Lithuania	Turkey
Bulgaria	Luxembourg	UAE
Canada	Macedonia	Ukraine
Chile	Malaysia	United Kingdom
China	Mexico	USA
Colombia	Netherlands	Venezuela
Costa Rica	New Zealand	Vietnam
Croatia	Norway	Yemen
Czech Republic	Oman	
Denmark	Paraguay	
Egypt	Peru	
Estonia	Philippines	
Finland	Poland	
France	Portugal	
Germany	Qatar	
Greece	Romania	
Hong Kong	Russia	
Hungary	Saudi Arabia	
Iceland	Serbia/	
India	Montenegro	
Indonesia	Singapore	
Iran	Slovakia	

Weidmüller is the leading manufacturer of components for electrical connection technology. The Weidmüller product portfolio ranges from terminal blocks, PCB connectors and terminals, protected components, Industrial Ethernet components and relay sockets to power supply and overvoltage protection modules suitable for all applications. Electrical installation and marking material, basic I/O components and a variety of tools round off the range. As an OEM supplier, the company sets global standards in the field of electrical connection technology.

Toronto

W Interconnections Canada Inc
10 Spy Court
Markham, ON L3R 5H6
Tel (905) 475-1507, (800) 268-4080
Fax (905) 475-2798
info1@weidmuller.ca
www.weidmuller.ca

Montréal

W Interconnections Canada Inc
1800 boul. Le Corbusier, Suite 100
Chomedey, Laval, QC H7S 2K1
Tel (450) 687-9030, (800) 361-9694
Fax (450) 687-9038

Order Number:

99990345/10/2006

Printed in Canada