



PPE Safety Solutions

3M™ Nuvo™ Reader Protective Eyewear, 11435-00000-20 Clear Lens, Gray Frame, +2.0 Diopter 20 ea/case

3M ID 70071539772 UPC# 10078371620636 3M Product Number 11435-00000-20 CAT# 11435

[Print](#)



[Like](#)

[Sign Up](#) to see what your friends like.

Need Help?

[Share](#)

Questions? We can help
[Contact Us](#)

Lightweight, retro-styled Nuvo protective eyewear features adjustable temples, an integral brow bar and soft nosepiece. Contoured frame and sideshields offer additional comfort.

Benefits

- Retro styling with molded-in magnifying diopters
- Integral brow bar and side shields
- Soft, adjustable nose bridge

Overview

Support

Nuvo protective eyewear combines a distinct, nostalgic look with reliable performance and flexible fit. It offers more than just a fashionable dual-lens profile with its tough, lightweight one-piece lens. With outstanding protection and comfort, Nuvo protective eyewear is also available in a bi-focal reader option for workers who are challenged by small print or detailed work.

- Clear lens.
- Gray frame.
- Bifocal readers with +2.0 magnification diopter.
- Polycarbonate lens absorbs 99.9% UV.
- Meets the requirements of CSA Z94.3-2007 and the High Impact Requirements of ANSI Z87.1-2003.
- 20 safety glasses per case.

Specifications

Color	Clear
Frame Color	Gray
Frame Style/Type	Half-frame
Lens Coating	Anti-Fog
Lens Color	Clear
Mission Type	Aircraft, Ships, Vehicles
Operation Type	Facility Safety, Maintenance, Repair & Operations, Overhaul
Product Type	Safety Glasses