

# Superbright LED Retrofit Bulb Dimmable



## Features:

- 7W LED lamp designed as high quality replacement of 40W traditional incandescent A19 lamps
- Dimmable 20-100%
- 25,000 hours rated life
- Suitable for indoor environments
- Available in 2,700K and 3,000K CCT with 80CRI
- Power factor 0.95
- Reduces energy consumption up to 80%
- Lasts 33 times longer than halogen lamps
- Mercury free
- UV and IR free
- UL File No. : E356190

## Specifications:

|                     |                      |
|---------------------|----------------------|
| Lamp Base Type      | : Edison Screw / E26 |
| CCT                 | : 2,700K             |
| LED Colour          | : Warm White         |
| Average Bulb Life   | : 25,000h            |
| Beam Angle          | : 120°               |
| Supply Voltage      | : 120V               |
| Power Rating        | : 7W                 |
| Power Factor        | : 0.95               |
| Bulb Size           | : 60mm               |
| Typical Lumens (lm) | : 420                |
| CRI                 | : 83                 |

## Application Information

### Where does it used

- Office Block
- Hospitality
- Residential
- Shopping Mall

### Applications

- Accent / Display Lighting
- Recessed Downlighting
- Showing Lighting
- Landscape Lighting

### Notes


- Operating temperature range between -20°C and +35°C
- Suitable for dimmers or in luminaires controlled by a dimmer
- Not intended for use with emergency light fixtures
- Not for use where exposed to weather
- Not for use in totally enclosed and insulated fixtures

# Superbright LED Retrofit Bulb

## Dimmable



### Dimension



| A<br>(mm) | B<br>(mm) | Weight<br>(g) |
|-----------|-----------|---------------|
| 60        | 114       | 240           |

### Part Number Table

| Description                     | Part Number              |
|---------------------------------|--------------------------|
| LED Lamp, E26, 120V, Warm White | A19-LED120V7WA-2700MCDIM |

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

