

Power Stud Blocks

600 Volts

Specifications:

- Connector, High Conductive Copper, Tin Plated
- Stud, Brass, Tin Plated
- Amp Rating Based on NEC Table 310-16 Using 75° C Copper Wire
- UL Recognized File No. E62806
- CSA Certified File No. LR19766
- CE



Power Blocks

Catalog#	Poles	Amps	Connector Configuration	Line Wire Range	Openings Per Pole	Connector Configuration	Load Wire Range	Openings Per Pole
1421123	1	200		1/4-20 Screw	1		1/4-20 Screw	1
1422123	2							
1423123	3							
1421122	1	200		1/4-20 X 9/16 Stud	1		1/4-20 X 9/16 Stud	1
1422122	2							
1423122	3							
1431563	1	230		3/8-16 X 1 3/16 Stud	1		3/8-16 X 1 3/16 Stud	1
1432563	2							
1433563	3							
1431561	1	230		3/8-16 X 1 3/16 Stud	1		1/4-20 X 1 3/16 Stud	1
1432561	2							
1433561	3							
1441122	1	260		3/8-16 X 1 7/16 Stud	1		1/4-20 X 9/16 Stud	2
1442122	2							
1443122	3							
1441553	1	230		3/8-16 X 1 7/16 Stud	1		3/8-16 X 1 7/16 Stud	1
1442553	2							
1443553	3							
1451606	1	410		1/2-13 X 1 7/16 Stud	1		1/2-13 X 1 7/16 Stud	1
1452606	2							
1453606	3							
1451573	1	360		3/8-16 X 1 7/16 Stud	1		3/8-16 X 1 7/16 Stud	2
1452573	2							
1453573	3							
1451583	1	360		3/8-16 X 1 7/16 Stud	1		1/4-20 X 1 7/16 Stud	2
1452583	2							
1453583	3							
1441614	1	840		3/8-16 X 1 Stud	1		3/8-16 X 1 Stud	1
1442614	2							
1443614	3							