

# SAFETY DATA SHEET EVO-STIK IMPACT CONTACT ADHESIVE

According to Regulation (EC) No 1907/2006

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

### 1.1. Product identifier

Product name Product No. EVO-STIK IMPACT CONTACT ADHESIVE

P038190, P038200, 389113, 389106, 347908, 347502, 348103, 348301, S348103, S348301

## 1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Adhesive.

## 1.3. Details of the supplier of the safety data sheet

| BOSTIK LIMITED    |
|-------------------|
| COMMON ROAD       |
| STAFFORD          |
| STAFFORDSHIRE     |
| ST16 3EH          |
| +44 1785 272625   |
| sds.uk@bostik.com |
|                   |

# 1.4. Emergency telephone number

+44 1785 272650 (24 Hours)

## **SECTION 2: HAZARDS IDENTIFICATION**

## 2.1. Classification of the substance or mixture

Classification (1999/45/EEC)

Xi;R36/38. F;R11. R52/53, R67.

## 2.2. Label elements

Labelling





Highly flammable

| Risk Phrases   |             |   |
|----------------|-------------|---|
| TASK T TILASES | <b>D</b> 44 |   |
|                | R11         | Highly flammable  |
|                | R36/38      | Irritating to eyes and skin.  |
|                | R52/53      | Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment. |
|                | R67         | Vapours may cause drowsiness and dizziness.   |
| Safety Phrases |             |   |
|                | S2          | Keep out of the reach of children.  |
|                | S9          | Keep container in a well-ventilated place.  |
|                | S16         | Keep away from sources of ignition - No smoking.  |
|                | S24/25      | Avoid contact with skin and eyes.   |
|                | S26         | In case of contact with eyes, rinse immediately with plenty of water and seek medical advice. |
|                | S36/37/39   | Wear suitable protective clothing, gloves and eye/face protection.                            |
|                | S46         | If swallowed, seek medical advice immediately and show this container or label.               |
|                | S51         | Use only in well-ventilated areas.  |
|                | S56         | Dispose of this material and its container to hazardous or special waste collection point.    |
|                | P14         | Contains ROSIN. May produce an allergic reaction.   |

# SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

# 3.2. Mixtures

| ACETONE  |                           |  | 10-30%                                |
|--|---------------------------|--|---------------------------------------|
|  |                           |  |                                       |
| CAS-No.: 67-64-1                                     | EC No.: 200-662-2         |  | Registration Number: 01-2119471330-49 |
| Classification (EC 1272/2008)                        |                           | Classification (67/548/EEC)            |                                       |
| Flam. Liq. 2 - H225<br>EUH066                        |                           | F;R11<br>Xi;R36                        |                                       |
| Eye Irrit. 2 - H319                                  |                           | R66                                    |                                       |
| STOT SE 3 - H336                                     |                           | R67                                    |                                       |
| BUTANONE   |                           |  | 10-30%                                |
| CAS-No.: 78-93-3                                     | EC No.: 201-159-0         |  | Registration Number: 01-2119457290-43 |
| Classification (EC 1272/2008)                        |                           | Classification (67/548/EEC)            |                                       |
| Flam. Liq. 2 - H225<br>EUH066                        |                           | F;R11<br>Xi;R36                        |                                       |
| Eye Irrit. 2 - H319                                  |                           | R66                                    |                                       |
| STOT SE 3 - H336                                     |                           | R67                                    |                                       |
| ETHYL ACETATE  |                           |  | 10-30%                                |
| CAS-No.: 141-78-6                                    | EC No.: 205-500-4         |  | Registration Number: 01-2119475103-46 |
|  |                           |  |                                       |
| Classification (EC 1272/2008)                        |                           | Classification (67/548/EEC)            |                                       |
| Flam. Liq. 2 - H225<br>EUH066                        |                           | F;R11<br>Xi;R36                        |                                       |
| Eye Irrit. 2 - H319                                  |                           | R66                                    |                                       |
| STOT SE 3 - H336                                     |                           | R67                                    |                                       |
| NAPHTHA (PETROLEUM), HYDROI                          | DESULFURIZED LIGHT, DEAF  | ROMATIZED; <0.1% BENZENE               | 10-30%                                |
| CAS-No.: 92045-53-9                                  | EC No.: 295-434-2         |  |                                       |
|  |                           |  |                                       |
| Classification (EC 1272/2008)<br>Flam. Liq. 2 - H225 |                           | Classification (67/548/EEC)<br>Xn;R65. |                                       |
| Skin Irrit. 2 - H315                                 |                           | Xi;R38.                                |                                       |
| STOT SE 3 - H336                                     |                           | F;R11.                                 |                                       |
| Asp. Tox. 1 - H304<br>Aquatic Chronic 2 - H411       |                           | N;R51/53.<br>R67.                      |                                       |
| NAPHTHA (PETROLEUM), HYDRO                           | TREATED LIGHT, <0.1% BENZ | ZENE,                                  | 5-10%                                 |
| CAS-No.: 64742-49-0                                  | EC No.:                   |  |                                       |
| Classification (EC 1272/2008)                        |                           | Classification (67/548/EEC)            |                                       |
| Flam. Liq. 2 - H225                                  |                           | Xn;R65.                                |                                       |
| Skin Irrit. 2 - H315<br>STOT SE 3 - H336             |                           | Xi;R38.<br>F;R11.                      |                                       |
| Asp. Tox. 1 - H304                                   |                           | N;R51/53.                              |                                       |
| Aquatic Chronic 2 - H411                             |                           | R67.                                   |                                       |

| ROSIN  |                   |   | < 1%                                  |
|--|-------------------|---|---------------------------------------|
| CAS-No.: 8050-09-7   | EC No.: 232-475-7 |   |                                       |
| Classification (EC 1272/2008)<br>Skin Sens. 1 - H317   |                   | Classification (67/548/EEC)<br>R43                        |                                       |
| XYLENE   |                   |   | 5-10%                                 |
| CAS-No.: 1330-20-7   | EC No.: 215-535-7 |   | Registration Number: 01-2119488216-35 |
| Classification (EC 1272/2008)<br>Flam. Liq. 3 - H226<br>Acute Tox. 4 - H312<br>Acute Tox. 4 - H332<br>Skin Irrit. 2 - H315 |                   | Classification (67/548/EEC)<br>R10<br>Xn;R20/21<br>Xi;R38 |                                       |

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

### **SECTION 4: FIRST AID MEASURES**

## 4.1. Description of first aid measures

Inhalation

Remove victim immediately from source of exposure. Move the exposed person to fresh air at once. Get medical attention.

Ingestion

DO NOT induce vomiting. Get medical attention immediately.

Skin contact

Promptly wash contaminated skin with soap or mild detergent and water. Promptly remove clothing if soaked through and wash as above. Get medical attention if irritation persists after washing.

Eye contact

Rinse the eye with water immediately. Continue to rinse for at least 15 minutes and get medical attention.

## 4.2. Most important symptoms and effects, both acute and delayed

#### 4.3. Indication of any immediate medical attention and special treatment needed

# SECTION 5: FIREFIGHTING MEASURES

#### 5.1. Extinguishing media

Extinguishing media

Fire can be extinguished using: Foam, carbon dioxide or dry powder.

#### 5.2. Special hazards arising from the substance or mixture

Specific hazards

Toxic gases/vapours/fumes of: Carbon dioxide (CO2). Carbon monoxide (CO).

5.3. Advice for firefighters

### SECTION 6: ACCIDENTAL RELEASE MEASURES

# 6.1. Personal precautions, protective equipment and emergency procedures

Follow precautions for safe handling described in this safety data sheet. Take precautionary measures against static discharges.

# 6.2. Environmental precautions

Avoid discharge to the aquatic environment.

6.3. Methods and material for containment and cleaning up

Stop leak if possible without risk. Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. **<u>6.4. Reference to other sections</u>** 

Wear protective clothing as described in Section 8 of this safety data sheet.

## SECTION 7: HANDLING AND STORAGE

#### 7.1. Precautions for safe handling

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

7.2. Conditions for safe storage, including any incompatibilities

Flammable/combustible - Keep away from oxidisers, heat and flames. Ground container and transfer equipment to eliminate static electric sparks. Store at moderate temperatures in dry, well ventilated area. Storage Class

Flammable liquid storage.

#### 7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

#### SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

#### 8.1. Control parameters

| Name          | STD | TWA            | - 8 Hrs          | STEL           | - 15 Min         | Notes |
|---------------|-----|----------------|------------------|----------------|------------------|-------|
| ACETONE       | WEL | 500 ppm        | 1210 mg/m3       | 1500 ppm       | 3620 mg/m3       |       |
| BUTANONE      | WEL | 200<br>ppm(Sk) | 600<br>mg/m3(Sk) | 300<br>ppm(Sk) | 899<br>mg/m3(Sk) |       |
| ETHYL ACETATE | WEL | 200 ppm        |                  | 400 ppm        |                  |       |
| XYLENE        | WEL | 50 ppm(Sk)     | 220<br>mg/m3(Sk) | 100<br>ppm(Sk) | 441<br>mg/m3(Sk) |       |

WEL = Workplace Exposure Limit.

Ingredient Comments WEL = Workplace Exposure Limits

#### 8.2. Exposure controls

Protective equipment



Engineering measures

Explosion-proof general and local exhaust ventilation.

Respiratory equipment

Respiratory protection must be used if air contamination exceeds acceptable level. Wear mask supplied with: Gas cartridge suitable for organic substances.

Hand protection

Protective gloves must be used if there is a risk of direct contact or splash. Use protective gloves made of: Nitrile.

Eye protection

Wear splash-proof eye goggles to prevent any possibility of eye contact.

Other Protection

Wear appropriate clothing to prevent repeated or prolonged skin contact.

Hygiene measures

Wash promptly if skin becomes contaminated. Wash hands at the end of each work shift and before eating, smoking and using the toilet.

### SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

#### 9.1. Information on basic physical and chemical properties

| Appearance | Liquid             |
|------------|--------------------|
| Colour     | Yellowish          |
| Odour      | of solvents        |
| Solubility | Insoluble in water |

| Initial boiling point and boiling range | Approx 56°C |
|---|-------------|
| Relative density                        | 0.84        |
| Flash point                             | - 20        |
|   |             |

#### 9.2. Other information

SECTION 10: STABILITY AND REACTIVITY

## 10.1. Reactivity

## 10.2. Chemical stability

Avoid Heat, sparks, flames.

10.3. Possibility of hazardous reactions

Not available.

10.4. Conditions to avoid

#### 10.5. Incompatible materials

#### 10.6. Hazardous decomposition products

Not known.

#### SECTION 11: TOXICOLOGICAL INFORMATION

#### 11.1. Information on toxicological effects

Inhalation Drowsiness, dizziness, disorientation, vertigo.

Skin contact Irritating to skin. Eye contact Irritating to eyes.

# SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity The product contains a substance which may have adverse effects on waste water treatment processes.

#### 12.1. Toxicity

No data available

#### 12.2. Persistence and degradability

Degradability There are no data on the degradability of this product.

#### 12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

# 12.4. Mobility in soil

Mobility: Mobile.

### 12.5. Results of PBT and vPvB assessment

No data available

# 12.6. Other adverse effects

Not available.

# SECTION 13: DISPOSAL CONSIDERATIONS

## 13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

| SECTION 14: TRANSPORT INFORMATION |                             |  |
|-----------------------------------|-----------------------------|--|
| 14.1. UN number                   |                             |  |
| UN No. (ADR/RID/ADN)              | 1133                        |  |
| UN No. (IMDG)                     | 1133                        |  |
| UN No. (ICAO)                     | 1133                        |  |
| 14.2. UN proper shipping na       | ne                          |  |
| Proper Shipping Name              | ADHESIVES                   |  |
| 14.3. Transport hazard class      | es)                         |  |
| ADR/RID/ADN Class                 | 3                           |  |
| ADR/RID/ADN Class                 | Class 3: Flammable liquids. |  |
| ADR Label No.                     | 3                           |  |
| IMDG Class                        | 3                           |  |
| ICAO Class/Division               | 3                           |  |
| Transport Labels                  |                             |  |



## 14.4. Packing group

| ADR/RID/ADN Packing group | ш   |
|---------------------------|-----|
| IMDG Packing group        | III |
| ICAO Packing group        | III |

## 14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant No.

## 14.6. Special precautions for user

| EMS                     | F-E, S-D |
|-------------------------|----------|
| Emergency Action Code   | •3YE     |
| Hazard No. (ADR)        | 33       |
| Tunnel Restriction Code | (D/E)    |
|                         |          |

## 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

# SECTION 15: REGULATORY INFORMATION

# 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Statutory Instruments

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I 2009 No. 716). Control of Substances Hazardous to Health.

#### Approved Code Of Practice

Safety Data Sheets for Substances and Preparations. Classification and Labelling of Substances and Preparations Dangerous for Supply. Guidance Notes

Workplace Exposure Limits EH40. Introduction to Local Exhaust Ventilation HS(G)37. CHIP for everyone HSG(108).

EU Legislation

Dangerous Substance Directive 67/548/EEC. Dangerous Preparations Directive 1999/45/EC.

#### 15.2. Chemical Safety Assessment

# **SECTION 16: OTHER INFORMATION**

#### General information

This product should be used as directed by Bostik Ltd. For further information consult the product data sheet or contact Technical Services. Information Sources

This safety data sheet was compiled using current safety information supplied by distributor of raw materials.

**Revision Comments** 

NOTE: Lines within the margin indicate significant changes from the previous revision. This safety data sheet supersedes all previous issues and users are cautioned to ensure that it is current. Destroy all previous data sheets and if in doubt contact Bostik Limited.

| Issued By                 | Approved LJ   |
|---------------------------|---|
| Revision Date             | Novemebr 2012   |
| Revision                  | 4   |
| Date                      | June 2009   |
| Risk Phrases In Full      |   |
| R10                       | Flammable.  |
| R20/21                    | Harmful by inhalation and in contact with skin.   |
| R52/53                    | Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment. |
| R65                       | Harmful: may cause lung damage if swallowed.  |
| R11                       | Highly flammable  |
| R36/38                    | Irritating to eyes and skin.  |
| R36                       | Irritating to eyes.   |
| R38                       | Irritating to skin.   |
| R43                       | May cause sensitisation by skin contact.  |
| R66                       | Repeated exposure may cause skin dryness or cracking.   |
| R51/53                    | Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.   |
| R67                       | Vapours may cause drowsiness and dizziness.   |
| Hazard Statements In Full |   |
| H319                      | Causes serious eye irritation.  |
| H315                      | Causes skin irritation.   |
| H226                      | Flammable liquid and vapour.  |
| H332                      | Harmful if inhaled.   |
| H312                      | Harmful in contact with skin.   |
| H412                      | Harmful to aquatic life with long lasting effects.  |
| H225                      | Highly flammable liquid and vapour.   |
| H304                      | May be fatal if swallowed and enters airways.   |
| H317                      | May cause an allergic skin reaction.  |
| H336                      | May cause drowsiness or dizziness.  |
| EUH066                    | Repeated exposure may cause skin dryness or cracking.   |
| H411                      | Toxic to aquatic life with long lasting effects.  |
|                           |   |