

SRM Series

Polyolefin Heat Shrink Tubing

pro-POWER



Description:

The SRM series is a semi-rigid, heat-shrinkable polyolefin tubing that is co-extruded and selectively cross-linked to provide an integral, meltable inner wall. When heated beyond the shrink temperature, the inner meltable wall of the tubing is simultaneously softened and forced by the shrink action into contact with all underlying surfaces and small voids. The SRM series provides a tough protective and insulating barrier, highly resistant to penetration by moisture and the attack of chemicals and solvents

Specifications:

Shrink Ratio	: 2.5 : 1
Shrink Temp.	: 135°C (275°F)
Operating Temp.	: -55°C to +110°C (-67°F to +230°F)

Physical

Tensile Strength	: 2,200 PSI
Ultimate Elongation	: 400%
Longitudinal Change	: +1%, -10%
Secant Modulus (2%)	: 27,000 PSI
*Heat Aging (168 hrs @ 175°C)	: Elongation 200%
*Heat Shock (4 hrs @ 250°C)	: No dripping, cracking, or flowing
*Low Temp Flexibility (4 hrs @ -55°C)	: No cracking
**Flexibility	: 7

Electrical

Dielectric Strength	: 900V/mil
Volume Resistivity	: 10 ¹⁵ Ω-cm

Chemical

Corrosive Effect	: Non-corrosive
Fluid Resistance JR4 Skydrol 600 Solution gasoline	: >1,500 PSI @ 600V/mil
Hydraulic fluid	
Water Absorption	: 0.1%
Fungus Resistance	: Non-nutrient
Applicable Specifications	: MIL-DTL-23053/4 Class 1

*Outer wall only.

**Flexibility: The materials are rated on a scale of 1 to 10. (1=most flexible and 10=most rigid)

SRM Series

Polyolefin Heat Shrink Tubing



Part Number Table

Dimensions				Standard Packages (Colour : Black)					
Size	Expanded I.D. (Min.)	Recovered I.D. (Max.)	Recovered Nominal Wall Thickness	4 Foot Lengths (+1", -0")			6 Inch Lengths (±.125")		
				Part Number	Pcs	Total Footage (ft)	Part Number	Pcs	Total Footage (ft)
1/8"	0.125"	0.023"	.038"	SRM-008-4025-BLK	25	100	SRM-008-6014-BLK	14	7
3/16"	0.187"	0.06"	.043"	SRM-012-4025-BLK	25	100	SRM-012-6012-BLK	12	6
1/4"	0.25"	0.08"	.047"	SRM-016-4025-BLK	25	100	SRM-016-6010-BLK	10	5
3/8"	0.375"	0.135"	.05"	SRM-024-4025-BLK	25	100	SRM-024-6008-BLK	8	4
1/2"	0.5"	0.195"	.055"	SRM-032-4005-BLK	5	20	SRM-032-6006-BLK	6	3
3/4"	0.75"	0.313"	.065"	SRM-048-4005-BLK	5	20	N/A	-	-
1"	1"	0.4"	.075"	SRM-064-4005-BLK	5	20	SRM-064-6002-BLK	2	1

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.