

# Ring Tongue Terminal



## Specifications:

Connector Type : Ring Tongue  
 Termination Method : Crimp  
 Stud/Tab Size : #10  
 Wire Size (AWG) : 18  
 Contact Material : Copper  
 Insulator Material : Uninsulated  
 Voltage Rating : 600V



## Part Number Table

Description	Pkg. Qty	Wire Range (AWG)	Stud Size	L	W	E	C	S	T	Thick-ness	Part Number
Non-Insulated Ring Tongue Terminals	50	12 ~ 10	6	0.68	0.28	0.54	0.29	0.143	0.135	0.04	CRS-TO-1006
	500										SPC3731
	50		8	0.73	0.38	0.69	0.44	0.174			CRS-TO-1008
	500										SPC3732
	50		10	0.96	0.53	0.69	0.44	0.2			CRS-TO-1010
	500										SPC3733
	50		1/4	0.96	0.53	0.69	0.44	0.264			CRS-TO-1025
	500										SPC3734
	50		5/16	0.96	0.53	0.69	0.44	0.328			CRS-TO-1031
	500										SPC3735
	50		3/8	0.96	0.53	0.69	0.44	0.39			CRS-TO-1037
	500										SPC3736

Dimensions : Inches



# Ring Tongue Terminal



Description	Pkg. Qty	Wire Range (AWG)	Stud Size	L	W	E	C	S	T	Thick-ness	Part Number
Non-Insulated Ring Tongue Terminals	100	16 ~ 14	6	0.6	0.25	0.47	0.22	0.148	0.09	0.03	CRS-TO-1406
	1,000										SPC3727
	100										8
	1,000		SPC3728								
	100		10	0.89	0.47	0.65	0.4	0.265			
	1,000										SPC3729
	100										1/4
	1,000		SPC3730								
	100		22 ~ 18	2	0.6	0.25	0.48	0.23			
	1,000	SPC3721									
	100	4		0.6	0.25	0.47	0.22	0.118	CRS-TO-1804		
	1,000								SPC3722		
	100	22 ~ 18	6	0.6	0.25	0.47	0.22	0.144	0.07	0.03	CRS-TO-1806
	1,000										SPC3723
	100										8
	1,000		SPC3724								
	100		10	0.74	0.31	0.58	0.33	0.195			
	1,000										SPC3725
	100										1/4
	1,000		SPC3726								
	100		26 ~ 24	0	0.32	0.14	0.24	0.11			
	1,000	SPC3717									
	100	2		0.31	0.14	0.24	0.11	0.09	CRS-TO-2202		
	1,000								SPC3718		
	100	4		0.45	0.2	0.35	0.21	0.116	CRS-TO-2204		
	1,000								SPC3719		
	100	6		0.45	0.2	0.35	0.21	0.143	CRS-TO-2206		
	1,000								SPC3720		

Dimensions : Inches

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

