


2000 Slide Switches - Snap fit and panel mount 10A 250Vac



- ▶ 2 way 'voltage selector'
- ▶ Ratings up to 16A, 250V ac
- ▶ Snap fit and panel mount
- ▶ PCB & solder terminals
- ▶ 2 and 3 position
- ▶ Choice of circuits
- ▶ Choice of actuators

Approvals and specifications



10 A 250Vac T85
6(3)A 250Vac T85



UL CSA 16A 250Vac Non Inductive
UL CSA 4A 300Vac
UL 65°C, file no. E45221, CSA file no. LR10990

µ contact gap

Please specify: Standard action (SP116) or light action (SP118).
2000 series lubrication is inorganic and does not degrade plastics.

Technical data on pages 4 & 5.

115/230 is preferred legend

T 2 2 20 5 B ---

TERMINAL SERIES POSITIONS CIRCUIT SLIDER BODY PRINT, COLOUR, ETC

TERMINAL	SERIES	POS'N	CIRCUIT <small>Viewed from back</small>	SLIDER				
K 2.8 x 0.8	2	Switching positions	10	0	6	C	L	S
			20	2	7	D	M	T
			30	3	8	E	N	
			40	4	9	H	P	
R 2.8 x 0.8	2	Switching positions	10	5	A	K	R	
			20	6				
			30	7				
			40	8				
T Solder	2	Switching positions	10	9				
			20					
			30					
			40					
X PCB 0.8 Sq. For mounting stability switches have extra "support" terminals * Nominal - Dimension varies with body type. For exact figure call sales	3	Switching positions	10	10				
			20					
			30					
			40					

slide switches



T22208E ---



T22308E ---



T2230MF ---



T22205B ---



T22305B ---




T23204B ---

BODY

OPTIONS

B With mounting holes



Colour


For custom slider colours call sales. A full range is available for large orders

Standard body colour is black

Legend printing

A wide range is available


E Snap fit



Cut-outs must be punched in the direction of insertion

For all options call sales

F Snap fit (single pole ON OFF only)




Cut-outs must be punched in the direction of insertion


DIMENSIONS (mm)

Cut-out / PCB Matrix



2 Pos B



3 Pos B





2 Pos E



Panel thickness	Dim. Y
0.8-1.2	29.75/29.85
1.63	30.15/30.25
2.0	30.35/30.45
2.5	30.55/30.65

2 Pos F



Panel thickness	Dim. Y
0.8-1.2	29.75/29.85
1.63	30.15/30.25
2.0	30.35/30.45
2.5	30.55/30.65

slide switches