


max. 24 m³/h

DC axial fans

Series 400 J 40 x 40 x 25 mm



Highlights:

- Very rigid compression curve for high air flow at high back pressure.
- Low operating noise level at high back pressure.

General characteristics:

- Material: fibreglass-reinforced plastic. Impeller PA, housing PBT.
- Fully integrated electronic commutation.
- Protected against reverse polarity and locking.
- Connection via single strands AWG 26, TR 64. Bared and tin-plated.
- Air exhaust over struts. Direction of rotation counter-clockwise, seen on rotor.
- Mass: 50 g.

Nominal data		Air flow	Air flow	Nominal voltage	Voltage range	Sound pressure level	Sound power level	Sinter sleeve bearings	Ball bearings	Power input	Nominal speed	Temperature range	Service life L ₁₀ (40 °C)	Service life L ₁₀ (T _{max})	Life expectancy L ₁₀ Δ	Curve	Specials
Type		m ³ /h	CFM	VDC	VDC	dB(A)	Bel(A)	■ / ■		Watts	RPM	°C	Hours	Hours	Hours		P. 110
412 J		19	11,2	12	8...14	39	5,5	■		2,4	10 300	-20...+70	60 000 / 30 000		120 000	1	
412 JH		22	12,9	12	8...13,5	43	5,8	■		3,0	11 700	-20...+70	60 000 / 30 000		120 000	2	/2
412 JHH		24	14,1	12	8...13,5	46	6,1	■		3,3	13 000	-20...+60	57 500 / 35 000		110 000	3	/2
414 J		19	11,2	24	18...27	39	5,5	■		2,4	10 300	-20...+70	60 000 / 30 000		120 000	1	
414 JH		22	12,9	24	18...27	43	5,8	■		3,0	11 700	-20...+70	60 000 / 30 000		120 000	2	/2
414 JHH		24	14,1	24	18...27	46	6,1	■		3,6	13 000	-20...+60	57 500 / 35 000		110 000	3	/2

