



Specifications:

Conductor	: Stranded Copper Conductor IEC 60228 Class-5
Insulation	: T12 Insulation Compound ACC. To VDE 0207
Bedding	: Filler Tape
Armour	: Copper Wire Braid Coverage > % 70
Sheath	: TM2 Sheathing Compound ACC.to VDE 207
Rated Voltage	: 300/500 V
Perm.working Temp. (Max)	: -20 to +70°C

Core Identification

Core Colour

JZ	: Black,white printed numbers and green/yellow earth core
OZ	: Black,white printed numbers ,without green/yellow earth core
JB	: Coloured corec according HD 308 S2

Sizes and Dimensions

Cross Section mm ²	Overall Dia mm	APP. Weight KG/KM
7 × 1.5	9.6	171

Part Number Table

Description	Part Number
Cable, CTRL, CY, 7 Core, 1.5mm, 50M	11070700-50M
Cable, CTRL, CY, 7 Core, 1.5mm, 100M	11070700-100M

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.