

Productname : FORMULA 6  
Ref.Nr.: UDS000133\_3\_20120515

Creationdate : 15.05.12 Version : 1.0  
Replaces: UK10005

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**FORMULA 6**  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Release Agents

### 1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.  
Ambersil House - Wylds Road  
Castlefield Industrial Estate  
TA6 4DD Bridgwater Somerset  
United Kingdom  
Tel.: +44 1278 727200  
Fax.: +44 1278 425644  
E-mail : hse.uk@crcind.com

### 1.4. Emergency telephone number

(+44)(0)1278 72 7200

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to 67/548/EEC or 1999/45/EC:

<b>Health:</b>	R38: Irritating to skin. R67: Vapours may cause drowsiness and dizziness.
<b>Physical:</b>	R12: Extremely flammable. EXTREMELY FLAMMABLE
<b>Environment:</b>	R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

### 2.2. Label elements

Warning symbol(s) : EXTREMELY FLAMMABLE



# Ambersil

1 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** FORMULA 6  
**Ref.Nr.:** UDS000133\_3\_20120515

**Creationdate :** 15.05.12 Version : 1.0  
**Replaces:** UK10005

Xi : IRRITANT



N : DANGEROUS FOR THE ENVIRONMENT



<b>Risk-phrase(s) :</b>	R12: Extremely flammable. R38: Irritating to skin. R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. R67: Vapours may cause drowsiness and dizziness.
<b>Safety-phrase(s) :</b>	S2: Keep out of the reach of children. S16: Keep away from sources of ignition - No smoking. S23: Do not breathe vapours/spray. S24: Avoid contact with skin. S51: Use only in well-ventilated areas.
<b>Extra label elements according to Aerosol Dispenser Directive 75/324/EC:</b>	Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material.
<b>Other extra label elements:</b>	Remark: Preparations classified as harmful on the basis of an aspiration hazard need not be labelled as harmful with R65 when placed on the market in aerosol containers or in containers fitted with a sealed spray attachment. (EU-Directive 67/548 Annex VI 9.4)

### 2.3. Other hazards

None

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	68512-91-4	270-990-9	30-60	F+	12	K
Naphtha (petroleum), hydrodesulfurized light (benzene<0.1%)	92045-53-9	295-434-2	30-60	F,Xn,N	11-38-51/53-65-67	B,P
ethanol; ethyl alcohol	64-17-5	200-578-6	1-5	F	11	B
methanol	67-56-1	200-659-6	0-1	F,T	11-23/24/25-39/23/24/25	A
<b>Explanation notes</b>						
A : substance with Community workplace exposure limit						
B : substance with national established workplace exposure limit						

**Productname :** FORMULA 6  
**Ref.Nr.:** UDS000133\_3\_20120515

**Creationdate :** 15.05.12 Version : 1.0  
**Replaces:** UK10005

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

P : not classified as carcinogen, less than 0.1% w/w benzene (Einecs-nr. 200-753-7)

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
ethanol; ethyl alcohol		64-17-5	200-578-6	1-5	Flam. Liq. 2	H225	B
methanol		67-56-1	200-659-6	0-1	Flam. Liq. 2, Acute Tox. 3, Acute Tox. 3, Acute Tox. 3, STOT SE 1	H225,H331,H311,H301,H370	A

#### Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

(\* Explanation phrases : see chapter 16)

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>Contact with eyes :</b>	If substance has got into eyes, immediately wash out with plenty of water Seek medical advice
<b>Contact with skin :</b>	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical advice
<b>Inhalation :</b>	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
<b>Ingestion :</b>	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

### 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	Irritating to skin Symptoms : redness and pain
<b>Eye contact :</b>	May cause irritation. Symptoms : redness and pain

### 4.3. Indication of any immediate medical attention and special treatment needed

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

**Productname :** FORMULA 6  
**Ref.Nr.:** UDS000133\_3\_20120515

**Creationdate :** 15.05.12 Version : 1.0  
**Replaces:** UK10005

foam, carbon dioxide or dry agent

### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.

### 7.2. Conditions for safe storage, including any incompatibilities

**Productname :** FORMULA 6  
**Ref.Nr.:** UDS000133\_3\_20120515

**Creationdate :** 15.05.12 Version : 1.0  
**Replaces:** UK10005

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
 Keep out of reach of children.

### 7.3. Specific end use(s)

Release Agents

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
methanol	67-56-1	TWA	200 ppm
<b>National established exposure limits, United Kingdom</b>			
ethanol; ethyl alcohol	64-17-5	TWA	1000 ppm
methanol	67-56-1	TWA	200 ppm
		STEL	250 ppm

### 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
<b>hands and skin :</b>	Wear suitable protective gloves (nitrile)
<b>eyes :</b>	Wear safety goggles.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

<b>Apperance : physical state :</b>	Propane/butane propelled liquid.
<b>colour :</b>	Colorless.
<b>odour :</b>	Solvent.
<b>pH :</b>	Not applicable.
<b>Boiling point/range :</b>	77 °C
<b>Flash point :</b>	- 4 °C
<b>Evaporation rate :</b>	Not available.

Productname : FORMULA 6  
Ref.Nr.: UDS000133\_3\_20120515

Creationdate : 15.05.12 Version : 1.0  
Replaces: UK10005

Explosion limits : upper limit :	19 %
lower limit :	1.1 %
Vapour pressure :	Not available.
Relative density :	0.735 g/cm <sup>3</sup> (@ 20°C).
Solubility in water :	Insoluble in water
Auto-ignition :	> 200 °C
Viscosity :	Not available.

## 9.2. Other information

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO<sub>2</sub>

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Irritating to skin
Eye contact :	May cause irritation.

### Toxicological data :



6 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** FORMULA 6  
**Ref.Nr.:** UDS000133\_3\_20120515

**Creationdate :** 15.05.12 Version : 1.0  
**Replaces:** UK10005

Hazardous ingredient	CAS-nr.	method	
ethanol; ethyl alcohol	64-17-5	LD50 oral rat	> 2000 mg/kg
		LD50 derm.rabit	> 2000 mg/kg

## SECTION 12: Ecological information

### 12.1. Toxicity

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

#### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
ethanol; ethyl alcohol	64-17-5	LC50 fish	> 100 mg/l

### 12.2. Persistence and degradability

No information available

### 12.3. Bioaccumulative potential

No information available

### 12.4. Mobility in soil

Insoluble in water

### 12.5. Results of PBT and vPvB assessment

No information available

### 12.6. Other adverse effects

No information available

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.  
**Contaminated packaging :** Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information



7 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Productname : FORMULA 6  
Ref.Nr.: UDS000133\_3\_20120515

Creationdate : 15.05.12 Version : 1.0  
Replaces: UK10005

#### 14.1. UN number

UN-number : 1950

#### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS (naphtha's)

#### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

#### 14.4. Packing group

Packing group: Not applicable.

#### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: Yes  
IMDG - Marine pollutant: Marine pollutant  
IATA/ICAO - Environmentally hazardous: Yes

#### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U  
IATA/ICAO - PAX: 203  
IATA/ICAO - CAO: 203

#### 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Dir. 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.  
EU-directive 99/45/EC  
Regulation (EC) No 1907/2006 (REACH)

#### 15.2. Chemical safety assessment

No information available



**Productname :** FORMULA 6  
**Ref.Nr.:** UDS000133\_3\_20120515

**Creationdate :** 15.05.12 Version : 1.0  
**Replaces:** UK10005

## SECTION 16: Other information

\*Explanation risk-phrases: R11: Highly flammable.  
R12: Extremely flammable.  
R38: Irritating to skin.  
R65: Harmful: may cause lung damage if swallowed.  
R67: Vapours may cause drowsiness and dizziness.  
R23/24/25: Toxic by inhalation, in contact with skin and if swallowed.  
R39/23/24/25: Toxic: danger of very serious irreversible effects through inhalation, in contact with skin and if swallowed.  
R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

\*Explanation hazard statements: H225 : Highly flammable liquid and vapour.  
H301 : Toxic if swallowed.  
H311 : Toxic in contact with skin.  
H331 : Toxic if inhaled.  
H370 : Causes damage to organs .

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.